

		REF. DWG. NO. E8-06																	DWG. NO. RE-E86-ADD2-2		ISSUED WITH ADD 002			
		PROJECT: NIAGARA OFFICE ADMINISTRATION FACILITY																	ARCHITECT: REBANKS PEPPER LITTLEWOOD		DRAWN BY: K.S.			
		DATE: MAY 30, 2012																						
		MCW Consultants Ltd.																	1185 West Georgia St, Suite 1400, Vancouver, BC, V6E 4E6					
'F1B'	PEERLESS SATURN	SDLC-DS-24G-228-OP-347																2	28W T5		●	ACCEPTABLE ALTERNATIVE	2'x4' FLUORESCENT SHALLOW SEMI-RECESSED DIRECT/INDIRECT FIXTURE WITH CENTRE-BASKET	
	ALTER	QVH-2G-PFOS-228-347		●																				
	VISONEERING	TDCLW-2x4-2L-T5-28-347																						
'F1D'	PINNACLE ADEO	AD24A-3T5-G1-347-1D-W																	3	28W T5	●	ACCEPTABLE ALTERNATIVE	2'x4' FLUORESCENT RECESSED DIRECT/INDIRECT FIXTURE WITH CENTRE BASKET AND DIMMABLE BALLAST	
	ALTER	QVS-2G-OLOP-328-347-DIM		●																				
	VISONEERING	TDLH-2x4-3L-T5-28-120-B04																						
'F2'	PEERLESS	LACH-24G-228-12																	2	28W T5		●	ACCEPTABLE ALTERNATIVE	2'x4' FLUORESCENT FIXTURE RECESSED IN TILE, C/W ACRYLIC LENS
	CFI	SQS2GFSVA-228-347-PV		●																				
	VISONEERING	MRCTB-2x4-2L-T5-28-347																						
'F3'	PEERLESS	LXHL-24-228-12																	2	28W T5		●	ACCEPTABLE ALTERNATIVE	1'x4' FLUORESCENT FIXTURE, MODULAR SURFACE MOUNTED WITH ACRYLIC LENS
	CFI	SLB1SFSVA-228-347-PV		●																				
	VISONEERING	MMAYS-1x4-2L-T5-28-347																						
'F4'	PEERLESS	NSMS-4-128																	2	28W T5		●	ACCEPTABLE ALTERNATIVE	4' LONG FLUORESCENT STRIP LIGHT SURFACE MOUNTED OR SUSPENDED, C/W WIREGUARD
	CFI	SV-4-S-228-347-SV5GXG3		●																				
	VISONEERING	FCOM-2-46-T5-28-347-W5																						
'F5'	PEERLESS	NIR-A-NR-4-228																	2	28W T5		●	ACCEPTABLE ALTERNATIVE	4' LONG INDUSTRIAL FLUORESCENT STRIP LIGHT SURFACE MOUNTED OR SUSPENDED, WITH SLOTTED APERATURE
	CFI	FF-228		●																				
	VISONEERING	MIND-2-48-T5-28-347																						
'F6'	PEERLESS	CIW-O-4-228																	2	28W T5		●	ACCEPTABLE ALTERNATIVE	4' LONG FLUORESCENT WALL BRACKET W/ WRAP AROUND LENS, WALL OR CEILING MOUNTED AS INDICATED
	CFI	CTW-228		●																				
	VISONEERING	CAD-2-48-T5-28-347																						
'F7'	SHAPER (COOPER)	600-24-T5/14/14-347-NA-DL																	2	14W T5		●	ACCEPTABLE ALTERNATIVE	2' LONG FLUORESCENT DECORATIVE WALL BRACKET MOUNTED ABOVE MIRRORS
	CFI	FBA5-347					●											2	14W T5					
	VISA	ASTA-CB6504-1FS24																1	24W T5					
'F8'	PEERLESS	NSL-4-228-WG																	1	28W T5		●	ACCEPTABLE ALTERNATIVE	4' LONG FLUORESCENT STRIPLIGHT, SIDE-MOUNT LAMP FOR VALENCE LIGHTING
	CFI	SM4S-128		●																				
	VISONEERING	FSM-1-46-T5-28-347																						
'F9'	PEERLESS	NSL-4-228																	2	28W T5		●	ACCEPTABLE ALTERNATIVE	4' LONG FLUORESCENT STRIPLIGHT, TWO-LAMP, MOUNTED IN ARCHITECTURAL COVE
	CFI	SV-4-S-228-347		●																				
	VISONEERING	FCOM-2-46-T5-28-347																						
'H1'	HESS	NV450SL-W-150-MH-347-W-SG-MG																	1	150W MH		●	ACCEPTABLE ALTERNATIVE	METAL HALIDE WALL BRACKET, DOWNLIGHT WITH WEDGE SHAPE SHROUD
	EXCELINE	ELA-15-4-EMA-BKX-IB-347					●																	
	SELUX	S453-W-3M-H15-BK-RBY																						
'S'	BEACON TRAVERSE	TRVD-36G-90W-T3-347-BB																		LED		●	ACCEPTABLE ALTERNATIVE	WALL MOUNTED LED FIXTURE AT APPROX. 14' AFF. BLACK FINISH REFER TO ARCHITECTURAL ELEVATIONS FOR EXACT MOUNTING HEIGHT
	WIDELITE	ASW-8015-4K-3-6-S-B																						
	ACCULITE	AW2-A050-4K-E34-WT-BL																						
'S1'	BEACON CRUZER	CRZ-60G-150W-T4-BS347-BB																	60	LED	●	ACCEPTABLE ALTERNATIVE	POLE MOUNTED SINGLE HEAD LED FIXTURE, BLACK C/W MATCHING 4500mmH ALUMINUM POLE, 100mmDIA. STRAIGHT, ON 600DIA x450H DECORATIVE CONCRETE BASE	
	WIDELITE	ASA-8015-4K-3-6-S-B																64						
	ACCULITE	AP2-90L-57K-E34-3-HT-BL																90						
	BEACON CRUZER	CRZ-2x60G-150W-T5R-347-BB																2x 60					POLE MOUNTED DOUBLE HEAD LED FIXTURE	