

ADDENDUM No.03, dated 2012-09-05.

This Addendum shall form part of documents referred to in "Articles of Agreement" as "Plans and Specifications".

The Plans and Specifications are amended as follows:

### **SPECIFICATIONS**

Add the attached document Unit Price Table to the specifications.

#### **CIVIL:**

	PILE TESTS	Sect 31 09 16.28
		2012-07-04

3.2 TESTING                      1.     Delete item 3.2.3.1 in its entirety.

### **DRAWINGS**

#### **ARCHITECTURAL:**

Dwgs A-520 and A-523:                      1.     Details 1/A-520, 2/A-520, 1/A-523 & 3/A-523 the description of the following wall construction - "Plaster, Glass fibre lath, 16 mm Cement board, 75 mm Rigid Insulation, vapour barrier, poured concrete grade beam", delete a reference to "vapour barrier" and replace with "waterproofing membrane".

#### **ELECTRICAL:**

Add the attached reference sketch - New 44kV Connection-1000kVA, dated 7/27/2012 and prepared by Hydro One, supplemented by the following note:

Note: Contact the Electrical Safety Authority (ESA) for your permit, the required inspections and authorizations. Contact the ESA at 1-877-372-7233 for an electrical inspection and fee estimate. It will allow to proceed with electrical work. Once the electrical work is complete contact the ESA again for an electrical inspection. The ESA will advise when the inspection is approved. Send a copy of the connection authorization directly to Hydro One. Hydro One will contact the Contractor to discuss scheduling the connection.

Add the attached reference sketch - Hydro One Trenching Guidelines, prepared by Hydro One.

Dwg.E-201  
Electrical Ground  
Floor Lighting

1. Provide two (2) recessed LED pot lights type 'H' in exterior canopy ceiling adjacent to entrance vestibule #100 and provide three (3) Recessed LED pot lights type 'H' in exterior canopy ceiling adjacent to resident entrance #111. Fixtures to be fed from exterior wall pack lighting circuit EM-9. Fixtures to be 141 mm D x 213 mm H, exterior damp location, vandal resistant rating, polycarbonate 0.1875" pattern 12 lens, 120V, exterior rated driver, LED 600 lumens, 2700k generation 3 luminaire.
2. Provide one (1) wall mount type 'F' on exterior wall near exit doors grid lines B/3.1 and connect fixtures to outside lighting circuit EM-9.
3. Provide one (1) wall mount type 'F' on exterior wall near exit doors grid lines C.1/4 and connect fixtures to outside lighting circuit EM-9.
4. Provide one (1) wall mount type 'F' on exterior wall near exit doors grid lines F/4 and connect fixtures to outside lighting circuit EM-9.

**ELECTRICAL/CIVIL:**

Dwgs.C-200 and  
C-200

1. Refer to the attached reference sketch -  
New 44kV Connection-1000kVA, dated 7/27/2012,  
for service location and Hydro, Contractor  
and customer's scope of work confirmation.

2. All wiring installed underground to be  
RWU90 rated.

End of Addendum No.03, dated 2012-09-05, consisting of 3 pages and  
the following attached documents:

Specifications:

New document - Unit Price Table (1 page)

Drawings:

Reference sketch - New 44kV Connection-1000kVA

Reference sketch - Hydro One Trenching Guidelines