



I EQUIPMENT LIST

| Data Sht | Rm Name | Equipment Name | Quantity | Relocate | Supply / Rough-in / Install | Size | Gas | Electrical Power – (estimated figure for information only). Verify during design stage. | Electrical Connection | Water | Floor Drain |
|----------|--------------------|---------------------------|----------|----------|-------------------------------|---------------------|-----|---|-----------------------|-------|-------------|
| 2 | Soil Potting Room | Autoclave | 1 | No (new) | Rough-in and install | | no | 208V,100Amp, 3 Phase | Hardwire | Yes | Yes |
| 2 | Soil Potting Room | Mobile soil mixer | 1 | No | Rough-in only | | no | 115/230V, 13/6.5A, 1Ph | Plug in | no | no |
| 2 | Soil Potting Room | Utility sink | 1 | No | Rough-in and install | 1800 x 760 | no | No | n/a | Yes | |
| 2 | Soil Potting Room | Pot Scrubber | 1 | No | Rough-in and install | | no | 115V, 1Ph, waterproof, GFCI | Plug in | | |
| 2 | Soil Potting Room | Potting table | 1 | No | Install | 3060x1010x920h | no | No | | | |
| | Soil Potting Room | Adjustable metal shelving | | No | Install | | no | No | | | |
| 3 | Pathology Lab 105 | Frig | 1 | No | Rough-in only | | no | 120V, 7A, 60Hz | Plug in | no | no |
| 3 | Pathology Lab 106 | Frig | 1 | No | Rough-in only | | no | 120V 7A, 60Hz | Plug in | no | no |
| 4 | Pathology Lab 104 | Frig | 1 | No | Rough-in only | | no | 120V, 7A , 60Hz | Plug in | no | no |
| 4 | Pathology Lab 107 | Frig | 1 | No | Rough-in only | | no | | Plug in | no | no |
| 5 | Glass Sealing Room | Glass Sealing Apparatus | 1 | No | Install only | 1800x300x300h | no | No | n/a | no | no |
| 5 | Glass Sealing Room | Vacuum Pump | 1 | No | Rough-in only | 300x400x500h | no | 115/230V, 1Ph, 8.6/4.3A | Plug-in | no | no |
| 9 | Pesticide Mixing | Fume Hood | 1 | No (New) | Supply & Rough-in and install | | | As per manufacturers requirements | | | no |
| 11 | Incubation Rm 1 | Dew Box | 1 | No | Rough-in only | 3200x1010x2200h | No | 120Volts ,15Amp | | | no |
| 11 | Incubation Rm 1 | Percival Dew Chamber | 4 | No | Rough-in only | 1500x840x2000h | No | 2x115/230V, 1Ph, 12&7A, 60Hz/ 2x115V, 30A, 1Ph, 60Hz | | | no |
| 12 | Incubation Rm2 | Dew Box | 6 | No | Rough-in only | 1020x770x1460h | No | | | | no |
| 12 | Incubation Rm2 | Humidifiers | 6 | No | Rough-in only | 300x200x300h | No | | | | no |
| 13 | Phytotron Room | Convion BDW40 | 10 | Yes | Rough-in only | 3050 x 1780 x 2900h | No | 120/208, 27Amp, 3 Phase | Hardwire | Yes | yes |
| 13 | Phytotron Room | Convion E15 | 4 | Yes | Rough-in only and Install | 2640 x 890 x 2600h | No | 3x120/208. 25Amp, 3Phase. 1x 120/208. 13Amp, 3Phase. | Hardwire | Yes | no |
| 13 | Phytotron Room | Upright Ultra-Low | 4 | No | Rough-in only | 970x1100x2000h | No | 230V, 50/60Hz, 12A 1Ph and/or 115V, 50/60Hz, 10A 1 Ph | Hardwire | | no |
| 14 | Phytotron Room | Percival Dew Cabinet | 1 | No | Rough-in only | 900x970x2000h | No | 115V, Single Ph. 9&10Amp | Hardwire? | No | no |