

**RETURN BIDS TO:**  
**RETOURNER LES SOUMISSIONS À:**  
Bid Receiving Public Works and Government  
Services Canada/Réception des soumissions Travaux  
publics et Services gouvernementaux Canada  
1713 Bedford Row  
Halifax, N.S./Halifax, (N.É.)  
B3J 1T3  
Bid Fax: (902) 496-5016

**SOLICITATION AMENDMENT**  
**MODIFICATION DE L'INVITATION**

The referenced document is hereby revised; unless otherwise  
indicated, all other terms and conditions of the Solicitation  
remain the same.

Ce document est par la présente révisé; sauf indication contraire,  
les modalités de l'invitation demeurent les mêmes.

Comments - Commentaires

Vendor/Firm Name and Address  
Raison sociale et adresse du  
fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution  
Acquisitions  
1713 Bedford Row  
Halifax, N.S./Halifax, (N.É.)  
B3J 3C9

Title - Sujet RENTAL - WASHERS AND DRYERS	
Solicitation No. - N° de l'invitation W010C-12C229/A	Amendment No. - N° modif. 003
Client Reference No. - N° de référence du client W010C-12-C229	Date 2012-08-17
GETS Reference No. - N° de référence de SEAG PW-\$HAL-219-8710	
File No. - N° de dossier HAL-1-66859 (219)	CCC No./N° CCC - FMS No./N° VME
Solicitation Closes - L'invitation prend fin at - à 02:00 PM on - le 2012-08-24	Time Zone Fuseau horaire Atlantic Daylight Saving Time ADT
F.O.B. - F.A.B. Plant-Usine: <input type="checkbox"/> Destination: <input checked="" type="checkbox"/> Other-Autre: <input type="checkbox"/>	
Address Enquiries to: - Adresser toutes questions à: Richard, Linda K.	Buyer Id - Id de l'acheteur hal219
Telephone No. - N° de téléphone (902) 496-5261 ( )	FAX No. - N° de FAX (902) 496-5016
Destination - of Goods, Services, and Construction: Destination - des biens, services et construction:	

Instructions: See Herein

Instructions: Voir aux présentes

Delivery Required - Livraison exigée	Delivery Offered - Livraison proposée
Vendor/Firm Name and Address Raison sociale et adresse du fournisseur/de l'entrepreneur	
Telephone No. - N° de téléphone Facsimile No. - N° de télécopieur	
Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) Nom et titre de la personne autorisée à signer au nom du fournisseur/ de l'entrepreneur (taper ou écrire en caractères d'imprimerie)	
Signature	Date

---

**AMENDMENT #3**

This document serves to amend the solicitation in response to the following.

**1. Question #1**

In the criteria it lists that the washers have to be 3.5 Cu. Ft., and we were thinking of putting non-coin commercial machines that are much more durable than domestic units. The largest that you can get these are 3.2 Cu. Ft. - would that still be acceptable.

**Answer #1**

3.2 Cu. Ft. Is acceptable

**2. Question #2**

The Washer's listed capacity is 3.5 - 4.4. Is this rating in IEC (The International Electro Technical Commission or DOA (Design Organisation Approvals) (ie. DOA capacity of 3.2 Cu. Ft. is equal to 3.7 Cu. Ft IEC). Can you clarify which one?

**Answer #2**

DOA rating should be used.

**3. Under Annex "C" Mandatory Technical Cross-Reference (Evaluation - Technical Phase 1)**

**Delete:** In its entirety

**Insert:** The following

**ANNEX "C"**  
**MANDATORY TECHNICAL CROSS-REFERENCE**  
**(EVALUATION - TECHNICAL PHASE 1)**

Bidders are requested to provide cross-reference below to identify the page(s) where each mandatory specification can be demonstrated in their technical documentation provided with their bid. Canada reserves the right to verify any and all information relating to mandatory requirements.

Item	Requirement	Cross-reference from Literature (please indicate brochure title, page number, etc.)
<b>2.1 Washers</b>		
.1	Non coin-operated machine	
.2	Energy efficient top load loading washing machine certified Energy Star	
.3	3.2 - 4.4 cu. Ft. Minimum capacity	
.4	White in color	
.5	120VAC, 60 Hz input voltage	
.6	Energy consumption not to exceed 300 kWh/year	
.7	As a minimum, temperature levels will be hot/cold, warm/cold and cold/cold (or equivalent)	
.8	As a minimum, wash cycles will be light, regular, permanent press (or equivalent)	
.9	Washer must have automatic water level control.	
.10	Washer must have provision for automatic dispensing of bleach and fabric softener.	
.11	Machines dimensions must allow installation in all sites identified in Annex "A".	
<b>2.2 Dryers</b>		
.1	Non coin operated machine	
.2	Electric	
.4	6.0 - 7.5 cu. Ft. capacity	
.5	White in color	
.6	120/240 VAC, 1Ph, 60Hz input voltage	
.7	As a minimum, dryer cycle selections will include delicate, permanent press, and regular (or equivalent) as well as ability to select a time cycle.	
.8	As a minimum, dryer must feature a temperature control (High/Medium/Low)	

Solicitation No. - N° de l'invitation

W010C-12C229/A

Client Ref. No. - N° de réf. du client

W010C-12-C229

Amd. No. - N° de la modif.

003

File No. - N° du dossier

HAL-1-66859

Buyer ID - Id de l'acheteur

hal219

CCC No./N° CCC - FMS No/ N° VME

---

.9	Moisture sensor	
.	Machines dimensions must allow installation in all sites identified in Annex A.	
.10	Dryer must have interior lighting.	
.11	Dryer must have lint screen.	

All other terms and conditions remain unchanged.