





SCHEMATIC



- 49 CENTRIFUGAL PUMP W/ MOTOR
- 50 HOSE REEL
- 51 HOSE
- 52 FOAM NOZZLE
- 53 BALL SHUT-OFF FOR 52

- 1227-11-1 ENGLISH LABEL
- 1227-11-2 FRENCH LABEL



| QTY REQ'D  | CODE IDENT | PART OR IDENTIFYING NO | NOMENCLATURE OR DESCRIPTION   | MATERIAL/SPECIFICATION | ITEM NO. |
|--|------------|------------------------|---|------------------------|----------|
| PARTS LIST   |            |                        |   |                        |          |
| REQUIREMENTS - UNLESS OTHERWISE SPECIFIED                |            |                        | CONTRACT NO.  |                        |          |
| GENERAL  |            |                        | LIMITS  |                        |          |
| 1. DIM'S. ARE IN INCHES.                                 |            |                        | 1. LINEAR DIM'S. 0 ± 0.03   |                        |          |
| 2. TOLERANCE SYMBOLS IN ACCORDANCE WITH ANSI Y14.5-1973. |            |                        | 2. FRACTIONS 1/16   |                        |          |
| 3. HOLES IN ACCORDANCE WITH AND 10387.                   |            |                        | 3. ANGLES ± 1/2°  |                        |          |
|  |            |                        | 4. CONCENTRICITY 0.05 T.I.R.  |                        |          |
|  |            |                        | 5. MACHINE FINISH 125 RMS.  |                        |          |
|  |            |                        | 6. INTERNAL RADII 015.  |                        |          |
|  |            |                        | 7. CHAMFER EXTERNAL CORNERS 12 ± 45°                                      |                        |          |
|  |            |                        | 8. DIMENSIONS LOCATING TRUE POSITION ARE BASIC                            |                        |          |
| DO NOT SCALE DWG.  |            |                        |   |                        |          |
| STRESS   |            |                        | DRAWN J.V. MAY 9/78   |                        |          |
| PROJ. ENG.   |            |                        | CHECK R.R.  |                        |          |
| DESIGN   |            |                        | DESIGN ACTIVITY   |                        |          |
| ADDITIONAL APPROVALS                                     |            |                        | CUSTOMER  |                        |          |
| DATE   |            |                        | TITLE   |                        |          |
| PART DASH NO.  |            |                        | DAF DAF INDAL LTD. 3570 HAWKESTONE RD., MISSISSAUGA, ONT., CANADA L5C 2V8 |                        |          |
| NEXT FINAL   |            |                        | SIZE CODE IDENT. NO. DWG. NO. REV.  |                        |          |
| QTY REQ'D PER ASSY                                       |            |                        | D 36334 1211-9 0  |                        |          |
| NEXT ASSY  |            |                        | SCALE 1/10 CALC. WT. ACT. WT. SHEET                                       |                        |          |
| USED ON  |            |                        |   |                        |          |
| APPLICATION  |            |                        |   |                        |          |