

**TABLE B1 - BASIS OF PRICING - INITIAL TWO YEAR PERIOD - SOLICITATION W0125-13EGS6/A**

The prices in Table B1 are firm prices for the initial two year period from Standing Offer issuance, GST/HST Extra, FOB Destination

Note 1: The Unit Price Quoted is per the Unit of Issue (U of I)

| Item No.                    | Part Number | Proposed Part Number | Description                                    | U of I | Est. Qty | Firm Unit Price | Extended Total |
|-----------------------------|-------------|----------------------|--|--------|----------|-----------------|----------------|
| CATEGORY 1 - WIRE AND CABLE |             |                      |  |        |          |                 |                |
| 1                           |             |                      | #14 awg T90 stranded wire black                | M      | 6000     |                 |                |
| 2                           |             |                      | #14 awg T90 stranded wire white                | M      | 6000     |                 |                |
| 3                           |             |                      | #14 awg T90 stranded wire Blue                 | M      | 6000     |                 |                |
| 4                           |             |                      | #14 awg T90 stranded wire Green                | M      | 6000     |                 |                |
| 5                           |             |                      | #6 awg T90 stranded wire Black                 | M      | 260      |                 |                |
| 6                           |             |                      | #6 awg T90 stranded wire red                   | M      | 260      |                 |                |
| 7                           |             |                      | #6 awg T90 stranded wire white                 | M      | 260      |                 |                |
| 8                           |             |                      | #6 awg T90 stranded wire green                 | M      | 260      |                 |                |
| 9                           |             |                      | 350 MCM T90                                    | M      | 2500     |                 |                |
| 10                          |             |                      | 750 MCM Cable                                  | M      | 1000     |                 |                |
| 11                          |             |                      | 500 MCM Cable                                  | M      | 2000     |                 |                |
| 12                          |             |                      | 350 MCM Cable Copper                           | M      | 2500     |                 |                |
| 13                          |             |                      | 300 MCM Cable Copper                           | M      | 2500     |                 |                |
| 14                          |             |                      | 250 MCM Cable Copper                           | M      | 2500     |                 |                |
| 15                          |             |                      | 0000 MCM Cable Copper                          | M      | 2500     |                 |                |
| 16                          |             |                      | 000 MCM Cable Copper                           | M      | 2500     |                 |                |
| 17                          |             |                      | 00 MCM Cable Copper                            | M      | 2500     |                 |                |
| 18                          |             |                      | 0 MCM Cable Copper                             | M      | 2500     |                 |                |
| 19                          |             |                      | 350 MCM Tech 4 Wire                            | M      | 1500     |                 |                |
| 20                          |             |                      | 1/2" Liquid Tite                               | M      | 400      |                 |                |
| 21                          |             |                      | #10 awg T90 stranded black                     | M      | 400      |                 |                |
| 22                          |             |                      | #10 awg T90 stranded red                       | M      | 400      |                 |                |
| 23                          |             |                      | # 18awg twisted pair, cat 5 non shielded       | M      | 260      |                 |                |
| 24                          |             |                      | #18awg twisted pair, cat 5 shielded            | M      | 260      |                 |                |
| 25                          |             |                      | #18awg fire wire (shielded)                    | M      | 260      |                 |                |
| 26                          |             | TB 1016BTB           | Grounding Plate                                | EA     | 40       |                 |                |
| CATEGORY 2 - CONDUIT        |             |                      |  |        |          |                 |                |
| 27                          | 1485C12     |                      | Hammond lay IN TYPE 12 WIRE WAY STRAIGHT 4 X 4 | EA     | 20       |                 |                |
| 28                          | 1485C24     |                      | Hammond lay IN TYPE 12 WIRE WAY STRAIGHT 4 X 4 | EA     | 20       |                 |                |
| 29                          | 1485C36     |                      | Hammond lay IN TYPE 12 WIRE WAY STRAIGHT 4 X 4 | EA     | 20       |                 |                |
| 30                          | 1485C48     |                      | Hammond lay IN TYPE 12 WIRE WAY STRAIGHT 4 X 4 | EA     | 20       |                 |                |

TABLE B1

| Item No.                                 | Part Number       | Proposed Part Number | Description   | U of I | Est. Qty | Firm Unit Price | Extended Total |
|--|-------------------|----------------------|---|--------|----------|-----------------|----------------|
| 31                                       | 1485CV2           |                      | box entry   | EA     | 10       |                 |                |
| 32                                       | 1485C9N           |                      | 90 elbow top opening                                      | EA     | 10       |                 |                |
| 33                                       | 1485C9P           |                      | 90 elbow inside opening                                   | EA     | 10       |                 |                |
| 34                                       | 1485B9Q           |                      | 90 elbow , outside opening                                | EA     | 10       |                 |                |
| 35                                       | 1485CL2           |                      | bracket hanger  | EA     | 60       |                 |                |
| 36                                       |                   |                      | 3/4" EMT CONDUIT  | 100 FT | 60       |                 |                |
| 37                                       |                   |                      | 1/2" EMT CONDUIT  | 100 FT | 400      |                 |                |
| 38                                       |                   |                      | 1" EMT CONDUIT  | 100 FT | 60       |                 |                |
| 39                                       |                   |                      | 2' EMT CONDUIT  | 100 FT | 5        |                 |                |
| 40                                       |                   |                      | 3" EMT CONDUIT  | 100 FT | 5        |                 |                |
| 41                                       |                   |                      | 2" LT   | M      | 20       |                 |                |
| 42                                       |                   |                      | 3" LT   | M      | 20       |                 |                |
| CATEGORY 3 - CONDUIT FITTINGS ETC.       |                   |                      |   |        |          |                 |                |
| 43                                       | 1485CFF           |                      | FLEX FITTING, hammond                                     | EA     | 10       |                 |                |
| 44                                       | 1485CX            |                      | TELESCOPE FITTING, hammond                                | EA     | 10       |                 |                |
| 45                                       |                   |                      | 3/4" EMT STRAPS   | EA     | 2000     |                 |                |
| 46                                       | EMCO 304-S3-PP-8P |                      | swage locks to fit 1/2" piping                            | EA     | 200      |                 |                |
| 47                                       | EMCO S-SO-SN      |                      | swage locks strut nuts                                    | EA     | 200      |                 |                |
| 48                                       | IBV BC52151K      |                      | 4x4 box   | EA     | 300      |                 |                |
| 49                                       | IBV BC52C1        |                      | 4x4 cover plate   | EA     | 100      |                 |                |
| 50                                       | IBV CITA12        |                      | 1/2" Tees   | EA     | 200      |                 |                |
| 51                                       | IBV BC1110        |                      | 4 x 2 boxes   | EA     | 400      |                 |                |
| 52                                       | IBV BC11C4        |                      | blank cover plates 4x 2 box                               | EA     | 100      |                 |                |
| 53                                       | NES 271           |                      | 1/2" liquid tight to EMT connectors (compression fitting) | EA     | 500      |                 |                |
| 54                                       | LMC 5262          |                      | receptacles   | EA     | 160      |                 |                |
| 55                                       |                   |                      | metal receptacle covers                                   | EA     | 160      |                 |                |
| 56                                       | IBV BC11C5        |                      | light switch cover  | EA     | 100      |                 |                |
| 57                                       |                   |                      | 1/2" EMT STRAPS   | EA     | 2000     |                 |                |
| CATEGORY 4 - PANELS/BREAKERS/DISCONNECTS |                   |                      |   |        |          |                 |                |
| 58                                       | SQUARE "D" ONLY   |                      | 1200 Amp fusible Disconnect Nema 3R/12                    | EA     | 6        |                 |                |
| 59                                       | SCH CH367AWK      |                      | 800 Amp fusible Disconnect Nema 3R/12                     | EA     | 8        |                 |                |
| 60                                       | SCH CH366AWK      |                      | 600 Amp fusible Disconnect Nema 3R/12                     | EA     | 12       |                 |                |
| 61                                       | SCH CH365AWK      |                      | 400 Amp Nema 3R/12disconnect                              | EA     | 10       |                 |                |
| 62                                       | SCH CH364AWK      |                      | 200 A NEMA 3R/12, 3 phase fused Disconnect                | EA     | 10       |                 |                |
| 63                                       | SCH CH361         |                      | 30 amp fusible disconnect, NEMA 1                         | EA     | 24       |                 |                |
| 64                                       |                   |                      | 30 amp fuse for above                                     | EA     | 40       |                 |                |

TABLE B1

| Item No.                               | Part Number      | Proposed Part Number | Description                                  | U of I | Est. Qty | Firm Unit Price | Extended Total |
|--|------------------|----------------------|--|--------|----------|-----------------|----------------|
| CATEGORY 5 - FUSES                     |                  |                      |  |        |          |                 |                |
| 65                                     | TRS200R          |                      | class J 200 amp time delay fuses for above   | EA     | 30       |                 |                |
| 66                                     | TRS400R          |                      | class J 400 amp time delay fuses             | EA     | 30       |                 |                |
| 67                                     | A4BT800          |                      | class J 800 amp time delay fuses             | EA     | 24       |                 |                |
| 68                                     | TRS600R          |                      | class J 600 amp time delay fuses for above   | EA     | 72       |                 |                |
| 69                                     | CQO124M126C60    |                      | LOAD CENTER, 60A, 12 POLE, 240V, SQUARE D    | EA     | 24       |                 |                |
| 70                                     |                  |                      | 15amp, single pole                           | EA     | 100      |                 |                |
| 71                                     |                  |                      | 15amp, double pole                           | EA     | 20       |                 |                |
| 72                                     |                  |                      | 30amp, double pole                           | EA     | 20       |                 |                |
| 73                                     |                  |                      | 20amp, double pole                           | EA     | 20       |                 |                |
| CATEGORY 6 - TRANSFORMERS              |                  |                      |  |        |          |                 |                |
| 74                                     | 600 TO 120/240 V |                      | TRANSFORMER 15 KVA wall mounted single phase | EA     | 24       |                 |                |
| 75                                     | 600 TO 120/208 V |                      | TRANSFORMER 15 KVA wall mounted three phase  | EA     | 5        |                 |                |
| CATEGORY 7 - THERMOSTATS/LOUVER MOTORS |                  |                      |  |        |          |                 |                |
| 76                                     | HON 50017460003U |                      | HONEYWELL TRANSFORMER 120V-24V               | EA     | 10       |                 |                |
| 77                                     | HON 27518U       |                      | Honeywell ball joint assembly                | EA     | 30       |                 |                |
| 78                                     |                  |                      | 1/4" x 24" Push rod for louver motor         | EA     | 20       |                 |                |
| 79                                     | HON 7616BRU      |                      | Honeywell crank arm and clip                 | EA     | 20       |                 |                |
| 80                                     | HON T6051A1057U  |                      | Thermostat, NC NO                            | EA     | 20       |                 |                |
| 81                                     | HON T921A1522U   |                      | Modulating Thermostat                        | EA     | 20       |                 |                |
| 82                                     | HON M9185D1004U  |                      | Louver Motor, 24v ac                         | EA     | 40       |                 |                |
| 83                                     | OUE ODSA05000BLT |                      | 5kW heater with built in thermostat          | EA     | 20       |                 |                |
| 84                                     | ACT (AFBUP)      |                      | Louver motor BELIMO                          | EA     | 80       |                 |                |
| 85                                     | ZG-AFB118        |                      | Accessories for motor                        | EA     | 80       |                 |                |
| 86                                     | BRK(KG-8)        |                      | Ball joint 5/16" Belimo                      | EA     | 80       |                 |                |
| CATEGORY 8 - FIRE ALARM EQUIPMENT      |                  |                      |  |        |          |                 |                |
| 87                                     | EDW FSP302G      |                      | Edwards fire alarm panel three zone          | EA     | 20       |                 |                |
| 88                                     | 1400A            |                      | Smoke detector with base                     | EA     | 20       |                 |                |
| 89                                     | 284 BPL          |                      | Heat detector                                | EA     | 20       |                 |                |
| 90                                     | 6251C-002A       |                      | Heat detector mounting base                  | EA     | 20       |                 |                |
| 91                                     | 757-A-WB         |                      | Waterproof box for horn/strobe               | EA     | 20       |                 |                |
| 92                                     | 757-7A-T         |                      | Horn/strobe                                  | EA     | 20       |                 |                |
| 93                                     | 12V485           |                      | System batteries 4.5 AH                      | EA     | 40       |                 |                |
| 94                                     | EOL-P1           |                      | End of line resistors /w assembly base       | EA     | 40       |                 |                |
| 95                                     | 270-SPO          |                      | Break glass manual pull station              | EA     | 20       |                 |                |
| 96                                     | 800-NX114        |                      | Emergency stop, Rockwell                     | EA     | 20       |                 |                |
| 97                                     | SPRE-500-9-C     |                      | 1/2" wire lome                               | 100 FT | 40       |                 |                |

TABLE B1

| Item No.   | Part Number          | Proposed Part Number | Description   | U of I | Est. Qty | Firm Unit Price | Extended Total |
|--|----------------------|----------------------|---|--------|----------|-----------------|----------------|
| CATEGORY 9 - BOXES AND ENCLOSURES                  |                      |                      |   |        |          |                 |                |
| 98   |                      |                      | HAMMOND 12" x 12" x 6" Box, NEMA 12                 | EA     | 4        |                 |                |
| 99   | F66LB                |                      | Box Connector                                       | EA     | 400      |                 |                |
| 100  | 1703                 |                      | 1/2"box connector W/ insulated throat               | EA     | 300      |                 |                |
| 101  | LTB-50               |                      | 1/2" Liquid tight box connector W/ insulated throat | EA     | 60       |                 |                |
| 102  | LTR50                |                      | 1/2" Liquid tight connector, 90, Female             | EA     | 40       |                 |                |
| 103  | 4203                 |                      | 1/2" Liquid tight connector, 90, Male thread        | EA     | 40       |                 |                |
| CATEGORY 10 - LIGHTING FIXTURES/CONTROLS           |                      |                      |   |        |          |                 |                |
| 104  | IBV BC11C5           |                      | light switch cover                                  |        |          |                 |                |
| 105  | LMC CSB115I          |                      | light switch  | EA     | 40       |                 |                |
| 106  | EV248232IST8ELE120V  |                      | flourecent light fixture                            | EA     | 40       |                 |                |
| 107  | F32T841K8RSG13STDESV |                      | Light bulbs for light fixture                       | EA     | 120      |                 |                |
| 108  | KEENE TLW070NLXLPC1  |                      | outdoor photocell light                             | EA     | 40       |                 |                |
| 109  | LUM RGC442MT9W       |                      | emergency lights 120vac (white), with batteries     | EA     | 40       |                 |                |
| CATEGORY 11 - PORTABLE POWER CABLES AND CONNECTORS |                      |                      |   |        |          |                 |                |
| 110  | 5100P9W              |                      | LAVITON PIN AND SLEEVE PLUGS, 100A, 3PH             | EA     | 20       |                 |                |
| 111  | 460P12W              |                      | LAVITON PIN AND SLEEVE PLUGS, 100A, SINGLE PH       | EA     | 20       |                 |                |
| 112  | 5100C9W              |                      | LAVITON PIN AND SLEEVE CONNECTOR, 100A, 3 PH        | EA     | 20       |                 |                |
| 113  | 460C12W              |                      | LAVITON PIN AND SLEEVE CONNECTOR, 60A, SINGLE PH    | EA     | 20       |                 |                |
| 114  |                      |                      | TYPE W PORTABLE POWER CABLE 2AWG, 5 WIRE            | M      | 300      |                 |                |
| 115  |                      |                      | TYPE W PORTABLE POWER CABLE 6AWG, 4 WIRE            | M      | 300      |                 |                |

TABLE B2 - BASIS OF PRICING - OPTION YEARS - SOLICITATION W0125-13EGS6/A

The Prices quoted in Table B2 are to be used for the evaluation of Option years 1 and 2. These prices must be in accordance with the Net Trade Prices, (GST/HST Extra, FOB destination), as shown in the manufacturer's published trade price lists, applicable zone, latest issue valid in the month prior to solicitation closing, with no volume discount applied. The volume discount quoted at Annex B herein shall be applied by the PWGSC Standing Offer Authority during the evaluation of the offer.

Note 1: The Unit Price Quoted is per the Unit of Issue (U of I)

| Item No.                    | Part Number | Proposed Part Number | Description                                    | U of I | Est. Qty | Firm Unit Price | Extended Total |
|-----------------------------|-------------|----------------------|--|--------|----------|-----------------|----------------|
| CATEGORY 1 - WIRE AND CABLE |             |                      |  |        |          |                 |                |
| 1                           |             |                      | #14 awg T90 stranded wire black                | M      | 6000     |                 |                |
| 2                           |             |                      | #14 awg T90 stranded wire white                | M      | 6000     |                 |                |
| 3                           |             |                      | #14 awg T90 stranded wire Blue                 | M      | 6000     |                 |                |
| 4                           |             |                      | #14 awg T90 stranded wire Green                | M      | 6000     |                 |                |
| 5                           |             |                      | #6 awg T90 stranded wire Black                 | M      | 260      |                 |                |
| 6                           |             |                      | #6 awg T90 stranded wire red                   | M      | 260      |                 |                |
| 7                           |             |                      | #6 awg T90 stranded wire white                 | M      | 260      |                 |                |
| 8                           |             |                      | #6 awg T90 stranded wire green                 | M      | 260      |                 |                |
| 9                           |             |                      | 350 MCM T90                                    | M      | 2500     |                 |                |
| 10                          |             |                      | 750 MCM Cable                                  | M      | 1000     |                 |                |
| 11                          |             |                      | 500 MCM Cable                                  | M      | 2000     |                 |                |
| 12                          |             |                      | 350 MCM Cable Copper                           | M      | 2500     |                 |                |
| 13                          |             |                      | 300 MCM Cable Copper                           | M      | 2500     |                 |                |
| 14                          |             |                      | 250 MCM Cable Copper                           | M      | 2500     |                 |                |
| 15                          |             |                      | 0000 MCM Cable Copper                          | M      | 2500     |                 |                |
| 16                          |             |                      | 000 MCM Cable Copper                           | M      | 2500     |                 |                |
| 17                          |             |                      | 00 MCM Cable Copper                            | M      | 2500     |                 |                |
| 18                          |             |                      | 0 MCM Cable Copper                             | M      | 2500     |                 |                |
| 19                          |             |                      | 350 MCM Tech 4 Wire                            | M      | 1500     |                 |                |
| 20                          |             |                      | 1/2" Liquid Tite                               | M      | 400      |                 |                |
| 21                          |             |                      | #10 awg T90 stranded black                     | M      | 400      |                 |                |
| 22                          |             |                      | #10 awg T90 stranded red                       | M      | 400      |                 |                |
| 23                          |             |                      | # 18awg twisted pair, cat 5 non shielded       | M      | 260      |                 |                |
| 24                          |             |                      | #18awg twisted pair, cat 5 shielded            | M      | 260      |                 |                |
| 25                          |             |                      | #18awg fire wire (shielded)                    | M      | 260      |                 |                |
| 26                          |             | TB 1016BTB           | Grounding Plate                                | EA     | 40       |                 |                |
| CATEGORY 2 - CONDUIT        |             |                      |  |        |          |                 |                |
| 27                          | 1485C12     |                      | Hammond lay IN TYPE 12 WIRE WAY STRAIGHT 4 X 4 | EA     | 20       |                 |                |
| 28                          | 1485C24     |                      | Hammond lay IN TYPE 12 WIRE WAY STRAIGHT 4 X 4 | EA     | 20       |                 |                |

TABLE B2

| Item No.                                 | Part Number       | Proposed Part Number | Description   | U of I | Est. Qty | Firm Unit Price | Extended Total |
|--|-------------------|----------------------|---|--------|----------|-----------------|----------------|
| 29                                       | 1485C36           |                      | Hammond lay IN TYPE 12 WIRE WAY STRAIGHT 4 X 4            | EA     | 20       |                 |                |
| 30                                       | 1485C48           |                      | Hammond lay IN TYPE 12 WIRE WAY STRAIGHT 4 X 4            | EA     | 20       |                 |                |
| 31                                       | 1485CV2           |                      | box entry   | EA     | 10       |                 |                |
| 32                                       | 1485C9N           |                      | 90 elbow top opening                                      | EA     | 10       |                 |                |
| 33                                       | 1485C9P           |                      | 90 elbow inside opening                                   | EA     | 10       |                 |                |
| 34                                       | 1485B9Q           |                      | 90 elbow , outside opening                                | EA     | 10       |                 |                |
| 35                                       | 1485CL2           |                      | bracket hanger  | EA     | 60       |                 |                |
| 36                                       |                   |                      | 3/4" EMT CONDUIT  | 100 FT | 60       |                 |                |
| 37                                       |                   |                      | 1/2" EMT CONDUIT  | 100 FT | 400      |                 |                |
| 38                                       |                   |                      | 1" EMT CONDUIT  | 100 FT | 60       |                 |                |
| 39                                       |                   |                      | 2' EMT CONDUIT  | 100 FT | 5        |                 |                |
| 40                                       |                   |                      | 3" EMT CONDUIT  | 100 FT | 5        |                 |                |
| 41                                       |                   |                      | 2" LT   | M      | 20       |                 |                |
| 42                                       |                   |                      | 3" LT   | M      | 20       |                 |                |
| CATEGORY 3 - CONDUIT FITTINGS ETC.       |                   |                      |   |        |          |                 |                |
| 43                                       | 1485CFF           |                      | FLEX FITTING, hammond                                     | EA     | 10       |                 |                |
| 44                                       | 1485CX            |                      | TELESCOPE FITTING, hammond                                | EA     | 10       |                 |                |
| 45                                       |                   |                      | 3/4" EMT STRAPS   | EA     | 2000     |                 |                |
| 46                                       | EMCO 304-S3-PP-8P |                      | swage locks to fit 1/2" piping                            | EA     | 200      |                 |                |
| 47                                       | EMCO S-SO-SN      |                      | swage locks strut nuts                                    | EA     | 200      |                 |                |
| 48                                       | IBV BC52151K      |                      | 4x4 box   | EA     | 300      |                 |                |
| 49                                       | IBV BC52C1        |                      | 4x4 cover plate   | EA     | 100      |                 |                |
| 50                                       | IBV CITA12        |                      | 1/2" Tees   | EA     | 200      |                 |                |
| 51                                       | IBV BC1110        |                      | 4 x 2 boxes   | EA     | 400      |                 |                |
| 52                                       | IBV BC11C4        |                      | blank cover plates 4x 2 box                               | EA     | 100      |                 |                |
| 53                                       | NES 271           |                      | 1/2" liquid tight to EMT connectors (compression fitting) | EA     | 500      |                 |                |
| 54                                       | LMC 5262          |                      | receptacles   | EA     | 160      |                 |                |
| 55                                       |                   |                      | metal receptacle covers                                   | EA     | 160      |                 |                |
| 56                                       | IBV BC11C5        |                      | light switch cover  | EA     | 100      |                 |                |
| 57                                       |                   |                      | 1/2" EMT STRAPS   | EA     | 2000     |                 |                |
| CATEGORY 4 - PANELS/BREAKERS/DISCONNECTS |                   |                      |   |        |          |                 |                |
| 58                                       | SQUARE "D" ONLY   |                      | 1200 Amp fusible Disconnect Nema 3R/12                    | EA     | 6        |                 |                |
| 59                                       | SCH CH367AWK      |                      | 800 Amp fusible Disconnect Nema 3R/12                     | EA     | 8        |                 |                |
| 60                                       | SCH CH366AWK      |                      | 600 Amp fusible Disconnect Nema 3R/12                     | EA     | 12       |                 |                |
| 61                                       | SCH CH365AWK      |                      | 400 Amp Nema 3R/12disconnect                              | EA     | 10       |                 |                |
| 62                                       | SCH CH364AWK      |                      | 200 A NEMA 3R/12, 3 phase fused Disconnect                | EA     | 10       |                 |                |
| 63                                       | SCH CH361         |                      | 30 amp fusible disconnect, NEMA 1                         | EA     | 24       |                 |                |
| 64                                       |                   |                      | 30 amp fuse for above                                     | EA     | 40       |                 |                |

TABLE B2

| Item No.                               | Part Number      | Proposed Part Number | Description                                  | U of I | Est. Qty | Firm Unit Price | Extended Total |
|--|------------------|----------------------|--|--------|----------|-----------------|----------------|
| CATEGORY 5 - FUSES                     |                  |                      |  |        |          |                 |                |
| 65                                     | TRS200R          |                      | class J 200 amp time delay fuses for above   | EA     | 30       |                 |                |
| 66                                     | TRS400R          |                      | class J 400 amp time delay fuses             | EA     | 30       |                 |                |
| 67                                     | A4BT800          |                      | class J 800 amp time delay fuses             | EA     | 24       |                 |                |
| 68                                     | TRS600R          |                      | class J 600 amp time delay fuses for above   | EA     | 72       |                 |                |
| 69                                     | CQO124M126C60    |                      | LOAD CENTER, 60A, 12 POLE, 240V, SQUARE D    | EA     | 24       |                 |                |
| 70                                     |                  |                      | 15amp, single pole                           | EA     | 100      |                 |                |
| 71                                     |                  |                      | 15amp, double pole                           | EA     | 20       |                 |                |
| 72                                     |                  |                      | 30amp, double pole                           | EA     | 20       |                 |                |
| 73                                     |                  |                      | 20amp, double pole                           | EA     | 20       |                 |                |
| CATEGORY 6 - TRANSFORMERS              |                  |                      |  |        |          |                 |                |
| 74                                     | 600 TO 120/240 V |                      | TRANSFORMER 15 KVA wall mounted single phase | EA     | 24       |                 |                |
| 75                                     | 600 TO 120/208 V |                      | TRANSFORMER 15 KVA wall mounted three phase  | EA     | 5        |                 |                |
| CATEGORY 7 - THERMOSTATS/LOUVER MOTORS |                  |                      |  |        |          |                 |                |
| 76                                     | HON 50017460003U |                      | HONEYWELL TRANSFORMER 120V-24V               | EA     | 40       |                 |                |
| 77                                     | HON 27518U       |                      | Honeywell ball joint assembly                | EA     | 80       |                 |                |
| 78                                     |                  |                      | 1/4" x 24" Push rod for louver motor         | EA     | 40       |                 |                |
| 79                                     | HON 7616BRU      |                      | Honeywell crank arm and clip                 | EA     | 40       |                 |                |
| 80                                     | HON T6051A1057U  |                      | Thermostat, NC NO                            | EA     | 20       |                 |                |
| 81                                     | HON T921A1522U   |                      | Modulating Thermostat                        | EA     | 20       |                 |                |
| 82                                     | HON M9185D1004U  |                      | Louver Motor, 24v ac                         | EA     | 40       |                 |                |
| 83                                     | OUE ODSA05000BLT |                      | 5kW heater with built in thermostat          | EA     | 20       |                 |                |
| 84                                     | ACT (AFBUP)      |                      | Louver motor BELIMO                          | EA     | 10       |                 |                |
| 85                                     | ZG-AFB118        |                      | Accessories for motor                        | EA     | 10       |                 |                |
| 86                                     | BRK(KG-8)        |                      | Ball joint 5/16" Belimo                      | EA     | 10       |                 |                |
| CATEGORY 8 - FIRE ALARM EQUIPMENT      |                  |                      |  |        |          |                 |                |
| 87                                     | EDW FSP302G      |                      | Edwards fire alarm panel three zone          | EA     | 20       |                 |                |
| 88                                     | 1400A            |                      | Smoke detector with base                     | EA     | 20       |                 |                |
| 89                                     | 284 BPL          |                      | Heat detector                                | EA     | 20       |                 |                |
| 90                                     | 6251C-002A       |                      | Heat detector mounting base                  | EA     | 20       |                 |                |
| 91                                     | 757-A-WB         |                      | Waterproof box for horn/strobe               | EA     | 20       |                 |                |
| 92                                     | 757-7A-T         |                      | Horn/strobe                                  | EA     | 20       |                 |                |
| 93                                     | 12V485           |                      | System batteries 4.5 AH                      | EA     | 40       |                 |                |
| 94                                     | EOL-P1           |                      | End of line resistors /w assembly base       | EA     | 40       |                 |                |
| 95                                     | 270-SPO          |                      | Break glass manual pull station              | EA     | 20       |                 |                |
| 96                                     | 800-NX114        |                      | Emergency stop, Rockwell                     | EA     | 20       |                 |                |
| 97                                     | SPRE-500-9-C     |                      | 1/2" wire lome                               | 100 FT | 40       |                 |                |

TABLE B2

| Item No.   | Part Number          | Proposed Part Number | Description   | U of I | Est. Qty | Firm Unit Price | Extended Total |
|--|----------------------|----------------------|---|--------|----------|-----------------|----------------|
| CATEGORY 9 - BOXES AND ENCLOSURES                  |                      |                      |   |        |          |                 |                |
| 98   |                      |                      | HAMMOND 12" x 12" x 6" Box, NEMA 12                 | EA     | 4        |                 |                |
| 99   | F66LB                |                      | Box Connector                                       | EA     | 400      |                 |                |
| 100  | 1703                 |                      | 1/2"box connector W/ insulated throat               | EA     | 300      |                 |                |
| 101  | LTB-50               |                      | 1/2" Liquid tight box connector W/ insulated throat | EA     | 60       |                 |                |
| 102  | LTR50                |                      | 1/2" Liquid tight connector, 90, Female             | EA     | 40       |                 |                |
| 103  | 4203                 |                      | 1/2" Liquid tight connector, 90, Male thread        | EA     | 40       |                 |                |
| CATEGORY 10 - LIGHTING FIXTURES/CONTROLS           |                      |                      |   |        |          |                 |                |
| 104  | IBV BC11C5           |                      | light switch cover                                  |        | 40       |                 |                |
| 105  | LMC CSB115I          |                      | light switch  | EA     | 40       |                 |                |
| 106  | EV248232IST8ELE120V  |                      | flourecent light fixture                            | EA     | 40       |                 |                |
| 107  | F32T841K8RSG13STDESV |                      | Light bulbs for light fixture                       | EA     | 120      |                 |                |
| 108  | KEENE TLW070NLXLPC1  |                      | outdoor photocell light                             | EA     | 40       |                 |                |
| 109  | LUM RGC442MT9W       |                      | emergency lights 120vac (white), with batteries     | EA     | 40       |                 |                |
| CATEGORY 11 - PORTABLE POWER CABLES AND CONNECTORS |                      |                      |   |        |          |                 |                |
| 110  | 5100P9W              |                      | LAVITON PIN AND SLEEVE PLUGS, 100A, 3PH             | EA     | 20       |                 |                |
| 111  | 460P12W              |                      | LAVITON PIN AND SLEEVE PLUGS, 100A, SINGLE PH       | EA     | 20       |                 |                |
| 112  | 5100C9W              |                      | LAVITON PIN AND SLEEVE CONNECTOR, 100A, 3 PH        | EA     | 20       |                 |                |
| 113  | 460C12W              |                      | LAVITON PIN AND SLEEVE CONNECTOR, 60A, SINGLE PH    | EA     | 20       |                 |                |
| 114  |                      |                      | TYPE W PORTABLE POWER CABLE 2AWG, 5 WIRE            | M      | 300      |                 |                |
| 115  |                      |                      | TYPE W PORTABLE POWER CABLE 6AWG, 4 WIRE            | M      | 300      |                 |                |