

**RETURN BIDS TO:**  
**RETOURNER LES SOUMISSIONS À:**  
 Bid Receiving Public Works and Government  
 Services Canada/Réception des soumissions Travaux  
 publics et Services gouvernementaux Canada  
 1713 Bedford Row  
 Halifax, N.S./Halifax, (N.É.)  
 B3J 1T3  
 Bid Fax: (902) 496-5016

## SOLICITATION AMENDMENT MODIFICATION DE L'INVITATION

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

### Comments - Commentaires

Vendor/Firm Name and Address  
 Raison sociale et adresse du  
 fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution  
 Acquisitions  
 1713 Bedford Row  
 Halifax, N.S./Halifax, (N.É.)  
 B3J 3C9

<b>Title - Sujet</b> RENTAL - WASHERS AND DRYERS	
<b>Solicitation No. - N° de l'invitation</b> W010C-12C229/A	<b>Amendment No. - N° modif.</b> 001
<b>Client Reference No. - N° de référence du client</b> W010C-12-C229	<b>Date</b> 2012-07-30
<b>GETS Reference No. - N° de référence de SEAG</b> PW-\$HAL-219-8710	
<b>File No. - N° de dossier</b> HAL-1-66859 (219)	<b>CCC No./N° CCC - FMS No./N° VME</b>
<b>Solicitation Closes - L'invitation prend fin at - à 02:00 PM on - le 2012-08-20</b>	<b>Time Zone</b> Fuseau horaire Atlantic Daylight Saving Time ADT
<b>F.O.B. - F.A.B.</b> <b>Plant-Usine:</b> <input type="checkbox"/> <b>Destination:</b> <input checked="" type="checkbox"/> <b>Other-Autre:</b> <input type="checkbox"/>	
<b>Address Enquiries to: - Adresser toutes questions à:</b> Richard, Linda K.	<b>Buyer Id - Id de l'acheteur</b> hal219
<b>Telephone No. - N° de téléphone</b> (902) 496-5261 ( )	<b>FAX No. - N° de FAX</b> (902) 496-5016
<b>Destination - of Goods, Services, and Construction:</b> <b>Destination - des biens, services et construction:</b>	

Instructions: See Herein

Instructions: Voir aux présentes

<b>Delivery Required - Livraison exigée</b>	<b>Delivery Offered - Livraison proposée</b>
<b>Vendor/Firm Name and Address</b> <b>Raison sociale et adresse du fournisseur/de l'entrepreneur</b>	
<b>Telephone No. - N° de téléphone</b> <b>Facsimile No. - N° de télécopieur</b>	
<b>Name and title of person authorized to sign on behalf of Vendor/Firm (type or print)</b> <b>Nom et titre de la personne autorisée à signer au nom du fournisseur/de l'entrepreneur (taper ou écrire en caractères d'imprimerie)</b>	
<b>Signature</b>	<b>Date</b>

## AMENDMENT 001

This amendment is raised to make the following changes:

### 1. Under Product Requirements Section 01 61 00 - 2.1 Washers

Delete: .9 Washers must have water level control.

Insert: .9 Washers must have automatic water level control.

### 2. Under Product Requirements Section 01 61 00 - 2.2 Dryers

Delete: .3 Energy efficient qualified Energy Star.

### 3. Under Annex "C" - Mandatory Technical Cross-Reference (Evaluation - Technical Phase 1)

Delete: In its entirety

Add:

## ANNEX "C" MANDATORY TECHNICAL CROSS-REFERENCE (EVALUATION - TECHNICAL PHASE 1)

Bidders are requested to provide cross-reference below to identify the page(s) where each mandatory specification can be demonstrated in their technical documentation provided with their bid. Canada reserves the right to verify any and all information relating to mandatory requirements.

Item	Requirement	Cross-reference from Literature (please indicate brochure title, page number, etc.)
<b>2.1 Washers</b>		
.1	Non coin-operated machine	
.2	Energy efficient front load loading washing machine certified Energy Star	
.3	3.5 - 4.4 cu. Ft. Minimum capacity	
.4	White in color	
.5	120VAC, 60 Hz input voltage	
.6	Energy consumption not to exceed 300 kWh/year	
.7	As a minimum, temperature levels will be	

	hot/cold, warm/cold and cold/cold (or equivalent)	
.8	As a minimum, wash cycles will be light, regular, permanent press (or equivalent)	
.9	Washer must have automatic water level control.	
.10	Washer must have provision for automatic dispensing of bleach and fabric softener.	
.11	Machines dimensions must allow installation in all sites identified in Annex "A".	
<b>2.2 Dryers</b>		
.1	Non coin operated machine	
.2	Electric	
.4	6.0 - 7.5 cu. Ft. capacity	
.5	White in color	
.6	120/240 VAC, 1Ph, 60Hz input voltage	
.7	As a minimum, dryer cycle selections will include delicate, permanent press, and regular (or equivalent) as well as ability to select a time cycle.	
.8	As a minimum, dryer must feature a temperature control (High/Medium/Low)	
.9	Moisture sensor	
.	Machines dimensions must allow installation in all sites identified in Annex A.	
.10	Dryer must have interior lighting.	
.11	Dryer must have lint screen.	

All other terms and conditions remain unchanged.