

RETURN BIDS TO:
RETOURNER LES SOUMISSIONS À:
**Public Works and Government Services / Travaux
publics et services gouvernementaux**
Kingston Procurement
Des Acquisitions Kingston
86 Clarence Street, 2nd floor
Kingston
Ontario
K7L 1X3
Bid Fax: (613) 545-8067

SOLICITATION AMENDMENT
MODIFICATION DE L'INVITATION

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

Comments - Commentaires

Vendor/Firm Name and Address
Raison sociale et adresse du
fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution
Public Works and Government Services / Travaux
publics et services gouvernementaux
Kingston Procurement
Des Acquisitions Kingston
86 Clarence Street, 2nd floor
Kingston
Ontario
K7L 1X3

Title - Sujet Custom Stainless Steel Table	
Solicitation No. - N° de l'invitation 21120-133617/A	Amendment No. - N° modif. 001
Client Reference No. - N° de référence du client 21120-13-3617	Date 2013-06-18
GETS Reference No. - N° de référence de SEAG PW-\$KIN-620-6129	
File No. - N° de dossier KIN-3-40032 (620)	CCC No./N° CCC - FMS No./N° VME
Solicitation Closes - L'invitation prend fin at - à 02:00 PM on - le 2013-07-22	
Time Zone Fuseau horaire Eastern Daylight Saving Time EDT	
F.O.B. - F.A.B. Specified Herein - Précisé dans les présentes Plant-Usine: <input type="checkbox"/> Destination: <input type="checkbox"/> Other-Autre: <input checked="" type="checkbox"/>	
Address Enquiries to: - Adresser toutes questions à: Porter, Marta M.	Buyer Id - Id de l'acheteur kin620
Telephone No. - N° de téléphone (613) 547-7587 ()	FAX No. - N° de FAX (613) 545-8067
Destination - of Goods, Services, and Construction: Destination - des biens, services et construction:	

Instructions: See Herein

Instructions: Voir aux présentes

Delivery Required - Livraison exigée	Delivery Offered - Livraison proposée
Vendor/Firm Name and Address Raison sociale et adresse du fournisseur/de l'entrepreneur	
Telephone No. - N° de téléphone Facsimile No. - N° de télécopieur	
Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) Nom et titre de la personne autorisée à signer au nom du fournisseur/ de l'entrepreneur (taper ou écrire en caractères d'imprimerie)	
Signature	Date

Solicitation No. - N° de l'invitation

21120-133617/A

Amd. No. - N° de la modif.

001

Buyer ID - Id de l'acheteur

kin620

Client Ref. No. - N° de réf. du client

21120-13-3617

File No. - N° du dossier

KIN-3-40032

CCC No./N° CCC - FMS No/ N° VME

Amendment 001 - Custom Stainless Steel Table

Is being raised to add a bilingual legend to Annex "C" as follows:


Refer: Annex "C" Drawings Bath and Millhaven Institutions/Bath and Millhaven Equipment List (attached)

Delete: In its Entirety


Insert: Annex "C" Drawings Bath and Millhaven Institutions/Bath and Millhaven Equipment List (attached)

BATH INSTITUTION - EQUIPMENT LIST

#	Qty	Equipment	Phase	Amps	Kw	Volts	H.P.	Height	c.w.	HW	Drain	Cashless	B.T.U/hr	Remarks
1		Storage system on rails, chrome shelving (610 x 1823) *												* (5) shelves per section
2		Storage system on rails, chrome shelving (487 x 1823) *												(5) shelves per section
3		Lot of DuraMag racks												
4		Lot of DuraMag racks												
5		Combination walk-in Cooler and Freezer, air cooled												
		Cooler section with floor and ramp *												
		Freezer section with floor, ramp and sliding door *	comp:	3	16.8	208	3				1"			* (2) Unit cooler 1.8 amps each
5A		Walk-in Dairy cooler (3000 x 3500) *	comp:	3	32.6	208	4				1"			* Fan 208 Volts, 1 PH 1.8amps Defrost 230 Volts 3PH
6			comp:	1	6.8	208	0.75				1"			* Evaporator: 115 Volts, 1 PH, 0.9 amps
7		Combi transport carts												
8		Walk-in cooler with 2 sliding doors, air cooled *	comp:	3	27	208	5				1"			* Unit cooler 208 Volts, 3PH / Heater 13 amps, 1PH / Fan 1.8 amps, 1PH
			comp:	3	13.7	208	2.25							* (5) Fans 1.35 amps each, m(2) Heaters 13 amps each
9		Roll-in Blast chillers, compressors to be located on the roof (Equipment to be supplied by client)				208/120	4"				1"			* Air cooled condensing unit
10	3	Cook-chill filling kettle 100 gal, with non tilt-out agitator				208								* Connected to grease trap / steam 1"
11	1	Utility raceways to support Cook Kettles and pump stations				208					1/2"			* All electrical, water, steam and air to run up the floor into the utility column of the utility chase
12	1	Kettle control panel on pedestal				208					1/2"			position of pedestal will be in front of the middle kettle
13		Walk-in Cooler w/tilt door & (1) sliding door, air cooled*		3	30	208								* Evaporator: 115 Volts, 1 PH, 2.7 amps
14		Walk-in Cooler w/tilt door & (1) sliding door, air cooled*		3	7.5	208	2				1"			* Evaporator: 115 Volts, 1 PH, 2.7 amps
15		Walk-in Cooler w/tilt door & (1) sliding door, air cooled*		3	7.5	208	2				1"			* Evaporator: 115 Volts, 1 PH, 2.7 amps
16		Walk-in Cooler w/tilt door & (1) sliding door, air cooled*		3	7.5	208	2				1"			* Evaporator: 115 Volts, 1 PH, 2.7 amps
17		Gas roll-in full combi oven		3	9.1	208	2.5				1"			* Evaporator: 115 Volts, 1 PH, 2.7 amps
18		Single gas Combi-oven/steamer with stand		15	120	120					2"		215,000	* Water filter system recommended
19		Heavy duty gas range w/infid on oven base 36"		29	120	120					2"		115,000	* Water filter system recommended
20		gas range w/tilt top on open base									1/2"		105,000	* Water filter system recommended
21		Stainless steel work table 1524 x 762 x 914 h		15		120		48"			1"		70,000	* Rear gas connection
22		Step-in Cooler with floor, air cooled (DWR33)				208/120								* Rear gas connection
23		Chill crates												(7) Utility plug total(1) utility pole w/2 plugs
24		Roll-in Insulated hot food holding, cabinet, sized for Combi Ovens		30	4	120/208								
25		Rapid product chiller/cook tank 100 gallons												
26		Mid volume rapid product chiller 6100 gal	3	20	208	208			1/2"	1/2"	2"			* Steam 3/4" - 90 lbs, connected to outside (Item #40) remote compressor
27		Salad dryer	3	20	208	208	48"		1/2"		3"			* Remote compressor
28		Stainless steel double pot sink w/drainboard 610 each side c/w faucet	1	2.5	120	120	48"							
29		Stainless steel work table 2134 x 763 x 914		15	120	120	48"		1/2"	1/2"	1 1/2"			* Connected to grease trap
30		Vegetable processor		5.3	208	208	4							(1) Utility plug
31		Mobile pump/fill station		10	208	208								Plug/NEMA1ULIS-20
32		Vacuum clipper w/vertical vacuum nozzle	1	10	208	208					2"			H* compress air inlet- 8 CFM @ 80 PS / * Ind ten watts
33		Automatic wrapping machine												IV compress air inlet- 8 CFM @ 80 PSI
34		Stainless steel work table 3050 x 762 x 914												
35		Refrigerated stainless steel ingredient table		15	120	120		48"						(2) Utility plugs, (1) on pole
36		80 quart mixer	1	14	120	120		48"						(1) Utility plug
37		Stainless steel work table 1524 x 762 x 914	1	15	120	120		48"						
38		Stainless steel work table 3050 x 762 x 914	1	15	120	120		48"						(1) Utility plug
39		Air cooled remote refrigeration package for chill tanks	1	15	120	120		48"						(1) Utility plug
40		Stainless steel work table 2134 x 762 x 914	3	15	120	120		48"						(2) Utility plugs
41		Air Compressor	1	30	208	208	4							* RLA 60 amps, MFRS125 amps - located outside
42		Grated floor trench with floor drain (1 existing, 1 new)	1	30	208	208								(1) Utility plug
43		Stainless steel sink wall mount 190S x 451 w/tilt(4) infra-red faucets												* Located in basement
44		Locker section: (3) 6 x K door per section, (2) 4 x 6 door per section												* Connected to grease trap
45		Lot of lockers for inmates (by Millwork)												
46		Shelving (5) 42" X 18", (10) 60" X 18"							1/2"	1/2"	1 1/2"			
47		Juice dispenser, bag-in-a-box- (4 flavors)												
48		Stainless steel work table 1219 x 914, secured	1		120				1/2"		1/2"			* With shut off valve
49		Rotary toaster												
50		Milk dispenser 2 spouts	1	19.4	4	208								
51		Hot food table w/tilt pick-up section, sneeze guard and tray rail *	1	20	4.9	208	Xnl							
52		Stainless steel work table 1219 x 914, secured	1	20	4.9	208								* With thermostatic controls ** With shut off valve
53		Rotary toaster	1	19.4	4	208								
54														
55														
56														
57														









DOUBLE POT SINK WITH DRAINBOARD
AND GARBAGE CHUTE #62

REVISION: REV.1 23-04-2012



MATERIAL:
 -ALL S/S MATERIAL:
 -TOP 18GA.; ALL SHELVES 18GA;
 -NON VISIBLE CHANNELS 14GA GALV
 -ALL WELDED AND POLISHED
NOTE:
 -REINFORCEMENTS REQUIRED FOR HEAVY EQUIPMENT

QTY: 1 REQUIRED



MILLHAVEN INSTITUTION

HEAVY DUTY STAND
 ITEM: #10

QTY: 1



QTY: 1

Document _001_EN_Floor Plan Millhaven.pdf

Drawing no. F211	N° du dessin F211
GROUND FLOOR EQUIPMENT AND FURNITURE PLAN	REZ-DE-CHAUSSEE PLAN DU MATÉRIEL ET DU MOBILIER
MILLHAVEN INSTITUTION NEW KITCHEN KINGSTON, ONTARIO	ÉTABLISSEMENT DE MILLHAVEN NOUVELLE CUISINE KINGSTON (ONTARIO)
ISSUED FOR TENDER	ÉMIS POUR SOUMISSION
INSTITUTION BUILDING #MHU LOCATION OF WORK	BÂTIMENT DE L'ÉTABLISSEMENT : USM EMPLACEMENT DES TRAVAUX
FREEZER	CONGÉLATEUR
KITCHEN	CUISINE
DRY STORAGE	ENTREPOSAGE SEC
GARBAGE ROOM	LOCAL DES DÉCHETS
GROUND FLOOR EQUIPMENT AND FURNITURE PLAN	REZ-DE-CHAUSSEE - PLAN DE MATÉRIEL ET DE MOBILIER

Document_002_EN_drawing MI WORK TABLE WITH SINK #8-PWGSC.pdf

S/S HEAVY DUTY TABLE WITH SINK	TABLE TRÈS ROBUSTE EN INOX AVEC ÉVIER
ITEM	ARTICLE
QTY	QTÉ
MILLHAVEN INSTITUTION	ÉTABLISSEMENT DE MILLHAVEN
MATERIAL: S/S TOP 16GA 304#4 VISIBLE CHANNELS 14GA NON VISIBLE CHANNELS 14GA. S/S ALL WELDED AND POLISHED DECK FAUCET 8"	MATÉRIAU : DESSUS EN INOX CAL. 16, NUANCE 304#4 PROFILÉS EN U APPARENTS CAL. 14 PROFILÉS EN U DISSIMULÉS INOX CAL. 14 ENTIÈREMENT SOUDÉ ET POLI ROBINET DE COMPTOIR 8"
10" X 14" X 7" DEEP WITH CENTER CRUMB CUP DRAIN	10" X 14" X 7" PROF. AVEC OUVERTURE DE VIDANGE CENTRALE ET GRILLE-PANIER
8.0000	8.0000
WELDED IN SINK	ÉVIER INTÉGRÉ
S/S 16GA. TOP	DESSUS EN INOX CAL. 16
S/S 16GA. UNDERSHELF	TABLETTE EN INOX CAL. 16
1.625" DIA. LEGS	PATTES DE 1,625" DIA.

S/S HEAVY DUTY TABLE WITH SINK	TABLE TRÈS ROBUSTE EN INOX AVEC ÉVIER
ITEM	ARTICLE
QTY	QTÉ
MILLHAVEN INSTITUTION	ÉTABLISSEMENT DE MILLHAVEN
30.0000	30.0000
WELDED IN SINK	ÉVIER INTÉGRÉ
S/S 16GA. TOP	DESSUS EN INOX CAL. 16
10" X 14" X 7" DEEP WITH CENTER CRUMB CUP DRAIN	10" X 14" X 7" PROF. AVEC OUVERTURE DE VIDANGE CENTRALE ET GRILLE-PANIER
1.625" DIA. LEGS	PATTE DE 1.625" DE DIA.
S/S 16GA. UNDERSHELF	TABLETTE EN INOX CAL. 16
MATERIAL : S/S TOP 16GA 304#4 VISIBLE CHANNELS 14GA NON VISIBLE CHANNELS 14GA. S/S ALL WELDED AND POLISHED DECK FAUCET 8"	MATÉRIAU : DESSUS EN INOX CAL. 16, NUANCE 304#4 PROFILÉS EN U APPARENTS CAL. 14 PROFILÉS EN U DISSIMULÉS INOX CAL. 14 ENTIÈREMENT SOUDÉ ET POLI ROBINET DE COMPTOIR 8"

HEAVY DUTY STAND	SUPPORT TRÈS ROBUSTE
ITEM	ARTICLE
QTY	QTÉ
MILLHAVEN INSTITUTION	ÉTABLISSEMENT DE MILLHAVEN
LIP 1" HIGH ALL AROUND	LÈVRE 1" HAUT. TOUT AUTOUR
S/S 16 GA. REINFORCED TOP	DESSUS RENFORCÉ EN INOX CAL. 16
MATERIAL : ALL S/S MATERIAL; TOP 16GA ; ALL SHELVES 16GA; NON VISIBLE CHANNELS 14GA GALV ALL WELDED AND POLISHED	MATÉRIAU : TOUT INOX : DESSUS CAL. 16; TOUTES LES TABLETTES CAL. 16; PROFILÉS EN U DISSIMULÉS CAL. 14, GALV. ENTIÈREMENT SOUDÉ ET POLI
NOTES : REINFORCEMENTS REQUIRED FOR HEAVY EQUIPMENT	NOTES : RENFORCEMENTS REQUIS POUR MATÉRIEL LOURD
QTY: 1 REQUIRED	QTÉ REQUISE : 1
72.0000	72.0000
S/S 16GA. BASE SHELF	TABLETTE DE BASE INOX CAL. 16
S/S 12GA. GALV HAT CHANELS LEGS WELDED TO CHANEL FOR STRENGTH	INOX CAL. 12, PROFILÉS EN U DE TYPE CHAPEAU GALV. PATTES SOUDÉES AU PROFILÉ EN U POUR RÉSISTANCE

DOUBLE POT SINK WITH DRAINBOARD AND GARBAGE CHUTE #62	ÉVIER À DEUX CUVES AVEC ÉGOUTTOIR ET CHUTE À DÉCHETS N° 62
REVISION: REV.1 23-04-2012	RÉVISION : RÉV.1 23-04-2012
97.2500	97.2500
ITEM #62 RUBBER SCRAP BLOCK INCLUDED	ARTICLE N° 62 GOULOT RACLOIR EN CAOUTCHOUC INCLUS
1.5" DRAIN	ORIFICE D'ÉVACUATION 1.5"
S/S SINKS	ÉVIERS EN INOX
DBL DRAINBOARDS	ÉGOUTTOIRS DOUBLES
CORNER DRAIN AND OVERFLOW	ORIFICE D'ÉVACUATION DE COIN ET TROP-PLEIN
GALV. LEGS	PATTES GALV.

