



13mm POLYCARBONATE SHEET  
 CLEAN EXISTING WINDOW BEFORE  
 INSTALLATION.

PROVIDE TAMPER PROOF EXPOSED FASTENERS THROUGH  
 EXISTING ALUMINIUM FRAME AT 300mm O.C. PROVIDE RUBBER  
 BASED CORROSION RESISTANT WASHER UNDER FASTENER TO  
 PENETRATE EXISTING WOOD FRAMING

FASTEN 13mm POLYCARBONATE SHEET TO EXISTING ALUMINIUM FRAME  
 WINDOW WITH TAMPERPROOF FASTENERS AT 200mm O.C.

SECURITY CAULKING CONTINUOUS AT PERIMETER OF POLYCARBONATE  
 SHEET TO 15.9mm PLYWOOD

HARDWOOD CORNER WITH EXPOSED 12mm RADIUS

PROVIDE INFILL BLOCKING AS REQUIRED

drawing title **WINDOW PROTECTION DETAIL**

project title **RENOVATIONS TO GOVERNMENT OF CANADA BUILDING  
 ULUKHAKTOK, NWT**

revision



BOX 2353, 5016 - 47th ST  
 YELLOWKNIFE, NT  
 CANADA X1A 2P7  
 TEL [867] 920-2609  
 FAX [867] 920-4261  
 EMAIL : PSAV@PSAV.CA

design by	G.D.
drawn by	AM
reviewed by	G.D.

job no.	2013-01
scale	1 : 75
date	MAY 28, 2013

dwg.no.  
**ASK  
 001**