


Job \_\_\_\_\_



## METRO BOW TIE™ DUNNAGE RACKS



Racks joined in "end-to-end" and "back-to-back" configuration.

### SPECIFICATIONS:

- Rotationally molded grey polyethylene construction
- Slotted top for air circulation
- Slots run front to back for easy loading and unloading
- All rack edges have generous radius to prevent product snagging or marking
- Weight capacity: 30" and 36" racks - 1,500 lbs.  
48" and 60" racks - 3,000 lbs.
- Each rack provided with separate polymer tie for joining racks in "end-to-end" and "back-to-back" configurations. Rack has a recess centered each side of top surface to accept polymer tie.
- Joining system tie drops in and is removed from top without the use of tools.

Cat. No.	Width		Length		Height		Approx. Pkg. Wt.	
	(in.)	(mm)	(in.)	(mm)	(in.)	(mm)	(lb.)	(kg)
HP2230PD	22	550	30	760	12	305	24	10.8
HP2236PD	22	550	36	910	12	305	26	11.7
HP2248PD	22	550	48	1220	12	305	34	15.3
HP2260PD	22	550	60	1525	12	305	42	19

Manufactured by:



**InterMetro Industries Corporation**  
 North Washington Street, Wilkes-Barre, PA 18705  
 Phone: 570-825-2741 • Fax: 570-825-2852  
 For Product Information Call: 1-800-433-2232  
 Visit Our Web Site: [www.metro.com](http://www.metro.com)

L03-105  
 Rev. 5/99  
 Printed in U.S.A.

Information and specifications are subject to change without notice. Please confirm at time of order.



Item# \_\_\_\_\_


Job \_\_\_\_\_



## METRO BOW TIE™ DUNNAGE RACKS



- **Versatile:** Racks join together easily without tools in “end-to-end” and “back-to-back” configurations with the exclusive bow-tie™ feature.
- **Durable:** Rust and corrosion proof polymer construction.
- **Strong:** Heavy-duty construction gives racks the strength to hold up to 3,000 lbs. per unit.
- **Unique Design:** Racks have front to back slots for easier loading and unloading and superior air flow which promotes longer shelf life.
- **Easy to Clean:** Smooth rotomolded polymer offers snag-free surfaces and promotes easy cleaning.
- **NSF Approved**
- **UPS Shippable**
- **No Assembly required.**



Racks joined in “end-to-end” configuration.



**InterMetro Industries Corporation**  
North Washington Street  
Wilkes-Barre, PA 18705  
[www.metro.com](http://www.metro.com)



Item # \_\_\_\_\_

Job \_\_\_\_\_




**Bow-Tie™ Dunnage Racks** with \*Microban® Antimicrobial Product Protection

## Metro® BOW-TIE™ DUNNAGE RACKS with \*Microban® Antimicrobial Product Protection

**Metro Bow-Tie Dunnage Racks with built-in Microban® antimicrobial product protection are protected from bacteria, mold, mildew and fungi that cause odors, stains and product degradation.**

- **Easy to Clean:** Smooth rotomolded polymer offers snag-free surfaces and promotes easy cleaning. Microban® antimicrobial product protection keeps dunnage racks “cleaner between cleanings” by inhibiting bacteria, mold, mildew and fungi that cause odors, stains and product degradation.
- **Versatile:** Racks join together easily without tools in “end-to-end” and “back-to-back” configurations with the exclusive bow-tie™ feature.
- **Durable:** Rust and corrosion proof polymer construction.
- **Strong:** Heavy-duty construction gives racks the strength to hold up to 3,000 lbs. (1,365kg) per unit.
- **Unique Design:** Racks have front to back slots for easier loading and unloading and superior air flow which promotes longer shelf life.
- **NSF Listed**
- **UPS Shippable**
- **No Assembly Required.**



*Racks joined in “end-to-end” configuration.*

\*MICROBAN® and the MICROBAN® symbol are registered trademarks of the Microban Products Company, Huntersville, NC.



**InterMetro Industries Corporation**  
North Washington Street  
Wilkes-Barre, PA 18705  
www.metro.com



**9.099A**

Job \_\_\_\_\_

# Metro® BOW-TIE™ DUNNAGE RACKS

with \*Microban® Antimicrobial Product Protection



*Racks joined in "end-to-end" and "back-to-back" configuration.*

## Specifications

- Rotationally molded grey polyethylene construction
- Slotted top for air circulation
- Slots run front to back for easy loading and unloading
- All rack edges have generous radius to prevent product snagging or marking
- Weight capacity: 30" (762mm) and 36" (914mm) racks — 1,500 lbs. (683kg)  
48" (1219mm) and 60" (1524mm) racks — 3,000 lbs. (1365kg)
- Each rack provided with separate polymer tie for joining racks in "end-to-end" and "back-to-back" configurations. Rack has a recess centered each side of top surface to accept polymer tie.
- Joining system bow-tie drops in and is removed from top without the use of tools.

Cat. No.	Width		Length		Height		Approx. Pkg. Wt.	
	(in.)	(mm)	(in.)	(mm)	(in.)	(mm)	(lb.)	(kg)
HP2230PDMB	22	559	30	762	12	305	24	10.9
HP2236PDMB	22	559	36	914	12	305	26	11.8
HP2248PDMB	22	559	48	1219	12	305	34	15.4
HP2260PDMB	22	559	60	1524	12	305	42	19

All Metro Catalog Sheets are available on our Web Site: [www.metro.com](http://www.metro.com)



### InterMetro Industries Corporation

North Washington Street, Wilkes-Barre, PA 18705  
Phone: 570-825-2741 • Fax: 570-825-2852

For Product Information Call: 1-800-433-2232

L03-105A  
Printed in U.S.A. Rev. 2/04

Information and specifications are subject to change without notice. Please confirm at time of order.

Copyright © 2003 InterMetro Industries Corp.