




SCALE : 1:25



0m 500m 1000m 1500m 2000m 2500m



SCALE : 1:5



SCALE : 1:5



0mm 100 200 300 400 500mm

S1

NOTE: 1. ALL 316 STAINLESS STEEL BEAMS, PLATES & ASSOCIATED NUTS, BOLTS & WASHERS ASSOCIATED WITH SEAM INSTALLATION ARE GOVERNMENT SUPPLIED.

2. CONTRACTOR SHALL SUPPLY ALL PLATES, PIPES, FITTINGS, AND BOLTS AND WASHERS FOR PIPE COLLAR. ALL SHALL BE 316 STAINLESS STEEL.

3. CONTRACTOR SHALL SUPPLY AND INSTALL ALL ROCK STEEL BOLTS AND ASSOCIATED NUTS, PLATES AND/OR WASHERS AS FOLLOWS:

- a) ALL BOLTS SHALL BE GALVANIZED SQUID DEFORMED BOLT WITH NOT LESS THAN 300 MM OF COARSE THREAD SUITABLE FOR TENSIONING BY MEANS OF TURNING WRENCH.
- b) THE DEFORMED STEEL BARS SHALL BE 25 MM DIAMETER WITH AN UNSTALLED LENGTH OF ROCK ANCHOR SHALL BE 1.5 TIMES THE LENGTH OF EACH ROCK BOLT SHALL HAVE
- i) GALVANIZED BEVELLED HAREDENED STEEL WASHERS (MIN. 2 PER BOLT).
- ii) GALVANIZED HEXAGONAL NUTS (MIN. 3 PER BOLT).
- iii) A STAINLESS STEEL ANCHOR.
- iv) GALVANIZED STEEL WASHERS SHALL BE CONFORM TO ASTM A325 AND FOR BEARING PLATES SHALL CONFORM TO CSA 335 OR EQUIVALENT. GALVANIZING SHALL CONFORM TO CSA G164.