



Royal Canadian Mounted Police
Gendarmerie royale du Canada

Government of Canada / Gouvernement du Canada

Solicitation No./No de l=invitation: M5000-14-0617

RETURN BIDS TO:
RETOURNER LES SOUMISSIONS A:
Bid Receiving/Réception des soumissions

Royal Canadian Mounted Police (RCMP)
NWR Procurement & Contracting Services
Place 123
#203, 12315 – Stony Plain Road
Edmonton, AB T5N 3Y8

SOLICITATION AMENDMENT
MODIFICATION DE L'INVITATION

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

Comments – Commentaries

Vendor/Firm Name and Address
Raison sociale et adresse du fournisseur/de l'entrepreneur

Telephone N no de téléphone:

Title-Sujet 22 All-Terrain Vehicles for RCMP Manitoba and Alberta	
Solicitation No. - No. de l=invitatio M5000-14-0617	Amendment No. - N° modif. 001
Client Reference No. - No. De Référence du Client 14-111 and 14-122	Date August 2, 2013
Solicitation Closes -L=invitation prend fin at - à 02:00 PM Mountain Daylight Time Zone on - le Tuesday September 3, 2013	
F.O.B. - F.A.B. Dsetination	
Address Enquiries to: - Adresser toutes questions à: Joanne Maybroda	
Telephone No. - No de téléphone (780-341-3037	Fax No. - N° de FAX: 780-454-4523
Destination of Goods, Services, and Construction: Destinations des biens, services et construction: SEE HEREIN	
This document does not contain a SECURITY requirement.	
Name and title of person authorized to sign on behalf of Vendor/Firm Nom et titre de la personne autorisée à signer au nom du fournisseur/de l=entrepreneur _____ Name Title	
_____ Signature Date	



Royal Canadian Mounted Police
Gendarmerie royale du Canada

Government
of Canada

Gouvernement
du Canada

Solicitation No./No de l=invitation: M5000-14-0617

Solicitation Amendment N° 001 is raised to change specifications as follows:

August 2, 2013

1. Under “ANNEX “A” REQUIREMENT

DELETE:

Item no.:	Category:	Description:
A.	Year	
1.		New 2013 (or the manufacturer's latest manufactured model)
B.	Engine	
1.	Engine Type:	4-Stroke
2.	Cooling:	Liquid cooled
3.	Displacement:	490cc – Minimum; 650cc - Maximum
4.	Starting:	Electric Start - minimum
5.	Carburetion:	Fuel Injection
6.	Transmission	Automatic Transmission including High, Low, Park, Neutral, Reverse gears with selectable 2WD and 4WD and Standard Engine Braking - Minimum
C.	Dimensions/Capacities	
1.	Length:	78” minimum – 85” maximum
2.	Width:	43” minimum
3.	Height:	42” minimum
4.	Wheelbase:	47” minimum – 53” maximum
5.	Ground Clearance:	8.5” minimum
6.	Fuel Tank Capacity:	14 L minimum
7.	Front Rack Capacity:	75 lb. (not a box) - minimum
8.	Rear Rack Capacity:	150 lb. (not convertible seat) - minimum
9.	Towing Capacity:	1000 lb. w/ one (1) 1 7/8” ball hitch - minimum
10.	Winch Capacity:	2000 lb. w/roller fairlead - minimum
D.	Tires	
1.	Tire Rim Diameter:	12” minimum; 14” maximum
E.	Suspension	
1.	Front & Rear	Standard w/ 7” travel - minimum
F.	Brakes	
1.	Front and Rear:	Disc or Drum Hydraulic
Item no.:	Category:	Description:
G.	Instrumentation	
1.	Speedometer/Odometer:	Manufacturer Standard
2.	Trip/Hour meter:	Manufacturer Standard
3.	Fuel Gage:	Manufacturer Standard
4.	Temp./Oil Light:	Manufacturer Standard
5.	Battery Voltmeter:	Manufacturer Standard
6.	Transmission/Gear Indicator:	Manufacturer Standard



Royal Canadian Mounted Police
Gendarmerie royale du Canada

Government
of Canada

Gouvernement
du Canada

Solicitation No./No de l=invitation: M5000-14-0617

7.	12V Outlet	Manufacturer Standard
H.	Occupational Health & Safety	
1.	Underbody Protection:	Must cover front, middle, sides, rear & A-Arm - minimum
2.	Seating:	Two (2) person capacity - minimum
a.		Passenger Back Rest
b.		Passenger Hand Grips
3.	Lighting:	Two (2) Headlights (Hi/Low) and one (1) Taillight - minimum
4.	Bumper:	Front and Rear
5.	Mirrors:	Left and Right – Manufacturer Standard
I.	Additional Features	
1.	Tool Kits:	Manufacturer Standard – One (1) for each unit
2.	Cover:	Factory Cover – All Weather; Trailer able with tie down capability; covers entire machine
3.	PDI:	Pre-Delivery Inspection - Standard
4.	Manuals:	Operators Manual – disc or hard copy - one (1) copy for each unit (English and French); French may be on-line
a.		Service & Parts Manual – disc, hard copy, or on-line – one (1) copy for each unit (English and French)
5.	Shipping/Crating:	Must be shipped assembled
6.	Warranty:	One (1) year minimum all-inclusive after-sales warranty. A combination of manufacturer and extended warranty covering the Manufacturer warranty is acceptable. Warranty service to be provided at service center. If no service center is available, Recall, Parts and/or After Sales Service must be shipped/provided within 48 hours.
7.	Delivery:	FOB Destination: Contractor to arrange offloading at the delivery location with no additional equipment or manpower to be provided by the client, between 9:00 AM and 3:00 PM MDT Monday through Friday.
8.	Color:	Industry Standard Commercial Paint
9.	Keys:	Two (2) sets per unit - minimum



Royal Canadian Mounted Police
Gendarmerie royale du Canada

Government
of Canada

Gouvernement
du Canada

Solicitation No./No de l=invitation: M5000-14-0617

INSERT:

Item no.:	Category:	Description:
A.	Year	
1.		New 2013 (or the manufacturer's latest manufactured model)
B.	Engine	
1.	Engine Type:	4-Stroke
2.	Cooling:	Liquid cooled
3.	Displacement:	490cc – Minimum; 700cc - Maximum
4.	Starting:	Electric Start - minimum
5.	Carburetion:	Fuel Injection
6.	Transmission	Automatic Transmission including High, Low, Park, Neutral, Reverse gears with selectable 2WD and 4WD and Standard Engine Braking - Minimum
C.	Dimensions/Capacities	
1.	Length:	78" minimum – 85" maximum
2.	Width:	42" minimum
3.	Height:	42" minimum
4.	Wheelbase:	47" minimum – 53" maximum
5.	Ground Clearance:	8.5" minimum
6.	Fuel Tank Capacity:	14 L minimum
7.	Front Rack Capacity:	75 lb. (not a box) - minimum
8.	Rear Rack Capacity:	150 lb. (not convertible seat) - minimum
9.	Towing Capacity:	1000 lb. w/ one (1) 1 7/8" ball hitch - minimum
10.	Winch Capacity:	2000 lb. w/roller fairlead - minimum
D.	Tires	
1.	Tire Rim Diameter:	12" minimum; 14" maximum
E.	Suspension	
1.	Front & Rear	Standard w/ 7" travel - minimum
F.	Brakes	
1.	Front and Rear:	Disc or Drum Hydraulic
Item no.:	Category:	Description:
G.	Instrumentation	
1.	Speedometer/Odometer:	Manufacturer Standard
2.	Trip/Hour meter:	Manufacturer Standard
3.	Fuel Gage:	Manufacturer Standard
4.	Temp./Oil Light:	Manufacturer Standard
5.	Battery Voltmeter:	Manufacturer Standard
6.	Transmission/Gear Indicator:	Manufacturer Standard
7.	12V Outlet	Manufacturer Standard
H.	Occupational Health & Safety	



Royal Canadian Mounted Police
Gendarmerie royale du Canada

Government
of Canada

Gouvernement
du Canada

Solicitation No./No de l=invitation: M5000-14-0617

1.	Underbody Protection:	Must cover front, middle, sides, rear & A-Arm – minimum
2.	Seating:	Two (2) person capacity - minimum
a.		Passenger Back Rest
b.		Passenger Hand Grips
3.	Lighting:	Two (2) Headlights (Hi/Low) and one (1) Taillight - minimum
4.	Bumper:	Front and Rear
5.	Mirrors:	Left and Right – Manufacturer Standard
I.	Additional Features	
1.	Tool Kits:	Manufacturer Standard – One (1) for each unit
2.	Cover:	Factory Cover – All Weather; Trailer able with tie down capability; covers entire machine
3.	PDI:	Pre-Delivery Inspection - Standard
4.	Manuals:	Operators Manual – disc or hard copy - one (1) copy for each unit (English and French); French may be on-line
a.		Service & Parts Manual – disc, hard copy, or on-line – one (1) copy for each unit (English and French)
5.	Shipping/Crating:	Must be shipped assembled
6.	Warranty:	One (1) year minimum all-inclusive after-sales warranty. A combination of manufacturer and extended warranty covering the Manufacturer warranty is acceptable. Warranty service to be provided at service center. If no service center is available, Recall, Parts and/or After Sales Service must be shipped/provided within 48 hours.
7.	Delivery:	FOB Destination: Contractor to arrange offloading at the delivery location with no additional equipment or manpower to be provided by the client, between 9:00 AM and 3:00 PM MDT Monday through Friday.
8.	Color:	Industry Standard Commercial Paint
9.	Keys:	Two (2) sets per unit - minimum



Royal Canadian Mounted Police
Gendarmerie royale du Canada

Government
of Canada

Gouvernement
du Canada

Solicitation No./No de l=invitation: M5000-14-0617

2. Under ANNEX “B” MANDATORY TECHNICAL CRITERIA

DELETE:

Item No.:	Category	Description	Meets or Exceeds	Not Met	Page Number Reference
I.	MANDATORY TECHNICAL CRITERIA				
A.	The All-Terrain Vehicles must :				
1.	Be from a manufacturer/reseller who has demonstrated acceptability by manufacturing and/or selling this type and size class of vehicle for at least 1 year.				
2.	Conform to all applicable laws, regulations and industrial standards governing manufactures, safety, noise levels and pollution in effect in Canada at the time of manufacture.				
B.	If the bidder is a reseller and not the manufacturer of the unit offered, the bidder must submit; with their bid, proof from the manufacturer of being an authorized reseller for the unit offered.				
II.	PERFORMANCE SPECIFICATIONS				
A.	Year				
1.		New 2013 (or the manufacturer's latest manufactured model)			
B.	Engine				
1.	Engine Type:	4-Stroke			
2.	Cooling:	Liquid cooled			
3.	Displacement:	490cc – Minimum; 650cc - Maximum			
4.	Starting:	Electric Start - minimum			
5.	Carburetion:	Fuel Injection			
6.	Transmission	Automatic Transmission including High, Low, Park, Neutral, Reverse gears with selectable 2WD and 4WD and Standard Engine Braking - Minimum			
Item No.:	Category	Description	Meets or Exceeds	Not Met	Page Number Reference
C.	Dimensions/Capacities:				
1.	Length:	78” minimum – 85” maximum			
2.	Width:	43” minimum			
3.	Height:	42” minimum			
4.	Wheelbase:	47” minimum – 53” maximum			
5.	Ground Clearance:	8.5” minimum			
6.	Fuel Tank Capacity:	14 L minimum			
7.	Front Rack Capacity:	75 lb. (not a box) - minimum			
8.	Rear Rack Capacity:	150 lb. (not convertible seat) - minimum			
9.	Towing Capacity:	1000 lb. w/ one (1) 1 7/8” ball hitch - minimum			
10.	Winch Capacity:	2000 lb. w/roller fairlead - minimum			



Royal Canadian Mounted Police
Gendarmerie royale du Canada

Government
of Canada

Gouvernement
du Canada

Solicitation No./No de l=invitation: M5000-14-0617

D.	Tires				
1.	Tire Rim Diameter:	12" minimum; 14" maximum			
E.	Suspension:				
1.	Front & Rear	Standard w/ 7" travel - minimum			
F.	Brakes:				
1.	Front and Rear:	Disc or Drum Hydraulic			
G.	Instrumentation:				
1.	Speedometer/Odometer:	Manufacturer Standard			
2.	Trip/Hour meter:	Manufacturer Standard			
3.	Fuel Gage:	Manufacturer Standard			
4.	Temp./Oil Light:	Manufacturer Standard			
5.	Battery Voltmeter:	Manufacturer Standard			
6.	Transmission/Gear Indicator:	Manufacturer Standard			
7.	12V Outlet	Manufacturer Standard			
H.	Occupational Health & Safety:				
1.	Underbody Protection:	Must cover front, middle, sides, rear & A-Arm - minimum			
2.	Seating:	Two (2) person capacity - minimum			
a.		Passenger Back Rest			
b.		Passenger Hand Grips			
3.	Lighting:	Two (2) Headlights (Hi/Low) and one (1) Taillight - minimum			



Royal Canadian Mounted Police
Gendarmerie royale du Canada

Government
of Canada

Gouvernement
du Canada

Solicitation No./No de l=invitation: M5000-14-0617

INSERT:

Item No.:	Category	Description	Meets or Exceeds	Not Met	Page Number Reference
I.	MANDATORY TECHNICAL CRITERIA				
A.	The All-Terrain Vehicles must :				
1.	Be from a manufacturer/reseller who has demonstrated acceptability by manufacturing and/or selling this type and size class of vehicle for at least 1 year.				
2.	Conform to all applicable laws, regulations and industrial standards governing manufactures, safety, noise levels and pollution in effect in Canada at the time of manufacture.				
B.	If the bidder is a reseller and not the manufacturer of the unit offered, the bidder must submit; with their bid, proof from the manufacturer of being an authorized reseller for the unit offered.				
II.	PERFORMANCE SPECIFICATIONS				
A.	Year				
1.		New 2013 (or the manufacturer's latest manufactured model)			
B.	Engine				
1.	Engine Type:	4-Stroke			
2.	Cooling:	Liquid cooled			
3.	Displacement:	490cc – Minimum; 700cc - Maximum			
4.	Starting:	Electric Start - minimum			
5.	Carburetion:	Fuel Injection			
6.	Transmission	Automatic Transmission including High, Low, Park, Neutral, Reverse gears with selectable 2WD and 4WD and Standard Engine Braking - Minimum			
Item No.:	Category	Description	Meets or Exceeds	Not Met	Page Number Reference
C.	Dimensions/Capacities:				
1.	Length:	78” minimum – 85” maximum			
2.	Width:	42” minimum			
3.	Height:	42” minimum			
4.	Wheelbase:	47” minimum – 53” maximum			
5.	Ground Clearance:	8.5” minimum			
6.	Fuel Tank Capacity:	14 L minimum			
7.	Front Rack Capacity:	75 lb. (not a box) - minimum			
8.	Rear Rack Capacity:	150 lb. (not convertible seat) - minimum			
9.	Towing Capacity:	1000 lb. w/ one (1) 1 7/8” ball hitch - minimum			
10.	Winch Capacity:	2000 lb. w/roller fairlead - minimum			



Royal Canadian Mounted Police
Gendarmerie royale du Canada

Government
of Canada

Gouvernement
du Canada

Solicitation No./No de l=invitation: M5000-14-0617

D.	Tires				
1.	Tire Rim Diameter:	12" minimum; 14" maximum			
E.	Suspension:				
1.	Front & Rear	Standard w/ 7" travel - minimum			
F.	Brakes:				
1.	Front and Rear:	Disc or Drum Hydraulic			
G.	Instrumentation:				
1.	Speedometer/Odometer:	Manufacturer Standard			
2.	Trip/Hour meter:	Manufacturer Standard			
3.	Fuel Gage:	Manufacturer Standard			
4.	Temp./Oil Light:	Manufacturer Standard			
5.	Battery Voltmeter:	Manufacturer Standard			
6.	Transmission/Gear Indicator:	Manufacturer Standard			
7.	12V Outlet	Manufacturer Standard			
H.	Occupational Health & Safety:				
1.	Underbody Protection:	Must cover front, middle, sides, rear & A-Arm - minimum			
2.	Seating:	Two (2) person capacity - minimum			
a.		Passenger Back Rest			
b.		Passenger Hand Grips			
3.	Lighting:	Two (2) Headlights (Hi/Low) and one (1) Taillight - minimum			