



**Royal Canadian Mounted Police**  
**Gendarmerie royale du Canada**

Government  
of Canada

Gouvernement  
du Canada

Solicitation No./No de l=invitation: M5000-14-0617

**RETURN BIDS TO:**  
**RETOURNER LES SOUMISSIONS A:**  
 Bid Receiving/Réception des soumissions

Royal Canadian Mounted Police (RCMP)  
 NWR Procurement & Contracting Services  
 Place 123  
 #203, 12315 – Stony Plain Road  
 Edmonton, AB T5N 3Y8

**SOLICITATION AMENDMENT**  
**MODIFICATION DE L'INVITATION**

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

**Comments – Commentaries**

**Vendor/Firm Name and Address**  
**Raison sociale et adresse du fournisseur/de l'entrepreneur**

**Telephone N no de téléphone:**

<b>Title-Sujet</b> 22 All-Terrain Vehicles for RCMP Manitoba and Alberta	
<b>Solicitation No. - No. de l=invitatio</b> M5000-14-0617	<b>Amendment No. - N° modif.</b> 004a
<b>Client Reference No. - No. De Référénc du Client</b> 14-111 and 14-122	<b>Date</b> August 16, 2013
<b>Solicitation Closes -L=invitation prend fin at - à 02:00 PM Mountain Daylight Time Zone on - le</b> Tuesday September 3, 2013	
<b>F.O.B. - F.A.B.</b> Dsetination	
<b>Address Enquiries to: - Adresser toutes questions à:</b> Joanne Maybroda	
<b>Telephone No. - No de téléphone</b> (780-341-3037	<b>Fax No. - N° de FAX:</b> 780-454-4523
<b>Destination of Goods, Services, and Construction:</b> <b>Destinations des biens, services et construction:</b>  <b>SEE HEREIN</b>	
<b>This document does not contain a SECURITY requirement.</b>	
<b>Name and title of person authorized to sign on behalf of Vendor/Firm</b> <b>Nom et titre de la personne autorisée à signer au nom du fournisseur/de l=entrepreneur</b>	
_____ Name	_____ Title
_____ Signature	_____ Date



**Royal Canadian Mounted Police  
Gendarmerie royale du Canada**

Government  
of Canada

Gouvernement  
du Canada

Solicitation No./No de l=invitation: M5000-14-0617

**Solicitation Amendment No. 004a is raised to** answer questions from a bidder and to change the specifications:

**August 16, 2013**

**A. Bidders Question**

**Question:**

Re.: Annex A, E.1 Suspension Front and Rear: Standard w/ 7” travel – minimum

"For the front wheels, our vehicle has a travel of 6.69 (this number is taken from the manufacturer, measured from the centre of the wheel). Can we submit a proposal with this slightly smaller travel?"

**Answer:**

We will not reduce our minimums.

**B. Change in Specification**

**Delete:**

Item no.:	Category:	Description:
<b>A.</b>	<b>Year</b>	
1.		New 2013 (or the manufacturer's latest manufactured model)
<b>B.</b>	<b>Engine</b>	
1.	Engine Type:	4-Stroke
2.	Cooling:	Liquid cooled
3.	Displacement:	490cc – Minimum; <b>700cc - Maximum</b>
4.	Starting:	Electric Start - minimum
5.	Carburetion:	Fuel Injection
6.	Transmission	Automatic Transmission including High, Low, Park, Neutral, Reverse gears with selectable 2WD and 4WD and Standard Engine Braking - Minimum
<b>C.</b>	<b>Dimensions/Capacities</b>	
1.	Length:	<b>78” minimum – 85” maximum</b>
2.	Width:	<b>42” minimum</b>
3.	Height:	42” minimum
4.	Wheelbase:	<b>47” minimum – 53” Maximum</b>
5.	Ground Clearance:	8.5” minimum
6.	Fuel Tank Capacity:	14 L minimum
7.	Front Rack Capacity:	75 lb. (not a box) - minimum
8.	Rear Rack Capacity:	150 lb. (not convertible seat) - minimum
9.	Towing Capacity:	1000 lb. w/ one (1) 1 7/8” ball hitch - minimum
10.	Winch Capacity:	2000 lb. w/roller fairlead - minimum
<b>D.</b>	<b>Tires</b>	
1.	Tire Rim Diameter:	12” minimum; 14” maximum



**Royal Canadian Mounted Police**  
**Gendarmerie royale du Canada**

Government  
of Canada

Gouvernement  
du Canada

Solicitation No./No de l=invitation: M5000-14-0617

<b>E.</b>	<b>Suspension</b>	
1.	Front & Rear	Standard w/ 7" travel - minimum
<b>F.</b>	<b>Brakes</b>	
1.	Front and Rear:	Disc or Drum Hydraulic
<b>G.</b>	<b>Instrumentation</b>	
1.	Speedometer/Odometer:	Manufacturer Standard
2.	Trip/Hour meter:	Manufacturer Standard
3.	Fuel Gage:	Manufacturer Standard
4.	Temp./Oil Light:	Manufacturer Standard
5.	Battery Voltmeter:	Manufacturer Standard
6.	Transmission/Gear Indicator:	Manufacturer Standard
7.	12V Outlet	Manufacturer Standard
<b>H.</b>	<b>Occupational Health &amp; Safety</b>	
1.	Underbody Protection:	Must cover front, middle, sides, rear & A-Arm - minimum
2.	Seating:	Two (2) person capacity - minimum
a.		Passenger Back Rest
b.		Passenger Hand Grips
3.	Lighting:	Two (2) Headlights (Hi/Low) and one (1) Taillight - minimum
4.	Bumper:	Front and Rear
5.	Mirrors:	Left and Right – Manufacturer Standard
<b>I.</b>	<b>Additional Features</b>	
1.	Tool Kits:	Manufacturer Standard – One (1) for each unit
2.	Cover:	Factory Cover – All Weather; Trailer able with tie down capability; covers entire machine
3.	PDI:	Pre-Delivery Inspection - Standard
4.	Manuals:	Operators Manual – disc or hard copy - one (1) copy for each unit (English and French); French may be on-line
a.		Service & Parts Manual – disc, hard copy, or on-line – one (1) copy for each unit (English and French)
5.	Shipping/Crating:	Must be shipped assembled
6.	Warranty:	One (1) year minimum all-inclusive after-sales warranty. A combination of manufacturer and extended warranty covering the Manufacturer warranty is acceptable. Warranty service to be provided at service center. If no service center is available, Recall, Parts and/or After Sales Service must be shipped/provided within 48 hours.
7.	Delivery:	FOB Destination: Contractor to arrange offloading at the delivery location with no additional equipment or manpower to be provided by the client, between 9:00 AM and 3:00 PM MDT Monday through Friday.
8.	Color:	Industry Standard Commercial Paint
9.	Keys:	Two (2) sets per unit - minimum



**Royal Canadian Mounted Police**  
**Gendarmerie royale du Canada**

Government  
of Canada

Gouvernement  
du Canada

Solicitation No./No de l=invitation: M5000-14-0617

**Insert:**

<b>Item no.:</b>	<b>Category:</b>	<b>Description:</b>
<b>A.</b>	<b>Year</b>	
1.		New 2013 (or the manufacturer's latest manufactured model)
<b>B.</b>	<b>Engine</b>	
1.	Engine Type:	4-Stroke
2.	Cooling:	Liquid cooled
3.	Displacement:	490cc – Minimum; 700cc - Maximum
4.	Starting:	Electric Start - minimum
5.	Carburetion:	Fuel Injection
6.	Transmission	Automatic Transmission including High, Low, Park, Neutral, Reverse gears with selectable 2WD and 4WD and Standard Engine Braking - Minimum
<b>C.</b>	<b>Dimensions/Capacities</b>	
1.	Length:	78" minimum
2.	Width:	42" minimum
3.	Height:	42" minimum
4.	Wheelbase:	47" minimum
5.	Ground Clearance:	8.5" minimum
6.	Fuel Tank Capacity:	14 L minimum
7.	Front Rack Capacity:	75 lb. (not a box) - minimum
8.	Rear Rack Capacity:	150 lb. (not convertible seat) - minimum
9.	Towing Capacity:	1000 lb. w/ one (1) 1 7/8" ball hitch - minimum
10.	Winch Capacity:	2000 lb. w/roller fairlead - minimum
<b>D.</b>	<b>Tires</b>	
1.	Tire Rim Diameter:	12" minimum; 14" maximum
<b>E.</b>	<b>Suspension</b>	
1.	Front & Rear	Standard w/ 7" travel - minimum
<b>F.</b>	<b>Brakes</b>	
1.	Front and Rear:	Disc or Drum Hydraulic
<b>G.</b>	<b>Instrumentation</b>	
1.	Speedometer/Odometer:	Manufacturer Standard
2.	Trip/Hour meter:	Manufacturer Standard
3.	Fuel Gage:	Manufacturer Standard
4.	Temp./Oil Light:	Manufacturer Standard
5.	Battery Voltmeter:	Manufacturer Standard
6.	Transmission/Gear Indicator:	Manufacturer Standard
7.	12V Outlet	Manufacturer Standard
<b>H.</b>	<b>Occupational Health &amp; Safety</b>	
1.	Underbody Protection:	Must cover front, middle, sides, rear & A-Arm - minimum
2.	Seating:	Two (2) person capacity - minimum
a.		Passenger Back Rest
b.		Passenger Hand Grips



**Royal Canadian Mounted Police**  
**Gendarmerie royale du Canada**

Government  
of Canada

Gouvernement  
du Canada

Solicitation No./No de l=invitation: M5000-14-0617

3.	Lighting:	Two (2) Headlights (Hi/Low) and one (1) Taillight - minimum
4.	Bumper:	Front and Rear
5.	Mirrors:	Left and Right – Manufacturer Standard
<b>I.</b>	<b>Additional Features</b>	
1.	Tool Kits:	Manufacturer Standard – One (1) for each unit
2.	Cover:	Factory Cover – All Weather; Trailer able with tie down capability; covers entire machine
3.	PDI:	Pre-Delivery Inspection - Standard
4.	Manuals:	Operators Manual – disc or hard copy - one (1) copy for each unit (English and French); French may be on-line
a.		Service & Parts Manual – disc, hard copy, or on-line – one (1) copy for each unit (English and French)
5.	Shipping/Crating:	Must be shipped assembled
6.	Warranty:	One (1) year minimum all-inclusive after-sales warranty. A combination of manufacturer and extended warranty covering the Manufacturer warranty is acceptable. Warranty service to be provided at service center. If no service center is available, Recall, Parts and/or After Sales Service must be shipped/provided within 48 hours.
7.	Delivery:	FOB Destination: Contractor to arrange offloading at the delivery location with no additional equipment or manpower to be provided by the client, between 9:00 AM and 3:00 PM MDT Monday through Friday.
8.	Color:	Industry Standard Commercial Paint
9.	Keys:	Two (2) sets per unit - minimum

**C. Change in Annex B**

Delete:

Item No.:	Category	Description	Meets or Exceeds	Not Met	Page Number Reference
<b>I.</b>	<b>MANDATORY TECHNICAL CRITERIA</b>				
<b>A.</b>	The All-Terrain Vehicles <b>must</b> :				
1.	Be from a manufacturer/reseller who has demonstrated acceptability by manufacturing and/or selling this type and size class of vehicle for at least 1 year.				
2.	Conform to all applicable laws, regulations and industrial standards governing manufactures, safety, noise levels and pollution in effect in Canada at the time of manufacture.				
<b>B.</b>	If the bidder is a reseller and not the manufacturer of the unit offered, the bidder <b>must</b> submit; with their bid, proof from the manufacturer of being an authorized reseller for the unit offered.				



**Royal Canadian Mounted Police**  
**Gendarmerie royale du Canada**

Government  
of Canada

Gouvernement  
du Canada

Solicitation No./No de l=invitation: M5000-14-0617

<b>II. PERFORMANCE SPECIFICATIONS</b>					
<b>Item No.:</b>	<b>Category</b>	<b>Description</b>	<b>Meets or Exceeds</b>	<b>Not Met</b>	<b>Page Number Reference</b>
<b>A.</b>	<b>Year</b>				
1.		New 2013 (or the manufacturer's latest manufactured model)			
<b>B.</b>	<b>Engine</b>				
1.	Engine Type:	4-Stroke			
2.	Cooling:	Liquid cooled			
3.	Displacement:	490cc – Minimum; 700cc - Maximum			
4.	Starting:	Electric Start - minimum			
5.	Carburetion:	Fuel Injection			
6.	Transmission	Automatic Transmission including High, Low, Park, Neutral, Reverse gears with selectable 2WD and 4WD and Standard Engine Braking - Minimum			
<b>C.</b>	<b>Dimensions/Capacities:</b>				
1.	Length:	78" minimum – 85" Maximum			
2.	Width:	42" minimum			
3.	Height:	42" minimum			
4.	Wheelbase:	47" minimum – 53" Maximum			
5.	Ground Clearance:	8.5" minimum			
6.	Fuel Tank Capacity:	14 L minimum			
7.	Front Rack Capacity:	75 lb. (not a box) - minimum			
8.	Rear Rack Capacity:	150 lb. (not convertible seat) - minimum			
9.	Towing Capacity:	1000 lb. w/ one (1) 1 7/8" ball hitch - minimum			
10.	Winch Capacity:	2000 lb. w/roller fairlead - minimum			
<b>D.</b>	<b>Tires</b>				
1.	Tire Rim Diameter:	12" minimum; 14" maximum			
<b>E.</b>	<b>Suspension:</b>				
1.	Front & Rear	Standard w/ 7" travel - minimum			
<b>F.</b>	<b>Brakes:</b>				
1.	Front and Rear:	Disc or Drum Hydraulic			
<b>G.</b>	<b>Instrumentation:</b>				
1.	Speedometer/Odometer:	Manufacturer Standard			
2.	Trip/Hour meter:	Manufacturer Standard			
3.	Fuel Gage:	Manufacturer Standard			
4.	Temp./Oil Light:	Manufacturer Standard			
5.	Battery Voltmeter:	Manufacturer Standard			
6.	Transmission/Gear Indicator:	Manufacturer Standard			
7.	12V Outlet	Manufacturer Standard			
<b>H.</b>	<b>Occupational Health &amp; Safety:</b>				



**Royal Canadian Mounted Police**  
**Gendarmerie royale du Canada**

Government  
of Canada

Gouvernement  
du Canada

Solicitation No./No de l=invitation: M5000-14-0617

1.	Underbody Protection:	Must cover front, middle, sides, rear & A-Arm - minimum			
2.	Seating:	Two (2) person capacity - minimum			
a.		Passenger Back Rest			
b.		Passenger Hand Grips			
3.	Lighting:	Two (2) Headlights (Hi/Low) and one (1) Taillight - minimum			
I.	Additional Features:				
1.	Tool Kits:	Manufacturer Standard – One (1) for each unit			
2.	Cover:	Factory Cover – All Weather; Trailer able with tie down capability; covers entire machine			
3.	Color:	Industry Standard Commercial Paint			

**Insert:**

Item No.:	Category	Description	Meets or Exceeds	Not Met	Page Number Reference
<b>I.</b>	<b>MANDATORY TECHNICAL CRITERIA</b>				
<b>A.</b>	<b>The All-Terrain Vehicles <b>must</b>:</b>				
1.		Be from a manufacturer/reseller who has demonstrated acceptability by manufacturing and/or selling this type and size class of vehicle for at least 1 year.			
2.		Conform to all applicable laws, regulations and industrial standards governing manufactures, safety, noise levels and pollution in effect in Canada at the time of manufacture.			
<b>B.</b>	If the bidder is a reseller and not the manufacturer of the unit offered, the bidder <b>must</b> submit; with their bid, proof from the manufacturer of being an authorized reseller for the unit offered.				
<b>II.</b>	<b>PERFORMANCE SPECIFICATIONS</b>				
Item No.:	Category	Description	Meets or Exceeds	Not Met	Page Number Reference
<b>A.</b>	<b>Year</b>				
1.		New 2013 (or the manufacturer's latest manufactured model)			
<b>B.</b>	<b>Engine</b>				
1.	Engine Type:	4-Stroke			
2.	Cooling:	Liquid cooled			
3.	Displacement:	490cc – Minimum; <b>700cc - Maximum</b>			
4.	Starting:	Electric Start - minimum			
5.	Carburetion:	Fuel Injection			



**Royal Canadian Mounted Police**  
**Gendarmerie royale du Canada**

Government  
of Canada

Gouvernement  
du Canada

Solicitation No./No de l=invitation: M5000-14-0617

<b>6.</b>	Transmission	Automatic Transmission including High, Low, Park, Neutral, Reverse gears with selectable 2WD and 4WD and Standard Engine Braking - Minimum			
<b>C.</b>	Dimensions/Capacities:				
<b>1.</b>	Length:	78" minimum			
<b>2.</b>	Width:	42" minimum			
<b>3.</b>	Height:	42" minimum			
<b>4.</b>	Wheelbase:	47" minimum			
<b>5.</b>	Ground Clearance:	8.5" minimum			
<b>6.</b>	Fuel Tank Capacity:	14 L minimum			
<b>7.</b>	Front Rack Capacity:	75 lb. (not a box) - minimum			
<b>8.</b>	Rear Rack Capacity:	150 lb. (not convertible seat) - minimum			
<b>9.</b>	Towing Capacity:	1000 lb. w/ one (1) 1 7/8" ball hitch - minimum			
<b>10.</b>	Winch Capacity:	2000 lb. w/roller fairlead - minimum			
<b>D.</b>	Tires				
<b>1.</b>	Tire Rim Diameter:	12" minimum; 14" maximum			
<b>E.</b>	Suspension:				
<b>1.</b>	Front & Rear	Standard w/ 7" travel - minimum			
<b>F.</b>	Brakes:				
<b>1.</b>	Front and Rear:	Disc or Drum Hydraulic			
<b>G.</b>	Instrumentation:				
<b>1.</b>	Speedometer/Odometer:	Manufacturer Standard			
<b>2.</b>	Trip/Hour meter:	Manufacturer Standard			
<b>3.</b>	Fuel Gage:	Manufacturer Standard			
<b>4.</b>	Temp./Oil Light:	Manufacturer Standard			
<b>5.</b>	Battery Voltmeter:	Manufacturer Standard			
<b>6.</b>	Transmission/Gear Indicator:	Manufacturer Standard			
<b>7.</b>	12V Outlet	Manufacturer Standard			
<b>H.</b>	Occupational Health & Safety:				
<b>1.</b>	Underbody Protection:	Must cover front, middle, sides, rear & A-Arm - minimum			
<b>2.</b>	Seating:	Two (2) person capacity - minimum			
<b>a.</b>		Passenger Back Rest			
<b>b.</b>		Passenger Hand Grips			
<b>3.</b>	Lighting:	Two (2) Headlights (Hi/Low) and one (1) Taillight - minimum			
<b>I.</b>	Additional Features:				
<b>1.</b>	Tool Kits:	Manufacturer Standard – One (1) for each unit			
<b>2.</b>	Cover:	Factory Cover – All Weather; Trailer able with tie down capability; covers entire machine			
<b>3.</b>	Color:	Industry Standard Commercial Paint			