



Royal Canadian Mounted Police
Gendarmerie royale du Canada

Doc. no: PD-PC-23

Date: 2013-01-08

Purchase Description

Shoe, Pump, Black, Female

This document has 7 pages including the drawings.

This document was created in English.

The document is available in English and French.

English/Anglais
Français/French

The photograph on this page is for reference only.

RCMP VIEWING SAMPLE

A viewing sample, when available, will be supplied to the successful tenderer.

This will be used for the guidance of the manufacturer in all factors not covered by this specification or referred to therein. Variation from the specification may appear in the sample in which case the specification shall govern.

It may be obtained from:

Royal Canadian Mounted Police
ATTN: Quality Control
(440 Coventry Road, Warehouse Building)
1200 Vanier Parkway
Ottawa, Ontario
K1A 0R2

It will be sent “prepaid” and is to be returned “prepaid”.

The viewing sample shall be returned to the RCMP in the same condition as received by the manufacturer. Lost or damaged viewing samples shall be replaced by an identical item or the RCMP shall be reimbursed for the cost of an acceptable replacement.

PURCHASE DESCRIPTION

SHOE, PUMP, BLACK, FEMALE

1. **SCOPE**

This purchase description describes the requirements for "Shoe, Pump, Black, Female" for use by Royal Canadian Mounted Police personnel.

2. **DETAILED DESCRIPTION**

- Full grain leather, black in colour. Finish to be semi-lustrous. Very shiny, 'patent leather' finish is not acceptable. Dull finish or suede material unacceptable.
- Shank of tempered steel or other suitable material guaranteed to provide adequate support.
- Female slip-on pump style.
- Rounded closed toe and plain upper (no adornments such as buckles, bows, decorative seam lines or cutout stencil-type patterns permitted)
- 4.5 to 7.0cm (1 ¾" - 2 ¾") tapered 'mid-height' heel. Wide to narrow tipped heels are considered acceptable.
- Foam interliner and sock liner. Other cushioning materials and designs unique to a particular style including wicking and moisture absorbing materials may be acceptable if suitable comfort and performance is provided. Shoes meeting the overall requirements are to be comfortable for an expected range of uses such as office/administrative duties, formal functions/occasions requiring the user to stand for several hours at a time. Wearers are not expected to perform operational police duties, such as running, jumping, arresting suspects, engage in physical altercations, etc., while wearing these shoes.
- Rubber outsole and heel cap. Leather or non-grip outsoles are not acceptable. Other 'non-slip' sole materials may be acceptable provided the performance is equal to a rubber outsole and heel cap for slip resistance.
- Felt or equivalent material fore-pad.
- Manufacturing standards to be of the highest commercial quality. Shoes will be deemed unacceptable if they are made with poor quality materials and workmanship.
- Sizes: 4 to 12, half sizes included; widths AA, B, and C (also: Narrow, Medium and Wide), North American commercial sizing standard to be used. Not all widths or sizes may be available in styles listed below. Manufacturers are required to advise the RCMP if the sizing of a particular design/last is at the smaller or larger end of a size tolerance –

for example, if users are recommended to use a half-size larger than their usual shoe size due to particular design features of the shoe.

RCMP Material Master Number (MMR#): MMR#5130

Packaging labeling & Shipping Details: Female Black Pumps shall be shipped in accordance with good commercial practice in boxes containing a single pair of shoes (one left, one right), all boxes to be the same size, and labelled with the following information, clearly legible:

- Manufacturer’s ID
- date of manufacture
- Item name/description & size
- RCMP MMR#
- RCMP contract number

Bulk orders shall be shipped with no more than 10 individual shoe pair boxes in a larger bulk container, each large container to contain, where possible, shoes of only one size, and labelled accordingly as per above for individual boxes.

Note: The following styles are known to meet these requirements:

Manufacturer/Brand	Model
Naturalizer	Deino (2 ½” heel) 
	Marianne (2 ½” heel) 
	Lennox (2 ¾” heel, w/ ½” platform)

	
Ros-Hommerson	Cabernet (2 1/4" heel) 
	Viva (2 1/2" heel) 
	Attack (2 1/8") 
Annie Shoes	Rocha (2 3/4 heel) 
	Cindee (2 3/4" heel) 
Trotters Shoes	Paulina (1 3/4" heel) 

	<p>Jana (1 3/4" heel)</p> 
<p>Easy Street</p>	<p>Major (2" heel)</p> 
<p>Nine West</p>	<p>Runit (2" heel)</p> 
<p>Rockport</p>	<p>Pilot Path (2 1/2" heel)</p> 