

FLOOR PLAN LEVEL 1
SCALE : 1:100
0m 1m 2m 3m 4m 5m 6m 7m 8m 9m 10m


LIGHTING LEGEND

	CEILING MOUNTED POT LIGHT OR WALL MOUNTED LIGHT FIXTURE. SEE FIXTURE SCHEDULE
	CEILING MOUNTED FLUORESCENT LIGHT FIXTURE. SEE FIXTURE SCHEDULE
	COVE LIGHTING. SEE FIXTURE SCHEDULE
	LIGHT FIXTURES AS ABOVE, TO BE ON NIGHT CIRCUIT
	CEILING OR WALL MOUNTED EXIT SIGN
	EMERGENCY LIGHTING BATTERY UNIT WITH TWO HEADS
	WALL OR CEILING MOUNTED EMERGENCY LIGHTING REMOTE FIXTURE. NUMBER OF HEADS AS INDICATED ON DRAWINGS
	SINGLE POLE TOGGLE SWITCH WITH ONE, TWO, OR THREE GANG COVER PLATE.
	"M" DENOTES MOTION SENSOR WALL SWITCH, NOT ON SYSTEM. COOPER #04W-N-W
	"N" DENOTES 2-BUTTON RAISE/LOWER WALL SWITCH, ON SYSTEM. LUTRON #P4-2BR-CW/WH
	"C" DENOTES LIGHTING SCENE CONTROLLERS, ZONE AS INDICATED WITHIN ROOM. PICD WIRED, C/W RAISE/LOWER CAPABILITY, ON SYSTEM. NUMBER OF BUTTONS TO MATCH NUMBER OF ZONES SHOWN ON DRAWINGS.
	SWITCHES AS ABOVE, SUBSCRIPT DENOTES 2 POLES, 2-WAY, 3-WAY, OR 4-WAY
	CEILING MOUNTED MOTION ACTIVATED LIGHT SWITCH. PROVIDE ALL POWER PACKS AS NECESSARY, RATING AS REQUIRED
	LUTRON IEC-R
	"O" DENOTES OCCUPANCY SENSOR, ON SYSTEM. LUTRON #LOS-COT-2000
	"O2" DENOTES OCCUPANCY SENSOR, ON SYSTEM. LUTRON #LOS-COT-500. ARROW DENOTES CENTER FIELD OF VIEW
	"O3" DENOTES OCCUPANCY SENSOR, NOT ON SYSTEM. COOPER #0AC-07-2000-MV
	A-1 CIRCUIT BREAKER IN PANEL. "L" DENOTES FIXTURE TO BE CONTROLLED BY LUTRON RELAY PANEL

FIXTURE SCHEDULE

FIXTURE	MANUFACTURER	MANUFACTURER	MANUFACTURER	DESCRIPTION	LAMP
A	COBELITE PWP-215-10-120V-AC48	LEDALITE 7705-H02-L-1-1	METALUMEN C75-BAU-AAW6A	4" ARCHITECTURAL SEMI-INDIRECT SUSPENDED FLUORESCENT LUMINAIRE. SUSPEND AT 450mm BELOW CEILING USING AIRCRAFT/CELESTIAL 120V RAPID START ELECTRONIC DIMMING BALLAST, LESS THAN 10% THD. EHD155AMU210 BALLAST	2xF54 T5HO
B	COBELITE PWP-115-10-120V-AC48	LEDALITE 7705-H01-L-1-1	METALUMEN C75-AAU-AAW6A	4" ARCHITECTURAL SEMI-INDIRECT SUSPENDED FLUORESCENT LUMINAIRE. SUSPEND AT 450mm BELOW CEILING USING AIRCRAFT/CELESTIAL 120V RAPID START ELECTRONIC DIMMING BALLAST, LESS THAN 10% THD. EHD155AMU110 BALLAST	1x154 T5HO
C	METALIX GC8-232A19-120V-ER81-U	CFI SPS1GFSKAQ32-H1-120	LITHONIA SP8C232-A19 MANUFACTURER'S SPECIFICATIONS	1'x4" RECESSED FLUORESCENT TROFFER SUITABLE FOR T-BAR OR DRYWALL MOUNTING WHERE INDICATED ON DRAWINGS. 120V RAPID START ELECTRONIC BALLAST, LESS THAN 10% THD. C/W K19 PRISMATIC LENS.	2x132 T8
D	LUMENCOVE LCSR0120V-XX-40K-CL-XX-WH-DM	PHILLIPS COLOR KINETICS #W COVE MAX POWERCORE 523-000050-13	ECOSENSE 05LC-XX-40-120-120	LED COVE LIGHTING	46.1W/m LED
E	PORTFOLIO LD15D-ERM840-RM	LIGHTOLIER CBL1520BL40K-CCL-W/ CBL15N1-120-0/100 DIM	EV0-41/14 6AR-MVOLT	CEILING RECESSED 150mm LED POT LIGHT C/W ELECTRONIC DIMMING BALLAST. 120V OPERATION WITH 1500 LUMENS AT 4000K	28W LED
F	METALIX SSF-232	CFI SB248-H1-120	LITHONIA C-2-32-MVOLT-CEB10P5	COMMERCIAL FLUORESCENT STRIP SURFACE MOUNTED LUMINAIRE. UL/CUL LISTED. SUITABLE FOR DAMP LOCATIONS. 120V RAPID START ELECTRONIC BALLAST, LESS THAN 10% THD.	2x132 T8
G	PORTFOLIO LD413D-ERM4-840-4LM11U	LIGHTOLIER C4110W-40K-CCL-W/ C4110N1-12-0/100DIM	GOTHAM EVO-WW-41/14 4AR-MVOLT	CEILING RECESSED 100mm LED WALL WASH POT LIGHT C/W ELECTRONIC DIMMING BALLAST. LUTRON HI-LUME. 120V OPERATION WITH 1300 LUMENS AT 4000K	24.4W LED
H	PORTFOLIO LD413D-ERM4-840-4LM1U	LIGHTOLIER C4110L-40K-CCL-W/ C4110N1-12-0/100DIM	GOTHAM EVO-41/14 4AR-MVOLT	CEILING RECESSED 100mm LED POT LIGHT C/W ELECTRONIC DIMMING BALLAST. 120V OPERATION WITH 1300 LUMENS AT 4000K	24.4W LED
K	MP LIGHTING LS2-2-W41	CALOULITE C2L04-DL30K47R	LITHONIA LHBLD212C35/LR2LH71C	44.5mm WALL WASH POT LIGHT. 120V OPERATION WITH 400 LUMENS AT 3000K	11W LED
L	METALIX VTZ-232	CFI VT248	LITHONIA DMW-232	HIGH IMPACT 4" VAPOR TIGHT FLUORESCENT. SURFACE MOUNTED C/W RAPID START ELECTRONIC BALLAST	2x132 T8
M	METALIX PB2L-C2C-AB-W30	BRUCK LIGHTING 222-850-MC-MP		12" TALL, 4" WIDE CABLE SUSPENDED PENDANT LUMINAIRE. 120V OPERATION.	6W LED
	AMITLIE EBST-24720M02Q0ATD			EXIT LIGHT TO MATCH TYPE INSTALLED ON 2nd FLOOR RENOVATION PROJECT	LED
	AMITLIE RMB5-24020			WALL OR CEILING MOUNTED EMERGENCY BATTERY UNIT. SINGLE OR DUAL HEAD AS INDICATED, MOUNTING AS REQUIRED	2x20W MR16
				REMOTE FIXTURE FOR USE WITH LUMACELL BATTERY UNIT. SINGLE OR DUAL HEAD AS INDICATED. MOUNTING AS REQUIRED.	20W MR16

00	ISSUED FOR ADDENDUM #2	09-16 2013
revisions		date
project	BUILDING MODERNIZATION PHASE II 10 Weldon Street Shediac, NB	
drawing	FLOOR PLAN LEVEL 1 ELECTRICAL LIGHTING	
designed	KJMR	concep
drawn	MML	designe
approved	MAL	approve
date	SEPTEMBER 2013	
date	SEPTEMBER 2013	
Tender		Submission
PM/SC Project Manager	Administrateur de projets TPSC	project number
	R.039554.001	
drawing no.	E-101	no. du dessin



00	ISSUED FOR ADDENDUM #2	09-16 2013
revisions		date

project BUILDING MODERNIZATION PHASE II
10 Weldon Street
Shediac, NB

drawing FLOOR PLAN LEVEL 3
dessin ELECTRICAL LIGHTING

designed KMR	conçu
date SEPTEMBER 2013	
drawn MML	dessiné
date SEPTEMBER 2013	
approved MAL	approuvé
date SEPTEMBER 2013	

Tender / Soumission
PWGSC Project Manager / Administrateur de projets TPSCC
project number / no. du projet
R.039554.001

drawing no. / no. du dessin
E-105

REFLECTED CEILING PLAN - LEVEL 3
SCALE: 1:100
0m 1m 2m 3m 4m 5m 6m 7m 8m 9m 10m

ALL THIRD FLOOR LIGHTING CONTROLS TO BE RUN BACK TO BRIDGE LOCATED IN ELECTRICAL ROOM 325.



00	ISSUED FOR ADDENDUM #2	09-16-2013
revisions		date

BUILDING MODERNIZATION PHASE II
10 Weldon Street
Shediac, NB

ELECTRICAL LIGHTING CONTROLS

designed	KMR	conçu
date	SEPTEMBER 2013	
drawn	MML	dessiné
date	SEPTEMBER 2013	
approved	MAL	approuvé
date	SEPTEMBER 2013	
Tender		Submission
Project Manager	Administrateur de projets TPSC	
project number	no. du projet	
	R.039554.001	
drawing no.	no. du dessin	
	E-111	

