



**Royal Canadian Mounted Police  
Gendarmerie royale du Canada**

Government of Canada / Gouvernement du Canada

Solicitation No./Sollicitation No.: M5000-14-2552

**RETURN BIDS TO:  
RETOURNER LES SOUMISSIONS A:  
Bid Receiving/Réception des soumissions**

Royal Canadian Mounted Police (RCMP)  
NWR Procurement & Contracting Services  
Place 123  
#203, 12315 – Stony Plain Road  
Edmonton, AB T5N 3Y8

**SOLICITATION AMENDMENT  
MODIFICATION DE L'INVITATION**

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

**Comments – Commentaries**

**Vendor/Firm Name and Address  
Raison sociale et adresse du fournisseur/de l'entrepreneur**

**Telephone N no de téléphone:**

<b>Title-Sujet</b> Snowmobiles for RCMP Regina, SK and Winnipeg, MB	
<b>Solicitation No. - No. de l=invitation</b> M5000-14-2552	<b>Amendment No. - N° modif.</b> 003
<b>Client Reference No. - No. De Référence du Client</b> 14-358 and 14-554	<b>Date</b> October 11, 2013
<b>GETS Reference No. - No. de Référence de SEAG</b> PW-13-00385644	
<b>Solicitation Closes -L=invitation prend fin</b> <b>at - à 16:00 Eastern Daylight Time (EDT)</b> <b>on - le Friday October 25<sup>th</sup>, 2013</b>	
<b>F.O.B. - F.A.B.</b> Destination	
<b>Address Enquiries to: - Adresser toutes questions à:</b> Joanne Maybroda	
<b>Telephone No. - No de téléphone</b> 780-341-3037	<b>Fax No. - N° de FAX:</b> 780-454-4523
<b>Destination of Goods, Services, and Construction:</b> <b>Destinations des biens, services et construction:</b>  <b>SEE HEREIN</b>	
<b>This document does not contain a SECURITY requirement.</b>	
<b>Name and title of person authorized to sign on behalf of Vendor/Firm</b> <b>Nom et titre de la personne autorisée à signer au nom du fournisseur/de l'entrepreneur</b>	
_____ Name	_____ Title
_____ Signature	_____ Date



**Solicitation Amendment N° 003** is raised to address bidder's questions, change the specification, change the delivery date, and change the Closing time and date.

**October 11, 2013**

**1. Change in the Closing Date**

**Delete:**

**Solicitation Closes -L=invitation prend fin**  
**at - à 16:00 Eastern Daylight Time (EDT)**  
**on - le Friday October 18<sup>th</sup>, 2013**

**Insert:**

**Solicitation Closes -L=invitation prend fin**  
**at - à 16:00 Eastern Daylight Time (EDT)**  
**on - le Friday October 25<sup>th</sup>, 2013**

---

**2. Change in the Delivery Date**

**Delete:**

**Delivery Requested by - Livraison Demandée par:**  
Tuesday November 12<sup>th</sup>, 2013

**Insert:**

**Delivery Requested by - Livraison Demandée par:**  
Monday November 18<sup>th</sup>, 2013

---

**3. Change in Specification derived from bidder's questions**

**Bidder's Questions:**

Re: C.8. Hitch - One (1) 1 7/8" Ball Hitch Installed - Minimum

Question: "This sounds like a requirement for an ATV Solicitation. Normally requested on a snowmobile solicitation would be a hitch with either a tongue style receiver or a "J" Hook receiver. Please clarify this requirement."

Re.: F.4. Underbody Protection - Must cover front,middle,sides,rear

Question: "This is the same wording that has been used with requests on ATV Solicitations. What kind of protection is required? Middle, side and rear protection on a snowmobile is not applicable."



**Royal Canadian Mounted Police**  
**Gendarmerie royale du Canada**

Government  
of Canada

Gouvernement  
du Canada

Solicitation No./Sollicitation No.: M5000-14-2552

**Delete: Under ANNEX “A”, Requirement, II. Performance Specifications:**

Item No.	Category	Description
<b>A.</b>	<b>YEAR</b>	
1.		New (or most current model of manufacture production)
<b>B.</b>	<b>ENGINE &amp; DRIVE TRAIN:</b>	
1.	Type:	2 Stroke or 4 Stroke
2.	Displacement:	490 cc – 600 cc
3.	Cooling:	Fan or liquid cooled
4.	Starting:	Electric - 2 Stroke, manual recoil - 4 Stroke
5.	Transmission:	Automatic, including Forward and Reverse Minimum
6.	Suspension:	Manufacturer Standard
<b>C.</b>	<b>DIMENSIONS/CAPACITIES:</b>	
1.	Length:	110” (minimum)
2.	Width:	42” (minimum)
3.	Height:	43” (minimum)
4.	Ski Stance:	35” (minimum)
5.	Track:	15” wide x 135” long x 1” high (minimum)
6.	Fuel Tank:	Manufacturer Standard
7.	Rack:	Rear Manufacturer Standard
8.	Hitch:	One (1) 1 7/8” ball hitch installed– minimum
<b>D.</b>	<b>BRAKES:</b>	
1.	Track:	Disc – Minimum
<b>E.</b>	<b>INSTRUMENTATION:</b>	
1.	Speedometer/Odometer:	Manufacturer Standard
2.	Trip/Hour meter:	Manufacturer Standard
3.	Fuel Gauge:	Manufacturer Standard
4.	Temp/Oil Light:	Manufacturer Standard
<b>F.</b>	<b>OCCUPATIONAL HEALTH &amp; SAFETY:</b>	
1.	Lighting:	One (1) Headlight (Hi/Low) and One (1) Taillight - Minimum
2.	Seating:	
a.		Two person Capacity (minimum)
b.		Passenger Back Rest
c.		Passenger Hand Grips
3.	Windshield:	19” high (minimum) - installed
4.	Underbody Protection:	Must Cover front, middle, sides, rear
5.	Hand & Thumb Warmers:	Manufacturer Standard
6.	Mirrors:	Left and Right – Manufacturer Standard
7.	12V Outlet	Manufacturer Standard



**Royal Canadian Mounted Police**  
**Gendarmerie royale du Canada**

Government  
of Canada

Gouvernement  
du Canada

Solicitation No./Sollicitation No.: M5000-14-2552

<b>G.</b>	<b>ADDITIONAL FEATURES:</b>	
1.	Tool Kits	Manufacturer Standard – one for each Unit
2.	Cover:	Factory Cover – All Weather; Trailerable with tie down capability; covers entire machine
3.	PDI:	Pre-Delivery Inspection – Standard
4.	Manuals:	
a.		Operators Manual – disc or hard copy – one copy for each unit (English)
b.		Service & Parts Manual – disc, hardcopy (copy for each) or on-line (English)
5.	Shipping/Crating:	Must be shipped assembled
6.	Warranty:	Warranty service to be provided at service center. If no service center is available, Recall, Parts and/or After Sales Service must be provided within 48 hours.
7.	Delivery:	Delivery to be made between 9:00 AM and 3:00 PM MDT Monday through Friday
8.	Color::	Industry Standard Commercial Paint
9.	Keys:	Two(2) sets per unit – minimum

**Insert: Under ANNEX “A”, Requirement, II. Performance Specifications:**

<b>Item No.</b>	<b>Category</b>	<b>Description</b>
<b>A.</b>	<b>YEAR</b>	
1.		New (or most current model of manufacture production)
<b>B.</b>	<b>ENGINE &amp; DRIVE TRAIN:</b>	
1.	Type:	2 Stroke or 4 Stroke
2.	Displacement:	490 cc – 600 cc
3.	Cooling:	Fan or liquid cooled
4.	Starting:	Electric - 2 Stroke, manual recoil - 4 Stroke
5.	Transmission:	Automatic, including Forward and Reverse Minimum
6.	Suspension:	Manufacturer Standard
<b>C.</b>	<b>DIMENSIONS/CAPACITIES:</b>	
1.	Length:	110” (minimum)
2.	Width:	42” (minimum)
3.	Height:	43” (minimum)
4.	Ski Stance:	35” (minimum)
5.	Track:	15” wide x 135” long x 1” high (minimum)
6.	Fuel Tank:	Manufacturer Standard
7.	Rack:	Rear Manufacturer Standard
8.	Hitch:	One (1) J/Tow Pindle Hitch & One (1) Tongue Hitch, included and installed. Only one (1) hitch to be installed, supply the other one with machine.
<b>D.</b>	<b>BRAKES:</b>	
1.	Track:	Disc – Minimum



**Royal Canadian Mounted Police  
Gendarmerie royale du Canada**

Government  
of Canada

Gouvernement  
du Canada

Solicitation No./Sollicitation No.: M5000-14-2552

<b>E. INSTRUMENTATION:</b>		
1.	Speedometer/Odometer:	Manufacturer Standard
2.	Trip/Hour meter:	Manufacturer Standard
3.	Fuel Gauge:	Manufacturer Standard
4.	Temp/Oil Light:	Manufacturer Standard
<b>F. OCCUPATIONAL HEALTH &amp; SAFETY:</b>		
1.	Lighting:	One (1) Headlight (Hi/Low) and One (1) Taillight - Minimum
2.	Seating:	
a.		Two person Capacity (minimum)
b.		Passenger Back Rest
c.		Passenger Hand Grips
3.	Windshield:	19" high (minimum) - installed
4.	Underbody Protection:	Must protect all vital engine and drive components
5.	Helmet Defrost Connector	Manufacturer Standard
6.	Hand & Thumb Warmers:	Manufacturer Standard
7.	Mirrors:	Left and Right – Manufacturer Standard
8.	12V Outlet	Manufacturer Standard
<b>G. ADDITIONAL FEATURES:</b>		
1.	Tool Kits	Manufacturer Standard – one for each Unit
2.	Cover:	Factory Cover – All Weather; Trailerable with tie down capability; covers entire machine
3.	PDI:	Pre-Delivery Inspection – Standard
4.	Manuals:	
a.		Operators Manual – disc or hard copy – one copy for each unit (English)
b.		Service & Parts Manual – disc, hardcopy (copy for each) or on-line (English)
5.	Shipping/Crating:	Must be shipped assembled
6.	Warranty:	Warranty service to be provided at service center. If no service center is available, Recall, Parts and/or After Sales Service must be provided within 48 hours.
7.	Delivery:	Delivery to be made between 9:00 AM and 3:00 PM MDT Monday through Friday
8.	Color::	Industry Standard Commercial Paint
9.	Keys:	Two(2) sets per unit – minimum



**Royal Canadian Mounted Police**  
**Gendarmerie royale du Canada**

Government  
of Canada

Gouvernement  
du Canada

Solicitation No./Sollicitation No.: M5000-14-2552

**Delete: Under ANNEX “B”, MANDATORY TECHNICAL CRITERIA, Mandatory Technical Criteria and Performance Specifications**

Item No.:	Category	Description	Meets	Not Met	Page Number Reference
<b>I.</b>	<b>MANDATORY TECHNICAL CRITERIA</b>				
<b>A.</b>	The Snowmobiles must:				
1.		Be from a manufacturer/reseller who has demonstrated acceptability by manufacturing and/or selling this type and size class of vehicle for at least 1 year.			
2.		Conform to all applicable laws, regulations and industrial standards governing manufactures, safety, noise levels and pollution in effect in Canada at the time of manufacture.			
<b>B.</b>	If the bidder is a reseller and not the manufacturer of the unit offered, the bidder must submit; with their bid, proof from the manufacturer of being an authorized reseller for the unit offered.				
<b>II.</b>	<b>PERFORMANCE SPECIFICATIONS</b>				
<b>A.</b>	<b>YEAR:</b>				
1.		New (or most current model of manufacture production)			
<b>B.</b>	<b>ENGINE &amp; DRIVE TRAIN:</b>				
1.	Type:	2 Stroke or 4 Stroke			
2.	Displacement:	490 cc – 600 cc			
3.	Cooling:	Fan or liquid cooled			
4.	Starting:	Electric - 2 Stroke, manual recoil - 4 Stroke			
5.	Transmission:	Automatic, Forward and Reverse minimum			
6.	Suspension:	Manufacturer Standard			
<b>C.</b>	<b>DIMENSIONS/CAPACITIES:</b>				
1.	Length:	110” (minimum)			
2.	Width:	42” (minimum)			
3.	Height:	43” (minimum)			
4.	Ski Stance:	35” (minimum)			
5.	Track:	15” wide x 135” long x 1” high (minimum)			
6.	Fuel Tank:	Manufacturer Standard			
7.	Rack:	Rear Manufacturer Standard			
8.	Hitch:	One (1) 1 7/8” ball hitch installed – minimum			



**Royal Canadian Mounted Police**  
**Gendarmerie royale du Canada**

Government  
of Canada

Gouvernement  
du Canada

Solicitation No./Sollicitation No.: M5000-14-2552

<b>D.</b>	<b>BRAKES:</b>			
1.	Track:	Disc – Minimum		
<b>E.</b>	<b>INSTRUMENTATION:</b>			
1.	Speedometer/Odometer:	Manufacturer Standard		
2.	Trip/Hour meter:	Manufacturer Standard		
3.	Fuel Gauge:	Manufacturer Standard		
4.	Temp/Oil Light:	Manufacturer Standard		
<b>F.</b>	<b>OCCUPATIONAL HEALTH &amp; SAFETY:</b>			
1.	Lighting:	One (1) Headlight (Hi/Low) and One (1) Taillight - Minimum		
2.	Seating:			
a.		Two person Capacity (minimum)		
b.		Passenger Back Rest		
c.		Passenger Hand Grips		
3.	Windshield:	19” high (minimum) - installed		
4.	Underbody Protection:	Must Cover front, middle, sides		
5.	Hand & Thumb Warmers:	Manufacturer Standard		
6.	Mirrors:	Left and Right – Manufacturer Standard		
7.	12V Outlet	Manufacturer Standard		
<b>G.</b>	<b>ADDITIONAL FEATURES:</b>			
1.	Tool Kits	Manufacturer Standard – one for each Unit		
2.	Cover:	Factory Cover – All Weather; Trailerable with tie down capability; covers entire machine		
3.	PDI:	Pre-Delivery Inspection – Standard		
4.	Manuals:			
a.		Operators Manual – disc or hard copy – one copy for each unit (English)		
b.		Service & Parts Manual – disc, hardcopy (copy for each) or on-line (English)		



**Royal Canadian Mounted Police**  
**Gendarmerie royale du Canada**

Government  
of Canada

Gouvernement  
du Canada

Solicitation No./Sollicitation No.: M5000-14-2552

5.	Shipping/Crating:	Must be shipped assembled			
6.	Warranty:	Warranty service to be provided at service center. If no service center is available, Recall, Parts and/or After Sales Service must be provided within 48 hours.			
7.	Delivery:	Delivery to be made between 9:00 AM and 3:00 PM MDT Monday through Friday			
8.	Color::	Industry Standard Commercial Paint			
9.	Keys:	Two(2) sets per unit – minimum			





**Royal Canadian Mounted Police**  
**Gendarmerie royale du Canada**

Government  
of Canada

Gouvernement  
du Canada

Solicitation No./Sollicitation No.: M5000-14-2552

**Insert: Under ANNEX “B”, MANDATORY TECHNICAL CRITERIA, Mandatory Technical Criteria and Performance Specifications**

Item No.:	Category	Description	Meets	Not Met	Page Number Reference
<b>I.</b>	<b>MANDATORY TECHNICAL CRITERIA</b>				
<b>A.</b>	The Snowmobiles must:				
<b>1.</b>	Be from a manufacturer/reseller who has demonstrated acceptability by manufacturing and/or selling this type and size class of vehicle for at least 1 year.				
<b>2.</b>	Conform to all applicable laws, regulations and industrial standards governing manufactures, safety, noise levels and pollution in effect in Canada at the time of manufacture.				
<b>B.</b>	If the bidder is a reseller and not the manufacturer of the unit offered, the bidder must submit; with their bid, proof from the manufacturer of being an authorized reseller for the unit offered.				
<b>II.</b>	<b>PERFORMANCE SPECIFICATIONS</b>				
<b>A.</b>	<b>YEAR:</b>				
<b>1.</b>	New (or most current model of manufacture production)				
<b>B.</b>	<b>ENGINE &amp; DRIVE TRAIN:</b>				
<b>1.</b>	Type:	2 Stroke or 4 Stroke			
<b>2.</b>	Displacement:	490 cc – 600 cc			
<b>3.</b>	Cooling:	Fan or liquid cooled			
<b>4.</b>	Starting:	Electric - 2 Stroke, manual recoil - 4 Stroke			
<b>5.</b>	Transmission:	Automatic, Forward and Reverse minimum			
<b>6.</b>	Suspension:	Manufacturer Standard			
<b>C.</b>	<b>DIMENSIONS/CAPACITIES:</b>				
<b>1.</b>	Length:	110” (minimum)			
<b>2.</b>	Width:	42” (minimum)			
<b>3.</b>	Height:	43” (minimum)			
<b>4.</b>	Ski Stance:	35” (minimum)			
<b>5.</b>	Track:	15” wide x 135” long x 1” high (minimum)			
<b>6.</b>	Fuel Tank:	Manufacturer Standard			
<b>7.</b>	Rack:	Rear Manufacturer Standard			
<b>8.</b>	<b>Hitch:</b>	<b>One (1) J/Tow Pindle Hitch &amp; One (1) Tongue Hitch, included and installed. Only one (1) hitch to be installed, supply the other one with machine.</b>			



**Royal Canadian Mounted Police**  
**Gendarmerie royale du Canada**

Government  
of Canada

Gouvernement  
du Canada

Solicitation No./Sollicitation No.: M5000-14-2552

<b>D.</b>	<b>BRAKES:</b>			
1.	Track:	Disc – Minimum		
<b>E.</b>	<b>INSTRUMENTATION:</b>			
1.	Speedometer/Odometer:	Manufacturer Standard		
2.	Trip/Hour meter:	Manufacturer Standard		
3.	Fuel Gauge:	Manufacturer Standard		
4.	Temp/Oil Light:	Manufacturer Standard		
<b>F.</b>	<b>OCCUPATIONAL HEALTH &amp; SAFETY:</b>			
1.	Lighting:	One (1) Headlight (Hi/Low) and One (1) Taillight - Minimum		
2.	Seating:			
a.		Two person Capacity (minimum)		
b.		Passenger Back Rest		
c.		Passenger Hand Grips		
3.	Windshield:	19” high (minimum) - installed		
4.	<b>Underbody Protection:</b>	<b>Must protect all vital engine and drive components</b>		
5.	<b>Helmet Defrost Connector</b>	<b>Manufacturer Standard</b>		
6.	Hand & Thumb Warmers:	Manufacturer Standard		
7.	Mirrors:	Left and Right – Manufacturer Standard		
8.	12V Outlet	Manufacturer Standard		
<b>G.</b>	<b>ADDITIONAL FEATURES:</b>			
1.	Tool Kits	Manufacturer Standard – one for each Unit		
2.	Cover:	Factory Cover – All Weather; Trailerable with tie down capability; covers entire machine		
3.	PDI:	Pre-Delivery Inspection – Standard		
4.	Manuals:			
a.		Operators Manual – disc or hard copy – one copy for each unit (English)		
b.		Service & Parts Manual – disc, hardcopy (copy for each) or on-line (English)		
5.	Shipping/Crating:	Must be shipped assembled		



**Royal Canadian Mounted Police**  
**Gendarmerie royale du Canada**

Government  
of Canada

Gouvernement  
du Canada

Solicitation No./Sollicitation No.: M5000-14-2552

<b>6.</b>	Warranty:	Warranty service to be provided at service center. If no service center is available, Recall, Parts and/or After Sales Service must be provided within 48 hours.			
<b>7.</b>	Delivery:	Delivery to be made between 9:00 AM and 3:00 PM MDT Monday through Friday			
<b>8.</b>	Color::	Industry Standard Commercial Paint			
<b>9.</b>	Keys:	Two(2) sets per unit – minimum			