



**RETURN BIDS TO:
RETOURNER LES SOUMISSIONS A :**

Procurement & Contracting Services
Bid Receiving Unit
VISITOR'S CENTRE
73 Leikin Drive
Ottawa, Ontario K1A 0R2
Canada

**SOLICITATION
AMENDMENT**

**MODIFICATION DE
L'INVITATION**

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

Comments: - Commentaries :

Vendor/Firm Name and Address
Raison sociale et adresse du fournisseur/de l'entrepreneur

Telephone No.
no de téléphone:

Title-Sujet Underwater Video Camera System and Umbilical Cable		Date November 4th ^t , 2013
Solicitation No. - No. de l'invitation 201403107		Amendment No. - N° de la modification 001
Client Reference No. - No. De Référence du Client 201403107		
Solicitation Closes - L'invitation prend fin at 2:00pm on November 18 th , 2013		
F.O.B. - F.A.B. Destination		
Address Enquiries to: - Adresser toutes questions à: Candice Therien		
Telephone No. - No de téléphone 613-843-3826	Fax No. - N° de FAX: 613-825-0082	
Destination of Goods and Services: Destinations des biens et services: National Underwater Recovery Training Centre 4416b Boban Drive Nanaimo, British Columbia, Canada V9T 5V9		
Delivery Required - Livraison exigée: 2014/03/31	Delivery Offered - Livraison proposée	
Name and title of person authorized to sign on behalf of Vendor/Firm - Nom et titre de la personne autorisée à signer au nom du fournisseur/de l'entrepreneur		
_____		_____
Signature		Date



This amendment is raised to address the following:

- To respond to questions received during the solicitation period; and
- To revise the solicitation accordingly, as applicable.

QUESTIONS AND ANSWERS

Question 1:

Section 2.2.4 the camera housing must be 5" or less in size

Does the length of 127mm include the connectors?

If yes, is 130mm satisfactory including 12mm brackets?

Can you change the tender document for a maximum diameter of 155mm to allow our Canadian products to qualify?

Answer 1:

We can increase the size of the Housing to 155 mm

Question 2:

Section 2.2.7: Underwater Color Video camera must be 1.5" or less in diameter

Can you change the tender for a maximum diameter of 57 mm (2.25") to allow our Canadian Product to qualify?

Answer 2:

We can increase the size of the housing to 57 mm

Question 3:

Section 2.3.4: Underwater lights. The dimensions must be 1.5" of less in diameter and no more than 6 " in length

Can you change the tender for a maximum diameter of 57mm (2.25") to allow our Canadian Products to qualify for this tender?

Answer 3:

We can increase the size diameter to 57 mm

Question 4

Section 2.3.6 Light output: minimum of 100 watt @ 1 meter

We manufacture a LED lamp in a box sturdy acetal for commercial diving (AxLIGHT 57): we measure the amount of light with a light meter. Our light measure an output of 1350 lumens.



Can you convert your specification for light output in lumens as prescribed in the metric system (lumens)? A measure of 100W @ 1m is not a measure of power or amount of light.
Can modify the tender for a minimum light output of 1200 lumens required?

Answer 4:

Yes we can modify the tender to a minimum of 1200 lumens. Critical to ensure that the lights do not wash out the camera picture.

Question 5:

Section 2.4.7 the LCD Monitor Screen must have a viewing screen of 10 inches or greater

Would you consider having two 7" LCD screens rather than having one 10" screen that you need to swing from one camera to the other?

If yes, can you change the tender to read "a minimum screen of 10" or two 7" screens"

Answer 5:

No, we require a minimum of 10 inch viewing area.

SOLICITATION REVISIONS

1) On page 14 at section 2.2.4,

DELETE: Camera housing must be 5" or less in size

INSERT: Camera housing must be 155mm or less in size

2) On page 14 at section 2.2.7,

DELETE: Dimensions: Must be 1.5" or less in diameter

INSERT: Dimensions: Must be 57mm or less in diameter

3) On page 14 at section 2.3.4

DELETE: Must be 1.5" or less in diameter and no more than 6" in length

INSERT: Must be 57mm in diameter and no more than 6" in length.

4) On page 14 at section 2.3.6

DELETE: Light Output: minimum of 100 watt @ 1 Meter

INSERT: Light Output: minimum of 1200 lumens. Critical to ensure that the lights do not wash out the camera picture.

ALL REMAINING TERMS AND CONDITIONS REMAIN THE SAME