

RETURN BIDS TO:
RETOURNER LES SOUMISSIONS À:
Bid Receiving - PWGSC / Réception des soumissions -
TPSGC
11 Laurier St. / 11, rue Laurier
Place du Portage, Phase III
Core 0A1 / Noyau 0A1
Gatineau, Québec K1A 0S5
Bid Fax: (819) 997-9776

SOLICITATION AMENDMENT
MODIFICATION DE L'INVITATION

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

Comments - Commentaires

Vendor/Firm Name and Address
Raison sociale et adresse du
fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution
Electrical & Electronics Products Division
11 Laurier St./11, rue Laurier
6B1, Place du Portage, Phase III
Gatineau, Québec K1A 0S5

Title - Sujet BETA-CALCO LIGHTING, FIXTURE	
Solicitation No. - N° de l'invitation U6800-141551/A	Amendment No. - N° modif. 001
Client Reference No. - N° de référence du client U6800-141551	Date 2013-11-18
GETS Reference No. - N° de référence de SEAG PW-\$\$HN-380-63839	
File No. - N° de dossier hn380.U6800-141551	CCC No./N° CCC - FMS No./N° VME
Solicitation Closes - L'invitation prend fin at - à 02:00 PM on - le 2013-12-18	Time Zone Fuseau horaire Eastern Standard Time EST
F.O.B. - F.A.B. Plant-Usine: <input type="checkbox"/> Destination: <input checked="" type="checkbox"/> Other-Autre: <input type="checkbox"/>	
Address Enquiries to: - Adresser toutes questions à: Bertrand, Maria	Buyer Id - Id de l'acheteur hn380
Telephone No. - N° de téléphone (819) 956-3484 ()	FAX No. - N° de FAX () -
Destination - of Goods, Services, and Construction: Destination - des biens, services et construction:	

Instructions: See Herein

Instructions: Voir aux présentes

Delivery Required - Livraison exigée	Delivery Offered - Livraison proposée
Vendor/Firm Name and Address Raison sociale et adresse du fournisseur/de l'entrepreneur	
Telephone No. - N° de téléphone Facsimile No. - N° de télécopieur	
Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) Nom et titre de la personne autorisée à signer au nom du fournisseur/ de l'entrepreneur (taper ou écrire en caractères d'imprimerie)	
Signature	Date

Solicitation No. - N° de l'invitation

U6800-141551/A

Amd. No. - N° de la modif.

001

Buyer ID - Id de l'acheteur

hn380

Client Ref. No. - N° de réf. du client

U6800-141551

File No. - N° du dossier

hn380U6800-141551

CCC No./N° CCC - FMS No/ N° VME

Amendement 1 est porté à ajouter des dessins techniques et des informations supplémentaires.

BUBBLE

600/1000/1800



■ GENERAL SPECIFICATION

Housing: Round metal frame consisting of modules combined together for electrical and mechanical connections. Bubble comes in the following diameters: 600mm (23.6"), 1000mm (39.4"), 1800mm (70.9") and 2800mm (110.0").

Diffusers: Injection molded, UV stabilized, opal polycarbonate. Diffusers are sectional with subtle but visible seams. Bubble 600, 3 diffusers; Bubble 1000, 3 diffusers; Bubble 1800, 8 diffusers and Bubble 2800, 16 diffusers.

Power cables: Luminaires supplied with 7.8m/20' of cable. Cables can be extended to a maximum overall distance of 20m/64'. Custom cable lengths can be supplied to special order.

Drivers: Luminaires supplied with HPF electronic drivers, 120/277V. 0-10V dimming standard.

Mechanical: Luminaires mount directly over a junction box.

Finish: White RAL 9003. Custom colors available to special order.

Approvals: ETL.

BUBBLE

600/1000/1800

A SPECIFY LAMP/LUMINAIRE TYPE

Code:	Lamp:	Color CCT:	Delivered lms:	Efficacy LPW:	L70 @25°C (77°F):	Diameter (A):	Diameter (B):	Depth (D):
BCBBWH156	100W LED	3000K	3836	38.2	> 50,000 hrs	600mm/23.6"	440mm/17.3"	191mm/7.5"
BCBBWH276	180W LED	3000K	6900	38.2	> 50,000 hrs	1000mm/39.4"	800mm/31.5"	241mm/9.5"
BCBBWH526	350W LED	3000K	13300	38.2	> 50,000 hrs	1800mm/70.9"	1600mm/63.0"	241mm/9.5"

B SPECIFY POWER SUPPLY AND ACCESSORIES

Bubble LED integral power supply in canopy.

BCLED6/N	Canopy with driver for Bubble 600
BCLED10/N	Canopy with driver for Bubble 1000
BCLED18/N	Canopy with driver for Bubble 1800


Bubble LED remote power supply (specify mounting canopy from bubble accessories as a separate line item).

BCLED6/R	Remote power supply for Bubble 600
BCLED10/R	Remote power supply for Bubble 1000
BCLED18/R	Remote power supply for Bubble 1800


Bubble LED accessories (for luminaires with remote power supplies only).

MEC1745AE	Ceiling canopy for installation to load bearing ceilings (max 32kg/70lbs) for Bubble 600 and Bubble 1000.
MEC2112AE	Ceiling canopy for installation to load bearing ceilings (max 100kg/220lbs) for Bubble 1800.
MEC1823AE	Ceiling canopy for installation into false ceilings or similar (cables are anchored to the load bearing ceiling).
MEC1820	Surface mounting kit for Bubble 600 and 1000.
MEC1821	Surface mounting kit for Bubble 1800.


Note: Due to constant changes in LEDs, please check our website for current product specifications.






BCLED6/N
BCLED10/N
BCLED18/N



BCLED6/R
BCLED10/R
BCLED18/R



MEC1823AE



Weights:

BCBBWH156	8.1kg/17.9lbs
BCBBWH276	16.1kg/35.5lbs
BCBBWH526	33.0kg/72.8lbs

Note: Due to constant changes in LEDs, please check our website for current product specifications.


BUBBLE

2800


SPECIFY LAMP/LUMINAIRE TYPE

LOW PROFILE PENDANT Luminaire complete with 8 suspension cables connected to the central joint for ceiling mounting.

Code:	Lamp:	Color CCT:	Delivered lms:	Efficacy LPW:	L70 @25°C (77°F):	Weight:
BCBBWH886R	590W LED, remote power supply	3000K	22500	38.2	> 50,000 hrs	63kg/138.9lb




BCBBWH886R




Remote power supply included.

ADJUSTABLE PENDANT Luminaire complete with 8 cables connected to the central joint and 4 adjustable cables for ceiling mounting.


Code:	Lamp:	Color CCT:	Delivered lms:	Efficacy LPW:	L70 @25°C (77°F):	Weight:
BCBBWH886PIN	590W LED, integral power supply	3000K	22500	38.2	> 50,000 hrs	75kg/165.3lb
BCBBWH886PR	590W LED, remote power supply	3000K	22500	38.2	> 50,000 hrs	67kg/147.7lb



BCBBWH886PIN



BCBBWH886PR



Remote power supply included.




Note: Due to constant changes in LEDs, please check our website for current product specifications.

BUBBLE

2800

CEILING MOUNTED Luminaire complete with 8 suspension cables L=2000mm/79".


Code:	Lamp:	Color CCT:	Delivered lms:	Efficacy LPW:	L70 @25°C (77°F):	Weight:
BCBBWH886CIN	590W LED, integral power supply	3000K	22500	38.2	> 50,000 hrs	74kg/163.1lb
BCBBWH886CR	590W LED, remote power supply	3000K	22500	38.2	> 50,000 hrs	66kg/145.5lb



Remote power supply included.

SPECIFY ACCESSORIES (REQUIRED)

150A031VE Umbrella tool for assembly.



Note: Due to constant changes in LEDs, please check our website for current product specifications.