

RETURN BIDS TO:
RETOURNER LES SOUMISSIONS À:
Bid Receiving - PWGSC / Réception des soumissions -
TPSGC
11 Laurier St. / 11, rue Laurier
Place du Portage, Phase III
Core 0A1 / Noyau 0A1
Gatineau, Québec K1A 0S5
Bid Fax: (819) 997-9776

SOLICITATION AMENDMENT
MODIFICATION DE L'INVITATION

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

Comments - Commentaires

Vendor/Firm Name and Address
Raison sociale et adresse du
fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution
Vehicles & Industrial Products Division
11 Laurier St./11, rue Laurier
7A2, Place du Portage, Phase III
Gatineau, Québec K1A 0S5

Title - Sujet Medium Truck	
Solicitation No. - N° de l'invitation 46533-146110/A	Amendment No. - N° modif. 004
Client Reference No. - N° de référence du client 46533-146110	Date 2013-11-20
GETS Reference No. - N° de référence de SEAG PW-\$\$HP-371-63565	
File No. - N° de dossier hp371.46533-146110	CCC No./N° CCC - FMS No./N° VME
Solicitation Closes - L'invitation prend fin at - à 02:00 PM on - le 2013-11-29	Time Zone Fuseau horaire Eastern Standard Time EST
F.O.B. - F.A.B. Plant-Usine: <input type="checkbox"/> Destination: <input checked="" type="checkbox"/> Other-Autre: <input type="checkbox"/>	
Address Enquiries to: - Adresser toutes questions à: Modérie, Christine	Buyer Id - Id de l'acheteur hp371
Telephone No. - N° de téléphone (819) 956-3970 ()	FAX No. - N° de FAX (819) 953-2953
Destination - of Goods, Services, and Construction: Destination - des biens, services et construction:	

Instructions: See Herein

Instructions: Voir aux présentes

Delivery Required - Livraison exigée	Delivery Offered - Livraison proposée
Vendor/Firm Name and Address Raison sociale et adresse du fournisseur/de l'entrepreneur	
Telephone No. - N° de téléphone Facsimile No. - N° de télécopieur	
Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) Nom et titre de la personne autorisée à signer au nom du fournisseur/ de l'entrepreneur (taper ou écrire en caractères d'imprimerie)	
Signature	Date

Solicitation No. - N° de l'invitation

46533-146110/A

Amd. No. - N° de la modif.

004

Buyer ID - Id de l'acheteur

hp371

Client Ref. No. - N° de réf. du client

46533-146110

File No. - N° du dossier

hp37146533-146110

CCC No./N° CCC - FMS No/ N° VME

Amendment No. 004 to the solicitation is raised revise Annex "A".

DELETE: Annex "A" in its integrity

INSERT: New revision of Annex "A"

DELETE: GVWR of 19,500 lbs. minimum

INSERT: GVWR of 21,000 lbs. minimum

All other terms and conditions remain unchanged.

ANNEX “A” – SPECIFICATIONS

PROPOSALS WILL BE EVALUATED IN ACCORDANCE WITH THE MANDATORY EVALUATION CRITERIA DETAILED BELOW.

2013 or Newer Medium Truck with Box and Lift Gate.

MANDATORY REQUIREMENTS FOR THE TRUCK

<u>Mandatory Specifications</u>	BIDDERS ARE TO SPECIFY THEIR CONFORMANCE TO THE SPECIFICATIONS. DESCRIBE THE DEVIATIONS:	
	<u>YES</u>	<u>NO</u>
1. Medium Truck	_____	_____
2. Conventional Cab and Chassis, 16' Box and Lift Gate Provided and Installed	_____	_____
3. GVWR of 21,000 lbs. minimum	_____	_____
4. Cab to axle dimension to accommodate an aluminum box of 16'. Should provide optimum axle loading.	_____	_____
5. Cab-to-End of Frame dimension – to accommodate length of body	_____	_____
6. 362 HP - minimum	_____	_____
7. Automatic Transmission	_____	_____
8. Air conditioning	_____	_____
9. Power Brakes	_____	_____
10. Two West Coast Type Heated Mirrors of approximately 150 x 400 mm (6 x 16 in) mounted on 5 arms - minimum	_____	_____
11. Front Seating must have seating for 3 people	_____	_____
12. Intermittent Wipers	_____	_____

MANDATORY REQUIREMENTS FOR THE TRUCK CONTINUE

	<u>YES</u>	<u>NO</u>
13. Step Rails (or equivalent) on Cab	_____	_____
14. Color: White	_____	_____
15. Type of Terrain: Flat and Hilly	_____	_____
16. Full Size Spare Tire on Rim	_____	_____
17. Alternator and Battery – Heavy duty, maximum capacity available for options required on model specified	_____	_____
18. Block Heater – Standard single element, 115 V, 400 W minimum	_____	_____
19. Cooling System operating range from -37°C to +37°C	_____	_____
20. Power Windows and Door Locks	_____	_____
21. Gauges for voltmeter, temperature and oil pressure	_____	_____
22. Performance. The power Train must provide a geared top speed of at least 105 Km/h. (Performance is to be in accordance with SAE J688 procedures. The driveline must provide a minimum grade ability of 0.50% at 90 km/h and a minimum grade ability of 30% at peak torque in first gear using full GVWR at sea level.)	_____	_____
23. Basic Manufacturer AM/FM Radio	_____	_____
24. Safety Features must meet the provisions of the Canada Motor Vehicle Safety Act and the Regulations made There under which are in effect on the date of manufacture.	_____	_____
25. Standard Exhaust	_____	_____

MANDATORY REQUIREMENTS FOR THE BOX**YES****NO**

- | | | |
|--|-------|-------|
| 1. Heavy Duty Aluminum box as per following dimensions:
Length: 16' (ft)
Width: 95 1/2" (in)
Height: 95" (in) | _____ | _____ |
| 2. Box floor must be compatible to height of dock at 53" | _____ | _____ |
| 3. Rear roll up door c/w side - seals with
86" (in) high x 86.5" (in) opening – minimum | _____ | _____ |
| 4. Heavy Gauge Satin coated steel rear door frame | _____ | _____ |
| 5. One piece roof with 2" top hat roof bows | _____ | _____ |
| 6. Deep aluminum extrusion bottom rail with built in rub rail | _____ | _____ |
| 7. 1 3/8" Ship Lap Hardwood Floor on 12" centre | _____ | _____ |
| 8. Recessed 3/16" steel checker plate threshold plate at
rear 48" deep | _____ | _____ |
| 9. 3" structural channel cross members with 5" structural
channel longsills | _____ | _____ |
| 10. 1/2" Plywood Lining on Walls, 3/4" on front wall | _____ | _____ |
| 11. 18" galvanized extruded scuffplate on walls & front | _____ | _____ |
| 12. Two rows on each wall 1806 cargo control 2' and 4' heights | _____ | _____ |
| 13. 3" X 5" x 1/4" front crash angle | _____ | _____ |
| 14. 2 Interior Dome lights with pilot light in cab | _____ | _____ |
| 15. One pair rubber grab handles on door pillars | _____ | _____ |
| 16. All Canada Motor Vehicle Safety Standards (CMVSS)
Body clearance lights and reflectors | _____ | _____ |
| 17. 1 pair splash shields | _____ | _____ |
| 18. Pre-painted white panels .040 ga aluminum | _____ | _____ |
| 19. Underbody "Tectyl" (or equivalent) undercoated | _____ | _____ |

<u>MANDATORY REQUIREMENTS FOR THE LIFT GATE</u>	<u>YES</u>	<u>NO</u>
1. Fold and Stow style – Level Ride	_____	_____
2. Capacity 3000 lbs minimum	_____	_____
3. Aluminum platform: 72” Wide x 60” deep * Maximum width must be less than 7 feet Wide since call site pillars are 7 feet apart.	_____	_____
4. Cart stop	_____	_____
5. Steel pump and motor enclosure	_____	_____
6. Heavy-duty dock bumpers _____	_____	_____
7. Side steps	_____	_____
8. Pump and motor enclosure	_____	_____
9. Dual hydraulics	_____	_____
10. Cab cut off switch	_____	_____
11. Underride	_____	_____