

LIGHTING FIXTURE SCHEDULE AND SPECIFICATION				
TYPE	DESCRIPTION	LAMP TYPE	NUMBER OF LAMPS	MANUFACTURER CATALOG No.
F1	610mm x 1220mm PREMIUM GRADE RECESSED LENSED TROFFER, A125 PRISMATIC LENS. COMPLETE WITH DRYWALL FRAME KIT, 120V	32W T8 LINEAR FLUORESCENT	2	CFI CAT NO. SPS2GFSVB232UNVPS METALUX CAT NO. 2GC-232A125-UNV-HR81-U LITHONIA CAT NO. 2SP-F-2-32-A12125-MVOLT-GE10PS
F2	610mm x 1220mm RECESSED FOOD GRADE LENSED FIXTURE, FOOD GRADE NSF2 RATED, A125 DIFFUSED LENS, COMPLETE WITH DRYWALL FRAME KIT, 120V	32W T8 LINEAR FLUORESCENT	2	KENALL CAT NO. CSEF024 2-32-RS-1-120-5F-2H-T FAILSAFE CAT NO. CFF-24-232-UNV-IK12-HR81-SSN NEWSTAR CAT NO. SCF24-HC-OP-2-32-1-A-12
F3	1220mm SURFACE MOUNTED VAPOURTIGHT, DIFFUSED LENS, GASKETED, NONMETALLIC HOUSING, 120V	32W T8 LINEAR FLUORESCENT	2	CFI CAT NO. VTN4232ST-UNV-PS METALUX CAT NO. VT3-232DR-100-UNV-EB81-WL-U LITHONIA CAT NO. DMW-2-32-MVOLT-GE10PS
F4	1220mm SURFACE MOUNTED WALL CUBE, VANDAL RESISTANT, ALLEN KEY FASTENERS, 120V	32W T8 LINEAR FLUORESCENT	2	KENALL CAT NO. WCD41-232-RS-1-120-1-2 FAILSAFE CAT NO. FMB-D-2/132-UNV-80/84-HR81-SF3 NEWSTAR CAT NO. 55W4-C-2-32-1-A/A-12AH
F5	610mm SURFACE MOUNTED WALL CUBE, VANDAL RESISTANT, ALLEN KEY FASTENERS, 120V	32W T8 LINEAR FLUORESCENT	2	KENALL CAT NO. WCD21-217-RS-1-120-1-2 FAILSAFE CAT NO. FMB-D-2/117-UNV-80/84-HR81-SF3 NEWSTAR CAT NO. 55W2-C-2-17-1-A/A-12AH
F6	RECESSED LENSED VOLUMETRIC FIXTURE, DIFFUSED LENS.COMPLETE WITH DRYWALL FRAME KIT, 120V	32W T8 LINEAR FLUORESCENT	2	LEDALITE CAT NO. 3324-D1-ST-T232-S-1-1-E METALUX CAT NO. 2ALNG-232-SDL-UNV-HR81 MARK LIGHTING CAT NO. WHS242T8EBSW-SW
F7	SUSPENDEED INDUSTRIAL STRIP WITH 10% UPLIGHT AND WIRE GUARD, 120V	32W T8 LINEAR FLUORESCENT	2	CFI CAT NO. FF248UNVHI-EE9G4 METALUX CAT NO. IAF-232-UNV-HR81-WG/ICF-4FT-U LITHONIA CAT NO. Z-2-32-MVOLT-GE10PS-Z8SMR48A8-WGZ8SMR48
L1	WALL MOUNTED EXTERIOR AREA LIGHT, ROUGH SURFACE, HIGH ABUSE. FULL CUTOFF, 230MM SQUARE, 4000K COLOR TEMPERATUREM 1100 LUMENS DELIVERED, HIGH IMPACT, UV STABILIZED, MARINE GRADE DIE CAST ALUMINUM HOUSING, CUSTOM COLOR TO MATCH CLADDING (COLOR "B" IN ARCH SPECS)	LED		KENALL CAT NO. FN9L-A-MB-CC-26L40K LUMARK CAT NO. XTOR3A DECO LIGHTING CAT NO. D445-LED-20-41-UNC-CC
L2	RECEESED MOUNTED 495MM X 519MM CANOPY FIXTURE WITH MOUNTING TRIM KIT, SUITABLE FOR WET LOCATION, POLYESTER POWDERCOAT FINISH	LED		GARDCO CAT NO. SFC-5W-105LA-NW-UNIV-NP MCGRAW-EDISON CAT NO. LRC-B64-4-LED-E1-MST-WH SDL CAT NO. 20RP-LE5-84L-120-E10
L3	SURFACE MOUNTED UNDER-COUNTER FIXTURE, HIGH ABUSE.PRISMATIC LENS, INTEGRAL TOGGLE SWITCH, 4000K COLOR TEMP, 800 LUMENS DELIVERED, 610MM LENGTH	LED		KENALL CAT NO. AUCLED-I-MW-11L40K-24-120-SW FAILSAFE CAT NO. UCL-2-LD2-40-A12125-ED-120 NEWSTAR MUS2-HA-L1-40-4A-12RS
L4	WALL MOUNTED EXTERIOR AREA LIGHT, ROUGH SURFACE, HIGH ABUSE. FULL CUTOFF, 381MM SQUARE, HIGH IMPACT, UV STABILIZED, MARINE GRADE DIE CAST ALUMINUM HOUSING, CUSTOM COLOR TO MATCH CLADDING (COLOR "A" IN ARCH SPECS)	LED		KENALL CAT NO. FN15L3-A-MB-CC-80L40K LUMARK CAT NO. XTOR9A LITHONIA CAT NO. ASW1-LED-1-63B350/50K-SR3-MVOLT-VG-CC
L6	POLE MOUNTED AREA LIGHT WITH ARM, NEUTRAL WHITE COLOR, TYPE 3 DIST, PHOTOCCELL AND RECEPTACLE	LED		GARDCO CAT NO. G18-1-3-95LA-NW-BRP-PC-MOUNTING ARM FOR POLE MCGRAW-EDISON CAT NO. GLEON-AA-02-LED-120-T3-BK-MA LITHONIA CAT NO. DSX0-40C-700-40K-T3M-MVOLT-SPA-PER-DBXD
	EXIT SIGN, NEMA 1, GREEN RUNNING MAN PICTOGRAM, LED, ALUMINUM HOUSING, VANDAL GUARD AND TAMPERPROOF SCREWS, BATTERY BACKUP 90 MINUTE MINIMUM, UNIVERSAL WALL OR CEILING MOUNTING, SINGLE FACE WITH ARROW PER LAYOUT	LED		LUMACELL CAT NO. LA1WUVR AIMLITE EQUIVALENT READY-LITE CAT NO. RA1WSPVR
	EXIT SIGN, WEATHERPROOF, NEMA 4X, GREEN RUNNING MAN, LED, NON METALLIC HOUSING, NSF2, BATTERY BACKUP 90 minute MINIMUM, UNIVERSAL WALL OR CEILING MOUNTING, SINGLE FACE NO ARROW	LED		LUMACELL CAT NO. LN1WSD AIMLITE EQUIVALENT READY-LITE RN1WSPD
	UNIT EQUIPMENT, NEMA 4X, DUAL 12V 4W LED MR16 HEAD, 120V INPUT, 12V OUTPUT, 72W CAPACITY, NSF2, IP65	LED		LUMACELL CAT NO. RG12NX722LD7 AIMLITE EQUIVALENT READY-LITE CAT NO. LDX12-722LD7
	REMOTE HEAD, NEMA 4X, DUAL 12V 4W LED MR16 HEAD, NSF2, IP65	LED		LUMACELL CAT NO. MQMP2NXLD7 AIMLITE EQUIVALENT READY-LITE CAT NO. NMMP2LD7
TABLE NOTES				
1	THE PRODUCT SPECIFICATIONS LISTED ABOVE REPRESENT THE BASIC CATALOG NUMBER INFORMATION. THE CONTRACTOR SHALL BE RESPONSIBLE FOR SUPPLYING AND INSTALLATING ALL NECESSARY SUPPORTS FITTINGS, TRIMS, HOUSINGS, CANOPIES, ETC TO MAKE A COMPLETE LIGHTING ASSEMBLY.			

0	ADDENDUM #1	JAN./13 2014
revisions		date
project		projet
NEW FOOD SERVICES BUILDING WESTMORLAND INSTITUTION DORCHESTER, NB		
drawing		dessin
REFERENCE DRAWING E2.2 REVISED LIGHTING FIXTURE SCHEDULE		
designed	MM	conçu
date	Jan. 13, 2014	
drawn	MM	dessiné
date	Jan. 13, 2014	
approved	TL	approuvé
date	Jan. 13, 2014	
Tender		Soumission
PWGSC Project Manager	Administrateur de projets	TPSGC
project number		no. du projet
R.061828.001		
drawing no.		no. du dessin
ESK2		