

RETURN BIDS TO:
RETOURNER LES SOUMISSIONS À:
Bid Receiving
PWGSC
33 City Centre Drive
Suite 480
Mississauga
Ontario
L5B 2N5
Bid Fax: (905) 615-2095

SOLICITATION AMENDMENT
MODIFICATION DE L'INVITATION

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

Comments - Commentaires

Vendor/Firm Name and Address
Raison sociale et adresse du
fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution
Public Works and Government Services Canada
Ontario Region
33 City Centre Drive
Suite 480
Mississauga
Ontario
L5B 2N5

Title - Sujet CCTV Camera -		
Solicitation No. - N° de l'invitation 47624-147827/A		Amendment No. - N° modif. 001
Client Reference No. - N° de référence du client 47624-147827		Date 2014-01-16
GETS Reference No. - N° de référence de SEAG PW-\$TOR-003-6461		
File No. - N° de dossier TOR-3-36207 (003)	CCC No./N° CCC - FMS No./N° VME	
Solicitation Closes - L'invitation prend fin at - à 02:00 PM on - le 2014-01-22		Time Zone Fuseau horaire Eastern Standard Time EST
F.O.B. - F.A.B. Plant-Usine: <input type="checkbox"/> Destination: <input checked="" type="checkbox"/> Other-Autre: <input type="checkbox"/>		
Address Enquiries to: - Adresser toutes questions à: Escander, Lisa		Buyer Id - Id de l'acheteur tor003
Telephone No. - N° de téléphone (905) 615-2062 ()		FAX No. - N° de FAX (905) 615-2060
Destination - of Goods, Services, and Construction: Destination - des biens, services et construction:		

Instructions: See Herein

Instructions: Voir aux présentes

Delivery Required - Livraison exigée	Delivery Offered - Livraison proposée
Vendor/Firm Name and Address Raison sociale et adresse du fournisseur/de l'entrepreneur	
Telephone No. - N° de téléphone Facsimile No. - N° de télécopieur	
Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) Nom et titre de la personne autorisée à signer au nom du fournisseur/ de l'entrepreneur (taper ou écrire en caractères d'imprimerie)	
Signature	Date

This Solicitation Amendment 001 is raised to answer Bidder's questions and amend the technical evaluation criteria and statement of requirement.

Questions and Answers

Question 1:

May a bidder submit multiple bids?

Answer 1:

Yes, bidders may submit multiple bids and each bid will be evaluated separately

Question 2:

Will a bid not in full compliance with all technical criteria be considered as an alternate proposal.

Answer 2:

No, any bid received that is not fully compliant with all mandatory elements of the solicitation will not be given any further consideration.

Question 3:

The tender stated "Resolution minimum range QCIF - 3MP" Should this read QCIF to 1.3MP

Answer 3:

The tender should have read QCIF to 1.3 MP. This was an error in submission

Question 4:

The tender stated "Min. IP66 rated for exterior model". Should this be deleted if the cameras are for indoors?

Answer 4:

Yes this item can be deleted as the cameras will be for indoor use. Upon further consideration exterior camera requirements are not required for this scope of work.

Question 5:

The tender stated "Operating Temperatures of -40 to 50 degrees Celsius" This is an outdoor model which would add unnecessary additional costs if the camera were to be installed indoors.

Answer 5:

As per question 4, exterior models are not required; the cameras are in fact for the interior and the range should be 0 to 50 degrees Celsius.

Question 6:

By "Omnicat" did you mean "Omnicast video management by Genetec"?

Answer 6:

Yes, this was an error. Please see amendment below.

Question 7:

What type of camera are you looking for? The solicitation is for 110 fixed ip dome cameras but the actual requirement has 3mm-6mm vari-focal lens. Does that mean it is not going to be fixed?

Answer 7:

The requirement is for 110 fixed dome cameras. The word "fixed" references that the cameras do not move/rotate. The cameras are to have a vari- focal lens with the requirement of 3mm-6mm. This will allow the camera lens to zoom in and out. So the actual camera is fixed and does not move/rotate however the lens is required to have the vari-focal capability.

Amendment to solicitation 001**At PART 4 - EVALUATION PROCEDURES AND BASIS OF SELECTION****At article 1 - Evaluation Procedures****At 1.1 - Technical Evaluation****At 1.1.1 - Mandatory Technical Criteria****At M1****At number 1)**

Delete: Omnicat

Insert: Omnicast

At number 5)

Delete: must have a minimum resolution range QCIF - 3MP

Insert: must have a minimum resolution range QCIF to 1.3 MP

At number 9)

Delete: Min. IP66 rated for exterior model

At number 10)

Delete: Operating Temperatures of -40 to 50 degrees Celsius.

Insert: Operating Temperatures of 0 to 50 degrees Celsius.

At ANNEX "A" - REQUIREMENT**At A3 SCOPE**

Delete: Omnicat

Insert: Omnicast

Delete: must have a minimum resolution range QCIF - 3MP

Insert: must have a minimum resolution range QCIF to 1.3 MP

Delete: Min. IP66 rated for exterior model

Delete: Operating Temperatures of -40 to 50 degrees Celsius.

Insert: Operating Temperatures of 0 to 50 degrees Celsius.