



**Royal Canadian Mounted Police**  
**Gendarmerie royale du Canada**

**RETOURNER LES  
 SOUMISSIONS A:  
 RETURN BIDS TO:  
 Bid Receiving/Réception des  
 sousmissions**

Procurement & Contracting Services  
 c/o Commissionaires, F Division  
 6101 Dewdney Ave  
 Regina, SK S4P 3K7

Fax No. - N° de FAX:  
 (306) 780-3466

**SOLICITATION AMENDMENT  
 MODIFICATION DE  
 L'INVITATION**

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les memes.

**Comments – Commentaries**

**Vendor/Firm Name and Address  
 Raison sociale et adresse du  
 fournisseur/de l'entrepreneur**

**Telephone No.  
 no de téléphone:**

<b>Title-Sujet:</b> Supply and Deliver a Monitor/Defibrillator, Regina, SK					
<b>Solicitation No. - No. de l'invitation</b> M5000-4-4725/A	<b>Date</b> 03 February 2014				
<b>Amendment No.-No modif</b> 001					
<b>Client Reference No. - No. De Référence du Client</b> PW-13-00609958					
<b>GETS Reference No.-No de Référence du SEAG</b> N/A					
<b>Solicitation Closes - L'invitation prend fin</b> at 2:00 p.m. Central Standard Time on 03 March 2013					
<b>F.O.B. - F.A.B.</b> Destination					
<b>Address Enquiries to: - Adresser toutes questions à:</b> Teresa Hengen					
<b>Telephone No. - No de telephone:</b> 306-780-8179	<b>Fax No. - N° de FAX:</b> 306-780-3466				
<b>Destination of Goods - Destinations des biens:</b> Royal Canadian Mounted Police-Depot Division 5600 11th Ave Regina, SK S4P 3J7					
<b>Delivery Required - Livraison exigée:</b> See Herein	<b>Delivery Offered - Livraison propose:</b> See Herein				
<b>Name and title of person authorized to sign on behalf of Vendor/Firm - Nom et titre de la personne autorisée à signer au nom du fournisseur/de l'entrepreneur</b>					
<table style="width:100%; border:none;"> <tr> <td style="border:none; width:50%; text-align:center;">_____</td> <td style="border:none; width:50%; text-align:center;">_____</td> </tr> <tr> <td style="border:none; text-align:center;">Name</td> <td style="border:none; text-align:center;">Title</td> </tr> </table>		_____	_____	Name	Title
_____	_____				
Name	Title				



This amendment is raised to address the following question:

Question 1: Would the ZOLL X Series Defibrillator be considered an equivalent to the LIFEPAK 15?

Answer 1: Yes, the ZOLL X Series would be considered an equivalent to the LIFEPAK 15.

**Annex A**  
**Statement of Requirement**

**Delete:**

1. LIFEPAK 15 V2 Monitor/Defibrillator or equivalent with Adaptive Biphasic, Manual and Automatic External Defibrillators (AED), Color LCD – minimum 8.4” diagonal screen, 100mm Printer with minimum print speed of 25mm/sec, Non-invasive Pacing – demand and non-demand rate, CPR Metronome, Trending, Pulse Oximetry (SpO2), Non-Invasive Blood Pressure (NIBP), 12-Lead ECG, End-tidal CO2 (EtCO2), temperature monitoring, Bluetooth capability;

**Insert:**

1. LIFEPAK 15 V2 Monitor/Defibrillator or equivalent with Adaptive Biphasic, Manual and Automatic External Defibrillators (AED), Color LCD – minimum 6.5” diagonal screen, 100mm Printer with minimum print speed of 25mm/sec, Non-invasive Pacing – demand and non-demand rate, CPR Metronome, Trending, Pulse Oximetry (SpO2), Non-Invasive Blood Pressure (NIBP), 12-Lead ECG, End-tidal CO2 (EtCO2), temperature monitoring, Bluetooth capability;

**Annex C**  
**Mandatory Technical Criteria**

**Delete:**

1. LIFEPAK 15 V2 Monitor/Defibrillator or equivalent with Adaptive Biphasic, Manual and Automatic External Defibrillators (AED), Color LCD – minimum 8.4” diagonal screen, 100mm Printer with minimum print speed of 25mm/sec, Non-invasive Pacing – demand and non-demand rate, CPR Metronome, Trending, Pulse Oximetry (SpO2), Non-Invasive Blood Pressure (NIBP), 12-Lead ECG, End-tidal CO2 (EtCO2), temperature monitoring, Bluetooth capability;

**Insert:**

1. LIFEPAK 15 V2 Monitor/Defibrillator or equivalent with Adaptive Biphasic, Manual and Automatic External Defibrillators (AED), Color LCD – minimum 6.5” diagonal screen, 100mm Printer with minimum print speed of 25mm/sec, Non-invasive Pacing – demand and non-demand rate, CPR Metronome, Trending, Pulse Oximetry (SpO2), Non-Invasive Blood Pressure (NIBP), 12-Lead ECG, End-tidal CO2 (EtCO2), temperature monitoring, Bluetooth capability;