

RETURN BIDS TO:
RETOURNER LES SOUMISSIONS À:
Public Works and Government Services / Travaux
publics et services gouvernementaux
Kingston Procurement
Des Acquisitions Kingston
86 Clarence Street, 2nd floor
Kingston
Ontario
K7L 1X3
Bid Fax: (613) 545-8067

SOLICITATION AMENDMENT MODIFICATION DE L'INVITATION

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

Comments - Commentaires

Vendor/Firm Name and Address
Raison sociale et adresse du
fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution
Public Works and Government Services / Travaux
publics et services gouvernementaux
Kingston Procurement
Des Acquisitions Kingston
86 Clarence Street, 2nd floor
Kingston
Ontario
K7L 1X3

Title - Sujet Small wares- CFB Borden	
Solicitation No. - N° de l'invitation W0113-13L029/A	Amendment No. - N° modif. 006
Client Reference No. - N° de référence du client W0113-13-L029	Date 2014-02-06
GETS Reference No. - N° de référence de SEAG PW-\$KIN-650-6254	
File No. - N° de dossier KIN-3-40138 (650)	CCC No./N° CCC - FMS No./N° VME
Solicitation Closes - L'invitation prend fin at - à 02:00 PM on - le 2014-02-11	Time Zone Fuseau horaire Eastern Standard Time EST
F.O.B. - F.A.B. Plant-Usine: <input type="checkbox"/> Destination: <input checked="" type="checkbox"/> Other-Autre: <input type="checkbox"/>	
Address Enquiries to: - Adresser toutes questions à: Rombough, Lori	Buyer Id - Id de l'acheteur kin650
Telephone No. - N° de téléphone (613) 545-8061 ()	FAX No. - N° de FAX (613) 545-8067
Destination - of Goods, Services, and Construction: Destination - des biens, services et construction:	

Instructions: See Herein

Instructions: Voir aux présentes

Delivery Required - Livraison exigée	Delivery Offered - Livraison proposée
Vendor/Firm Name and Address Raison sociale et adresse du fournisseur/de l'entrepreneur	
Telephone No. - N° de téléphone Facsimile No. - N° de télécopieur	
Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) Nom et titre de la personne autorisée à signer au nom du fournisseur/ de l'entrepreneur (taper ou écrire en caractères d'imprimerie)	
Signature	Date

Solicitation No. - N° de l'invitation

W0113-13L029/A

Client Ref. No. - N° de réf. du client

W0113-13-L029

Amd. No. - N° de la modif.

006

File No. - N° du dossier

KIN-3-40138

Buyer ID - Id de l'acheteur

kin650

CCC No./N° CCC - FMS No/ N° VME

AMENDMENT #006

The intent of this amendment is to answer questions from potential bidders and revise Annex "A" & Annex "B-2".

Q1. Within Annex "A", under: 2.1 Specification, minimum requirements , Item #198 Cooling rack

Q1.1 The cooling racks will hold solid food trays... Could you please specify the size of the food trays.

A1.1 This cooling rack is intended for bakers cookie sheets not food trays. It must hold bun pan sized 26 inches by 18 inches, quantities of 20 full size sheet pans or 40 half size pans, with 3" of spacing between the slides.

Q1.2 What is the requested quantity?

A1.2 Requested total item quantity of 10 is indicated in the fillable spreadsheet available at: <https://buyandsell.gc.ca/procurement-data/tender-notice/PW-KIN-650-6254>

Q2. Within Annex "A", under: Item #219 Storage (Dunnage) rack

Q2.1 Could you please reconfirm the dimensions. Storage shelving (as per RFP picture) standard dimensions are:

minimum standard length : 24" (610 mm)

standard depth: 14" (356 mm), 18" (457 mm), 21" (533 mm), 24" (610 mm)

Posts standard height: 54" (1372 mm), 63" (1600 mm), 72" (1829 mm)

A2.1 The client has confirmed the correct size and weight should be: 60" high x 21" wide x 12" deep and hold up to 3,000lbs.

Q2.2 What is the requested quantity?

A2.2 Requested total item quantity of 20 is indicated in the ENGLISH fillable spreadsheet available at: <https://buyandsell.gc.ca/procurement-data/tender-notice/PW-KIN-650-6254>

NOTE: Within the FRENCH fillable spreadsheet, the description and quantity for item #219 is incorrect and revisions are noted in the French version of this amendment.

Description : Support de rangement

Taille approximative : 12 po x 21 po x 60 po, capacité de 3 000 lb

UD : ch.

Taille du Paquet: ch.

Quantité par paquet: 1

Quantité: 20

Quantité totale d'articles: 20

Q2.3 Do you need assembling and put in place?

A2.3 No, the client does not require assembly or placement.

Q2.4 Item # 219: You requested bun racks that can contain 12 trays measuring 18" x 26". In the description in the request for quote (see attachment), the storage rack measures 12" x 21" x 60" in height with 4 trays. How can 12 trays measuring 18" x 26" be stored on a rack that holds 4 trays measuring 12" x 21"?

A2.4 This question has been answered in A2.2.

Q3. Received the Base Borden quote, but something occurred to us, the request for inserts was not very clear, they asked for insert pans, but specified no gauge, either 24 gauge or 22 gauge. Since these

pans are going to be used in a very rough way, I would think 22 gauge would be best, maybe 24 gauge at the least. Could you please clarify what gauge should be used?

A3. The client requires 22 Gauge

Q4 Item #193: What is the length of the mixer required?

A4 Dimensions: 12" x 1 5/16" x 1"

Q5 Item #45: Comes in a package of 6 units.

A5 The client requires a quantity of 10 of this item

Q6 Items # 105 and 117: Comes in a package of 6 units.

A6 The client requires quantities of 25 each for items #105 and #117.

Q7 Item # 159: Comes in a package of 3 units.

A7 I require 24 each of this item

Q8. Could we get description clarification on some of the requested smallware items:

Q8.1 line 47 - cheese blocker 17" x 17 1/4" x 32"

A8.1 made of stainless steel with a Cut Size: 1/2"

Q8.2 line 59 - stainless steel scoop 52 ml

A8.2 Capacity 52 ML was put in error should read 52 Oz 1537.8 ml

Q8.3 line 77 - stainless steel measuring tools 1/4 qt

A8.3 should read stainless steel measuring cup 1/4 qt

Q8.4 line 78 - stainless steel measuring tools 4 qts

A8.4 should read stainless steel measuring cup 4 qts

Q8.5 line 89 - market trays (desserts) 10 7/16" x 3/4"

A8.5 used for displaying breads, bakery items, and sliced deli meat,

- heavy-duty fiberglass construction, with metal reinforced rods
- has air-flow corners reduce drying time;
- NSF Listed

Q8.6 line 90 - display tray 12" x 20"

A8.6 Dimensions (W x D): 12" x 20"

Plastic type: Polycarbonate

Q8.7 line 101 - Cambro camwear polycarbonate storage bins (no substitute) - fits 18" x 26"

A8.7 Bins will be used to keep bulk produce, fish, meat, or poultry fresh and organized with this 18" x 26" x 15" Cambro Camwear 182615CW135 clear polycarbonate food storage box. It's made of durable clear polycarbonate that resists stains and odors, and can withstand temperatures from -40 to 160 degrees Fahrenheit, for use in coolers and freezers.

A textured bottom reduces scratching, and molded-in handles make carrying this food storage box a breeze. NSF Listed.

Q8.8 line 178 - Revolving cake stand non slip 12" diam x 3.25 high impact plastic

A8.8 Size: 12-in.x3.25 high, colour white.

- Professional quality revolving cake stand, made of high impact plastic
- Use to easily decorate cakes
- Includes one non-slip pad

Q8.9 line 179 - Fondant smoother 6" x 3"

A8.9 To be used for shaping and smoothing rolled fondant, 6 inches long x 3 inches wide and dishwasher safe.

Q8.10 line 180 - Decorating comb and icing smoother 3.8" x 6"

A8.10 to be used to smooth or create designs on the side or top of cakes. Made with aluminum.

Q8.11 line 182 - Pastry cutter, 9" handle

A8.11 Stainless steel, smooth rounded handle and thumb tab. Dishwasher safe

Q8.12 line 183 - Bench scraper 4" x 3"

A8.12 Stainless steel blade, extra long wooden handle and brass rivets. Dimensions are changed to 6" x 3"

Q8.13 line 185 - Non stick loaf pan set - assorted sizes?

A8.13 9 1/4 x 5 1/4 x 2 3/4 in. Metal-Safe Non-Stick Loaf Pan

Q8.14 line 195 - Donut cutter standard size

A8.14 Standard industry size; diameter 3", height 2 1/2".
Designed for commercial use. One piece heavy weight stainless steel.

Q8.15 line 197 - Muffin pan aluminized steel overall frame 14" x 20.5" for 24 muffins

A8.15 Dimensions are changed to 14" x 20", vertical depth 1 3/8", volume to brimful 3.8".

Q8.16 line 199 - Bread and bun basket 9.25" x 5.88" x 5.88" (what material?)

A8.16 Polyethylene (PE)

Q8.17 line 206 - Paring knife sheath - nylon sheath (size?)

A8.17 Paring Knife Pouch with Clip, Accepts 3 1/4" Blade

Q9. Item #45 - Soup pot, 11qt: I presume this is a stock pot and not for service? If so, do you require aluminum or stainless steel? Also, do you require lids?

A9. No this pot is for service and will need to fit inside a soup warmer kettle. Stainless steel is required. No lids are required but will be acceptable if they are included in the set.

Q10. Item #81 - Mixing bowl, 24 qt

24 quart does not appear to be an available size in mixing bowls - the sizes jump from 20 quart to 30 quart. If your kitchen currently has a 24 quart bowl, are they able to provide a make and model number?

A10. If 24 Qt is not available then a 30 qt is acceptable

Q11. Item #156 - Shakers (complete with lids) cheese, 10 oz

Are these polycarbonate? If so, how are they different from item #157? Just the cheese-specific lid that it comes with?

A11. #156 is the glass shaker with the Stainless steel lid

#157 is the polycarbonate for use in the kitchen area (these are two different requirements)

Q12. Item #133 - Measuring jug, 4 quart

Is this aluminum, stainless steel or polycarbonate? If polycarbonate, how does it differ from Item #176

A12. #133 is a Stainless steel measuring jug 4 qt

Q13. For all Cambro polycarbonate products (food storage containers, hotel pans, etc.), are there colour specifications, or are all items clear plastic (Cambro colour code #135)?

Solicitation No. - N° de l'invitation
W0113-13L029/A
Client Ref. No. - N° de réf. du client
W113-13-L029

Amd. No. - N° de la modif.
006
File No. - N° du dossier
KIN-3-40138

Buyer ID - Id de l'acheteur
kin650
CCC No./N° CCC - FMS No/ N° VME

- A13.** #135 colour code is required for all Cambro (no substitute) polycarbonate products.
- Q14.** For Item #200, tulip cups, 5 oz - are you looking for disposable or regular? Also, will you require lids?
- A14.** The client requires regular cups with no lids.

DELETIONS & INSERTIONS

#1. Under: ANNEX "A" – Requirement

Within: Item #219 - Storage (Dunnage) Rack

Configuration

The unit must have:

Delete: Dimensions of 304mm x 533mm x 1524mm (12" L x 21" D x 60" H)

Insert: Dimensions of 1524mm high x 533mm wide x 304mm deep (60" high x 21" wide x 12" deep)

#2. Under: ANNEX B-2 - Canadian Forces Support Training Group, MLS Supply, 247 Cambrai Road (bldng 0-111)

DELETE ITEM #8:

<u>8</u>	Cleantech ELF 400 Series (or equivalent)	Wall mounted, Dimension: 20"L x 21" wide x 33" High Automatic via infrared photo-optical sensor 0.6 gallons at a 10-second cycle water consumption 100-250 VAC 50/60Hz. 300 watts 3/4" male garden hose, minimum 4 GPM, 40-100 PSI, hot and cold lines
----------	--	--