


BECLAWAT



72172 - Fixed Steel Weld-In Watertight Window



This heavy marine all weld-in mild steel or stainless steel fixed watertight window is available in custom shapes and sizes. The steel window frame is usually sandblasted and weld-able primer to suit most specifications. The stainless is either 304 or 316 grade.

It will suit a glass thickness of 10mm or thicker.

ABS type approved.

Pictured window has radius corners naval brass retaining rings. Unless otherwise required 304 stainless retaining rings are standard.

Glass is clear laminated. Other tinted and various glass thickness options are available.

Heated glass can be adapted to this type of frame.

For more information
Call: 613-966-5611

Email:
info@beclawat.com



BECLAWAT Manufacturing Inc.
90 Hanna Crt. Belleville, ON K8P 5H2 Canada
Ph: 613-966-5611 Fx: 613-966-0878 www.beclawat.com

