



TEST REPORT

In charge

Checked

Approved



MODEL

SERIAL No

DATE

HIAB201-2

S201000034

2009. 6. 30.

1. SPECIFICATION

Crane weight $\rightarrow 2520 \text{ kg}$
Height in folded position $\rightarrow 2.8 \text{ m}$
Width in folded position $\rightarrow 2.55 \text{ m}$

DESCRIPTION		SPECIFICATION	REMARKS
SAFETY WORKING LOAD		8.3 m x 2,160 kg	
MAX. WORKING RADIUS		8.3 m	
BOOM LUFFING RANGE		-58° ~ 80°	
HOIST	LOAD	-	
	SPEED	-	
	HEIGHT	-	
SWING	RANGE	400° LIMITED	
	SLOPE	5° HEEL & 2° TRIM	
	SPEED	7.2 deg/sec	
WORKING PRESSURE		25 MPa	
WORKING OIL FLOW		40 L/min	
WIRE ROPE		-	
ELEC. SOURCE	POWER	-	
	CONTROL	-	
ELEC. MOTOR	POWER	-	
	POLES	-	
	SPEED	-	