



CANADIAN MUSEUM FOR
HUMAN RIGHTS
MUSÉE CANADIEN POUR LES
DROITS DE LA PERSONNE

Demande de propositions

Services de fonctionnement et d'entretien du système audiovisuel du Musée

Numéro de la demande de soumissions :	MCDP 2014-71
Date de la demande de soumissions :	29 mai 2014
Date limite de question :	6 juin 2014 – 14 h (HAC)
Date et heure de clôture :	18 juin 2014 – 14 h (HAC)
Date d'attribution prévue :	juillet 2012

Addenda # 1
2 juin, 2014

Appendix H modifié

APPENDIX H – Équipement AVS à être couvert par les services

Accell	17
J129B-003B - HDMI to VGA adapter	17
Acoustic Enhancements	65
ASP-CUST1 - Custom Activated Sound drivers attached internally to the side walls of the Table	24
ASP-CUST2 - In Wall "Invisible" Speaker	18
ASP-CUST3 - Field installed Stereo Activated Sound Panel behind acoustically transparent material.	1
ASP-SW1 - Stereo activated Sound Panel (36" x 48")	8
ASP-W1 - Stereo activated Sound Panel (21" x 32")	9
ASP-W2 - Activated Sound Panel - 36"x48"	5
Adtec	5
SignEdge - Video Server	1
SignEdge - Video Server	4
Apple	122
iPad 4 - 10" tablet	6
Mac Mini - Mac Mini w/ 2 x 1TB Serial ATA HDD, 8GB RAM	2
Mac Mini - Playback PC	34
Mac Mini - Small Form Factor PC	31
Mac Mini Server - Mac Mini w/ 2 x 1TB Serial ATA HDD, 8GB RAM	4
Mac Pro Tower - Mac Pro Tower w/ 2 x 1TB HDD, ATI Radeon HD 5770 1GB - 1 Output	9
Mac Pro Tower - Mac Pro Tower w/ 2 x 1TB HDD, ATI Radeon HD 5770 1GB - 2 Outputs	6
Mac Pro Tower - Mac Pro Tower w/ 2 x 1TB HDD, ATI Radeon HD 5770 1GB - 3 Output	1
Mac Pro Tower - Mac Pro Tower w/ 2 x 1TB HDD, ATI Radeon HD 5770 1GB - 3 Outputs	1
Mac Pro Tower - Mac Pro Tower w/ 2 x 1TB HDD, ATI Radeon HD 5770 1GB - 4 Output	1
Mac Tower - Mac Pro Tower w/ 2 x 1TB HDD, ATI Radeon HD 5770 1GB - 2 Outputs	1
MB571Z/A - Mini Display port to DVI adapters	23
MB571Z/B - Mini Display port to DVI adapters	3
Asus	5
Xtion PRO LIVE - Game motion tracker	5
Atlona	64
AT-HDRX-RSNET - HDMI/Serial Signal Extender over CAT5/6/7 Receiver	32
AT-HDTX-RSNET - HDMI/Serial Signal Extender over CAT5/6/7 Transmitter	32
Bag End	5
IPS10E-SHV3 - 10" Powered Subwoofer with Integrated Infra Processor	2
IPS12E-I - InfraSub Loudspeaker Powered with Integrated Infra Processor	3
Barco	64
CNWU-61B - 6000 lm, 1 chip DLP projector (WUXGA 1920 x 1200)	22
CNWU-61B - 6000 lm, 1 Chip DLP Projector (WUXGA 1920 x 1200) - under review	1
EN11 - 1.60:1 to 2.32:1 lens	4
EN13 - 1.24 - 1.6:1 lens	1
EN13 - 1.24 - 1.60:1 lens	2
EN13 - 1.24 to 1.6:1 lens	1

EN13 - 1.24:1 to 1.60:1 lens	4
EN13 - 1.24-1.6:1 lens	7
EN14 - 2.37 - 3.79 :1 Lens	1
EN16 - 3.80:1 to 6.50:1 lens	2
EN46 - 0.75:1 to 1.13:1 lens	1
HDX-W14 - 14,000 lumens, WUXGA DLP projector	2
HDX-W20 - 20,000 lumens, WUXGA, 3-chip DLP projector (1920 x 1200)	3
RLDW 0.77:1 - 0.77:1 fixed lens	4
RLM-W8 - 8,000 Lumen, WUXGA, 3 Chip Projector	4
TDL 1.2:1 - Lens 1.2:1	2
TLD 0.73:1 - 0.73:1 fixed lens	3
Behringer	62
Uphoria - USB to analog audio	61
Uphoria - USB to analog audio (is experience audio free?)	1
Beyer Dynamic	1
M59 - Hypercardiod Dynamic Microphone	1
BiAmp	249
AUDIA EXPI - CobraNet to 8 analog line inputs, 1RU	2
Audia EXPI - DSP Cobranet 8 input	2
Audia EXPI/0-2 - DSP Cobranet I/O - 2 in, 2 out - with power supply	59
Audia EXPI/0-2 - DSP Cobranet I/O - 2 in, 2 out - with power supply - Sound Masking	6
AUDIA EXPO - CobraNet to 8 analog line outputs, 1RU	4
AUDIAFLEX-CM - DSP Chassis	15
EXPI-4 - DSP CobraNet 4 input	3
IP-2 - Input Card	3
IP-2 - 2 Channel Input Card	14
IP-2 - Input cards	5
OP-2e - 2 Channel Output Card	69
OP-2e - 2 Channel Output Card	7
OP-2e - 2-Channel output card	29
OP-2e - Output card, 2-channel	31
Brainstorm	2
SR-28 - LTC Distribution Amplifier	2
Brightsign	4
XD230 - Digital Signage Player w/ WiFi	4
Brown Innovations	53
MF-CT-24 - 24"x24" Focused Array Loudspeaker suspended from ceiling.	12
Sonic Beam 40 / MA - 40" Powered Mini Line Array Speaker	2
Sonic Beam 40/ MA - 40" Powered Mini Line Array Speaker	2
SonicBeam 24/ MA - 24" Powered Mini Array Speaker	2
SonicBeam 24/MA - 24" Powered Mini Array Speaker	19
SonicBeam 30/MA - 30" Powered Mini Array Speaker	14
SonicBeam 40 / MA - 40" Powered Mini Line Array Speaker	2

BSI	2
PMS5120N - 10.4" Panel PC for Language and ADA Select	1
PMS5120N - 10.4" Panel PC for museum control	1
Chief	52
FSRV - Mount	3
LSAU - Wall Mount	3
MTMPU - Mount	9
RPA091 - Ceiling Mount	13
RPA091 - Ceiling Mount (Barco)	1
RPA091 - Mount	2
RPAA1 - Ceiling Mount	1
RPMA1 - Ceiling Mount	4
RPMA1 - Ceiling Mount (Viewsonic)	1
VCM100B - Projector Mount	2
VCM35B - Ceiling Mount	7
VCMU - Ceiling Mount	4
XSMU - Wall mount	2
Cisco	1
3750 - Ethernet switch	1
Custom	140
Custom - Mirror mounting frame	1
Custom - UKP Type A (USB and audio)	9
Custom - UKP Type B (audio only)	22
Custom - UKP Type A	1
Custom - UKP Type A (USB and audio)	39
Custom - UKP Type B (audio only)	32
Custom - UKP Type B (audio)	26
TBD - Speaker Bracket	10
Dataton	4
3150 - WATCHOUT v5.5.1 License	1
Watchout V5 - Watchout Software Key	3
ELO	68
3243L - 32" Touch display with IntelliTouch USB interface	1
3243L - 32" Touch Monitor	3
4201L / E561836 - 42" Touch Monitor	6
E005277 - Power supply, 12V, 4.16A, 50W	27
E178661 - 2400LM - 24" Touch Screen Monitor (1920x1200) w/Serial Interface	4
E220828 - 2740L - 27" Touch screen monitor, USB, Intellitouch Plus	27
EloTouch	34
1247L / E655204 - 12" Touchscreen	2
1537L / E512043 - Touchscreen, 15", open frame	15
E005277 - Power supply, 12V, 50W	17

Enttec	1
DMX USB PRO - USB to DMX Interface	1
Extron	12
DTP HDMI 230 D TX - HDMI video of CAT6 Transmitter - Presentation Input Panel	6
DTP HDMI 230 RX - HDMI video of CAT6 Receiver	6
Gefen	3
GTV-AUDDEC - Digital Audio Decoder for HDMI	3
Icron	9
Ranger 2201 - USB Extender	5
RG2201 - USB Dual Port Cat 5e 100 meter extender	4
Innovox	50
SHA-15.4.4 - Display/bench speaker - 15"Wx4"Hx4"D	3
SHA-15.4.4 - Display/bench speaker - 15"Wx4"Hx4"D -need ability to set tilt angle with gimble bracket attachment.	20
SHA-15.4.4 - Linear Speaker - 15"Wx4"Hx4"D	8
SHA-15.4.4 - Low profile ceiling speaker - 15"Wx4"Hx4"D -need ability to set tilt angle with gimble bracket.	16
SHA-15.4.4 - Monitor speaker - 15"Wx4"Hx4"D -need ability to set tilt angle with custom floor bracket	3
James	10
650PTM - Subwoofer, pipe	8
QX1020 - Dual 10" In Wall Subwoofer	2
JoeCo	2
BBP1-B - 24 Track Audio Player with Time Code Follow and Balanced in/out	2
Lite Panel	7
900-3017 - 1x1 Honeycomb Grid - 30 Degree	2
900-3021 - 1x1 4-Way Barndoors	2
903-0006 - DMX Adaptor Cable	1
903-2076 - 1'x1' LED Light Panel Bi-Focus	2
Logitech	2
C920 (USB) - HD Web Camera	2
Microsoft	4
Kinect 360 (original) - Game motion tracker	4
MoTu	2
24I/O - Computer Recording System PCI	1
MAPCIE424 - PCIe-424 Card - Card for PCI Express Core System	1
MTS	34
BB-200 - Microwave Proximity Sensor	28
BB-200 - Motion Sensor	6
Multitouch	13
MT553UTB - 55" Touchscreen with Ultrathin Bezel	12
MTPCLA12 - Multitouch Application PC for 12 Displays	1
NEC	9
AS241W-BK - 24" Monitor, 1920x1080	5

LCD-175M-BK - 17" Monitor	4
On Stage Stands	1
MSA9030-13C - Gooseneck mount - 13"	1
Panasonic	8
ET-D75LE10 - 1.4 - 1.8:1 lens	1
ET-D75LE6 - 1.0 - 1.2:1 lens	3
PTDS20KU - 20,000 lumen 1400 x 1050 video projector	4
Peerless	2
SF632 - Mount	1
SF632P - Mount	1
QSC	28
CX-168 - 8 channel amplifier, 90W/ch.	4
CX-168 - 8 Channel Power Amplifier - 90W/Channel	1
CX168 - 8 channel, 90W/ch amplifier	1
CX-168 - 8 channel, 90W/ch amplifier	4.5
CX-168 - 8-channel amplifier, 90W/ch	6
CX-168 - 8-channel amplifier, 90W/channel	10
CX-168 - Amplifier, 8-channel	1.5
RDL	9
STD-10k - Audio combiner	9
Renkus Heinz	31
CFX81 - 2-Way 8" Speaker: 120 x 60 Deg	7
CFX81 - Main Speakers, non-powered	4
IC215S-FR - Dual 15" Powered Subwoofers	2
IC7 - Powered Line Array Speaker	4
ICL-FR DUAL - Active, Steerable Line Array Speaker	2
ICX7 - Compact Line Array Speaker, Non-Powered	2
PNX112 - 12" non-powered subwoofer	2
TBD - Mounting Hardware	2
TBD - Wall Mounting Bcket	4
TRX82/12 - Main Speakers, non-powered	2
Samsung	23
MD65C - 65" LCD Display 1920 x 1080	3
ME32C - 32" display	1
ME32C - 32" LCD monitor (Digital Signage)	4
ME46C - 46" LCD Display	2
ME55C - 55" display	1
ME55C - 55" LCD Display	8
ME75C - 75" LCD Display	2
UD46C - Ultra- Thin Mullion 46" LCD Display	2
Showsage	5
Model 6444 - Quad Output Server - Extreme	5

Sonus	3
HP4 - Headphone amplifier with 4 outputs	3
Soundtube	1
SA502 - Class D Power Amplifier - 50 Watts @ 8 Ohm per Channel	1
Storm	3
1200-00200[x] - USB Cable kit	1
2210 - Vandal Resistant Keyboard	1
2210-MK000[x] - Under Panel Fixing Kit (place holder)	1
SuperLooper	1
Gigabit Crossover Adapter - Patch cable to Crossover converter	1
Synnaccess	1
NP-16A30S or NPB-20A30 - PDU for automatically turning on/off equipment	1
Tangband	15
W3-881SJF - Small F/X speakers embedded in table with grille cover	15
Tannoy	37
Di5DC - 4.5" All Weather Wall Mount speaker (Black)	2
Di5DC - Di5 - 5" speaker (Black), non-powered	6
Di5DC - Di5 - 5" speaker (White), non-powered	6
Di5DC - Di5 - 5" non-powered speaker (Black)	9
Di5DC - On wall loudspeaker (Black)	2
Di6DC - 6" non-powered speaker (Black)	8
Di6DC - Speaker - suspended overhead (White)	4
TBD	9
Motion Sensor - Motion Sensor - TBD. May be Kinect	1
TBD - camera for monitoring	4
TBD - Wireless microphone and receiver	4
Unibrain	1
CAT5 Repeater-400 - Firewire Repeater / Extender (TBD - depends on Motion Sensor spec)	1
Viewsonic	6
PJD8633WS - 3000 lm ultra short throw projector, 1280 x 800	5
PJD8633WS - 3000 lm, Ultra short throw DLP projector, 1280 x 800	1