

**RETURN BIDS TO:**  
**RETOURNER LES SOUMISSIONS À:**  
**Bid Receiving - PWGSC / Réception des soumissions**  
**- TPSGC**  
**11 Laurier St./ 11, rue Laurier**  
**Place du Portage, Phase III**  
**Core 0A1 / Noyau 0A1**  
**Gatineau, Québec K1A 0S5**  
**Bid Fax: (819) 997-9776**

**SOLICITATION AMENDMENT**  
**MODIFICATION DE L'INVITATION**

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

**Comments - Commentaires**

**Vendor/Firm Name and Address**  
**Raison sociale et adresse du**  
**fournisseur/de l'entrepreneur**

**Issuing Office - Bureau de distribution**  
**Clothing and Textiles Division / Division des**  
**vêtements et des textiles**  
**11 Laurier St./ 11, rue Laurier**  
**6B1, Place du Portage**  
**Gatineau, Québec K1A 0S5**

<b>Title - Sujet</b> Snow Mantra Parka or equivalent	
<b>Solicitation No. - N° de l'invitation</b> T8518-130107/A	<b>Amendment No. - N° modif.</b> 001
<b>Client Reference No. - N° de référence du client</b> T8518-130107	<b>Date</b> 2014-06-25
<b>GETS Reference No. - N° de référence de SEAG</b> PW-\$\$PR-723-65286	
<b>File No. - N° de dossier</b> pr723.T8518-130107	<b>CCC No./N° CCC - FMS No./N° VME</b>
<b>Solicitation Closes - L'invitation prend fin</b> <b>at - à 02:00 PM</b> <b>on - le 2014-07-30</b>	<b>Time Zone</b> <b>Fuseau horaire</b> Eastern Daylight Saving Time EDT
<b>F.O.B. - F.A.B.</b> Specified Herein - Précisé dans les présentes <b>Plant-Usine:</b> <input type="checkbox"/> <b>Destination:</b> <input type="checkbox"/> <b>Other-Autre:</b> <input checked="" type="checkbox"/>	
<b>Address Enquiries to: - Adresser toutes questions à:</b> Gravel, Sylvie	<b>Buyer Id - Id de l'acheteur</b> pr723
<b>Telephone No. - N° de téléphone</b> (819) 956-3832 ( )	<b>FAX No. - N° de FAX</b> (819) 956-5454
<b>Destination - of Goods, Services, and Construction:</b> <b>Destination - des biens, services et construction:</b>	

**Instructions: See Herein**

**Instructions: Voir aux présentes**

<b>Delivery Required - Livraison exigée</b>	<b>Delivery Offered - Livraison proposée</b>
<b>Vendor/Firm Name and Address</b> <b>Raison sociale et adresse du fournisseur/de l'entrepreneur</b>	
<b>Telephone No. - N° de téléphone</b> <b>Facsimile No. - N° de télécopieur</b>	
<b>Name and title of person authorized to sign on behalf of Vendor/Firm</b> <b>(type or print)</b> <b>Nom et titre de la personne autorisée à signer au nom du fournisseur/</b> <b>de l'entrepreneur (taper ou écrire en caractères d'imprimerie)</b>	
<b>Signature</b>	<b>Date</b>

Solicitation No. - N° de l'invitation

T8518-130107/A

Amd. No. - N° de la modif.

001

Buyer ID - Id de l'acheteur

pr723

Client Ref. No. - N° de réf. du client

T8518-130107

File No. - N° du dossier

pr723T8518-130107

CCC No./N° CCC - FMS No/ N° VME

---

## **SNOW MANTRA PARKA OR EQUIVALENT**

Solicitation Amendment No. 001 is raised to provide Annex B (technical specification for the winter parka) which was omitted from the RFP.

All other terms and conditions remain the same.

A bid already submitted may be amended prior to RFP closing time by sending the amended correspondence to Bid Receiving Unit, the envelope/message bearing the PWGSC file number and the most current closing date.

## TECHNICAL SPECIFICATIONS

### Transport Canada Inspector's Winter Parka

#### PURPOSE:

To provide Transport Canada Inspectors with Winter Parkas as defined below. Men's sizing X-Small to 3-XLarge.

#### GENERAL DESIGN:

The Winter Parkas must be dark navy blue colour and made of durable water resistant material. The parkas must have goose down filling, a cold weather rating of -30° to -50° and must be warm and dry in extreme conditions.

#### Design Details:

##### Hood:

- Hood with a removable coyote fur ruff around a 3-way adjustable tunnel hood.
- Hood must have an adjustable (removable) bracing wire to reduce the wind penetration by allowing the user to adjust the opening size as conditions dictate.

##### Storm Flap:

- Storm flap over a heavy-duty two way locking front slide fastener.

##### Pockets:

##### Chest Pockets:

- Bellowed chest pockets with pocket flaps with hook and loop closure.  
Pocket – width 5-1/2" (minimum)  
Pocket Flap – width 5-1/2" (minimum), depth 2-1/2" (minimum)

##### Bottom Front Pockets:

- Bellowed bottom front pockets with pocket flaps on left and right front of parka.

##### Utility Pocket – Sleeve:

- Utility pocket on left sleeve with slide fastener closure (on side of pocket closest to chest).

Snow Belt (Draft Baffle):

- Snow belt (with elasticized casing on bottom edge) stitched to inside lining of jacket.
- Center front closure with Hook & Loop.

Reinforced Elbows:

- Sleeves must have double- reinforced elbows for durability.

Recessed Cuffs:

- Recessed folded rib-knit cuffs are required.

Inside Yoke Flap Cover:

- Inside yoke flap cover (throat latch) lined with fleece.

Grab straps:

- Grab straps on shoulders and upper center back for easy lifting and rescue access.

Tab with D-Ring:

- Tab with D-Ring to be inserted in to bottom of left or right front chest pocket.

Sizing:

- Men's Sizing - Sizes XSmall, Small, Medium, Large, XLarge, 2XLarge & 3XLarge.
- Center back length (size Large) – minimum 38-1/2"

Materials:

Outer Shell:

- The outer shell must be made from plain weave, fabric treated with water repellent fabric protector – 85 % Polyester / 15% Cotton - (tolerance +/-5%)
- Colour – Dark Navy Blue.

Fur Ruff:

- Coyote fur ruff surrounding hood. Coyote fur is required because it never freezes, does not hold water and the uneven hair lengths create a windbreak.

Lining (parka lining, snow belt and pocket lining):

- The lining must be plain weave fabric – 100% nylon – colour to match the outer shell.

Interlining:

- The interlining must be plain weave 'down proof' fabric - 100% nylon.

Fleece Lining:

- 100% Polyester Fleece lining for inside yoke flap cover.

Inner Knit Cuffs:

- 1 x 1 ribbing for knit cuffs. Colour – Black or colour to match shell fabric.

Fur Ruff:

- Removable Coyote fur ruff surrounding hood. Coyote fur is required because it never freezes, does not hold water and the uneven hair lengths create a windbreak.

Fill – Insulation Material:

- The jacket fill must be White Goose Down - minimum 675 fill power.

Grab Straps:

- Twill Nylon tape for grab straps on shoulders and top center back - Black or colour to match shell fabric.
- Width of tape - minimum 1-1/2"

Straps for Hood adjustment and D-Ring (chest pocket):

- Twill Nylon tape for hood adjustment and tab for D-Ring (chest pocket) – 1" wide - Black or colour to match shell fabric.

Slide Fasteners:

Center Front closure and Side Seams:

- Heavy duty slide fasteners for center front closure and side seams (from waist to hem) - open ended, 2 way separating fasteners, Black or colour to match shell fabric.
- The automatic sliders will be injection molded
- Metal slide fastener pulls.
- Nylon ribbon pulls to be applied to the sliders.

Sleeve Utility Pocket closure and Hood (for removable of fur ruff):

- Slide fasteners for sleeve utility pocket closure and hood - 1 way separating fasteners, Black or colour to match shell fabric.
- Metal slide fastener pulls.

Draw-Cord:

- For waist (Front & Back casing) and hood (adjustment): braided spun synthetic staple fibre (polyester or nylon) - Black or colour to match shell fabric.

Toggles (Cord Stoppers):

- Two (2), spring loaded – Black or colour to match shell fabric - for each single draw-cord.

Eyelets:

- For draw-cords - brass, Black or colour to match shell fabric.

Snap Fasteners:

- Snap fasteners for hood (fastener for fur ruff) – brass, spring loaded, Black or colour to match shell fabric.

D-Ring:

- One (1) metal D-Ring – 1" diameter - to be inserted on nylon tape tab on bottom front chest pocket.

Hook & Loop Tape:

- Hook & loop tape required for closure on Chest and Lower Front Pockets (pocket flaps and pocket), Center Front Storm Flap closures (storm flap and center front) and Snow Belt (closure on tab).
- Woven nylon hook and loop tape, Black or colour to match shell fabric.

**Labelling:**

Each jacket (outer shell and fleece liner) shall be permanently identified with a bilingual label indicating:

1. Size designation
2. Fiber content of shell, lining and interlining.
3. Care instructions —



Remove fur

Dry-clean, normal cycle, any solvent except trichloroethylene

Do not wash

Do not bleach

Do not tumble dry

Do not iron or press

4. Contract serial number.

**Packaging:**

Jackets shall be packaged separately in an unsealed plastic bag or plastic wrapping.

