

**RETURN BIDS TO:**  
**RETOURNER LES SOUMISSIONS À:**  
 Bid Receiving Public Works and Government  
 Services Canada/Réception des soumissions Travaux  
 publics et Services gouvernementaux Canada  
 800 Burrard Street, Room 219  
 800, rue Burrard, pièce 219  
 Vancouver, BC V6Z 0B9  
 Bid Fax: (604) 775-7526

**Revision to a Request for a Standing Offer**

**Révision à une demande d'offre à commandes**

Regional Individual Standing Offer (RISO)

Offre à commandes individuelle régionale (OCIR)

The referenced document is hereby revised; unless  
 otherwise indicated, all other terms and conditions of the  
 Offer remain the same.

Ce document est par la présente révisé; sauf indication  
 contraire, les modalités de l'offre demeurent les mêmes.

**Comments - Commentaires**

**Vendor/Firm Name and Address**

Raison sociale et adresse du  
 fournisseur/de l'entrepreneur

**Issuing Office - Bureau de distribution**

Public Works and Government Services Canada -  
 Pacific Region  
 219 - 800 Burrard Street  
 800, rue Burrard, pièce 219  
 Vancouver, BC V6Z 0B9

<b>Title - Sujet</b> 100% Cotton Leno Weave Fabric		
<b>Solicitation No. - N° de l'invitation</b> 21C81-140101/A		<b>Date</b> 2014-08-15
<b>Client Reference No. - N° de référence du client</b> 21C81-140101		<b>Amendment No. - N° modif.</b> 001
<b>File No. - N° de dossier</b> VAN-4-37060 (524)	<b>CCC No./N° CCC - FMS No./N° VME</b>	
<b>GETS Reference No. - N° de référence de SEAG</b> PW-\$VAN-524-7281		
<b>Date of Original Request for Standing Offer</b> Date de la demande de l'offre à commandes originale		2014-07-17
<b>Solicitation Closes - L'invitation prend fin</b> <b>at - à 02:00 PM</b> <b>on - le 2014-09-02</b>		<b>Time Zone</b> <b>Fuseau horaire</b> Pacific Daylight Saving Time PDT
<b>Address Enquiries to: - Adresser toutes questions à:</b> Yamamoto, Albert		<b>Buyer Id - Id de l'acheteur</b> van524
<b>Telephone No. - N° de téléphone</b> (604) 775-7549 ( )	<b>FAX No. - N° de FAX</b> (604) 775-7526	
<b>Delivery Required - Livraison exigée</b>		
<b>Destination - of Goods, Services, and Construction:</b> <b>Destination - des biens, services et construction:</b>		
<b>Security - Sécurité</b> This revision does not change the security requirements of the Offer. Cette révision ne change pas les besoins en matière de sécurité de la présente offre.		

Instructions: See Herein

Instructions: Voir aux présentes

<b>Acknowledgement copy required</b> <b>Accusé de réception requis</b>	<b>Yes - Oui</b> <input type="checkbox"/>	<b>No - Non</b> <input type="checkbox"/>
<b>The Offeror hereby acknowledges this revision to its Offer.</b> <b>Le proposant constate, par la présente, cette révision à son offre.</b>		
<b>Signature</b>	<b>Date</b>	
Name and title of person authorized to sign on behalf of offeror. (type or print) Nom et titre de la personne autorisée à signer au nom du proposant. (taper ou écrire en caractères d'imprimerie)		
<b>For the Minister - Pour le Ministre</b>		

---

## PART 2 - OFFEROR INSTRUCTIONS

### M0280T (2007-05-25) Document Required for Offers Evaluation Purposes CAN/CGSB 4.1 Textile Test Methods:

Delete:

2. Colourfastness to laundering, 19.1-M minimum acceptable grade on Gray scale is 3 or higher.

Insert:

2. Colourfastness to laundering, 19.1.2.2 (R2013) minimum acceptable grade on Gray scale is 3 +.

### Samples Required for Offers Evaluation Purposes

Insert:

Bidders may also provide samples in another colour, but samples must be as specified in the bidding requirements and must meet all of the requirements specified in Annex A.

If samples are provided in a different colour, a pre-production sample in the specified colour (Classic blue -Pantone colour No. 19-4052 TP) will be required from the successful bidder for prior approval on call-ups.

### Annex B - Basis of Payment

Insert:

All pricing must be FOB destination (3 locations):

Ferndale Institution  
33737 Dewdney Trunk Rd.,  
Mission, British Columbia, Canada V2V 4L8

Matsqui Institution  
33344 King Rd,  
Abbotsford, British Columbia,  
Canada V2S 4P3

Mountain Institution  
4732 Cemetery Rd., Agassiz, British Columbia  
Canada V0M 1A0

Solicitation No. - N° de l'invitation

21C81-140101/A

Client Ref. No. - N° de réf. du client

21C81-140101

Amd. No. - N° de la modif.

001

File No. - N° du dossier

VAN-4-37060

Buyer ID - Id de l'acheteur

van524

CCC No./N° CCC - FMS No/ N° VME

---

## **Annex A - Requirement**

Delete Annex A in its entirety

Insert Annex A attached.

## **ANNEX A REQUIREMENT (2014/05/29)**

Requirement: To supply and deliver 100% Cotton Leno Weave Fabric to Correctional Service Canada at Mission, Agassiz and Abbotsford, British Columbia on an as-and-when requested basis, in accordance with the specifications below.

Estimated usage 40,000 metres per year

Fabric will be supplied in 50 metre rolls, individually wrapped in plastic. Each roll must not exceed 30Kg.

Minimum quantity per call-up is 10,000 metres

Period of standing offer: 2 years

Delivery required: Within **sixty (60) calendar days** of receipt of a call-up against the standing offer.

Product must meet the following specifications:

CAN/CGSB-4.2-M: Textile Test Methods:

No. 5.1-M: Mass of Fabrics

No. 6-M: Woven Fabric Count

No. 18.3-M: Textiles – Test for colourfastness PART B02:

Colourfastness to artificial light: XENON ARC FADE LAMP TEST

*No. 19.1.2.2 Test # 2 (R2013): Colourfastness to washing*

No. 22-M Colourfastness to Crocking, Dry & Wet (Water)

Fibre: 100% cotton, tolerance -5% other fibre/fibres can be added.

Yarn Number (Size of Yarn): 105-130 tex (5.4 - 4.75's Cotton count), 2-ply carded cotton in warp and weft.

Weave: Leno weave (body). Plain weave 1 x 1 (stabilizing bars)

Yarn Count for Leno Weave: Warp 33/10cm (Greige stage), Weft 35/10cm (Griege stage)

Finish: Pre-Shrunk

Note: Pre-shrinking process must be applied prior to determining the results of the following properties including CAN/CGSB 4.1 Textile Test Methods

Mass: 285 g/m2 – (minus) 10% tolerance.

Colour: Classic Blue. The colour must be in accordance with Pantone colour No. 19-4052TP\* TP-Textiles. Fabric can be piece dyed or yarn dyed.

**Pantone Color Selector 1000 and/or Pantone  
Textile Color Guide (TCX)**

The above color reference is available from:

Pantone Customer Service in Canada  
Keng Seng Enterprises  
4030 rue St. Ambroise, Suite 227  
Montreal, Quebec H4C 2C7  
Tel: (514) 939-3971

Size of fabric: 180 cm width +/- 5%

Stabilizing Bars: The following options are acceptable:

Each end must be 12 cm wide (max 18 cm) & one in centre 5 cm (max 10 cm), OR  
One in centre 12 – 15 cm wide, OR all three max 12 cm (one centre + 2 ends)