



RETURN BIDS TO:

RETOURNER LES SOUMISSIONS À:

Parks Canada Agency
P.O. Box 220
Mckay Compound, Stores Building
6300 Highway 93S
Radium, BC V0A 1M0

SOLICITATION AMENDMENT

MODIFICATION DE L'INVITATION

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same

Ce document est par la présente revise; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

Comments - Commentaries

Vendor/Firm Name and Address

Raison sociale et adresse du fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution

Parks Canada Agency
Lake Louise, Yoho, Kootenay Field Unit
P.O. Box 220
Radium, BC V0A 1M0

Title-Sujet FOURNITURE ET INSTALLATION DE FENÊTRES DANS LES LOGEMENTS 1 À 38 DU 202 SADDLEBACK CRESCENT, À LAKE LOUISE		Date 03 octobre, 2014
Solicitation No. - No. de l'invitation 5P424-14-0229/A	Amendment No. - No modif. 003	
GETS Reference No. - No de reference de SEAG N/A		
Solicitation Closes L'invitation prend fin - at - à 02:00 PM on - le 07 octobre, 2014	Time Zone Fuseau horaire - (HAR)	
F.O.B. - F.A.B.		
Address Inquiries to: - Adresser toute demande de renseignements à :		
Eloise Meredith		eloise.meredith@pc.gc.ca
Telephone No. - No de téléphone (250) 347-6622	Fax No. - No de FAX: (250) 347-6621	
Destination of Goods, Services, and Construction: Destinations des biens, services et construction: Unité de gestion de Lake Louise, Yoho et Kootenay, Colombie-Britannique 202 SADDLEBACK CRESCENT, À LAKE LOUISE		
Vendor/Firm Name and Address Raison sociale et adresse du fournisseur/de l'entrepreneur		
Name and title of person authorized to sign on behalf of the Vendor/Firm Nom et titre de la personne autorisée a signer au nom du fournisseur/ de l'entrepreneur		
Signature	Date	

L`appel d`offers est amendé pour corriger les stipulations.

Enlever

2.02 MATERIALS

Glass Units:

All glass units shall be;

Sealed Insulating Glass:

Insulating glass units: Factory Sealed Double Glazed Units: To CAN2-12.8-M76

All glass units to be factory sealed units double pane, with Low E coating and Argon gas.

Inner and outer pane of ¼” Glass, ½” air space.

Must be at or exceeds CSA A440-00 Standard:

Air Infiltration : A3

Water Penetration: B3

Wind Load: C4

PVC Windows:

Frame: PVC Profiles;

Sash: PVC Profiles

Screen: Fiberglass wire mesh on a Aluminum Frame

Opening Devices: Sliders and awnings as per Manufactures Standards

Including: End Strips, Chairs, Anchors, Splice, locking latch

Color: Beige

New windows to be nail-in flange style with no brickmould

Exterior caulking, exterior commercial grade, color to match exterior color

Interior caulking, interior commercial grade, conceal sealant within units.

PVC Patio Doors:

Materials: to CAN/CGSB – 82.1 supplemented as follows:

Silding doors by same manufacturer of windows

Panel Sash: vinyl, thermally broken,

Main Frame: vinyl,

Screen: Fiberglass wire mesh on a Aluminum Frame

Opening Devices: as per Manufactures Standards

Including: End Strips, Chairs, Anchors, Splice, locking latch

Color: Beige

Exterior caulking, exterior commercial grade, color to match exterior color.

Exterior trim to match existing trim

Interior caulking, interior commercial grade, conceal sealant within units.

2.03 EXECUTION

1. Install windows to CSA A440.4 “Window Installation Guidelines”
2. Install patio doors and frames in accordance with CAN/CGSB 82.1- M89, “Sliding Doors”
3. Vinyl frames will have a 25 year warranty against fading, discoloring, warping and cracking.
4. Sealed units will have a minimum 5 year warranty against failure.
5. Setting spacer blocks, Neoprene, Block size to suit glass
6. Supply and install primed and painted (grey) 1x4 and 2x6 cedar casing to match existing design around windows and doors

Remplacer par

2.02 MATERIALS

Glass Units:

All glass units shall be;

Sealed Insulating Glass:

Insulating glass units: Factory Sealed Double Glazed Units: To CAN2-12.8-M76

All glass units to be factory sealed units double pane, with Low E coating and Argon gas.

Inner and outer pane of 1/4" Glass, 1/2" air space.

Must be at or exceeds CSA A440-00 Standard:

Air Infiltration : A3

Water Penetration: B3

Wind Load: C3

PVC Windows:

Frame: PVC Profiles;

Sash: PVC Profiles

Screen: Fiberglass wire mesh on a Aluminum Frame

Opening Devices: Sliders and awnings as per Manufactures Standards

Including: End Strips, Chairs, Anchors, Splice, locking latch

Color: Beige

New windows to be nail-in flange style with no brickmould

Exterior caulking, exterior commercial grade, color to match exterior color

Interior caulking, interior commercial grade, conceal sealant within units.

PVC Patio Doors:

Materials: to CAN/CGSB – 82.1 supplemented as follows:

Silding doors by same manufacturer of windows

Panel Sash: vinyl, thermally broken,

Main Frame: vinyl,

Screen: Fiberglass wire mesh on a Aluminum Frame

Opening Devices: as per Manufactures Standards

Including: End Strips, Chairs, Anchors, Splice, locking latch

Color: Beige

Exterior caulking, exterior commercial grade, color to match exterior color.

Exterior trim to match existing trim

Interior caulking, interior commercial grade, conceal sealant within units.

2.03 EXECUTION

1. Install windows to CSA A440.4 "Window Installation Guidelines"
2. Install patio doors and frames in accordance with CAN/CGSB 82.1- M89, "Sliding Doors"
3. Vinyl frames will have a 20 year warranty against fading, discoloring, warping and cracking.
4. Sealed units will have a minimum 5 year warranty against failure.
5. Setting spacer blocks, Neoprene, Block size to suit glass
6. Supply and install primed and painted (grey) 1x4 and 2x6 cedar casing to match existing design around windows and doors

Sauf indication contraire, les modalités de l'invitation demeurent les mêmes.