



Q&R #5

Date: le 8 octobre 2014

Projet: Modernisation de l'éclairage – Conversion des appareils fluorescents T12 au T8

Les soumissionnaires doivent s'assurer que leurs propositions soient basées sur la version la plus récente des documents de soumission publiés et prennent en considération les informations ci-dessous, incluant toute information déjà publiée lors d'amendements ou Q&Rs antérieurs.

Les propositions ne respectant pas cette exigence seront rejetées.

Question 11: Je voudrais soumettre pour approbation un autre appareil en équivalence pour le projet cité ci-haut. La fiche technique complétée du manufacturier est jointe en annexe pour votre revue.

Réponse 11 : Les luminaires (boîtier et réflecteur) doivent être peints et le fini doit être en émail blanc cuit. Le luminaire proposé n'est pas un équivalent approuvé.

TOUS LES TERMES ET CONDITIONS DEMEURENT INCHANGÉS

BJTSP SERIES T5/T8 INDUSTRIAL STRIP FIXTURE

OPTICS:

Multi-faceted reflector engineered to maximize lamp performance.

Reflector materials available include:

- High Reflectance White Steel
- High Reflectance White Aluminum
- Standard Anodized Aluminum
- Upgraded Anodized Aluminum

CONSTRUCTION

- Formed white steel for added strength and rigidity
- End brackets screw mounted and have knock outs to allow for row mounting

OPTIONS

- Custom lengths up to 8 ft.
- 1 lamp to 4 lamp cross sections available
- Specific reflector types to suit your requirements
- Wire Guard
- Cords, plugs and outlets
- Suitable for continuous row mounting
- Master / satellite

APPLICATIONS

- Ideal for warehouse, utility rooms, aisle lighting, and other indoor applications.

APPROVALS

- UL & CSA approved for Canada & USA





Specifications may change without notice.
Some configurations may not be available.


BJTSP SERIES T5/T8 INDUSTRIAL STRIP FIXTURE

BJ TAKE ENERGY EFFICIENT LIGHTING

BJTSP Series Fixture Options



Order Code Logic



Optional Accessories:

Battery Backup
(needs to be specified)

Sensors
Motion Sensor (MS)
Motion Sensor with Photo Cell (MPS)

Wire Guard (WG)

Hangers
V-Hanger
5' Aircraft Kit
10' Aircraft Kit
15' Aircraft Kit

Reflector
White Steel Reflector (WH)
White Aluminum Reflector (WHAL)
Anodized Aluminum Reflector (AL)
Upgraded Anodized Aluminum Reflector (AL+)

Cord
6' Black 16/3
6' White 16/3
6' Black 16/4
6' White 16/4
10' Black 16/3
10' White 16/3
10' Black 16/4
10' White 16/4