

Addenda #3 RFP 201500057

CLARIFICATION

- 1 – The interior dimensions of the shelter are based on the amount of equipment to be installed. The manufacturer must provide a shelter with an interior floor space of 10' x 12'
- 2 – Article 5 Electricity – plywood surface is to be mounted on Wall F (12') adjacent to the door.
- 3 – Article 11 Electricity – All interior lighting must be Philips LED model LF4FR3940ULAG (or similar). Disregard all reference to fluorescent lighting
- 4 – Article 13 Electricity – All exterior lighting must be LED type Lumark Crosstour™ LED Wall Pack Series (Model #: XTOR2A-N-PC1) (or similar). Exterior lighting to be on 120v system complete with timer switch mounted on the interior of the shelter near the door. Exterior light must have protective cage.
- 5 – Article 18 Electricity – Cable entry to be 4 x 5" weather-proof boots.