



Canadian Museum of  
Immigration at Pier 21  
Musée canadien de  
l'immigration du Quai 21

## Stage - Room 145-145B

	Item	Quantity	Manufacturers	Model	Type/Description
<b>Lighting Fixture - Type A</b>	A1	36	Electronic Theatre Controls	Source Four® PAR-EA	Wash Fixture
	A2	36	Electronic Theatre Controls	400CC	C-Clamp
	A3	36	Electronic Theatre Controls	400SC	Safety Cable
	A4	36	Hubbell	Twist-Lock® HBL2311BK	In-line Connector
	A5	36	USHIO	HPL-575/120X	Bulb
<b>Lighting Fixture - Type B</b>	B1	36	Electronic Theatre Controls	Source Four® jr 26° - 426JL	Profile Fixture
	B2	36	Electronic Theatre Controls	400CC	C-Clamp
	B3	36	Electronic Theatre Controls	400SC	Safety Cable
	B4	12	Electronic Theatre Controls	400JRS	Drop-in Iris
	B5	12	Electronic Theatre Controls	400pH-M	Pattern Holder (M size)
	B6	36	Hubbell	Twist-Lock® HBL2311BK	In-line Connector
	B7	36	USHIO	HPL-575/120X	Bulb
<b>Dimmer Rack</b>	C1	1	Electronic Theatre Controls	Sensor3™ 120V UL SR3-48	Module Rack - Dimmer Enclosure
	C2	48	Electronic Theatre Controls	D20	Dual 20A Dimmer Module - 350µS
<b>Lighting Controler/Board</b>	D1	1	Electronic Theatre Controls	SmartFade SF1248	Lighting Board
	D2	3	Custom	DMX-512 XLR-5 2.5m, 5m, 15m	Data Control Cable
<b>Electric Chain Hoist</b>	E	8	Chain Master	TourRig 500Kg D8+ 3PH 16-fmp + accessories	Electric Chain Hoist 30ft H.o.L
<b>Motor Power Distribution</b>	F	1	Show Distribution	SD-800	Power Distribution for 8 Motors
	F1	Lot	Custom	Various	Power Cable to Motor
<b>Motor Control</b>	G	1	Show Distribution	SD-PRC-8	8 Channel Standard Remote
	G1	1	Custom	50m	Motor Control Cable
<b>Trusses + Rigging Hardware</b>	H	12	JTE or TOMCAT	Core truss 12" x 12" x 10' Plated Black Powder Coat Finish	Medium Duty Truss
	H1	8	Columbus McKinnon	Screwlok 09001W	Beam Clamp
	H2	8	The Light Source Inc.	MTP12MHB	12" Truss Hanger 1 Ton, Blk. Anodized
	H3	Lot	Custom	Various	Wire Rope and Aircraft Cable
	H4	Lot	Crosby	G20910C	Shackle 5/8" - 3.25 Ton Rated
<b>Circuits Panel Box</b>	I	Lot	Custom	Fixed Patch for 16 Break-in Socapex Type Connectors - Black	Dimmer Ouputs to Femelle Socapex Type Connectors
<b>Circuits Distribution Cables</b>	J	16	Custom	50m - 6 Circuits 20A Multi Cable - Blk	Typical Socapex/Veam/Phase 3 Cable
<b>Circuits Distribution Break-in Boxes</b>	K	16	Custom	6 Circuits Patch Box for Trusses + Safe Chain - Black	Typical Socapex/Veam/Phase 3 to TL-3
<b>Cable</b>	L	Lot	Custom	20 x 1.5M - 20 x 3m - 20 x 8m - 20 x 15m	Extension Cords SOOW 12/3 + HBL2311BK/HBL2313BK
<b>Cable Coupler-2Fers</b>	M	24	Custom	2 legs .5m coupler-2Fer - Blk	Extension Cords SOOW 12/3 + HBL2311BK/HBL2313BK
<b>Cable Adaptor</b>	M1	12	Custom	.25m AC HBL2313BK - HBL5269CM2	Break-in Adaptor TL-3 M to Straight Blade U-Ground F



Canadian Museum of  
Immigration at Pier 21  
Musée canadien de  
l'immigration du Quai 21

## Kenneth C. Rowe Hall - Room 133

	Item	Quantity	Manufacturers	Model	Type/Description
<b>Lighting Fixture - Type A</b>	A1	60	Electronic Theatre Controls	Source Four® PAR-EA	Wash Fixture
	A2	60	Electronic Theatre Controls	400CC	C-Clamp
	A3	60	Electronic Theatre Controls	400SC	Safety Cable
	A6	60	Electronic Theatre Controls	400-XWFL	Extra Wide Flood Lens
	A4	60	Hubbell	Twist-Lock® HBL2311BK	In-line Connector
	A5	60	USHIO	HPL-575/120X	Bulb
<b>Dimmer Rack</b>	C3	2	Electronic Theatre Controls	Sensor3™ 120V UL SR3-24	Module Rack - Dimmer Enclosure
	C2	24	Electronic Theatre Controls	D20	Dual 20A Dimmer Module - 350µS
	C4	1	Electronic Theatre Controls	ELTS2-1-M-3P-2-12	Emergency Lighting Transfer System
<b>Data Management Network Hub &amp; Distribution</b>	N	8	Pathway Connectivity	C6203	Bi-directional Data Node - CAT6 Bridge In/Out
	N1	1	Pathway Connectivity	VIA10	10 Ports - 10 Gigabit Ethernet Switch
	N2	Lot	N/S	N/S	Network - Standard Ethernet for Lighting - TIA/EIA-568
<b>Wall Control Station</b>	O	5	Electronic Theatre Controls	EPS10	10-button Preset Station
	O1	Lot	Belden	8471	Wiring
<b>Network CAT6 Patch Bay</b>	P	1	N/S	N/S	24 Port CAT6 Patch Bay Unit
	P1	Lot	N/S	N/S	CAT6 Cables
<b>Cable</b>	L	Lot	Custom	10 x 1.5M - 10 x 3m - 10 x 8m - 10 x 15m - Blk	Extension Cords SOOW 12/3 + HBL2311BK/HBL2313BK
<b>Cable Coupler-2Fers</b>	M	12	Custom	2 legs .5m coupler-2Fer - Blk	Extension Cords SOOW 12/3 + HBL2311BK/HBL2313BK
<b>Cable Adaptor</b>	M1	12	Custom	.25m AC HBL2313BK - HBL5269CM2	Break-in Adaptor TL-3 M to Straight Blade U-Ground F



Canadian Museum of  
Immigration at Pier 21

Musée canadien de  
l'immigration du Quai 21

## Chrysler Canada Pavilion - Room 125

	Item	Quantity	Manufacturers	Model	Type/Description
<b>Lighting Fixture - Type A</b>	A1	32	Electronic Theatre Controls	Source Four® PAR-EA	Wash Fixture
	A2	32	Electronic Theatre Controls	400CC	C-Clamp
	A3	32	Electronic Theatre Controls	400SC	Safety Cable
	A6	32	Electronic Theatre Controls	400-XWFL	Extra Wide Flood Lens
	A4	32	Hubbell	Twist-Lock® HBL2311BK	In-line Connector
	A5	32	USHIO	HPL-575/120X	Bulb
<b>Dimmer Rack</b>	C3	1	Electronic Theatre Controls	Sensor3™ 120V UL SR3-24	Module Rack - Dimmer Enclosure
	C2	24	Electronic Theatre Controls	D20	Dual 20A Dimmer Module - 350µS
<b>Data Management Network Hub</b>	N	2	Pathway Connectivity	C6203	Bi-directional Data Node - CAT6 Bridge In/Out
	N2	Lot	N/S	N/S	Network - Standard Ethernet for Lighting - TIA/EIA-568
<b>Wall Control Station</b>	O	2	Electronic Theatre Controls	EPS10	10-button Preset Station
	O1	Lot	Belden	8471	Wiring
<b>Cable</b>	L	Lot	Custom	5 x 1.5M - 5 x 3m - 5 x 8m - 5 x 15m - Blk	Extension Cords SOOW 12/3 + HBL2311BK/HBL2313BK
<b>Cable Coupler-2Fers</b>	M	6	Custom	2 legs .5m coupler-2Fer - Blk	Extension Cords SOOW 12/3 + HBL2311BK/HBL2313BK
<b>Cable Adaptor</b>	M1	6	Custom	.25m AC HBL2313BK - HBL5269CM2	Break-in Adaptor TL-3 M to Straight Blade U-Ground F