
Partie 1 General

1.1 RELATED REQUIREMENTS

- .1 The list of Work in this division is indicative but non-limiting. It does not exclude Work described in other specification divisions shown on the drawings or required for full execution of the Work as intended on the drawings.
- .2 Section 03 30 00 Cast-in-place Concrete.
- .3 Section 04 22 00 Concrete Unit Masonry.
- .4 Section 05 50 00 Metal Fabrications.
- .5 Section 07 44 56 Mineral Fiber Reinforced Cementitious Panels.
- .6 Section 07 92 00 Joint Sealants.
- .7 Section 08 11 00 Metal Doors and Frames.
- .8 Section 08 11 16 Aluminum Doors and Frames.
- .9 Section 08 36 12 Sectional Metal Doors.
- .10 Section 09 21 16 Gypsum Board Assemblies.
- .11 Section 09 91 23 Exterior Painting.

1.2 REFERENCES

- .1 American Society for Testing and Materials International (ASTM)
 - .1 ASTM A653/A653M-[01a], Standard Specification for Steel Sheet, Zinc-Coated, (Galvanized) or Zinc-Iron Alloy-Coated (Galvannealed) by the Hot-Dip Process.
- .2 Canadian General Standards Board (CGSB)
 - .1 CAN/CGSB-1.81-M90, Air Drying and Baking Alkyd Primer for Vehicles and Equipment.
 - .2 CAN/CGSB-1.88-92, Gloss Alkyd Enamel, Air Drying and Baking.
 - .3 CAN/CGSB-1.104-M91, Semigloss Alkyd, Air Drying and Baking Enamel.
- .3 Canadian Standards Association (CSA)/CSA International
 - .1 CSA-G40.20-F04/G40.21-F02, General Requirements for Rolled or Welded Structural Quality Steel/Structural Quality Steel.
 - .2 CAN/CSA-G164-FM92(C2003), Hot Dip Galvanizing of Irregularly Shaped Articles.
 - .3 CSA W59-F03, Welded Steel Construction (Metal Arc Welding).
- .4 Green Seal Environmental Standards
 - .1 Standard GC-03-93, Anti-Corrosive Paints.
 - .2 Standard GS-11-97, Architectural Paints.

- .5 Health Canada/Workplace Hazardous Materials Information System (WHMIS)
 - .1 Material Safety Data Sheets (MSDS).
- .6 South Coast Air Quality Management District (SCAQMD), California State
 - .1 SCAQMD Rule 1113-04, Architectural Coatings.
- .7 The Master Painters Institute (MPI)
 - .1 Architectural Painting Specification Manual - February 2004.
 - .1 MPI No. 76, Quick Dry Alkyd Metal Primer.
 - .2 MPI No. 81, Machinery Enamel.
 - .3 MPI No. 96, Quick Dry Enamel Gloss.

1.3 ACTION AND INFORMATIONAL SUBMITTALS

- .1 Provide submittals in accordance with Section 01 33 00 - Submittal Procedures.
- .2 Product Data:
 - .1 Submit manufacturer's printed product literature for wire mesh partitions or components, specifications and datasheet and include product characteristics, performance criteria, physical size, finish and limitations.
 - .2 Submit two copies WHMIS MSDS - Material Safety Data Sheets in accordance with Section 02 81 01 - Hazardous Materials.
- .3 Shop Drawings:
 - .1 Submit drawings stamped and signed by professional engineer registered or licensed in Quebec, Canada.
 - .2 Indicate partition panel modules and types, materials, gauges, finishes, door and other openings, hardware, fastening methods to adjacent structure, ceiling details, and assembly methods.
- .4 Samples:
 - .1 Submit duplicate 300 x 300 mm samples of each type partition and colour and finish on actual base metal.
 - .2 Sample to show basic construction, door construction, hardware, and finishes.
 - .3 Erect trial assembly of at least two modules of partition, on site where directed by Departmental Representative.
- .5 Sustainable Design Submittals:
- .6 Quality control submittals: submit following in accordance with Section 01 45 00 - Quality Control.
 - .1 Manufacturer's Instructions: submit manufacturer's installation instructions and special handling criteria, installation sequence, and cleaning procedures.
 - .2 Manufacturer's Field Reports: submit manufacturer's written reports within 3 days of review, verifying compliance of Work, as described in PART 3 - FIELD QUALITY CONTROL.

1.4 QUALITY ASSURANCE

- .1 Mock-ups:
 - .1 Construct mock-ups in accordance with Section 01 45 00 - Quality Control.
 - .2 Erect one of each type door and two of each type partition panel.
 - .3 Allow 24 hours for inspection of mock-up by Departmental Representative before proceeding with work.
 - .4 When accepted, mock-up will demonstrate minimum standard for this work.
 - .5 Mock-up may remain as part of finished work.
- .2 Pre-Installation Meetings: convene pre-installation meeting one week prior to beginning on-site installation, with Departmental Representative Section 01 32 16.07 - Construction Progress Schedule - Bar (GANTT) Chart to:
 - .1 Verify project requirements.
 - .2 Review installation and substrate conditions.
 - .3 Co-ordination with other building subtrades.
 - .4 Review manufacturer's installation instructions and warranty requirements.

1.5 DELIVERY, STORAGE AND HANDLING

- .1 Deliver, store and handle materials in accordance with Section 01 61 00 - Common Product Requirements.
- .2 Waste Management and Disposal:
 - .1 Separate waste materials for reuse and recycling in accordance with Section 01 74 21 - Construction/Demolition Waste Management and Disposal.

1.6 ACCEPTABLE PRODUCTS AND MATERIALS

- .1 Where a particular brand name is stipulated, see Instructions to Bidders for procedure for requesting approval of substitute materials and products

Partie 2 Products

2.1 MATERIALS

- .1 Partition mesh: painted:
 - .1 Welded steel wire fabric: painted, opening size 50 mm x 50 mm, 3.5 mm diameter, welded edges.
- .2 Steel sections and plates: to CAN/CSA-G40.20, type 44W.
 - .1 Posts: hollow steel tubing, square 50 mm x 50 mm, galvanized, bolted, designed to fasten to floors and walls, minimum wall thickness 2 mm.
 - .2 Extension posts: 38 mm x 38 mm hollow steel tubing, minimum wall thickness 1.6 mm.
 - .3 Angle frame: 32 x 32 x 3 mm.

- .4 Post caps: manufacturer's standard formed cap; finish to match other components.
- .3 Welding materials: to CSA W59.
- .4 Boulons, attaches et dispositifs de fixation : de fabrication courante, convenant aux caractéristiques de conception et d'installation.

2.2 ACCESSOIRES

- .1 Bolts, fasteners and fastening hardware: manufacturer's standard to suit design and application.

2.3 FABRICATION

- .1 Panels:
 - .1 Fabricate panels 2400 x 1200 mm and special sizes or shapes as required, consisting of wire mesh as indicated, welded at 100 mm on centre to angle frame.
 - .2 Mitre and weld frame corners.
 - .3 Provide 20 x 6 mm flat bars across panels at third points on 2400 mm dimension.
- .2 Posts:
 - .1 Full height with floor and ceiling plates for fixing and post cap.
 - .2 Include corner, wall, door and other special posts to manufacturer's standard.
- .3 Post extensions:
 - .1 Length required to telescope 300 mm into post and extend posts to ceiling.
 - .2 Weld ceiling plate on upper end for fixing.
 - .3 Supply extension posts for every post where indicated.
- .4 Swing doors: standard doors:
 - .1 900 x 2100 mm.
 - .2 Construct doors and transom above of angle frame, and wire mesh.
 - .3 Reinforce door with 40 x 5 mm or equivalent flat bar centre rail and 20 x 6 mm or equivalent flat bar bracing from centre rail to opposite corners on hinge side.
- .5 Swing door hardware:
 - .1 Equip doors with stops, keeper and hasp for padlock.
 - .2 Equip standard doors with 1-1/2 pair of butts.
- .6 Sliding doors:
 - .1 Total opening: 3660 mm wide x 3050 mm high.
 - .2 Construct of angle frame mesh, same as panels.
 - .3 Reinforce corners and at intermediate points horizontally and vertically, reinforced with welded 38 mm x 38 mm x 2 mm square tube.
 - .4 Equip sliding doors with:

- .1 Box type sliding door track, 135 kg capacity, fabricated from 1.6 mm thick galvanized steel.
- .2 Supply 3 hanger/trolleys per door.
- .3 Door guides, door stops, keeper, hasp for padlock.

2.4 FINISH

- .1 After fabrication, clean and paint components with manufacturer's standard primer and 2 coat enamel finish.
 - .1 Standard grey colour selected by Departmental Representative.

Partie 3 Execution

3.1 MANUFACTURER'S INSTRUCTIONS

- .1 Compliance: comply with manufacturer's written recommendations or specifications, including product technical bulletins, handling, storage and installation instructions, and datasheets.

3.2 ERECTION

- .1 Install mesh enclosures and doors in accordance with manufacturer's printed instructions.
- .2 Erect enclosures plumb, level, straight, rigidly supported, and securely fastened to abutting surfaces, free from superimposed loads.
- .3 Fix to masonry and concrete using lag bolts and shields; to hollow walls using bolts and toggle type anchors; to steel supports with bolts in threaded holes or spot welds.
 - .1 Locate fasteners on interior side where possible for maximum security.
- .4 Install doors and adjust for proper closing, locking and smooth operation.
 - .1 Mount sliding doors on exterior side of enclosed area.

3.3 FIELD QUALITY CONTROL

- .1 Manufacturer's Field Services:
 - .1 Provide manufacturer's field services consisting of product use recommendations and periodic site visits for inspection of product installation in accordance with manufacturer's instructions.

3.4 CLEANING

- .1 Proceed in accordance with Section 01 74 11 - Cleaning.
- .2 On completion and verification of performance of installation, remove surplus materials, excess materials, rubbish, tools and equipment.

END OF SECTION