

RETURN BIDS TO:
RETOURNER LES SOUMISSIONS À:
**Bid Receiving Public Works and Government
Services Canada/Réception des soumissions Travaux
publics et Services gouvernementaux Canada**
John Cabot Building
10 Barters Hill, P.O. Box 4600
St. John's
Newfoundland and Labrador
A1C 5T2
Bid Fax: (709) 772-4603

SOLICITATION AMENDMENT MODIFICATION DE L'INVITATION

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

Comments - Commentaires

Vendor/Firm Name and Address
**Raison sociale et adresse du
fournisseur/de l'entrepreneur**

Issuing Office - Bureau de distribution
PWGSC/TPSGC-Nfld Region/Real Property
John Cabot Building
10 Barters Hill, P.O. Box 4600
St. John's
Newfoundl
A1C 5T2

Title - Sujet Interior Office Fit-up -CSC - CB NL		
Solicitation No. - N° de l'invitation EA003-151701/A		Amendment No. - N° modif. 001
Client Reference No. - N° de référence du client R.063761.003		Date 2015-01-20
GETS Reference No. - N° de référence de SEAG PW-\$PWD-010-6261		
File No. - N° de dossier PWD-4-37174 (010)	CCC No./N° CCC - FMS No./N° VME	
Solicitation Closes - L'invitation prend fin at - à 02:00 PM on - le 2015-01-28		Time Zone Fuseau horaire Newfoundland Standard Time NST
F.O.B. - F.A.B. Plant-Usine: <input type="checkbox"/> Destination: <input type="checkbox"/> Other-Autre: <input type="checkbox"/>		
Address Enquiries to: - Adresser toutes questions à: Chaulk, Patricia		Buyer Id - Id de l'acheteur pwd010
Telephone No. - N° de téléphone (709) 772-8357 ()		FAX No. - N° de FAX (709) 772-4603
Destination - of Goods, Services, and Construction: Destination - des biens, services et construction:		

Instructions: See Herein

Instructions: Voir aux présentes

Delivery Required - Livraison exigée	Delivery Offered - Livraison proposée
Vendor/Firm Name and Address Raison sociale et adresse du fournisseur/de l'entrepreneur	
Telephone No. - N° de téléphone Facsimile No. - N° de télécopieur	
Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) Nom et titre de la personne autorisée à signer au nom du fournisseur/ de l'entrepreneur (taper ou écrire en caractères d'imprimerie)	
Signature	Date

Solicitation No. - N° de l'invitation

EA003-151701/A

Amd. No. - N° de la modif.

001

Buyer ID - Id de l'acheteur

pwd010

Client Ref. No. - N° de réf. du client

R.063761.003

File No. - N° du dossier

PWD-4-37174

CCC No./N° CCC - FMS No/ N° VME

**Aménagement de locaux intérieurs -
Service correctionnel du Canada (SCC) -
Corner Brook (T.-N.-L.)**

MODIFICATION N° 001 À L'INVITATION

Addendum No. 1 (des modifications aux spécifications)

Solicitation No. - N° de l'invitation

EA003-151701/A

Client Ref. No. - N° de réf. du client

R.063761.003

Amd. No. - N° de la modif.

001

File No. - N° du dossier

PWD-4-37174

Buyer ID - Id de l'acheteur

pwd010

CCC No./N° CCC - FMS No/ N° VME

**Interior Office Fit-up -
Correctional Services Canada (CSC) -
Corner Brook, NL**

AMENDMENT # 1

THE FOLLOWING AMENDMENT TO THE TENDER DOCUMENTS IS EFFECTIVE IMMEDIATELY. THE AMENDMENT
SHALL FORM A PART OF THE CONTRACT DOCUMENTS.

SPECIFICATIONS

1. Reference Specification Section 10 28 10 – Toilet and Bath Accessories

.1 Add specification section 10 28 10 - Toilet and Bath Accessories (Attached).

By submission of its tender, the Tenderer confirms that it has read and understands the requirements expressed in all addenda and has included all costs of these requirements in its Total Tender Amount.

All other terms & conditions remain unchanged.

PART 1 GENERAL

- | | | |
|--|----|---|
| <u>1.1 REFERENCES</u> | .1 | ASTM International |
| | .1 | ASTM A167-99(2009), Standard Specification for Stainless and Heat-Resisting Chromium-Nickel Steel Plate, Sheet, and Strip. |
| | .2 | ASTM B456-03, Standard Specification for Electrodeposited Coatings of Copper Plus Nickel Plus Chromium and Nickel Plus Chromium. |
| | .3 | ASTM A653/A653M-09, Standard Specification for Steel Sheet, Zinc-Coated (Galvanized) or Zinc-Iron Alloy-Coated (Galvannealed) by the Hot-Dip Process. |
| | .4 | ASTM A924/A924M-09, Standard Specification for General Requirements for Steel Sheet, Metallic-Coated by the Hot-Dip Process. |
| | .2 | Canadian General Standards Board (CGSB) |
| | .1 | CAN/CGSB-1.81-M90, Air Drying and Baking Alkyd Primer for Vehicles and Equipment. |
| | .2 | CAN/CGSB-1.88-92, Gloss Alkyd Enamel, Air Drying and Baking. |
| | .3 | CGSB 31-GP-107MA-90, Non-inhibited Phosphoric Acid Base Metal Conditioner and Rust Remover. |
| | .3 | CSA International |
| | .1 | CAN/CSA-B651-04, Accessible Design for the Built Environment. |
| | .2 | CAN/CSA-G164-M92(R2003), Hot Dip Galvanizing of Irregularly Shaped Articles. |
| <u>1.2 ACTION AND INFORMATIONAL SUBMITTALS</u> | .1 | Provide submittals in accordance with Section 01 33 00 - Submittal Procedures. |
| | .2 | Product Data: |
| | .1 | Provide manufacturer's printed product literature and data sheets and include |

product characteristics, performance criteria, physical size, finish and limitations.

.3 Shop Drawings.

- .1 Indicate size and description of components, base material, surface finish inside and out, hardware and locks, attachment devices, description of rough-in-frame, building-in details of anchors for grab bars.

1.3 CLOSEOUT
SUBMITTALS

- .1 Provide maintenance data for toilet and bath accessories for incorporation into manual specified in Section 01 78 00 - Closeout Submittals.

1.4 MAINTENANCE
MATERIAL
SUBMITTALS

- .1 Tools:
 - .1 Provide special tools required for assembly, disassembly or removal for toilet and bath accessories in accordance with requirements specified in Section 01 78 00 - Closeout Submittals.
 - .2 Deliver special tools to Departmental Representative.

1.5 DELIVERY,
STORAGE AND
HANDLING

- .1 Deliver, store and handle materials in accordance with Section 01 61 00 - Common Product Requirements and with manufacturer's written instructions.
- .2 Delivery and Acceptance Requirements: deliver materials to site in original factory packaging, labelled with manufacturer's name and address.
- .3 Storage and Handling Requirements:
 - .1 Store materials off ground indoors in dry location and in accordance with manufacturer's recommendations in clean, dry, well-ventilated area.
 - .2 Store and protect toilet and bathroom accessories from nicks, scratches, and blemishes.

- .3 Replace defective or damaged materials with new.
- .4 Packaging Waste Management: remove for reuse and return by manufacturer of pallets, crates, padding, packaging materials in accordance with Section 01 74 21 - Construction/Demolition Waste Management and Disposal.

PART 2 PRODUCTS

2.1 MATERIALS

- .1 Sheet steel: to ASTM A653/A653M with ZF001 designation zinc coating.
- .2 Stainless steel sheet metal: to ASTM A167, Type 305, with satin finish.
- .3 Stainless steel tubing: Type 305, commercial grade, seamless welded, 1.2 mm wall thickness.
- .4 Fasteners: concealed screws and bolts hot dip galvanized, exposed fasteners to match face of unit. Expansion shields fibre, lead or rubber as recommended by accessory manufacturer for component and its intended use.

2.2 COMPONENTS

- .1 Toilet tissue dispenser: double roll type, surface mounted, chrome plated steel frame, capacity of 500 double ply roll, roll under spring tension for controlled delivery.
- .2 Combination towel dispenser/waste receptacle: recessed wall unit, approximately 355 mm wide, 710 mm high, 190 mm deep. Interior of 0.8 mm galvanized steel, exterior of 0.8 mm stainless steel. Suitable for dispensing folded or roll paper towels. Removable galvanized steel waste receptacle, lockable access door with continuous full height stainless steel hinge.
- .3 Soap dispenser: liquid push-in valve, self contained 1.14 L tank, stainless steel piston and valve assembly, tamper proof

filler lock, surface mounted, exposed metal components satin finish.

- .4 Grab bars: 30/32 mm x 1.6 mm wall tubing of stainless steel, 76 mm diameter wall flanges, concealed screw attachment, flanges welded to tubular bar, provided with steel back plates and all accessories. Knurl bar at area of hand grips. Grab bar material and anchorage to withstand downward pull of 2.2 kN.
- .5 Mirror: wall mounted unit, fixed framed mirror 6 mm, stainless steel frame.
- .6 Urinal screen: floor, ceiling and wall mounted 38 mm x 38 mm aluminum frame complete with stops as required with 19 mm clear polycarbonate screen as indicated on drawings.

2.3 FABRICATION

- .1 Weld and grind joints of fabricated components flush and smooth. Use mechanical fasteners only where approved.
- .2 Wherever possible form exposed surfaces from one sheet of stock, free of joints.
- .3 Brake form sheet metal work with 1.5 mm radius bends.
- .4 Form surfaces flat without distortion. Maintain flat surfaces without scratches or dents.
- .5 Back paint components where contact is made with building finishes to prevent electrolysis.
- .6 Hot dip galvanize concealed ferrous metal anchors and fastening devices to CAN/CSA-G164.
- .7 Shop assemble components and package complete with anchors and fittings.
- .8 Deliver inserts and rough-in frames to job site at appropriate time for building-in. Provide templates, details and instructions for building in anchors and inserts.
- .9 Provide steel anchor plates and components

for installation on studding and building framing.

- 2.4 FINISHES .1 Chrome and nickel plating: to ASTM B456, satin finish.
- .2 Manufacturer's or brand names on face of units not acceptable.

PART 3 EXECUTION

- 3.1 EXAMINATION .1 Verification of Conditions: verify that conditions of substrates and surfaces to receive toilet and bathroom accessories previously installed under other Sections or Contracts are acceptable for product installation in accordance with manufacturer's instructions prior to toilet and bathroom accessories installation.
- .2 Inform Departmental Representative of unacceptable conditions immediately upon discovery.
- .3 Proceed with installation only after unacceptable conditions have been remedied and after receipt of written approval from Departmental Representative.

- 3.2 INSTALLATION .1 Install and secure accessories rigidly in place as follows:
- .1 Stud walls: install steel back-plate to stud prior to plaster or drywall finish. Provide plate with threaded studs or plugs.
- .2 Hollow masonry units, existing plaster or drywall: use toggle bolts drilled into cell or wall cavity.
- .3 Solid masonry, marble, stone or concrete: use bolt with lead expansion sleeve set into drilled hole.
- .4 Toilet and shower compartments: use male to female through bolts.

- .2 Install grab bars on built-in anchors provided by bar manufacturer.
- .3 Use tamper proof screws/bolts for fasteners.
- .4 Fill units with necessary supplies shortly before final acceptance of building.
- .5 Install mirrors in accordance with Section 08 80 50 - Glazing.

3.3 ADJUSTING

- .1 Adjust toilet and bathroom accessories components and systems for correct function and operation in accordance with manufacturer's written instructions.
- .2 Lubricate moving parts to operate smoothly and fit accurately.

3.4 CLEANING

- .1 Progress Cleaning: clean in accordance with Section 01 74 11 - Cleaning.
 - .1 Leave Work area clean at end of each day.
- .2 Final Cleaning: upon completion remove surplus materials, rubbish, tools and equipment in accordance with Section 01 74 11 - Cleaning.

3.5 PROTECTION

- .1 Protect installed products and components from damage during construction.
- .2 Repair damage to adjacent materials caused by toilet and bathroom accessories installation.

3.6 SCHEDULE

- .1 Locate accessories where indicated. Exact locations determined by Departmental Representative.
- .2 Toilet tissue dispenser: one as per drawings.
- .3 Combination towel dispenser/waste receptacles: one where indicated. Maximum height of dispenser and operable part from floor 1200 mm.
- .4 Soap dispenser: one at each wash basin.

- .5 Grab bar: two in each handicapped toilet compartment. Height of grab bar from floor 750 mm. Side grab bar: maximum distance from rear wall 300 mm, minimum distance passed front edge of toilet 450 mm.
- .6 Mirror: one at each accessible wash basin, height of bottom edge of mirror from floor 1000 mm.

END OF SECTION