



**RETURN BIDS TO:
RETOURNER LES SOUMISSIONS A :**

Procurement & Contracting Services
Services d'acquisitions et des marchés
Bid Receiving Unit/Centre des visiteurs
73 Leikin Drive
Ottawa, Ontario K1A 0R2
Canada

**SOLICITATION
AMENDMENT**

**MODIFICATION DE
L'INVITATION**

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

Comments: - Commentaries :

Vendor/Firm Name and Address
Raison sociale et adresse du fournisseur/de l'entrepreneur

Telephone No.
no de téléphone:

Title-Sujet Mail Screening X-Ray Machine		Date January 29, 2015
Solicitation No. - No. de l'invitation 201501900		Amendment No. - N° de la modification 003
Client Reference No. - No. De Référence du Client 201501900		
Solicitation Closes - L'invitation prend fin at 2:00pm on February 4, 2015		
F.O.B. - F.A.B. Does not change – Ne change pas		
Address Enquiries to: - Adresser toutes questions à: Candice Therien Candice.therien@rcmp-grc.gc.ca		
Telephone No. - No de téléphone 613-843-3826		Fax No. - N° de FAX: 613-825-0082
Destination of Goods and Services: Destinations des biens et services: Does not change – Ne change pas		
Delivery Required - Livraison exigée: Does not change – Ne change pas		Delivery Offered – Livraison proposée
Name and title of person authorized to sign on behalf of Vendor/Firm - Nom et titre de la personne autorisée à signer au nom du fournisseur/de l'entrepreneur		
_____ Signature		_____ Date



This amendment is raised to address the following:

- To respond to questions received during the solicitation period;
- To revise the solicitation accordingly.

QUESTIONS AND ANSWERS

Q1: Would a tunnel opening of 650mm x 450mm be acceptable?

A1: No. The tunnel opening must be a minimum of 750mm (W) x 500mm (H) due to large packages received. See amendment to solicitation below.

Q2: Would a system width of 1734mm and height of 1959mm be acceptable since the unit only needs to fit into an enclosure of 5918.2mm length x 4318.0 width?

A2: The overall height can be increased to 3000mm, but the remaining specifications outlined in 2.3 remain unchanged. The additional space is for non-related equipment. See amendment to solicitation below.

Q3: Is there a specific size door that this unit needs to fit through in order to arrive at its mailroom destination? If so, what are the dimensions?

A3: Yes. Garage Door Opening: The size of the opening is 3657 mm (W) x 3657 mm (H) or 12 " x 12"

Q4: At 2.2.1, would the supply of two 19" LCD monitors with 1440x900 screen resolution be acceptable?

A4: No. Two 20" color LCD monitors with 1280 x 1024 resolution are required.

Q5: At 2.3, can the overall dimensions be modified to allow for larger units as per the following: Length: 4800mm, Width: 2000mm; Height: 2100mm? As stated in 2.3.6, these modified dimensions would still easily fit within the enclosure.

A5: The overall height can be increased to 3000mm, but the remaining specs outlined in 2.3 remain unchanged. See answer 2 above and amendment to solicitation below.

Q6: At 2.5.3, the industry standard specifications, i.e. IEC Standard IEC 61000-4-4:2012 (Electrical Fast Transient Burst) are listed below:

- a) +2kV pulse of 50nS duration at every 0.2mS for 15mS. The burst of pulses repeat every 300mS for 60S
- b) -2kV pulse of 50nS duration at every 0.2mS for 15mS. The burst of pulses repeat every 300mS for 60S

As these specifications are an industry standard, can you please confirm that this would be acceptable?

A6: The equipment must meet the industry standard for the Electrical Fast Transient/Burst.

Q7: At 2.9.2, our proposed system can export images in our proprietary format and these can be reformatted into various formats (jpeg, bmp); would this be acceptable as it allows for the flexibility of various file formats?

A7: The unit must be capable of exporting or reformatting images in multiple common data formats (e.g. JPEG, BMP). See solicitation amendment below.

Q8: At 2.9.8, Would a non-stepless zoom be acceptable as the functionality of the zoom feature remains the same?

A8: The unit must have a zoom overview and stepless or non-stepless zoom. See solicitation amendment below.



SOLICITATION AMENDMENTS

1) At Annex A Requirement, section 2.3.3 and Annex D item 2.3.3 Overall height

DELETE: Overall height: minimum 1250 mm to maximum 1700 mm;

INSERT: Overall height: minimum 1250 mm to maximum 3000 mm;

2) At Annex A Requirement, section 2.3.4 and Annex D item 2.3.4 Tunnel Opening

DELETE: 750mm x 500mm

INSERT: 750mm (W) x 500 (H) mm

3) At Annex A Requirement, section 2.9.2 and Annex D item 2.9.2

DELETE: Ability to export images in multiple common data formats (e.g. JPEG, BMP);

INSERT: Ability to export or reformat images or in multiple common data formats (e.g. JPEG, BMP);

4) At Annex A Requirement, section 2.9.8 and Annex D item 2.9.8

DELETE: Zoom overview and stepless zoom;

INSERT: Zoom overview and stepless or non-stepless zoom;

ALL OTHER TERMS AND CONDITIONS REMAIN UNCHANGED.