

NOTIFICATION OF REVISION

Public Works and Government
Services Canada

Addendum No. 6

Solicitation Name: CFIA GTA Laboratory Expansion and Fit-up
Solicitation Number: R.061999.001

Date: Wednesday, February 4, 2015

1. MECHANICAL

1.1 SPECIFICATIONS

.1 N/A

1.2 DRAWINGS

.1 Drawing M-6.01, ME Schedules Proposed,

.1 Revise motorized damper schedule to include size and material of new motorized dampers as shown on the attached drawing.

End of Addendum No. 6

MOTORIZED DAMPER SCHEDULE (NEW & EXISTING)								
TAG	ROOM #	DESCRIPTION	MODEL	SIZE (in)	MATERIAL	OCCUPIED FLOWS (CFM)	UNOCCUPIED FLOWS (CFM)	NOTES
MD-1	327	MOTORIZED DAMPER	-	14x12	ALUMINUM	950	475	LAB GENERAL EXHAUST
MD-2	325	MOTORIZED DAMPER	-	12x10	ALUMINUM	760	380	LAB GENERAL EXHAUST
EX. MD-3	325	MOTORIZED DAMPER	-	-		760	380	LAB GENERAL EXHAUST
EX. MD-4	323	MOTORIZED DAMPER	-	-		415	207	LAB GENERAL EXHAUST
EX. MD-5	321	MOTORIZED DAMPER	-	-		425	212	LAB GENERAL EXHAUST
EX. MD-6	321	MOTORIZED DAMPER	-	-		425	212	LAB GENERAL EXHAUST
EX. MD-7	321	MOTORIZED DAMPER	-	-		425	212	LAB GENERAL EXHAUST
EX. MD-8	317B	MOTORIZED DAMPER	-	-		325	163	LAB GENERAL EXHAUST
EX. MD-9	317A	MOTORIZED DAMPER	-	-		195	97	LAB GENERAL EXHAUST
MD-10	316	MOTORIZED DAMPER	-	10x8	ALUMINUM	250	125	LAB GENERAL EXHAUST
MD-11	328	MOTORIZED DAMPER	-	16x10	ALUMINUM	810	405	LAB GENERAL EXHAUST
EX. MD-12	337	MOTORIZED DAMPER	-	-		450	225	LAB GENERAL EXHAUST
MD-13	341	MOTORIZED DAMPER	-	10x10	ALUMINUM	400	200	LAB GENERAL EXHAUST
EX. MD-14	341	MOTORIZED DAMPER	-	-		400	200	LAB GENERAL EXHAUST
MD-15	342	MOTORIZED DAMPER	-	10x8	ALUMINUM	240	120	LAB GENERAL EXHAUST
MD-16	345	MOTORIZED DAMPER	-	10x10	316 STAINLESS STEEL	600	300	LAB GENERAL EXHAUST
MD-17	345	MOTORIZED DAMPER	-	10x10	316 STAINLESS STEEL	600	300	LAB GENERAL EXHAUST
MD-18	345	MOTORIZED DAMPER	-	10x10	316 STAINLESS STEEL	600	300	LAB GENERAL EXHAUST
MD-19	347	MOTORIZED DAMPER	-	10x8	ALUMINUM	350	175	LAB GENERAL EXHAUST
MD-20	347	MOTORIZED DAMPER	-	10x8	ALUMINUM	350	175	LAB GENERAL EXHAUST
EX. MD-21	355A	MOTORIZED DAMPER	-	-		250	125	LAB GENERAL EXHAUST
EX. MD-22	355B	MOTORIZED DAMPER	-	-		420	210	LAB GENERAL EXHAUST
EX. MD-23	355	MOTORIZED DAMPER	-	-		200	100	LAB GENERAL EXHAUST
EX. MD-24	355C	MOTORIZED DAMPER	-	-		255	127	LAB GENERAL EXHAUST
EX. MD-25	355C	MOTORIZED DAMPER	-	-		255	127	LAB GENERAL EXHAUST
MD-26	327	MOTORIZED DAMPER	-	14x12	ALUMINUM	750	375	LAB GENERAL SUPPLY
EX. MD-27	325	MOTORIZED DAMPER	-	-		456	228	LAB GENERAL SUPPLY
EX. MD-28	325	MOTORIZED DAMPER	-	-		303	152	LAB GENERAL SUPPLY
EX. MD-29	325	MOTORIZED DAMPER	-	-		456	228	LAB GENERAL SUPPLY
MD-30	323	MOTORIZED DAMPER	-	10x10	ALUMINUM	415	207	LAB GENERAL SUPPLY
EX. MD-31	321	MOTORIZED DAMPER	-	-		1020	510	LAB GENERAL SUPPLY
EX. MD-32	317B	MOTORIZED DAMPER	-	-		260	130	LAB GENERAL SUPPLY
MD-33	317A	MOTORIZED DAMPER	-	8x8	ALUMINUM	155	77	LAB GENERAL SUPPLY
MD-34	316	MOTORIZED DAMPER	-	8x8	ALUMINUM	200	100	LAB GENERAL SUPPLY
MD-35	328	MOTORIZED DAMPER	-	14x12	ALUMINUM	650	325	LAB GENERAL SUPPLY
EX. MD-36	337	MOTORIZED DAMPER	-	-		360	180	LAB GENERAL SUPPLY
EX. MD-37	335	MOTORIZED DAMPER	-	-		200	100	LAB GENERAL SUPPLY
EX. MD-38	341	MOTORIZED DAMPER	-	-		640	320	LAB GENERAL SUPPLY
MD-39	342	MOTORIZED DAMPER	-	8x8	ALUMINUM	190	95	LAB GENERAL SUPPLY
EX. MD-40	345	MOTORIZED DAMPER	-	-		360	180	LAB GENERAL SUPPLY
EX. MD-41	345	MOTORIZED DAMPER	-	-		1080	540	LAB GENERAL SUPPLY
EX. MD-42	368	MOTORIZED DAMPER	-	-		200	100	LAB GENERAL SUPPLY
EX. MD-43	347	MOTORIZED DAMPER	-	-		1300	650	LAB GENERAL SUPPLY
EX. MD-44	366	MOTORIZED DAMPER	-	-		200	100	LAB GENERAL SUPPLY
MD-45	347A	MOTORIZED DAMPER	-	8x6	ALUMINUM	150	75	LAB GENERAL SUPPLY
EX. MD-46	355A	MOTORIZED DAMPER	-	-		390	195	LAB GENERAL SUPPLY
EX. MD-47	355B	MOTORIZED DAMPER	-	-		420	210	LAB GENERAL SUPPLY
EX. MD-48	355	MOTORIZED DAMPER	-	-		100	50	LAB GENERAL SUPPLY
EX. MD-49	355C	MOTORIZED DAMPER	-	-		635	317	LAB GENERAL SUPPLY



MCW Consultants Ltd.

Ste 600, 156 Front Street West, Toronto, Ont. M5J 2L6

PROJECT:

**CFIA GTA LABORATORY
EXPANSION AND FIT-UP**

ARCHITECT:

RPL ARCHITECTS INC.

DATE:

FEB 4, 2015

DRAWN BY:

D.R.

REF. DWG. NO.

M-6.01

DWG. NO.

SKM-1

ISSUED WITH

ADD #006