

**RETURN BIDS TO:**  
**RETOURNER LES SOUMISSIONS À:**  
**Bid Receiving Public Works and Government  
Services Canada/Réception des soumissions Travaux  
publics et Services gouvernementaux Canada**  
**1713 Bedford Row**  
**Halifax, N.S./Halifax, (N.É.)**  
**B3J 1T3**  
**Bid Fax: (902) 496-5016**

## **SOLICITATION AMENDMENT MODIFICATION DE L'INVITATION**

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

### **Comments - Commentaires**

**Vendor/Firm Name and Address**  
**Raison sociale et adresse du  
fournisseur/de l'entrepreneur**

**Issuing Office - Bureau de distribution**  
Atlantic Region Acquisitions/Région de l'Atlantique  
Acquisitions  
1713 Bedford Row  
Halifax, N.S./Halifax, (N.É.)  
B3J 3C9  
Nova Scot

<b>Title - Sujet</b> Resistive Load Bank, Outdoor	
<b>Solicitation No. - N° de l'invitation</b> W355B-151477/B	<b>Amendment No. - N° modif.</b> 002
<b>Client Reference No. - N° de référence du client</b> W355B-15-1477	<b>Date</b> 2015-03-26
<b>GETS Reference No. - N° de référence de SEAG</b> PW-\$HAL-503-9460	
<b>File No. - N° de dossier</b> HAL-4-73137 (503)	<b>CCC No./N° CCC - FMS No./N° VME</b>
<b>Solicitation Closes - L'invitation prend fin at - à 02:00 PM on - le 2015-03-31</b>	<b>Time Zone</b> Fuseau horaire Atlantic Daylight Saving Time ADT
<b>F.O.B. - F.A.B.</b> <b>Plant-Usine:</b> <input type="checkbox"/> <b>Destination:</b> <input checked="" type="checkbox"/> <b>Other-Autre:</b> <input type="checkbox"/>	
<b>Address Enquiries to: - Adresser toutes questions à:</b> Forward (HAL), LeeAnne	<b>Buyer Id - Id de l'acheteur</b> hal503
<b>Telephone No. - N° de téléphone</b> (902) 496-5070 ( )	<b>FAX No. - N° de FAX</b> (902) 496-5016
<b>Destination - of Goods, Services, and Construction:</b> <b>Destination - des biens, services et construction:</b>	

**Instructions: See Herein**

**Instructions: Voir aux présentes**

<b>Delivery Required - Livraison exigée</b>	<b>Delivery Offered - Livraison proposée</b>
<b>Vendor/Firm Name and Address</b> <b>Raison sociale et adresse du fournisseur/de l'entrepreneur</b>	
<b>Telephone No. - N° de téléphone</b> <b>Facsimile No. - N° de télécopieur</b>	
<b>Name and title of person authorized to sign on behalf of Vendor/Firm (type or print)</b> <b>Nom et titre de la personne autorisée à signer au nom du fournisseur/ de l'entrepreneur (taper ou écrire en caractères d'imprimerie)</b>	
<b>Signature</b>	<b>Date</b>

---

The purpose of this amendment is to respond to the following questions:

Q1. Item 13. Louvers

Louvers are not motorized. We cannot add motorized louvers even for extra charge. Do you require motorized louvers?

A1. Motorized Louvers are required

Q2. Item 15 - Point 2

DC IP 67 rated for temporary water immersion 30 minutes, our provided contactors are not designed for temporary water immersion. Is this required?

A2. IP67 rated contactors are required

Q3. Item 16

The following items on your specifications are not available to us, are these required or are there equivalencies or substitutions that would be acceptable?

Double inlet - N/A

Vane inlet - N/A

Power connection via separate gland plate - N/A

600V - Blower is 3 phase rated for 575Vac.

Max 100A - N/A

Soft start control - N/A

A3. For item 16 the N/A items will be acceptable as long as an equivalent method of ventilation is provided for the load bank cooling. The alternative method is not indicated in the question so I cannot confirm that it will be acceptable as an equivalent at this point.

Q4. Item 17

Local controls are included. Remote 3 location requirement is NA as this description is very vague. Please provide more detail.

A4. Intention is for the control panel to be unplugged from the load bank unit and relocated to 3 other locations. Owners will run cables from load bank to the 3 remote locations.

Q5. Item 4

316L stainless shell painted ASA 61 grey, what portion of the container will be Stainless Steel ? Does the container need to be IP 67 as per item 15? Would an IP 55 container with Marine coating which has as good or better corrosion factor than Stainless be considered as an approved equal?

Solicitation No. - N° de l'invitation

W355B-151477/B

Client Ref. No. - N° de réf. du client

W355B-15-1477

Amd. No. - N° de la modif.

002

File No. - N° du dossier

HAL-4-73137

Buyer ID - Id de l'acheteur

hal503

CCC No./N° CCC - FMS No/ N° VME

---

A5. All surfaces exposed to the outside elements (the shell) shall be 316L Stainless Steel including fasteners and bolts as per section 4.0.

Q6. Item 15

If Contactors are to be IP 67 does this mean the entire enclosure which houses these contactors requires to be IP 67? Or just the contactor themselves be rated for IP 67?

A6. Item 15 only applies to contactors.