

RETURN BIDS TO:
RETOURNER LES SOUMISSIONS À:
Bid Receiving
PWGSC
33 City Centre Drive
Suite 480C
Mississauga
Ontario
L5B 2N5
Bid Fax: (905) 615-2095

SOLICITATION AMENDMENT
MODIFICATION DE L'INVITATION

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

Comments - Commentaires

Vendor/Firm Name and Address
Raison sociale et adresse du
fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution
Public Works and Government Services Canada
Ontario Region
33 City Centre Drive
Suite 480
Mississauga
Ontario
L5B 2N5

Title - Sujet Mobile Tower Trailer	
Solicitation No. - N° de l'invitation KM061-141223/B	Amendment No. - N° modif. 002
Client Reference No. - N° de référence du client KM061-141223	Date 2015-05-21
GETS Reference No. - N° de référence de SEAG PW-\$TOR-015-6840	
File No. - N° de dossier TOR-4-37093 (015)	CCC No./N° CCC - FMS No./N° VME
Solicitation Closes - L'invitation prend fin at - à 02:00 PM on - le 2015-06-10	Time Zone Fuseau horaire Eastern Daylight Saving Time EDT
F.O.B. - F.A.B. Plant-Usine: <input type="checkbox"/> Destination: <input checked="" type="checkbox"/> Other-Autre: <input type="checkbox"/>	
Address Enquiries to: - Adresser toutes questions à: Abela, Aaron	Buyer Id - Id de l'acheteur tor015
Telephone No. - N° de téléphone (905) 615-2061 ()	FAX No. - N° de FAX (905) 615-2060
Destination - of Goods, Services, and Construction: Destination - des biens, services et construction:	

Instructions: See Herein

Instructions: Voir aux présentes

Delivery Required - Livraison exigée	Delivery Offered - Livraison proposée
Vendor/Firm Name and Address Raison sociale et adresse du fournisseur/de l'entrepreneur	
Telephone No. - N° de téléphone Facsimile No. - N° de télécopieur	
Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) Nom et titre de la personne autorisée à signer au nom du fournisseur/ de l'entrepreneur (taper ou écrire en caractères d'imprimerie)	
Signature	Date

Solicitation No. - N° de l'invitation

KM061-141223/B

Amd. No. - N° de la modif.

002

Buyer ID - Id de l'acheteur

tor015

Client Ref. No. - N° de réf. du client

KM061-141223

File No. - N° du dossier

TOR-4-37093

CCC No./N° CCC - FMS No/ N° VME

See attached ...

Solicitation Amendment No. 002 being issued to reflect the following:

A) Amend Annex "A" - Requirement, Section 4.0 - Additional Mandatory Mobile Tower Trailer Specifications, Item 20

B) Questions and Answers

A) At Annex "A" - Requirement, Section 4.0 - Additional Mandatory Mobile Tower Trailer Specifications, Item 20

Delete in its entirety;

Insert:

The trailer must include an enclosure (1.75m (Length) x 1.75m (Width) x 1.5m (Height)) on the front platform, to house instrumentation during deployment and include each of the following items:

- a) Constructed with parts that are designed for multi-year outdoor use.
- b) NEMA-3S equivalent (but certification not required).
- c) Doors on the two outer sides (i.e. not the front and back). The doors must have a minimum width of 1.2m and minimum height of 1.2m
- d) Removable panels on the other two sides (facing the tower and the hitch), near the top, for openings of 60cm x 30cm.
- e) A power panel, mounted inside to accommodate 6-8 standard 110V plugs, centrally on the side facing the tower.

B) Questions and Answers

Q1: Does the shelter have to be NEMA 4 rated or can it be constructed based on NEMA 4 standards?

A1: Reference Section A) above.

Q2: With regards to the opening on the front and back of the enclosure. The spec states the removable panels must be 60cm x 30cm. How big is the actual opening supposed to be? It is clear the panel should cover the opening, but based on the NEMA 4 requirement, there has to be some type of gasket around the opening to keep water and dirt out. This will reduce the opening slightly to ensure there is room for the gasket.

A2: Reference Section A) above.

Q3: Regarding the anti-sway control, is an electronic anti-sway control system acceptable?

A3: Yes, electronic anti-sway is fine.

Q4: On the power panel, what is the ingress outlet requirement? In other words, there is typically Shore Power outlet on the outside of the enclosure rated for "x" amount of amps. Nothing is listed.

A4: Ingress outlet: 1, two sockets, total 15A

Solicitation No. - N° de l'invitation
KM061-141223/B
Client Ref. No. - N° de réf. du client
KM061-141223

Amd. No. - N° de la modif.
002
File No. - N° du dossier
TOR-4-37093

Buyer ID - Id de l'acheteur
tor015
CCC No./N° CCC - FMS No./N° VME

Q5: The shelter now has to be a NEMA 4 rated shelter. This will increase the weight considerably which actually puts our tower of choice for this offering over the 4500kg. The PCTEL EHD-106 is our tower of choice because it is built stronger and can take a higher payload and has redundant cabling so the NEMA 4 shelter adds another 440kg and puts the tower over weight. Does the shelter need a formal NEMA 4 rating? If so can the bid be amended for a higher weight?

A5: Reference Section A) above.

Q6: The next best tower is the MAG-106 which barely meets the payload requirements but is lighter. Non redundant cables and motors cannot be locked. Outriggers are not 5 metres. All other towers I know of currently being built in the USA or Canada will NOT meet this requirement without heavy modifications which of course will drive up the prices. So the outriggers on the Mag-106 are 4.77metres, which is under the 5 metre minimum. Is this close enough? Not having a locking mechanism on the motors is a major re-design, is there any leeway here?

A6: Reference Section A) above.

Q7: The enclosure, the re-moveable openings at the front and back of the enclosure, can they be doors? Keeping the NEMA 4 rating is going to be difficult with re-moveable panels but if they were doors it would be cheaper and easier to maintain the NEMA 4 rating.

A7: Removable panels are preferred to doors.

ALL OTHER TERMS AND CONDITIONS REMAIN THE SAME