

Part 1 General**1.1 RELATED SECTIONS**

- .1 Section 21 05 01 – Common Work Results for Mechanical.

1.2 REFERENCES

- .1 Canadian Gas Association (CGA)
 - .1 CSA/CGA B149.1-10, Natural Gas and Propane Installation Code.
- .2 Canadian General Standards Board (CGSB)
 - .1 CAN/CGSB-1.60-97, Interior Alkyd Gloss Enamel.
 - .2 CAN/CGSB-24.3-92, Identification of Piping Systems.
- .3 National Fire Protection Association (NFPA)
 - .1 NFPA (Fire) 13, Standard for the Installation of Sprinkler Systems. 2013 Edition.
 - .2 NFPA (Fire) 14, Standard for the Installation of Standpipe and Hose Systems. 2013 Edition.

1.3 SUBMITTALS

- .1 Product Data:
 - .1 Submittals: in accordance with Section 01 00 10 – General Instructions.
 - .2 Product data to include paint colour chips, other products specified in this section.

1.4 DELIVERY, STORAGE, AND HANDLING

- .1 Packing, shipping, handling and unloading:
 - .1 Deliver, store and handle materials in accordance with manufacturer's written instructions.

Part 2 Products**2.1 MANUFACTURER'S EQUIPMENT NAMEPLATES**

- .1 Metal or plastic laminate nameplate mechanically fastened to each piece of equipment by manufacturer.
- .2 Lettering and numbers raised or recessed.
- .3 Information to include, as appropriate:
 - .1 Equipment: manufacturer's name, model, size, serial number, capacity.
 - .2 Motor: voltage, Hz, phase, power factor, duty, frame size.

2.2 SYSTEM NAMEPLATES

- .1 Colours:
 - .1 Hazardous: red letters, white background.

- .2 Elsewhere: black letters, white background (except where required otherwise by applicable codes).
- .2 Construction:
 - .1 3 mm thick laminated plastic or white anodized aluminum, matte finish, with square corners, letters accurately aligned and machine engraved into core.
- .3 Sizes:
 - .1 Conform to following table:

Size # mm	Sizes (mm)	No. of Lines	Height of Letters (mm)
1	10 x 50	1	3
2	13 x 75	1	5
3	13 x 75	2	3
4	20 x 100	1	8
5	20 x 100	2	5
6	20 x 200	1	8
7	25 x 125	1	12
8	25 x 125	2	8
9	35 x 200	1	20

- .2 Use maximum of 25 letters/numbers per line.
- .4 Locations:
 - .1 Terminal cabinets, control panels: use size # 5.
 - .2 Equipment in Mechanical Rooms: use size # 9.
- .5 Identification:
 - .1 Use arrangement of Main identifier, Source identifier, Destination identifier.
 - .2 Equipment in Mechanical Room:
 - .1 Main identifier: size #9.
 - .2 Source and Destination identifiers: size #6.
 - .3 Terminal cabinets, control panels: size #5.
 - .3 Equipment elsewhere: sizes as appropriate.

2.3 PIPING SYSTEMS GOVERNED BY CODES

- .1 Identification:
 - .1 Standpipe and hose systems: to NFPA 14.

2.4 IDENTIFICATION OF PIPING SYSTEMS

- .1 Identify contents by background colour marking, pictogram (as necessary), legend; direction of flow by arrows. To CAN/CGSB 24.3 except where specified otherwise.
- .2 Pictograms:
 - .1 Where required: Workplace Hazardous Materials Information System (WHMIS) regulations.
- .3 Legend:
 - .1 Block capitals to sizes and colours listed in CAN/CGSB 24.3.

- .4 Arrows showing direction of flow:
- .1 Outside diameter of pipe or insulation less than 75 mm: 100 mm long x 50 mm high.
 - .2 Outside diameter of pipe or insulation 75 mm and greater: 150 mm long x 50 mm high.
 - .3 Use double-headed arrows where flow is reversible.
- .5 Extent of background colour marking:
- .1 To full circumference of pipe or insulation.
 - .2 Length to accommodate pictogram, full length of legend and arrows.
- .6 Materials for background colour marking, legend, arrows:
- .1 Pipes and tubing 20 mm and smaller: waterproof and heat-resistant pressure sensitive plastic marker tags.
 - .2 Other pipes: pressure sensitive vinyl with protective overcoating, waterproof contact adhesive undercoating, suitable for ambient of 100% RH and continuous operating temperature of 150°C and intermittent temperature of 200°C.
- .7 Colours and Legends:
- .1 Where not listed, obtain direction from Departmental Representative.
 - .2 Colours for legends, arrows: to following table:

Background colour:	Legend, arrows:
Yellow	BLACK
Green	WHITE
Red	WHITE

- .3 Background colour marking and legends for piping systems

Contents	Background colour marking	Legend
Glycol supply	Green	GLY. SUP ALIM. GLY.
Glycol return	Green	GLY. RET RET. GLY.
Make-up glycol	Yellow	MAKE-UP GLY. GLY. APPOINT
Condenser water supply	Green	COND. WTR. SUP ALIM. EAU COND.
Condenser water return	Green	COND. WTR. RET RET. EAU COND.
Chilled water Supply	Green	CHW. SUP EGL ALIM
Chilled water Return	Green	CHW. RET EGL ALIM
Dom. HWS recirculation	Green	DHWR ECDR
Domestic cold water supply	Green	DCW EFD
Sanitary	Green	SAN.

Contents	Background colour marking	Legend
Storm	Green	STORM PLUV.
Plumbing vent	Green	VENT

2.5 IDENTIFICATION DUCTWORK SYSTEMS

- .1 50 mm high stencilled letters and directional arrows 150 mm long x 50 mm high.
- .2 Colours: black, or co-ordinated with base colour to ensure strong contrast.

2.6 VALVES, CONTROLLERS

- .1 Brass tags with 12 mm stamped identification data filled with black paint.
- .2 Include flow diagrams for each system, of approved size, showing charts and schedules with identification of each tagged item, valve type, service, function, normal position, location of tagged item.

2.7 CONTROLS COMPONENTS IDENTIFICATION

- .1 Identify all systems, equipment, components, controls, sensors with system nameplates specified in this section.
- .2 Inscriptions to include function and (where appropriate) fail-safe position.

2.8 LANGUAGE

- .1 Identification in English and French.

Part 3 Execution

3.1 MANUFACTURER'S INSTRUCTIONS

- .1 Compliance: comply with manufacturer's written recommendations or specifications, including product technical bulletins, handling, storage and installation instructions, and datasheet.

3.2 TIMING

- .1 Provide identification only after painting specified on architectural drawings has been completed.

3.3 INSTALLATION

- .1 Perform work in accordance with CAN/CGSB-24.3 except as specified otherwise.
- .2 Provide ULC or CSA registration plates as required by respective agency.

3.4 NAMEPLATES

- .1 Locations:
 - .1 In conspicuous location to facilitate easy reading and identification from operating floor.
- .2 Standoffs: Provide for nameplates on hot and/or insulated surfaces.
- .3 Protection: Do not paint, insulate or cover.

3.5 LOCATION OF IDENTIFICATION ON PIPING AND DUCTWORK SYSTEMS

- .1 On long straight runs in open areas in boiler rooms, equipment rooms: at not more than 17 m intervals and more frequently if required to ensure that at least one is visible from any one viewpoint in operating areas and walking aisles.
- .2 Adjacent to each change in direction.
- .3 At least once in each small room through which piping or ductwork passes.
- .4 On both sides of visual obstruction or where run is difficult to follow.
- .5 On both sides of separations such as walls, floors, partitions.
- .6 Where system is installed in pipe chases, ceiling spaces, confined spaces, at entry and exit points, and at access openings.
- .7 At beginning and end points of each run and at each piece of equipment in run.
- .8 At point immediately upstream of major manually operated or automatically controlled valves, and dampers. Where this is not possible, place identification as close as possible, preferably on upstream side.
- .9 Identification easily and accurately readable from usual operating areas and from access points.
 - .1 Position of identification approximately at right angles to most convenient line of sight, considering operating positions, lighting conditions, risk of physical damage or injury and reduced visibility over time due to dust and dirt.

3.6 VALVES, CONTROLLERS

- .1 Valves and operating controllers, except at plumbing fixtures, radiation, or where in plain sight of equipment they serve: Secure tags with non-ferrous chains or closed "S" hooks.
- .2 Install one copy of flow diagrams, valve schedules mounted in frame behind non-glare glass in the equipment room. Provide one copy (reduced in size if required) in each operating and maintenance manual.
- .3 Number valves in each system consecutively.

END OF SECTION