

File: F6855-150777

Q: Please provide the name of the shipyard where the vessel was built and the hull number.

A: Marystown, Hull 37.

Q: Please confirm if the actuators are set up double acting or spring return, and if they are spring to open or close.

A: Double acting, actuators are solenoid controlled.

Q: Please advise line pressure and temperature to size the actuators accordingly.

A: Minimum 20 psig, recommended 80 psig, maximum 125 psig, -40c to 80c ambient.

Q: For actuator model 790, is it a double acting or single acting actuator?

A: Double Acting

Q: For CSA NEMA 4 solenoid valve 791-4, what is the required voltage 120VAC or 24 VDC?

A: 120 VAC

Q: Can you direct me or provide me with the class approved by TCMS recognized under IASC as specified in 2.1?

A: These are Classification societies as part of the International Association of Classification Societies (IACS) IE. Lloyd's, DNV-GL, BV, ABS.