

RETURN BIDS TO:
RETOURNER LES SOUMISSIONS À:
Public Works and Government Services Canada
ATB Place North Tower
10025 Jasper Ave./10025 ave. Jasper
5th floor/5e étage
Edmonton
Alberta
T5J 1S6
Bid Fax: (780) 497-3510

SOLICITATION AMENDMENT
MODIFICATION DE L'INVITATION

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

Comments - Commentaires

Vendor/Firm Name and Address
Raison sociale et adresse du
fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution
Public Works and Government Services Canada
ATB Place North Tower
10025 Jasper Ave./10025 ave Jasper
5th floor/5e étage
Edmonton
Alberta
T5J 1S6

Title - Sujet Sally Port Gates and Fence Repair	
Solicitation No. - N° de l'invitation EV385-160418/B	Amendment No. - N° modif. 003
Client Reference No. - N° de référence du client csc EV385-160418	Date 2015-09-03
GETS Reference No. - N° de référence de SEAG PW-\$PWU-183-10530	
File No. - N° de dossier PWU-5-38073 (183)	CCC No./N° CCC - FMS No./N° VME
Solicitation Closes - L'invitation prend fin at - à 02:00 PM on - le 2015-09-11	Time Zone Fuseau horaire Mountain Daylight Saving Time MDT
F.O.B. - F.A.B. Plant-Usine: <input type="checkbox"/> Destination: <input type="checkbox"/> Other-Autre: <input type="checkbox"/>	
Address Enquiries to: - Adresser toutes questions à: Tikhonovitch (RPC), Alex	Buyer Id - Id de l'acheteur pwu183
Telephone No. - N° de téléphone (780) 901-7940 ()	FAX No. - N° de FAX (780) 497-3510
Destination - of Goods, Services, and Construction: Destination - des biens, services et construction:	

Instructions: See Herein

Instructions: Voir aux présentes

Delivery Required - Livraison exigée	Delivery Offered - Livraison proposée
Vendor/Firm Name and Address Raison sociale et adresse du fournisseur/de l'entrepreneur	
Telephone No. - N° de téléphone Facsimile No. - N° de télécopieur	
Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) Nom et titre de la personne autorisée à signer au nom du fournisseur/ de l'entrepreneur (taper ou écrire en caractères d'imprimerie)	
Signature	Date

Solicitation No. - N° de l'invitation

EV385-160418/B

Amd. No. - N° de la modif.

003

Buyer ID - Id de l'acheteur

pwu183

Client Ref. No. - N° de réf. du client

csc EV385-160418

File No. - N° du dossier

PWU-5-38073

CCC No./N° CCC - FMS No/ N° VME

This solicitation amendment has been raised to answer to following question:

Question: Would the enclosed gate operator acceptable for Specification Section 32 31 00?

Answer: This gate operator is acceptable. However, the entire gate system must be in accordance the contract documents.

All other terms and conditions of the Invitation to Tender remain unchanged.

SECUR-PAK SYSTEMS

Maximum Security

SECUR-PAK SYSTEMS

9100A VEHICLE GATE OPERATOR

9100A VEHICLE GATE OPERATOR

The 9100A Operator is designed for use on vehicular entrances in a perimeter security fence.

FUNCTION:

A remote switch activates a motor which raises a vertical lock bar and propels the gate open or closed.

MECHANICAL:

In an electrical emergency, the gate is manually unlocked and propelled open by use of a hand crank located in the motor box.

SAFETY:

The 9100 gate operator meets current UL 325 requirements for Class IV (Guarded Applications). Primary entrapment protection is provided by constant pressure pushbutton controls with the audio alarm establishes the secondary safety device to meet UL 325 safety requirements. Additionally, the gate operator is UL listed for Class III.

SECURE:

Sallyport locking system that features a keyless three-point positive locking capability making it impossible to open gate except by electrical operation or emergency hand-cranking.

SERVICABLE:

Motor assembly is located at ground level providing easy access for routine inspection of the motor unit and limit assembly.

DURABLE:

The entire drive and locking assemblies are encased in a 10 gauge hot-dip galvanized steel enclosure providing superior protection from inmate tampering and inclement weather conditions.



TECHNICAL DATA:

- **GATE SIZES:**
Standard gate clear opening width 12' to 30' with 1' increments and 14' to 18' clear height with 1' increments
- **ELECTRICAL:**
Electro-mechanical (non-solid state) Controller, motor 1 HP, 110, 120 Volt 60Hz, Single Phase – 208/230, 460 Volt 60Hz, Three-Phase. Variable Speed Controller, motor 1 HP, 208, 230 Volt Single-Phase – 208, 230 Volt Three-Phase. This electrical package offers gate speeds up to 2.2 feet per second.
- **CONTROL WIRING:**
24 Volt
- **GEAR BOX HEATER:**
110 Volt electrical service providing power directly to thermostat controlling the internal gearbox heater
- **MOTOR BOX HOUSING:**
10 gauge galvanized steel containing NEMA 4 electrical enclosure meeting the requirements of UL and equipped with a 6 tumbler paracentric mechanical lock.
- **OVERHEAD TRACK:**
Two 8" (2.03 mm) structural steel channels joined together weighing a total of 34.5 lbs/ft (15.65kg/m).
- **GATE TROLLEYS:**
Milled from a single block of stainless steel and use 2 sealed ball bearings per wheel, 6 wheels per trolley.
- **SUPPORT STRUCTURE:**
4" OD schedule 40 pipe
- **LOCKING COLUMN:**
W-4 "H" beam @ 13 lbs/ft (101.6 mm x 18.9 kg/m)
- **DRIVE CHAIN:**
#60 roller chain



SECUR-PAK SYSTEMS

Maximum Security

SECUR-PAK SYSTEMS

9100A VEHICLE GATE OPERATOR

STANDARD FEATURES:

- Six tumbler paracentric key motor box locks
- 208 VAC Three-Phase
- Easy-to-reach mechanical operation and maintenance access
- Three-point locking
- Enclosed drive
- Manual hand cranking
- Gate sizes 12'-30' wide, 14' to 18' high
- Gear box heater: 110 Volt electrical service providing power directly to thermostat controlling the internal gearbox heater

OPTIONAL FEATURES:

- Remote control panel
- 110 or 220 Volt 60Hz single-phase power
- 460 Volt 60Hz three-phase power
- 50 Hz motors are offered for international projects
- Custom Gate openings
- Photo eyes and/or safety edges
- Special keying

NOTE: The optional features will increase lead time. Also, additional charges will apply depending on application.

