

**Part Numbers and Physical Characteristics**

Listing	Part Number <sup>1</sup>	Configuration	Fiber Type	Fiber Count	Nominal Diameter in (mm)	Nominal Weight lbs/ kft (kg/ km)	Maximum Tensile Loading		Minimum Bend Radius		Package
							Install lbs (N)	Long Term lbs (N)	Install in (mm)	Long Term in (mm)	
OFNR	33004yGzz	Round	Multimode	4	0.20 (5.0)	15 (23)	100 (440)	30 (130)	3.0 (75)	2.0 (50)	<i>use key</i>

**PACKAGING**

	Cut to Length Plywood Reel	1,000 ft BrakeBox	1,500 ft BrakeBox	2,000 ft BrakeBox
<sup>2</sup> Replace "zz" with:	01	BB	BD	BC

**MULTIMODE OPTICAL FIBER TYPES**

	TeraGain® 62.5/125	TeraGain Laser Optimized 50/125			TeraFlex Bend Resistant Laser Optimized 50/125		
		10G/150	10G/300	10G/550	10G/150	10G/300	10G/550
<sup>2</sup> Replace "y" with:	6	A	B	F	M	N	P
Standard Jacket Colors*	Orange	Aqua					