



E5.1–E5.3

- DETAIL NOTES:
1. ALL SECURITY APPLIANCES (CCTV, ACCESS CONTROL) ARE TO BE INSTALLED IN ONE (1) 42U FLOOR MOUNTED LOCKABLE ENCLOSURE.
 2. UPS IS TO BE SIZED TO RUN ALL SECURITY EQUIPMENT FOR ONE (1) HOUR.
 3. PERSONAL PROTECTION DEVICES ARE TO COMMUNICATE WIRELESSLY VIA RF
 4. RISER DIAGRAM IS REPRESENTATIVE OF GENERAL SYSTEM ARCHITECTURE AND APPROXIMATE DEVICE/EQUIPMENT TYPES AND LOCATIONS. PROJECT SPECIFIC Riser DIAGRAM IS TO BE PROVIDED WITH SHOP DRAWINGS AND SHALL BE LAID OUT PER THE MANUFACTURER'S BEST PRACTICES TO ACHIEVE THE DESIGN INTENT RESULTS.

E5.1–E5.3



E5.1–E5.3



E5.1–E5.3