

Annex 1 to Part 4
Technical Evaluation Sheet

MANDATORY REQUIREMENT										TECHNICAL BID				
ITEM NO.	COMPONENT CODE	COMPONENT NAME/DESCRIPTION	SPECIFICATIONS FOR EQUIVALENT PRODUCTS	LISTED PRODUCT			QUANTITY	DELIVERY REQUIRED (Yes/No)	INSTALL REQUIRED (Yes/No)	LISTED PRODUCT PROPOSED? YES/NO	PROPOSED EQUIVALENT PRODUCT			
				PRODUCT NUMBER/DESCRIPTION	MANFACTURER	COLOUR/FINISH					PRODUCT NUMBER/ DESCRIPTION	MANFACTURER	COLOUR/FINISH	SUBSTANTIATION
1	ICEC-01	Ice Caddy	- Dimension: 559mm W (with handle) x 781mm D (with handle) x 927 mm H (22"W x 30.75"D x 36.5"H) - 91 KG (200 lb.) ice capacity (approximately 95 L [25 gallons]) - NSF International Certified - Foam insulation - Rounded inside corners - Interior sloped base for complete water drainage; Water must drain away from ice - Front faucet - Removable lid iwth stainless steel, reinforced hinges to open and lay flat against side of unit - Rolling, heavy-duty casters; 254mm (10") non-marking back wheels - Dual handles - Color: Black	Heavy Duty Insulated Ice Caddy Model #IC222003 Cater aide™ Ice Caddy 200 lb. of ice	Carlisle Foodservice Products	Color: Black	16	YES	YES					
2	Cooler	Cooler	- Maximum Dimension: 914 mmL x 457 mmW x 432 mmH (36"L x 18"W x 17"H) - 95 Liter (100 Quarts) Capacity - Fits 2-liter bottles upright - Quick access hatch - Stain and odor resistant liner - UV inhibitors in body and lid - Reinforced swing-up handles with tie-down loop - Dual snap-fit lid latches secure lid closure - Threaded drain plug for hose hook up - Keeps ice solid for five (5) days - Color: White	Portable Quick & Cool 100 Quart 95 Liter (100 Quart) Capacity Dimension: 895 mmL x 441 mmW x 425 mmH (35-1/4"L x 17.38"W x 16-3/4"H)	Igloo by Brandshop	Color: White	5	YES	YES					
3	CART-17	Cart - Utility	- 1149 mmL x 657 mmW x 845 mm (25.9"L x 45.2"W x 33.2"H) - Minimum mass capacity: 226.8 kg (500 lbs.) - Structural foam molding, won't rust, dent, chip, peel proof - High density structural resin construction - Molded-in storage compartments, holster, hooks and notches - Rounded corners - 127 mm (5") non-marking swivel casters - Push handle - Perimeter lip around shelves for containing contents - Easy-access bottom shelf - Color: Black	Heavy-duty Order No.: FG452088 BLA 4520-88 HD 2-Shelf Utility Cart w/Lipped Shelf (med)	Rubbermaid Commercial Products	Color: Black	16	YES	YES					
4	CART-06	Cart - Food Pan	- Holds 24 qty. 64 mm (2-1/2" Deep), 16 qty. 100 mm (4") Deep, 12 qty. 152 mm (6") Deep, 8 qty. 203 mm (8") Deep Food Pans of hot or cold food - Maximum Size: 864 mmD x 762 mmW x 1397 mmH (34"D x 30"W x 55"H) - Fully insulated throughout to hold and transport food safely 4 + hours with no electricity needed - Airtight gasket and vent caps on doors to maintain balance of food moisture and heat - NSF International Certified - Color: No specific color required	Thermal UPC1600 Ultra Camcarts for Food Pans Dimension: 815 mmD x 710 mmW x 1375 mmH (32-1/4"D x 28-1/8"W x 53-1/4"H)	Cambro USA	No specific color required	6	YES	YES					
5	CART-07	Cart - Food Pan	- Holds 8 qty. 100 mm (4") deep food pans - Maximum Dimension: 762 mmD x 609 mmW x 1524 mmH (30"D x 24"W x 60"H) - Electric cart (110V) to hold hot food a minimum of 4 hours - Energy-efficient heaters in the doors; resets to safe temps within 3 minutes - To use less energy than 3 standard 100 watt light bulbs - NSF International Certified - Color: No specific color required	Heated Electric Model: UPOCH800 Heated Carts Heated Camcart, 110V Dimension: 690 mmD x 520 mmW x 1372 mmH (27-1/8"D x 20-1/2"W x 54"H)	Cambro USA	Color: Black 110	4	YES	YES					

6	CART-11	Cart - Queen Mary	<ul style="list-style-type: none"> - Designed for setting-up and bussing of banquets, heavy loads - Five (5) Shelves Sized: 686 mm (27") x 1524 mm (60"), spaced 305 mm (12") apart - Shelf Edges Up: 3 Sides Up - Front Edge Down - Heavy-duty, high tensile extruded aluminum and .090 aluminum sheet - All welded construction - no rivet - Open Welded Tubular Frame - Full wrap around perimeter non-marking bumper - NSF International Approved 203 mm x 51 mm (8" x 2") polyurethane casters, two (2) rigid and two (2) swivel with brake - One (1) aluminum handle tubing welded to unit - 2000 lb. capacity - Color / Finish: No specific color required - Minimum Two (2) Year Warranty 	Model: UCU-60-512AL Heavy-Duty Aluminum Utility Carts Series: UC-AL Five (5) Shelves Sized 686 mm x 1524 mm (27" x 60") Two (2) Year Warranty	Food Warming Equipment Company Inc.	No specific color required	4	YES	NO					
7	SMAL-01_001	Bus Box	<ul style="list-style-type: none"> - Bus / Utility Box, Single Compartment - Minimum dimension: 508 mmD x 381 mmW x 127 mmH (20"D x 15"W x 5"H) - BPA-Free (bisphenol A) - NSF International Certified - Commercial grade plastic - Reinforced handles, bottom and ribs - Rounded Corners - Commercial dishwasher safe - Color: Gray 	Single Compartment, Gray Order No.: FG334900 GRAY 3349 Bus / Utility Box 17.5 Liter (4-5/8 Gallon) (12 per pack)	Rubbermaid Commercial Products	Color: Gray	96	YES	NO					
8	SMAL-01_002	Bus Box	<ul style="list-style-type: none"> - Bus / Utility Box, Single Compartment - Minimum dimension: 508 mm (20")D x 381 mm (15")W x 127 mm (5")H - BPA-Free (bisphenol A) - NSF International Certified - Commercial grade plastic - Reinforced handles, bottom and ribs - Rounded Corners - Commercial dishwasher safe - Color: White 	Single Compartment, White Order No.: FG334900 WHT 3349 Bus / Utility Box 17.5 Liter (4-5/8 Gallon) (12 per pack)	Rubbermaid Commercial Products	Color: White	49	YES	NO					
9	SMAL-01_003	Can Opener	<ul style="list-style-type: none"> - Bottle / Can opener - Overall Length: 178 mm (7") Long - Hardened carbon steel cutting wheel - All steel construction - Crank handle with comfort grips - Color: No specific color required 	Portable Can Opener Swing-A-Way	Amco Houseworks	Color: White	4	YES	NO					
10	SMAL-01_004	Carafe - Thermal Cream	<ul style="list-style-type: none"> - Thermal Carafe, round - Capacity: 946 ml (32 oz.) - Minimum Dimensions: 150 mmL x 100 mm W x 279 mm H (5.9"L x 3.9"W x 11"H) - Handle for no spill pouring - Etched with "Cream" in black lettering - Dishwasher safe - 2-3 hour cold temperature retention - Minimum Five Year Warranty - Base Finish: Stainless steel - Lid and Handle Color: Black 	Model: 24989 Thermos Stainless Steel Thermal Carafe Cream 946 ml (32 oz.), Etched with "Cream" Five (5) Year Warranty	Hubert Canada	Base Finish: Stainless steel Lid and Handle Color: Black	6	YES	NO					
11	SMAL-01_005	Carafe - Thermal Milk	<ul style="list-style-type: none"> - Thermal Carafe, round - Capacity: 946 ml (32 oz.) - Minimum Dimensions: 150 mmL x 100 mmW x 279 mmH (5.9"L x 3.9"W x 11"H) - Handle for no spill pouring - Etched with "Milk" in black lettering - Dishwasher safe - 2-3 hour cold temperature retention - Minimum Five Year Warranty - Base Finish: Stainless steel - Lid and Handle Color: Black 	Model: 36578 Thermos Stainless Steel Thermal Carafe Milk 946 ml (32 oz.), Etched with "Milk" Five (5) Year Warranty	Hubert Canada	Base Finish: Stainless steel Lid and Handle Color: Black	6	YES	NO					

12	SMAL-01_006	Carafe - Thermal Skim Milk	<ul style="list-style-type: none"> - Thermal Carafe, round - Capacity: 946 ml (32 oz.) - Minimum Dimensions: 150 mmL x 100 mmW x 279 mmH (5.9"L x 3.9"W x 11"H) - Handle for no spill pouring - Etched with "Skim" in black lettering - Dishwasher safe - 2-3 hour cold temperature retention - Minimum Five Year Warranty - Base Finish: Stainless steel - Lid and Handle Color: Black 	Model: 35735 Thermos Stainless Steel Thermal Carafe Skim 946 ml (32 oz.), Etched with "Skim" Five (5) Year Warranty	Hubert Canada	Base Finish: Stainless steel Lid and Handle Color: Black	6	YES	NO						
13	SMAL-01_007	Carafe - Thermal Server	<ul style="list-style-type: none"> - 2 Liter (64 oz.) Capacity carafe - Shatterproof vacuum stainless steel liner - Outer Body: Industry strength stainless steel - Keeps beverage hot or cold up to 8 hours - Lock design - Press and Pour thumb lever - Ergonomic handle - Commercial dishwasher safe - Identity arrow coding system for content identification - Outer Body Finish: Stainless Steel - Lever and Handle Color: Black 	Insulated Product No.: 4120/20 Aromis Thermal Server 4120 2 Liter (64 oz.) Capacity	Kinox	Outer Body Finish: Stainless Steel Lever and Handle Color: Black	48	YES	NO						
14	SMAL-01_008	Chafing Dish - Electric	<ul style="list-style-type: none"> - Rectangular - Set to include: - <u>Chafer with Frame:</u> - 9L (2.3gal)- 13.5L (3.56gal) - Two (2) 100 mm (4") deep food pans - Frame - Cover - Wire lid holder - Finish: Stainless Steel - Color: No specific color required - <u>Electric Water Pan</u> - Temperature Control - Compatible with wire lid on chafer 	Chafer with Frame Model: X81187A-3 Full size electric chafer with frame Shape: Rectangular Two (2) 100 mm (4") Deep Food Pans, Electric Water Basin, Includes Cover and Wire Lid Holder Electric Water Pan Model: 82189A-3	Sunnex	Chafer Finish: Stainless Steel <u>Electric Water Pan</u> Colour: Black	24	YES	NO						
15	SMAL-01_009	China Cap Strainer	<ul style="list-style-type: none"> - To make fine stuffings and to strain sauces - Minimum Handle Size: 190 mm (7-1/2") - Heat resistant up to 221° C (430° F) - Dishwasher safe - Body and handle made of composite material - One-piece ergonomic, insulated handle - Hygienic stainless steel mesh - Stainless steel protective cross wires - Two (2) hooks for extra stability - Color: No specific color required 	Bouillon Model: 017360 Exoglass Bouillon Strainer 203 mm (8") Cone	Matfer Bourgeat	Color: Black	2	YES	NO						
16	SMAL-01_010	Cleaning Brush	<ul style="list-style-type: none"> - Wire brushes and stainless steel metal scrapers to remove heavy Carbon deposits, rust and burned-on food build up - Minimum Length: 215 mm (8.5") - Minimum Width: 127 mm (5") - Minimum Height: 381 mm (1.5") - Overall Length Minimum 774 mm (30.5") - Treated wooden head with two-sided Stainless or Carbon Steel bristles, a metal end Scraper - Double-sided: One side of the brush with semi-stiff bristles and one side with stiff bristles - Color: No specific color required 	Broiler / Panini Machine Item No.: 4029000 Product No.: 40290 Sparta Broiler Master with Stainless Steel Bristles 3.5"	Carlisle Foodservice Products	Color: No specific color required	6	YES	NO						

17	SMAL-01_011	Cutting Board	<p>Item No.: 1088600 Product No.: 10886 Spectrum Cutting Board Assortment Pack 15", 20" x 1/2" Dimension: 457 mm x 610 mm x 13 mm (15" x 20" x 1/2")</p> <ul style="list-style-type: none"> - Assortment of six (6) boards, size: 368-394mm x 495-521mm x 12.7-19mm (14.5-15.5" x 19.5-20.5" x 1/2-3/4") - Meets HACCP guidelines - High Density Polyethylene construction - Warp-resistant cutting board - Surface texture to prevent deep cuts - NSF International Certified; (Permanent NSF International logo) - Dishwasher safe - Rounded corners - BPA (Bisphenol A) free - Color: Six (6) different colored cutting boards required (Colors to include: blue, green, red, white, yellow, and tan) 	Assortment Pack of Six (6) Qty., Color Coded assortment	Carlisle Foodservice Products	Color Pack Assortment, One (1) each of: Blue, Green, Red, White, Yellow, and Tan	12 (boards)	YES	NO					
18	SMAL-01_012	Cutting Board	<ul style="list-style-type: none"> - Assortment of six (6) boards, size: 446-470mm x 597-622mm x 12.7-19mm (17.5-18.5" x 23.5-24.5" x 1/2-3/4") - Meets HACCP guidelines - High Density Polyethylene construction - Warp-resistant cutting board - Surface texture to prevent deep cuts - NSF International Certified; (Permanent NSF International logo) - Dishwasher safe - Rounded corners - BPA (Bisphenol A) free - Color: Six (6) different colored cutting boards required (Colors to include: blue, green, red, white, yellow, and tan) 	Assortment Pack of Six (6) Qty., Color Coded assortment Item No.: 1088300 Product No.: 10883 Spectrum Cutting Board Assortment Pack 18", 24", 1/2" Dimension: 457 mm x 610 mm x 13 mm (18" x 24" x 1/2") (6 per pack)	Carlisle Foodservice Products	Color Pack Assortment: One (1) each of: Blue, Green, Red, White, Yellow, and Tan	12 (boards)	YES	NO					
19	SMAL-01_013	Cutting Board - Rack	<ul style="list-style-type: none"> - Maximum overall dimension: 279 mm x 229 mm x 279 mm (11"L x 9"W x 11"H) - Holds up to six (6) boards measuring up to 19mm (3/4") thick, with the dimensions ranging from 229 mm x 309 mm x to 610 mm x 457 mm (9" x 12" to 24" x 18") - Stainless Steel construction - Handles and non-flip feet - Rust resistant - Dishwasher safe - Finish: Stainless steel - Color: Not applicable 	Counter Model: KLRST Cutting Board Accessories Cutting board storage stand with non-slip feet 6-Board Capacity	San Jamar	Finish: Stainless Steel Color: Not applicable	2	YES	NO					
20	SMAL-01_014	Disher	<ul style="list-style-type: none"> - 33.3 mil (1.13oz. / 2-1/4 Tablespoons) Capacity - Bowl diameter: 48 mm (1-7/8") - Stainless steel bowl and shaft - Extended length handle to work with all steamable pan depths - NSF International Certified - Color coded for easy size identification - Capacity marked on disher for accurate portion control - 2 part construction to prevent loss of parts - Thumb or hand squeeze operation with integral return mechanism with no springs to break - Universal handle for right or left handed users - Not required for use with ice cream, frozen foods or other hard food products - All dishes to be from same manufacturer and series - Handle Color: Black 	Model: 47377 Extended Length Color-Coded Squeeze Dishes 33.3 mil (1.13 oz. / 2-1/4 Tablespoons) Capacity	The Vollrath Company	Handle Color: Black	6	YES	NO					
21	SMAL-01_015	Disher	<ul style="list-style-type: none"> - 59.5 mil (2 oz. / 1/4 Cup) Capacity - Bowl diameter: 57 mm (2-1/4") - Stainless steel bowl and shaft - Extended length handle to work with all steamable pan depths - NSF International Certified - Color coded for easy size identification - Capacity marked on disher for accurate portion control - 2 part construction to prevent loss of parts - Thumb or hand squeeze operation with integral return mechanism with no springs to break - Universal handle for right or left handed users - Not required for use with ice cream, frozen foods or other hard food products - All dishes to be from same manufacturer and series - Handle Color: Royal Blue 	Model: 47374 Extended Length Color-Coded Squeeze Dishes 59.5 mil (2 oz. / 1/4 Cup) Capacity	The Vollrath Company	Handle Color: Royal Blue	6	YES	NO					

22	SMAL-01_016	Disher	<ul style="list-style-type: none">- 83.6 mil (2.8 oz. / 1/3 Cup) Capacity- Bowl diameter: 64 mm (2-1/2")- Stainless steel bowl and shaft- Extended length handle to work with all steamable pan depths- NSF International Certified- Color coded for easy size identification- Capacity marked on disher for accurate portion control- 2 part construction to prevent loss of parts- Thumb or hand squeeze operation with integral return mechanism with no springs to break- Universal handle for right or left handed users- Not required for use with ice cream, frozen foods or other hard food products- All dishers to be from same manufacturer and series- Handle Color: Green	Model: 47373 Extended Length Color-Coded Squeeze Dishers 83.6 mil (2.8 oz. / 1/3 Cup) Capacity	The Vollrath Company	Handle Color: Green	6	YES	NO					
23	SMAL-01_017	Disher	<ul style="list-style-type: none">- 109.5 mil (3.7 oz. / 1/2 Cup) Capacity- Bowl diameter: 73 mm (2-7/8")- Stainless steel bowl and shaft- Extended length handle to work with all steamable pan depths- NSF International Certified- Color coded for easy size identification- Capacity marked on disher for accurate portion control- 2 part construction to prevent loss of parts- Thumb or hand squeeze operation with integral return mechanism with no springs to break- Universal handle for right or left handed users- Not required for use with ice cream, frozen foods or other hard food products- All dishers to be from same manufacturer and series- Handle Color: Grey	Model: 47371 Extended Length Color-Coded Squeeze Dishers 109.5 mil (3.7 oz. / 1/2 Cup) Capacity	The Vollrath Company	Handle Color: Grey	6	YES	NO					
24	SMAL-01_018	Dishware Rack - Base	<ul style="list-style-type: none">- For pots, pans, bowls and large prep, service and display items- No extender- Minimum Inside Rack Height: 83 mm (3-1/4")- Minimum Outside Rack Height: 101 mm (4")- Polypropylene construction to withstand chemicals and high temperatures up to 200°F (93.3°C)- Inter-stacks with all other racks- Fits through any commercial dishwasher- Color: No specific color required	Model: BR258 Camrack Base Racks, Full Size, No Extender	Cambro USA	Color: Soft Grey (151)	16	YES	NO					
25	SMAL-01_019	Dishware Rack - Cup	<ul style="list-style-type: none">- Wash, store and transport mugs and cups- 16 Compartment- Maximum Cup Diameter with Handle: 111 mm (4-3/8")- Maximum Cup Height: 66 mm (2-5/8")- Open inside compartments- Closed external walls- Tilt feature drains- Smooth sides, rounded corners and top rim- Polypropylene construction withstands chemicals and high temperatures up to 200°F (93.3°C)- Fits through any commercial dishwasher- Color: No specific color required	Model: 16C258 Camrack Cup Racks Full Size, 16 Compartment	Cambro USA	Color: Soft Grey (151)	48	YES	NO					
26	SMAL-01_020	Dishware Rack - Flatware	<ul style="list-style-type: none">- Soak, wash and display silverware- Inside Rack Height: 67 mm (2-5/8")- Outside Rack Height: 101 mm (4")- Open design to promote thorough washing and complete drainage- Polypropylene construction to withstand chemicals and high temperatures up to 200°F (93.3°C)- Smooth top rim- Inter-stacks with all other racks- Fits through any commercial dishwasher- Color: No specific color required	Model: FR258 Camrack Flatware Racks Full Flatware Rack	Cambro USA	Color: Soft Grey (151)	16	YES	NO					
27	SMAL-01_021	Dishware Rack - Flatware	<ul style="list-style-type: none">- Soak, wash and display silverware- Inside Rack Height: 12 mm (4-3/4")- Outside Rack Height: 184 mm (7-1/4")- Open design to promote thorough washing and complete drainage- Durable polypropylene to withstand chemicals and high temperatures up to 200°F (93.3°C)- Smooth top rim- Inter-stacks with all other racks- Fits through any commercial dishwasher- Color: No specific color required	Model: 8FB434 Camrack Flatware Racks 8 Compartment Half Size Flatware Rack	Cambro USA	Color: Soft Grey (151)	12	YES	NO					

28	SMAL-01_022	Dishware Rack - Glass	<ul style="list-style-type: none"> - For large diameter beverage glasses, red wine stems, goblets, and most rocks glasses - Compartment size: 89 mm (3-1/2") x 89 mm (3-1/2") - Inside Rack Height: 161 mm (6.36") - Outside Rack Height: 180 mm (7.12") - Accommodates glasses up to 83mm (3-1/4") in diameter - Made of polypropylene - Dishwasher safe - NSF International Certified - Color: No specific color required 	Full Size, 25-Compartment Item No.: RG25-214 Product No.: RG25-2 Opticlean 25-Compartment Glass Rack, w/2 Extenders, Carlisle Blue	Carlisle Food Service Products	Colour: Carlisle Blue (14)	48	YES	NO					
29	SMAL-01_023	Dishware Rack - Peg & Tray	<ul style="list-style-type: none"> - For plates, bowls, trays and plate covers - 9 x 9 row peg rack for standard plates - Inside Rack Height: 83 mm (3-1/4") - Polypropylene construction to withstand chemicals and high temperatures up to 200°F (93,3°C) - Smooth top rim - Inter-stacks with all other racks - Fits through any commercial dishwasher - No specific color required 	Full Size Model: PR314 Camrack Peg and Tray Racks 9 Rows by 9 Rows, No Extenders	Cambro USA	Color: Soft Grey (151)	16	YES	NO					
30	SMAL-01_024	Dishware - Coffee Cup	<ul style="list-style-type: none"> - Capacity: 207 mL (7 oz.) coffee cup - Fully glazed vitrified china - Fully glazed foot - Stackable - Color: White - Dishware Coffee Cup - Saucer to be compatible with both Dishware - Coffee Cup and Dishware - Soup / Fruit Salad Cup - All dishware to be from the same manufacturer and pattern/series 	Model: 810-70C 207 mL (7oz), Coffee Cup Stackable (Standard Foot) Pattern: Diana	Cameo China	Color: White	1512	YES	NO					
31	SMAL-01_025	Dishware - Coffee Cup, Saucer	<ul style="list-style-type: none"> - 152 mm dia. (6") coffee cup saucer - Fully glazed vitrified china - Fully glazed foot - Stackable - Color: White - Dishware Coffee Cup - Saucer to be compatible with both Dishware Coffee Cup and Dishware Soup Cup / Fruit Salad - All dishware to be from the same manufacturer and pattern/series 	Model: 810-70S Pattern: Diana 152 mm Diameter, (6") Saucer	Cameo China	Color: White	1512	YES	NO					
32	SMAL-01_026	Dishware - Deep Plate / Pasta Bowl	<ul style="list-style-type: none"> - 292 mm, 340 mL (11-1/2", 16 oz.) deep pasta/soup plate - Fully glazed vitrified china thin - Fully glazed foot - Stackable - Color: White - All plates and bowls to be compatible - All dishware to be from the same manufacturer and pattern/series 	Model: 810-112 Pattern: Diana 292 mm Diameter, 340 mL (11-1/2", 16 oz.) Soup Plate	Cameo China	Color: White	372	YES	NO					
33	SMAL-01_027	Dishware - Flat Plate	<ul style="list-style-type: none"> - 159 mm (6-1/4") dia. rimmed plate - Fully glazed vitrified china - Fully glazed foot - Stackable - Color: White - All plates and bowls to be compatible - All dishware to be from the same manufacturer and pattern/series 	Bread Butter Model: 810-61 Pattern: Diana 159 mm (6-1/4") Diameter Rim Plate	Cameo China	Color: White	1512	YES	NO					
34	SMAL-01_028	Dishware - Flat Plate	<ul style="list-style-type: none"> - Maximum Size: 254 mm (10") rimmed plate - Fully glazed vitrified china thin - Fully glazed foot - Stackable - Color: White - All plates and bowls to be compatible - All dishware to be from the same manufacturer and pattern/series 	Luncheon Model: 810-91A Pattern: Diana 250.8 mm 9-7/8") Diameter Rim Plate	Cameo China	Color: White	1512	YES	NO					
35	SMAL-01_029	Dishware - Soup / Fruit Salad Cup	<ul style="list-style-type: none"> - 102 mm dia., 295 mL (4", 10 oz.), soup cup no handle - Fully glazed vitrified china thin - Fully glazed foot - Stackable - Color: White - Dishware - Coffee Cup, Dishware - Coffee Cup, Saucer and Dishware - Soup / Fruit Salad Cup to be compatible - All plates and bowls to be compatible - All dishware to be from the same manufacturer and pattern/series 	Model: 810-40CN Pattern: Diana 102 mm Diameter., 295 mL (4", 10 oz.). Soup Cup No Handle (Standard Foot)	Cameo China	Color: White	912	YES	NO					

36	SMAL-01_030	Dispenser - Film and Foil	<ul style="list-style-type: none"> - Maximum Size: 508 mm Long x 216 mm Wide x 178 mm High (20" Long x 8.5" Wide x 7" High) - Holds film and foil rolls minimum up to 914.4 meter (3000 feet), and range from 304 mm (12") or 457 mm (18") wide - Table Model - Construction, Body is: Hi Impact ABS plastic and Lid: Polycarbonate - NSF International Certified - Complies with HACCP (Hazard analysis and critical control points) and Food Code standards - Dishwasher safe - 100% Finger access - Safety blade or slide cutter - Non slip feet - Accommodates end spindles or dowel rod - Integrated blade storage - Adjustable clips to center 12" or 15" rolls to up to 914.4 meter (3000 feet) - Color: No specific color required 	Model: KenKut 3 Film and Foil Dispenser/Cutter Holds Rolls up to: 457 mm Wide x 914.4 Meters Long (18" Wide x 3,000 Feet Long) Dimension: 508 mm Long x 216 mm Wide x 178 mm High (20" Long x 8-1/2" Wide x 7" High)	KenKut	Color: White	4	YES	NO					
37	SMAL-01_031	Dispenser - Film and Foil	<ul style="list-style-type: none"> - Maximum Size: 686 mmL x 216 mmW x 178 mmH (27" Long x 8.5" Wide x 7" High) - Holds film and foil rolls minimum up to 914.4 meter (3000 feet), and maximum 610 mm (24") wide - Table Model - Construction: Body is Hi Impact ABS plastic and Lid: Polycarbonate - NSF International Certified - Complies with HACCP (Hazard analysis and critical control points) and Food Code standards - Dishwasher safe - 100% Finger access - Safety blade or slide cutter - Non slip feet - Accommodates end spindles or dowel rod - Integrated blade storage - Adjustable clips to center 12" or 15" rolls to up to 914.4 meter (3000 feet) - Color: No specific color required 	Model: KenKut 2.5 Film and Foil Dispenser/Cutter Holds Rolls up to: 610 mm Wide x 914.4 Meters Long (24" Wide x 3,000 Feet Long) Dimension: 686 mm Long x 216 mm Wide x 190 mm High (27" Long x 8-1/2" Wide x 7-1/2" High)	KenKut	Color: White	6	YES	NO					
38	SMAL-01_033	Dough Scraper	<ul style="list-style-type: none"> - 152 mm x 76 mm (6" x 3") - Blade size: 152 mm (6") - Heavy duty stainless steel blade - Dishwasher safe - Polypropylene handle - Handle Color: No specific handle color required 	Model: 16267 Hubert 152 mm x 76 mm (6" x 3") Dough Scraper With Black Handle	Hubert Canada	Handle Color: Black	6	YES	NO					
39	SMAL-01_034	Flatware - Fork	<ul style="list-style-type: none"> - Maximum Size: 190 mm (7-1/2") Long Fork - 18/0 stainless steel - Finish: Polished Chrome - Dishwasher safe - Smooth basic pattern - All flatware to be from the same manufacturer and series 	Model: S603 Pattern: Windsor Medium weight, 18/0 stainless steel 181 mm (7-1/8") Long Fork	Alegacy, Foodservice Products Group, Inc.	Finish: Polished Chrome	1512	YES	NO					
40	SMAL-01_035	Flatware - Knife	<ul style="list-style-type: none"> - Maximum Size: 203 mm (8") Long Wave Cut Knife - 18/0 stainless steel - Finish: Polished Chrome - Dishwasher safe - Smooth basic pattern - All flatware to be from the same manufacturer and series 	Model: S900 Pattern: Windsor Medium weight, 18/0 stainless steel 200 mm (7-7/8") Long Knife-Wave Cut	Alegacy, Foodservice Products Group, Inc.	Finish: Polished Chrome	1512	YES	NO					
41	SMAL-01_036	Flatware - Spoon	<ul style="list-style-type: none"> - Maximum Size: 178 mm (7") Long Dessert Spoon - 18/0 stainless steel - Finish: Polished Chrome - Dishwasher safe - Smooth basic pattern - All flatware to be from the same manufacturer and series 	Dessert Spoon Model: S604 Pattern: Windsor Medium weight, 18/0 stainless steel 175 mm (6-7/8) Long Dessert Spoon	Alegacy, Foodservice Products Group, Inc.	Finish: Polished Chrome	1512	YES	NO					

42	SMAL-01_037	Flatware - Spoon	<ul style="list-style-type: none"> - 152 mm (6") Long Teaspoon - 18/0 stainless steel - Finish: Polished Chrome - Dishwasher safe - Smooth basic pattern - All flatware to be from the same manufacturer and series 	Teaspoon Model: 5602 Pattern: Windsor Medium weight, 18/0 stainless steel 152 mm (6") Long	Alegacy, Foodservice Products Group, Inc.	Finish: Polished Chrome	1512	YES	NO					
43	SMAL-01_038	Flatware - Knife	<ul style="list-style-type: none"> - Maximum Overall Length: 216 mm (8 1/2") - Stainless Steel Blade - Poly Handle 	Steak Knife Model: 201 2705 Plastic & Stainless Steel Handled Steak Knives Overall Length: 216 mm (8 1/2") Economy Poly Handle	Libbey Inc.	Handle Color: Black	132	YES	NO					
44	SMAL-01_039	Flatware - Storage Bin	<ul style="list-style-type: none"> - 4 compartment storage/dispensing of silverware and condiment packets - Maximum Size: 546 mm L (21.5") x 292 mm W (11.5") x 100 mm H (4") - Commercial grade plastic; injection molded - Ribbed design - BPA-Free (Bisphenol A) - Color: No specific color required 	Order No.: FG336200 GRAY Cutlery Bin, 4 Compartments Dimensions: 540 mm Long x 292 mm Wide x 95 mm High (21.2" Long x 11.5" Wide x 3.8" High)	Rubbermaid Commercial Products	Color: Gray	7	YES	YES					
45	SMAL-01_040	Food Pan - Hot/Cold	<ul style="list-style-type: none"> - 8.5 Liter (8.9 Quart) Capacity - 65 mm (2-1/2") Deep - Polycarbonate construction - Withstands temperatures from -40° F -210° F (-40°C -99°C) - Precisely designed to Gastronorm GN specifications - Non-stick smooth interior surface - Uniform 1.27 cm (1/2") flange - Stack neatly, without wedging or sticking - NSF International Certified - Color: Clear - All Food Pan - Hot/Cold and Lids to be from same manufacturer and series 	Model: 12CW Camwear Pans Full Size 8.5 Liter (8.9 Quart) Capacity 65 mm (2-1/2") Deep	Cambro USA	Colour: Clear (135)	24	YES	NO					
46	SMAL-01_041	Food Pan - Hot/Cold	<ul style="list-style-type: none"> - 13.0 Liter (13.7 Quart) Capacity - 100 mm (4") Deep - Polycarbonate construction - Withstands temperatures from -40° F -210° F (-40°C -99°C) - Precisely designed to Gastronorm GN specifications - Non-stick smooth interior surface - Uniform 1.27 cm (1/2") flange - Stack neatly, without wedging or sticking - NSF International Certified - Color: Clear - All Food Pan - Hot/Cold and Lids to be from same manufacturer and series 	Model: 14CW Camwear Pans Full Size 13.0 Liter (13.7 Quart) Capacity 100 mm (4") Deep	Cambro USA	Colour: Clear (135)	24	YES	NO					
47	SMAL-01_042	Food Pan - Hot/Cold Lid	<ul style="list-style-type: none"> - Maximum Size: 533 mm x 330 mm (21" x 13") - Polycarbonate construction - Withstands temperatures from -40° F -210° F (-40°C -99°C) - Color: Clear - All Food Pan - Hot/Cold and Lids to be from same manufacturer and series 	Model: 10CWCH Camwear Food Pan Lids Full Size, Lid with Handle Dimensions: 530 mm x 325 mm (20-7/8" x 12-3/4")	Cambro USA	Colour: Clear (135)	48	YES	NO					
48	SMAL-01_043	Food Pan - Hot/Cold	<ul style="list-style-type: none"> - 3.9 Liter (4.1 Quart) Capacity - 65 mm (2.5") Deep - Polycarbonate construction - Withstands temperatures from -40° F -210° F (-40°C -99°C) - Precisely designed to Gastronorm GN specifications - Non-stick smooth interior surface - Uniform 1.27 cm (1/2") flange - Stack neatly, without wedging or sticking - NSF International Certified - Color: Clear - All Food Pan - Hot/Cold and Lids to be from same manufacturer and series 	Model: 22CW Camwear Pans Half Size 3.9 Liter (4.1 Quart) Capacity 65 mm (2-1/2") Deep	Cambro USA	Colour: Clear (135)	24	YES	NO					
49	SMAL-01_044	Food Pan - Hot/Cold	<ul style="list-style-type: none"> - 5.9 Liter (6.3 Quart) Capacity - 100 mm (4") Deep - Polycarbonate construction - Withstands temperatures from -40° F -210° F (-40°C -99°C) - Precisely designed to Gastronorm GN specifications - Non-stick smooth interior surface - Uniform 1.27 cm (1/2") flange - Stack neatly, without wedging or sticking - NSF International Certified - Color: Clear - All Food Pan - Hot/Cold and Lids to be from same manufacturer and series 	Model: 24CW Camwear Pans Half Size 5.9 Liter (6.3 Quart) Capacity 100 mm (4") Deep	Cambro USA	Colour: Clear (135)	24	YES	NO					

50	SMAL-01_045	Food Pan - Hot/Cold Lid	<ul style="list-style-type: none"> - Maximum Size: 330 mm x 280 mm (13" x 11") - Polycarbonate construction - Withstands temperatures from -40° F -210° F (-40°C -99°C) - Color: Clear - All Food Pan - Hot/Cold and Lids to be from same manufacturer and series 	Model: 20CWCH Camwear Food Pan Lids Half Size, Cover with Handle Dimension: 325 mm x 265 mm (12-3/4" x 10-7/16")	Cambro USA	Colour: Clear (135)	48	YES	NO					
51	SMAL-01_046	Food Pan - Hot/Cold	<ul style="list-style-type: none"> - 3 Liter (3.2 Quart) Capacity - 65 mm (2.5") Deep - Polycarbonate construction - Withstands temperatures from -40° F -210° F (-40°C -99°C) - Precisely designed to Gastronorm GN specifications - Non-stick smooth interior surface - Uniform 1.27 cm (1/2") flange - Stack neatly, without wedging or sticking - NSF International Certified - Color: Clear - All Food Pan - Hot/Cold and Lids to be from same manufacturer and series 	Model: 22LPCW Camwear Pans Half Size Long 3 Liter (3.2 Quart) Capacity 65 mm (2.5") Deep	Cambro USA	Colour: Clear (135)	12	YES	NO					
52	SMAL-01_047	Food Pan - Hot/Cold	<ul style="list-style-type: none"> - 5 Liter (5.3 Quart) Capacity - 100 mm (4") Deep - Polycarbonate construction - Withstands temperatures from -40° F -210° F (-40°C -99°C) - Precisely designed to Gastronorm GN specifications - Non-stick smooth interior surface - Uniform 1.27 cm (1/2") flange - Stack neatly, without wedging or sticking - NSF International Certified - Color: Clear - All Food Pan - Hot/Cold and Lids to be from same manufacturer and series 	Model: 24LPCW Camwear Pans Half Size Long 5 Liter (5.3 Quart) Capacity 100 mm (4") Deep	Cambro USA	Colour: Clear (135)	12	YES	NO					
53	SMAL-01_048	Food Pan - Hot/Cold Lid	<ul style="list-style-type: none"> - Maximum Size: 533 mm x 178 mm (21" x 7") - Polycarbonate construction - Withstands temperatures from -40° F -210° F (-40°C -99°C) - Color: Clear - All Food Pan - Hot/Cold and Lids to be from same manufacturer and series 	Model: 20LPCWC Camwear Food Pan Lids Half Size Long, Flat Cover Dimensions: 530 mm x 162 mm (20-7/8" x 6-3/8")	Cambro USA	Colour: Clear (135)	24	YES	NO					
54	SMAL-01_049	Food Pan - Hot/Cold	<ul style="list-style-type: none"> - 2.4 Liter (2.5 Quart) Capacity - 65 mm (2.5") Deep - Polycarbonate construction - Withstands temperatures from -40° F -210° F (-40°C -99°C) - Designed to Gastronorm GN specifications - Uniform 127 mm (1/2") flange, to fit in prep tables and food bars - Non-stick smooth interior surface - Stack neatly, without wedging or sticking - NSF International Certified - Color: Clear - All Food Pan - Hot/Cold and Lids to be from same manufacturer and series 	Model: 32CW Camwear Pans Third Size 2.4 Liter (2.5 Quart) Capacity 65 mm (2.5") Deep	Cambro USA	Colour: Clear (135)	24	YES	NO					
55	SMAL-01_050	Food Pan - Hot/Cold	<ul style="list-style-type: none"> - 3.6 Liter (3.8 Quart) Capacity - 100 mm (4") Deep - Polycarbonate construction - Withstands temperatures from -40° F -210° F (-40°C -99°C) - Designed to Gastronorm GN specifications - Uniform 127 mm (1/2") flange, to fit in prep tables and food bars - Non-stick smooth interior surface - Stack neatly, without wedging or sticking - NSF International Certified - Color: Clear - All Food Pan - Hot/Cold and Lids to be from same manufacturer and series 	Model: 34CW Camwear Pans Third Size 3.6 Liter (3.8 Quart) Capacity 100 mm (4") Deep	Cambro USA	Colour: Clear (135)	24	YES	NO					
56	SMAL-01_051	Food Pan - Hot/Cold	<ul style="list-style-type: none"> - 5.3 Liter (5.6 Quart) Capacity - 152 mm (6") Deep - Polycarbonate construction - Withstands temperatures from -40° F -210° F (-40°C -99°C) - Designed to Gastronorm GN specifications - Uniform 127 mm (1/2") flange, to fit in prep tables and food bars - Non-stick smooth interior surface - Stack neatly, without wedging or sticking - NSF International Certified - Color: Clear - All Food Pan - Hot/Cold and Lids to be from same manufacturer and series 	Model: 36CW Camwear Pans Third Size 5.3 Liter (5.6 Quart) Capacity 152 mm (6") Deep	Cambro USA	Colour: Clear (135)	12	YES	NO					

57	SMAL-01_052	Food Pan - Hot/Cold Lid	- Maximum Size: 330 mm x 178 mm (13" x 7") - Polycarbonate construction - Withstands temperatures from -40° F -210° F (-40°C -99°C) - Color: Clear - All Food Pan - Hot/Cold and Lids to be from same manufacturer and series	Model: 30CWCH Camwear Pans Third Size, Lid with Handle Dimension: 325 mm x 176 mm (12-3/4" x 6-15/16")	Cambro USA	Colour: Clear (135)	60	YES	NO					
58	SMAL-01_053	Food Pan - Hot/Cold	- 1 L (1.1 Quart) Capacity - 65 mm (2-1/2") Deep - Polycarbonate construction - Withstands temperatures from -40° F -210° F (-40°C -99°C) - Precisely designed to Gastronorm GN specifications - Non-stick smooth interior surface - Uniform 1.27 cm (1/2") flange - Stack neatly, without wedging or sticking - NSF International Certified - Color: Clear - All Food Pan - Hot/Cold and Lids to be from same manufacturer and series	Model: 62CW Camwear Pans Sixth Size 1 L (1.1 Quart) Capacity 65 mm (2-1/2") Deep	Cambro USA	Colour: Clear (135)	12	YES	NO					
59	SMAL-01_054	Food Pan - Hot/Cold	- 1.5 Liter (1.6 Quart) Capacity - 100 mm (4") Deep - Polycarbonate construction - Withstands temperatures from -40° F -210° F (-40°C -99°C) - Precisely designed to Gastronorm GN specifications - Non-stick smooth interior surface - Uniform 1.27 cm (1/2") flange - Stack neatly, without wedging or sticking - NSF International Certified - Color: Clear - All Food Pan - Hot/Cold and Lids to be from same manufacturer and series	Model: 64CW Camwear Pans Sixth Size 1.5 Liter (1.6 Quart) Capacity 100 mm (4") Deep	Cambro USA	Colour: Clear (135)	24	YES	NO					
60	SMAL-01_055	Food Pan - Hot/Cold	- 2.2 Liter (2.4 Quart) Capacity - 150 mm (6") Deep - Polycarbonate construction - Withstands temperatures from -40° F -210° F (-40°C -99°C) - Precisely designed to Gastronorm GN specifications - Non-stick smooth interior surface - Uniform 1.27 cm (1/2") flange - Stack neatly, without wedging or sticking - NSF International Certified - Color: Clear - All Food Pan - Hot/Cold and Lids to be from same manufacturer and series	Model: 66CW Camwear Pans Sixth Size 2.2 Liter (2.4 Quart) Capacity 150 mm (6") Deep	Cambro USA	Colour: Clear (135)	24	YES	NO					
61	SMAL-01_56	Food Pan - Hot/Cold Lid	- Maximum Size: 178 mm x 178 mm (7" x 7") - Polycarbonate construction - Withstands temperatures from -40° F -210° F (-40°C -99°C) - Color: Clear - All Food Pan - Hot/Cold and Lids to be from same manufacturer and series	Model: 60CWCH Camwear Food Pan Lids Sixth Size, Lid with Handle Dimensions: 176 mm x 162 mm (6-15/16" x 6-3/8")	Cambro USA	Colour: Clear (135)	60	YES	NO					
62	SMAL-01_057	Food Pan - Hot/Cold	- .57 Liter (.6 Quart) - 65 mm (2-1/2") Deep - Polycarbonate construction - Withstands temperatures from -400 F -2100 F (-400C -990C) - Precisely designed to Gastronorm GN specifications - Non-stick smooth interior surface - Uniform 1/2" (1.27cm) flange - Stack neatly, without wedging or sticking - NSF International Certified - Color: Clear - All Food Pan - Hot/Cold and Lids to be from same manufacturer and series	Model: 92CW Camwear Pans Ninth Size .57 Liter (.6 Quart) 65 mm (2-1/2") Deep	Cambro USA	Colour: Clear (135)	12	YES	NO					
63	SMAL-01_058	Food Pan - Hot/Cold	- .85 Liter (.9 Quart) - 100 mm (4") Deep - Polycarbonate construction - Withstands temperatures from -40 F -210 F (-40C -99C) - Precisely designed to Gastronorm GN specifications - Non-stick smooth interior surface - Uniform 1/2" (1.27cm) flange - Stack neatly, without wedging or sticking - NSF International Certified - Color: Clear - All Food Pan - Hot/Cold and Lids to be from same manufacturer and series	Model: 94CW Camwear Pans Ninth Size .85 Liter (.9 Quart) 100 mm (4") Deep	Cambro USA	Colour: Clear (135)	12	YES	NO					

64	SMAL-01_059	Food Pan - Hot/Cold Lid	<ul style="list-style-type: none"> - Maximum Size: 178 mm x 114 mm (7" x 4-1/2") - Polycarbonate construction - Withstands temperatures from -40 F -210 F (-40C -99C) - Color: Clear - All Food Pan - Hot/Cold and Lids to be from same manufacturer and series 	Model: 90CWC Camwear Food Pan Lids Ninth Size, Flat Lid Dimensions: 176 mm x 108 mm (6-15/16" x 4-1/4")	Cambro USA	Colour: Clear (135)	24	YES	NO					
65	SMAL-01_060	Food Pan / Steam Table - Adapter Bar	<ul style="list-style-type: none"> - Length: 324 mm (12-3/4") - Width: 25 mm (1") - 18-8 Stainless Steel - BPA (Bisphenol A) Free - Dishwasher safe - NSF International Certified - Color: Not applicable 	Model: 6071A DuraPan Adapter Bar 12-3/4" Dimension: 324 mm x 25 mm (12-3/4" x 1")	Carlisle Foodservice Products	Not applicable	24	YES	NO					
66	SMAL-01_061	Food Pan / Steam Table - Adapter Bar	<ul style="list-style-type: none"> - Length: 520 mm (20-1/2") - Width: 25 mm (1") - 201 Stainless Steel - BPA (Bisphenol A) Free - Dishwasher safe - NSF International Certified - Color: Not applicable 	Model: 6070A DuraPan Adapter Bar 20-1/2" Dimension: 520 mm x 25 mm (20-1/2" x 1")	Carlisle Foodservice Products	Not applicable	24	YES	NO					
67	SMAL-01_062	Food Pan / Steam Table - Wire Grate	<ul style="list-style-type: none"> - 298 mm (11.75")W x 419 mm (16.5")D - Pan Size: Half Sheet Pan - Heavy-duty 300 stainless steel wire construction - No plating to flake off - Finger room in grate corner for easy removal from pan - Color: Not applicable 	Half Size Sheet Pan Model: 20248 Super Pan V Wire Grates	The Vollrath Company	Not applicable	6	YES	NO					
68	SMAL-01_063	Food Storage Container	<ul style="list-style-type: none"> - 3.8 Liter (4 Quart) Capacity - Maximum Dimension: 190 mmL x 190 mmW x 203 mmH (7-1/2"L x 7-1/2"W x 8"H) - Easy-to-read printed graduations on outside of container - Stackable - Withstands temperatures from -40°F to 210°F (-40°C to 99°C) - Commercial Dishwasher Safe - Polycarbonate construction - NSF International Certified - All Food Storage Containers and Lids to be from the same manufacturer and series - Color: Clear 	Square Model: 45FSCW CamSquares - Camwear 3.8 Liter (4 Quart) Dimension: 185 mmL x 185 mmW x 187 mmH (7-1/4"L x 7-1/4"W x 7-3/8"H)	Cambro USA	Colour: Clear (135)	6	YES	NO					
69	SMAL-01_064	Food Storage Container Lid	<ul style="list-style-type: none"> - Food Storage Container Lid: 1.9 Liter or 3.8 Liter (2 or 4 Quart) - Maximum Dimension: 190 mm x 190 mm (7-1/2" x 7-1/2") - Inner and outer seal for spill resistance, even during transport - Withstands temperatures from -40°F to 210°F (-40°C to 99°C) - Includes hole on the corner for hanging during storage - NSF International Certified - All Food Storage Containers and Lids to be from the same manufacturer and series - Color: Translucent 	Model: SFC25SCP Seal Covers for Camwear CamSquares (Lid for 1.9 or 3.8 Liter (2 or 4 Quart) Food Storage Container) Dimension: 185 mm x 185 mm (7-1/4" x 7-1/4")	Cambro USA	Color: Translucent (190)	6	YES	NO					
70	SMAL-01_065	Food Storage Container	<ul style="list-style-type: none"> - 5.7 Liter (6 Quart) Capacity - Maximum Dimension: 229 mmL x 229 mmW x 190 mmH (9"L x 9"W x 7-1/2"H) - Easy-to-read printed graduations on outside of container - Stackable - Withstands temperatures from -40°F to 210°F (-40°C to 99°C) - Commercial Dishwasher Safe - Polycarbonate construction - NSF International Certified - All Food Storage Containers and Lids to be from the same manufacturer and series - Color: Clear 	Square Model: 65FSCW CamSquares - Camwear 5.7 Liter (6 Quart) Dimension: 215 mmL x 215 mmW x 185 mmH (8-3/8"L x 8-3/8"W x 7-1/4"H)	Cambro USA	Colour: Clear (135)	6	YES	NO					
71	SMAL-01_066	Food Storage Container	<ul style="list-style-type: none"> - 7.6 Liter (8 Quart) Capacity - Maximum Dimension: 229 mmL x 229 mmW x 241 mmH (9"L x 9"W x 9-1/2"H) - Easy-to-read printed graduations on outside of container - Stackable - Withstands temperatures from -40°F to 210°F (-40°C to 99°C) - Commercial Dishwasher Safe - Polycarbonate construction - NSF International Certified - All Food Storage Containers and Lids to be from the same manufacturer and series - Color: Clear 	Square Model: 85FSCW CamSquares - Camwear 7.6 Liter (8 Quart) Dimension: 215 mmL x 215 mmW x 230 mmH (8-3/8"L x 8-3/8"W x 9-1/8"H)	Cambro USA	Colour: Clear (135)	6	YES	NO					

72	SMAL-01_067	Food Storage Container Lid	<ul style="list-style-type: none"> - Food Storage Container Lid: 5.7 or 7.6 Liter (6 or 8 Quart) - Maximum Dimension: 190 mm x 190 mm (7-1/2" x 7-1/2") - Inner and outer seal for spill resistance, even during transport - Withstands temperatures from -40°F to 210°F (-40°C to 99°C) - Includes hole on the corner for hanging during storage - NSF International Certified - All Food Storage Containers and Lids to be from the same manufacturer and series - Color: Translucent 	Square Model: SFC6SCPP Seal Covers for Camwear CamSquares (Lid for 5.7 or 7.6 Liter (6 or 8 Quart) Food Storage Container) Dimension: 185 mm x 185 mm (7-1/4" x 7-1/4")	Cambro USA	Color: Translucent (190)	12	YES	NO						
73	SMAL-01_068	Food Storage Container	<ul style="list-style-type: none"> - 11.4 Liter (12 Quart) Capacity - Maximum Dimension: 292 mmL x 318 mmW x 216 mmH (11-1/2"L x 12-1/2"W x 8-1/2"H) - Easy-to-read printed graduations on outside of container - Stackable - Withstands temperatures from -40°F to 210°F (-40°C to 99°C) - Commercial Dishwasher Safe - Polycarbonate construction - NSF International Certified - All Food Storage Containers and Lids to be from the same manufacturer and series - Color: Clear 	Square Model: 12SFSCW CamSquares - Camwear 11.4 Liter (12 Quart) Dimension: 256 mmL x 310 mmW x 210 mmH (11-1/4"L x 12-1/4"W x 8-1/4"H)	Cambro USA	Colour: Clear (135)	6	YES	NO						
74	SMAL-01_069	Food Storage Container Lid	<ul style="list-style-type: none"> - Food Storage Container Lid: 11.4, 17.2, or 20.8 Liter (12 Quart, 18 Quart or 22 Quart) - Maximum Dimension: 292 mm x 317 mm (11-1/2" x 12-1/2") - Inner and outer seal for spill resistance, even during transport - Withstands temperatures from -40°F to 210°F (-40°C to 99°C) - Includes hole on the corner for hanging during storage - NSF International Certified - Color: Translucent - All Food Storage Containers and Lids to be from the same manufacturer and series 	Square Model: SFC12SCPP Seal Lid for Camwear CamSquares (Lid for 11.4, 17.2, or 20.8 Liter (12, 18 or 22 Quart) Food Storage Container) Dimension: 256 mm x 310 mm (11-1/4" x 12-1/4")	Cambro USA	Color: Translucent (190)	6	YES	NO						
75	SMAL-01_070	Drinking Glass	<ul style="list-style-type: none"> - Maximum Capacity: 177 mL (6 oz.) - Maximum Height: 95 mm (3-3/4") - Maximum Dia.: 57 mm (2-1/4") - Faceted design glassware - Fully tempered - Color: Clear Glass 	Model: 53664 Product Line: Arcoroc Pattern Name: Artic Juice 6 oz. 3-3/4" 177 mL (6 oz.) Capacity, Dimension: 95 mm (3-3/4") High, 57 mm (2-1/4") Dia.	Cardinal International Inc.	Color: Clear (135)	1212	YES	NO						
76	SMAL-01_071	Gloves - Chemical Resistant	<ul style="list-style-type: none"> - Maximum Length: 381 mm (15") Long - Minimum Thickness: 40 mil thick - Glove Size: Large - Unlined natural rubber latex, chemical-resistant gloves - Heavy-duty, liquid proof for dip tank applications where acids are used - Texturized grip - ANSI/ISEA 105-2005 Performance: Abrasion: 2; Cut-Resistance: 1; Puncture: 0 - Color: Two-toned color (One color outside/ one color inside) 	Model: 55-09 Best Natural Rubber HD, Heavy-weight Natural Rubber Glove 55 Glove Size: Large 381 mm (15") Long 40 mils thick, Unlined	Showa Best Glove, Inc. (Chemrest)	Colour: Two color - Black outside/ Red inside	12	YES	NO						
77	SMAL-01_072	Gloves - Food Service	<ul style="list-style-type: none"> - For food service, handling and kitchen use - Maximum Length: 220 mm (13") Long - Glove Size: Medium - Unsupported / unlined 100% Nitrile glove, 12 mil, straight cuff - Component materials comply with FDA Regulations for Food Contact Micro - Pattern grip - Color: No specific color required 	Food Service Gloves: Nitril Unsupported Gloves Series: 504, NITRIFit Glove Size: 50480, Medium 220 mm (13") Long Unlined 100% Nitrile, 12 mil, Straight Cuff	Summit Glove Incorporated	Color: Green	12 (individual pairs)	YES	NO						
78	SMAL-01_073	Knife - Boning	<ul style="list-style-type: none"> - Blade Length: 153 mm (6") - Maximum Handle Length: 114 mm (4-1/2") - Maximum Overall Length: 267 mm (10-1/2") - Stainless steel, forged blades - Soft handles for comfortable, sure grip - Edges ground and honed - NSF International Certified - Color: No specific color required 	Product Number / SKU: 30400 iCut-Pro, 6 Inch Forged Narrow Boning Knife 153 mm (6")	Dexter-Russell Inc.	Not applicable	6	YES	NO						
79	SMAL-01_074	Knife - Chef	<ul style="list-style-type: none"> - Blade Length: 254 mm (10") - Maximum Handle Length: 127 mm (5") - Maximum Overall Length: 381 mm (15") - Stainless steel, forged blades - Soft handles for comfortable, sure grip - Edges ground and honed - NSF International Certified - Color: No specific color required 	Product No.: IC6102-10PCP SKU No.: 31803 iCut-Pro, 10 Inch Forged Chef's Knife 254 mm (10")	Dexter-Russell Inc.	Not applicable	6	YES	NO						

80	SMAL-01_075	Knife - Paring	<ul style="list-style-type: none"> - Blade Length: 89 mm (3-1/2") - Maximum Handle Length: 102 mm (4") - Maximum Overall Length: 190 mm (7-1/2") - Stainless steel, forged blades - Soft handles for comfortable, sure grip - Edges ground and honed - NSF International Certified - Color: No specific color required 	Product No.: 30408 SKU No.: 30408 iCut-Pro, 3-1/2 Inch Forged Paring Knife 89 mm (3-1/2")	Dexter-Russell Inc.	Not applicable	6	YES	NO					
81	SMAL-01_076	Knife - Rack	<ul style="list-style-type: none"> - Corrosion resistant stainless steel skirt and back plate - Minimum 356 mm (14") skirt wrap to protect blades & operators - "V"- slot insert design - Dishwasher safe - Holds 8 chef's knives, plus 2 smaller knives, 1 steel and 1 scissors - NSF International Certified - Color: Not applicable 	Rectangular, Includes Skirt with Back Model: KR- 700 Product Code: 39920 Knife Rack with 14" skirt and stainless steel back plate	Edlund Company Inc.	Not applicable	2	YES	NO					
82	SMAL-01_077	Knife - Spreader Sandwich	<ul style="list-style-type: none"> - Minimum Blade Length: 89 mm (3 1/2") - Maximum Handle Length: 102 mm (4") - Rubber grip handle - Scalloped blade - Stain-free, high-carbon steel construction - NSF International Certified - Color: No specific color required 	Product No.: SG1735C-PCP SKU No.: 24403 SofGrip, 3.5 Inch Scalloped Sandwich Spreader	Dexter-Russel Inc.	Color: White	6	YES	NO					
83	SMAL-01_078	Knife - Sharpener	<ul style="list-style-type: none"> - Removable, easy to clean, replaceable knife guidance system - Easy-track guidance system - ABS (Acrylonitrile butadiene styrene) plastic knife guide - Replaceable grinding wheel assembly - Sharpen knives ranging from 14.3 mm (3/16") to cleaver blades - NSF International Certified - Color: Not applicable 	Electric, Table Model: 401 Product Code: 40000 Electric Knife Sharpener, with Removeable Guidance System 115 Volt	Edlund Company Inc.	Not applicable	1	YES	NO					
84	SMAL-01_079	Ladle	<ul style="list-style-type: none"> - Capacity: 25 ml (3/4 oz.) - Maximum Handle Length: 216 mm (8-1/2") - Polycarbonate body - NSF International Certified - Angled handle c/w side rest - Color: No specific color required - All polycarbonate ladles to be from the same manufacturer and series 	Polycarbonate Model: LD85 Camwear Ladles 25 ml (3/4 oz.) Capacity 216 mm (8-1/2") Long	Cambro USA	Color: Black (110)	48	YES	NO					
85	SMAL-01_080	Ladle	<ul style="list-style-type: none"> - Capacity: 30 ml (1 oz.) - Maximum Handle Length: 279 mm (11") - Polycarbonate body - NSF International Certified - Angled handle c/w side rest - Color: No specific color required - All polycarbonate ladles to be from the same manufacturer and series 	Polycarbonate Model: LD105 Camwear Ladles 30 ml (1 oz.) Capacity 268 mm (10-9/16") Long	Cambro USA	Color: Black (110)	48	YES	NO					
86	SMAL-01_081	Ladle	<ul style="list-style-type: none"> - Bowl dimensions: 89 mm (3-1/2") Dia. - Bowl capacity: 177.4 ml (6 oz.) - Minimum Handle Length: 330 mm (13") - Heavy-gauge stainless steel shafts and bowls - NSF International Certified - Antimicrobial handle - Capacities clearly stamped on product - One-piece construction - Cool-to-the-touch, plastic-coated handle, heat resistant up to 180°F (82°C) - Hooked handle - Handle Color: No specific color required - All stainless steel ladles to be from the same manufacturer and series 	Stainless Steel Model: 4980620 Ladle with Black Kool-Touch Handles 177.4 ml (6 oz.) Capacity 89 mm (3-1/2") Diameter	The Volrath Company	Handle Color: Black	48	YES	NO					
87	SMAL-01_082	Ladle	<ul style="list-style-type: none"> - Bowl dimensions: 102 mm (4") Dia. - Bowl capacity: 236.6 ml (8 oz.) - Minimum Handle Length: 330 mm (13") - Heavy-gauge stainless steel shafts and bowls - NSF International Certified - Antimicrobial handle - One-piece construction - Capacities clearly stamped on product for easy identification - Cool-to-the-touch, plastic-coated handle, heat resistant up to 180°F (82°C) - Hooked handle - Handle Color: No specific color required - All stainless steel ladles to be from the same manufacturer and series 	Stainless Steel Model: 4980820 Ladle with Black Kool-Touch Handles 236.6 ml (8 oz.) Capacity 102 mm (4") Diameter	The Volrath Company	Handle Color: Black	48	YES	NO					

88	SMAL-01_083	Mat - Anti Fatigue	<ul style="list-style-type: none"> - For kitchens, dishwashing areas, walk-in freezers and coolers - Size: 914 mm x 2743 mm (36"D x 108"L) - Diamond patterned grit-top providing a slip-resistance surface in wet and oily environments - Grease and oil proof, chemical resistant - Beveled edges - Lifetime anti-microbial treatment - Flexible for easy handling - Backing designed to resist movement under wheeled/cart traffic - Type/Style: Drainable (with holes) - Color: Black 	Traction Hog II	Source Floor & Specialties Inc.	Color: Black	6	YES	NO						
89	SMAL-01_084	Mat - Anti Fatigue	<ul style="list-style-type: none"> - Size: 914 mmD x 1524 mmL (36"D x 60"L) - Thickness: 16 mm (5/8" thick) - Deck plate surface fused to a high-grade foam backing - Beveled edges and rounded corners - Resistant to most common fluids and chemicals - Color: Black - Type: Drainable (with holes) 	Solid Top Model: 540 Workers-Delight Deck Plate	Crown Mats & Matting	Color: Black	12	YES	NO						
90	SMAL-01_085	Oven Mitt	<ul style="list-style-type: none"> - Constructed of institutional-grade terry cloth - Maximum Size: 432 mm (17") Long - Heat protection up to 500°F (260°C) for 30 seconds - Machine washable - Hanging loop - Sold in pairs - Color: No specific color required 	Heavy-duty Institutional-grade Model: 817TM Terry Oven Mitt Size: Medium 432 mm (17") Long	San Jamar	Colour: Natural	12 (pairs)	YES	NO						
91	SMAL-01_086	Pail - Cleaning Solution	<ul style="list-style-type: none"> - Maximum Capacity: 5.68 Liter (6 Quart) - "Cleaner" printing and imprints. Bilingual: English/French on front and back panel - Meets HACCP (Hazard Analysis Critical Control Point) guidelines - Color: Green 	Model: KP196-GN Kleen-Pail 5.68 Liter (6 Quart) "Cleaner" printing and imprint on pail (Trilingual: English/Spanish on front panel and English/French on back panel)	San Jamar	Color: Green	24	YES	NO						
92	SMAL-01_087	Pail - Sanitizer Solution	<ul style="list-style-type: none"> - Minimum Capacity: 5.68 Liter (6 Quart) - "Sanitizer" printing and imprints. Bilingual: English/French on front and back panel - Meets HACCP (Hazard Analysis Critical Control Point) guidelines - Color: Red 	Model: KP196-RD Kleen-Pail 5.68 Liter (6 Quart) "Sanitizer" Trilingual printing and imprint on pail (Trilingual: English/Spanish on front panel and English/French on back panel)	San Jamar	Color: Red	24	YES	NO						
93	SMAL-01_088	Pan - Egg Poacher	<ul style="list-style-type: none"> - Includes maximum size 229 mm (9") lidded fry pan - 18/10 stainless steel - Six (6) non-stick coated removable egg cups - Stay cool handle and knob, including see-through vented tempered glass lid - Color: No specific color required 	SKU No.: 522 Category: Cookware Stainless Steel 6 Egg Poacher Includes: 229 mm (9") lidded frypan and Six (6) removable egg cups	Cook Pro Inc.	No specific color required	2	YES	NO						
94	SMAL-01_089	Pan - Fry	<ul style="list-style-type: none"> - 203 mm (8") Diameter - Maximum Height: 51 mm (2") - Gauge: 10 Aluminium - Made without PFOA (Perfluorooctanoic acid) - Dual-layer reinforced non-stick cooking coating - Riveting system to prevent loose rivets - Cool-to-the-touch handle - NSF International Certified - Color: No specific color required 	Model: S4008 Wear-Ever Fry Pans with PowerCoat 2 Non-Stick Finish and Cool Handle 203 mm (8") Diameter	The Vollrath Company	Not applicable	6	YES	NO						
95	SMAL-01_090	Pan - Fry	<ul style="list-style-type: none"> - 304 mm (12") Diameter - Maximum Height: 63 mm (2-1/2") - Gauge: 8 Aluminium - Made without PFOA (Perfluorooctanoic acid) - Dual-layer reinforced non-stick cooking coating - Riveting system to prevent loose rivets - Cool-to-the-touch handle - NSF International Certified - Color: No specific color required 	Model: S4012 Wear-Ever Fry Pans with PowerCoat 2 Non-Stick Finish and Cool Handle 305 mm (12") Diameter	The Vollrath Company	Not applicable	6	YES	NO						

96	SMAL-01_091	Pan - Fry	<ul style="list-style-type: none"> - 203 mm (8.5") Diameter - Maximum Height: 51 mm (2") - 16 Gauge Carbon steel construction - Cool-to-the-touch handle - Non-stick induction; can be used on 120v ranges (1.8kw or less) electric top, gas top, induction ready, ceramic top - Plated steel handle is riveted with stay-cool technology - Riveted plated steel handles, silicone insulated handles rated 232°C (450°F) - Color: No specific color required - All Pan - Fry to be from the same manufacturer and series and must be available in other sizes up to 279 mm (11") diameter 	Model: 59900 Induction Fry Pans with SteelCoat x3 216 mm (8.5") Diameter	The Vollrath Company	Color: Black	24	YES	NO					
97	SMAL-01_092	Pan - Fry	<ul style="list-style-type: none"> - 279 mm (11") Diameter - Maximum Height: 51 mm (2") - 16 Gauge Carbon steel construction - Cool-to-the-touch handle - Non-stick induction; can be used on 120v ranges (1.8kw or less) electric top, gas top, induction ready, ceramic top - Riveted plated steel handles, silicone insulated handles rated 232°C (450°F) - Color: No specific color required - All Pan - Fry to be from the same manufacturer and series and must be available in other sizes up to 279 mm (11") Diameter 	Model: 59920 Induction Fry Pans with SteelCoat x3 279 mm (11") Diameter	The Vollrath Company	Color: Black	24	YES	NO					
98	SMAL-01_093	Pitcher - Complete with Lid	<ul style="list-style-type: none"> - 1.9 Liter (64 oz.) Capacity - Minimum Height with Lid: 254 mm (10") - Maximum Diameter with Handle: 203 mm (8") dia. - Polycarbonate construction - Three-position lid to strain ice, free pour, or close to protect contents - Ergonomic handle with a thumb grip - Slotted base for complete and sanitary drying - NSF International Certified - Color: Clear 	Model: PC64CW Pitchers - Camwear 1.9 Liter (64 oz.) Capacity	Cambro USA	Color: Clear (135)	51	YES	NO					
99	SMAL-01_094	Safety Goggle	<ul style="list-style-type: none"> - Wide-angle wraparound lens and frame - Large lens opening to accommodate most prescription eyewear - "Side-to-side" peripheral vision - Direct ventilation, indirect ventilation - Elastic neoprene strap - Standards/Approvals: CSA (Canadian Standards Association) Z94.3-2007, ANSI (American National Standards Institute) Z87.1-2003 - Lens Coating: Anti-fog - Lens Color: Clear 	3M Centurion Safety Goggles	3M	Lens Color: Clear	6	YES	NO					
100	SMAL-01_095	Salad Spinner	<ul style="list-style-type: none"> - Minimum Capacity: 9.5 Liter (2-1/2 Gallon); approximately 2 to 3 lettuce heads - Maximum Diameter: 381 mm (15") - Polypropylene body and basket - Polycarbonate transparent lid - To include drainage tube - Aerated basket - Multiple gear system - Color: No specific color required 	Model: 215582 Matfer Swing Salad Spinner 2-1/2 Gallons 9.5 Liter (2-1/2) Gallon 374 mm (14-3/4") Diameter	Matfer Bourgeat	Color: No specific color required	1	YES	NO					
101	SMAL-01_096	Salad Spinner	<ul style="list-style-type: none"> - Minimum Capacity: 19 Liter (5 gallon); approximately 4 to 5 lettuce heads - Maximum Diameter: 483 mm (19") - Polypropylene body and basket - Polycarbonate transparent lid - To include drainage tube - Aerated basket - Multiple gear system - Color: No specific color required 	Model: 215580 Matfer Swing Salad Spinner 5 Gallons 19 Liter (5 Gallon) 460 mm (18-1/8") Diameter	Matfer Bourgeat	Color: No specific color required	1	YES	NO					
102	SMAL-01_097	Scale - Digital Portion Control	<ul style="list-style-type: none"> - 5000 g x 1 g (10 lb x 0.05 oz. / 10 lb x 0.002 lb / 160 oz. x 0.05 oz.) Capacity - Minimum Size: 120 mm x 150 mm (4.75" x 5.9") removable stainless steel platform - IP65 rated moisture-resistant sealed components - Digital: 20 mm (0.8") LCD digits in a 23 mm (0.9") readout - Calibration feature for in-field adjustment - Tare function - Auto off and disable auto off feature - Low battery and overload indicators - Operates on AC adapter (included) or 1.9-volt battery (not included) - NSF International Certified - Color: Not applicable 	Table Model Model: TE10CSW Water Resistant Digital 10lb Portion Control Scale 5000 g x 1g (10 lb x 0.05 oz.) Capacity	Taylor Precision Products Inc. (Taylor USA)	Not applicable	2	YES	NO					

103	SMAL-01_098	Spoon - Serving	<ul style="list-style-type: none">- Maximum Size: 356 mm (14") Long- One-piece construction- Antimicrobial- Heavy-gauge stainless steel shaft and bowls, resistant to corrosion- Ergonomic, textured surface, heat resistant nylon handle to 450°F (232°C)- Built-in stopper notch- Bowl shape with contoured end to fit corners of pan- 3-sided spoon has a straight-sided "cutting" edge- Handle Color: Black- All Spoon - Serving to be from the same manufacturer and series	Model: 64130 Collection: Jacobs Pride Heavy-Duty Stainless Steel Basting Spoon with Ergo Grip Handles 351 mm Long (13-13/16")	The Volrath Company	Handle Color: Black	12	YES	NO							
104	SMAL-01_099	Spoon - Serving	<ul style="list-style-type: none">- Maximum Size: 356 mm (14") Long- One-piece construction- Antimicrobial- Heavy-gauge stainless steel shaft and bowls, resistant to corrosion- Ergonomic, textured surface, heat resistant nylon handle to 450°F (232°C)- Built-in stopper notch- Bowl shape with contoured end to fit corners of pan- 3-sided spoon has a straight-sided "cutting" edge- Handle Colour: Red- All Spoon - Serving to be from the same manufacturer and series	Model: 6414040 Collection: Jacobs Pride Heavy-Duty Stainless Steel Basting Spoon with Ergo Grip Handles 352 mm Long (13-13/16")	The Volrath Company	Handle Colour: Red	12	YES	NO							
105	SMAL-01_100	Spoon - Serving	<ul style="list-style-type: none">- Maximum Size: 356 mm (14") Long- One-piece construction- Antimicrobial- Heavy-gauge stainless steel shaft and bowls, resistant to corrosion- Ergonomic, textured surface, heat resistant nylon handle to 450°F (232°C)- Built-in stopper notch- Bowl shape with contoured end to fit corners of pan- 3-sided spoon has a straight-sided "cutting" edge- Handle Colour: Blue- All Spoon - Serving to be from the same manufacturer and series	Model: 6414030 Collection: Jacobs Pride Heavy-Duty Stainless Steel Basting Spoon with Ergo Grip Handles 352 mm Long (13-13/16")	The Volrath Company	Handle Colour: Blue	12	YES	NO							
106	SMAL-01_101	Spoon - Serving	<ul style="list-style-type: none">- Maximum Size: 356 mm (14") Long- One-piece construction- Antimicrobial- Heavy-gauge stainless steel shaft and bowls, resistant to corrosion- Ergonomic, textured surface, heat resistant nylon handle to 450°F (232°C)- Built-in stopper notch- Bowl shape with contoured end to fit corners of pan- 3-sided spoon has a straight-sided "cutting" edge- Handle Colour: Yellow- All Spoon - Serving to be from the same manufacturer and series	Model: 6414050 Collection: Jacobs Pride Heavy-Duty Stainless Steel Basting Spoon with Ergo Grip Handles 353 mm Long (13-13/16")	The Volrath Company	Handle Colour: Yellow	12	YES	NO							
107	SMAL-01_102	Table Linen - Napkins	<ul style="list-style-type: none">- Maximum Size: 508 mm x 508 mm (20" x 20")- Soil release technology- Protection against bleach- No lint transfer- Shrink resistant- High color retention- Ability to wash at low temperature- No iron required- Color: White- All Table Linen napkins, table cloths and skirting fabric to be from same manufacturer and series. All fabrication to be from same supplier.	Series: Visa Plus 508 mm x 508 mm (20" x 20")	Milliken & Company	Color: White 9660	1200	YES	NO							
108	SMAL-01_103	Table Linen - Table Cloth	<ul style="list-style-type: none">- 2286 mm (90") x 3048 mm (120")- Soil release technology- Protection against bleach- No lint transfer- Shrink resistant- High color retention- Ability to wash at low temperature- No iron required- Color: White- All Table Linen napkins, table cloths and skirting fabric to be from same manufacturer and series. All fabrication to be from same supplier	Series: Visa Plus 2286 mm x 3048 mm (90" X 120")	Milliken & Company	Color: White 9660	120	YES	NO							
Intentionally left blank																

110	SMAL-01_105	Table Linen - Table Cloth	<ul style="list-style-type: none">- 2287 mm x 2287 mm (90" x 90")- Soil release technology- Protection against bleach- No lint transfer- Shrink resistant- High color retention- Ability to wash at low temperature- No iron required- Color: White- All Table Linen napkins, table cloths and skirting fabric to be from same manufacturer and series. All fabrication to be from same supplier.	Square Visa Plus 2287 mm x 2287 mm (90" X 90")	Series: Milliken & Company	Color: White 9660	120	YES	NO					
111	SMAL-01_106	Tableware - Glass Shaker	<ul style="list-style-type: none">- Capacity: 355 ml (12 oz.)- Stain proof- Dishwasher safe- Shaker Base Finish: Clear Glass- Top Finish: Stainless, Threaded Top	Sugar, Complete with Threaded Stainless Top Model: GLA316 355 ml (12 oz.), Glass Shaker, Sugar Complete	American Metalcraft Inc.	Shaker Base Finish: Glass Top Finish: Stainless	48	YES	NO					
112	SMAL-01_107	Tableware - Napkin Dispenser	<ul style="list-style-type: none">- Maximum Dimension: 95 mmW x 178 mmD x 190 mmH (3-3/4"W x 4"D x 7-1/2"H)- For tallfold napkins sized: 89 mm x 176 mm (3-1/2" x 6-7/8")- Two (2) sided dispenser- 125 to 150 napkin capacity- 22 gauge stainless steel- Finish: Satin Stainless Steel	Tabletop Model H900X Classic Tabletop, Napkin Dispensers Two-sided, 150 Tallfold (T) Napkin Capacity	Model: San Jamar	Finish: Satin Stainless Steel	48	YES	NO					
113	SMAL-01_108	Tablware - Napkin Holder	<ul style="list-style-type: none">- Square Napkin Holder- Maximum Size: 140 mm x 140 mm x 102 mm (5.5" x 5.5" x 4")- Stainless Steel with open 'dot' detail	Model: BHO039BSS21 SS Napkin Holder, Dots 140 mm x 140 mm x 102 mm (5.5" x 5.5" x 4")	Front of The House	Finish: Stainless Steel	24	YES	NO					
114	SMAL-01_109	Tablware - Sampler Holder	<ul style="list-style-type: none">- Rectangular Sampler Holder- Maximum Size: Square, 229 mm x 152 mm x 57 mm (9" x 6" x 2-1/4")- Stainless Steel with open 'dot' detail	Model: BHO042BSS21 9" x 6" SS Holder, Dots 229 mm x 152 mm x 57 mm (9" x 6" x 2-1/4")	Front of The House	Finish: Stainless Steel	24	YES	NO					
115	SMAL-01_110	Tableware - Salt & Pepper	<ul style="list-style-type: none">- Maximum Height: 114 mm (4")- Maximum Capacity: 29.6 mil (1 oz.) glass base- Top Design: 'tower shaped'- Finish: Stainless Steel	Model: SP126 Glass Salt & Pepper Shakers Eiffel Tower 29.6 mil (1 oz.) / 114 mm High (4")	American Metalcraft Inc.	Finish: Stainless Steel	126	YES	NO					
116	SMAL-01_111	Thermometer - Digital Cooking	<ul style="list-style-type: none">- Capable of being recalibrated- Display that shows timer, current temperature and alarm temp setting- Stainless steel curved probe(maximum length 165mm [6.5"]) on a minimum heat resistant cable (length 762mm [30"])- Temperature alarms for cooking and cooling and timer for cumulative heat / cold time- Timer counts from 24 hours and may be set in 1 minute increments- Range from: -50 - 200°C (-58 - 392°F)- Resolution: 0.1°C (°F)- Accuracy: 1°C- Probe: 6.5L (1.7 Gallons)- Color: Not applicable	Model: 100120-020 Digital cooking thermometer with remote probe	Testek Instruments Inc.	Not applicable	12	YES	NO					

117	SMAL-01_112	Thermometer - Digital Cooking	<ul style="list-style-type: none"> - To include meter, probe and foam tape <u>Meter:</u> <ul style="list-style-type: none"> - Fully submersible probe (excluding connector) - High accuracy to ±0.9°F (±0.5°C) - Penetrates sealed bag without leakage - Digital display - To include NIST-Traceable Certificate (The National Institute of Standards and Technology) - Range: -148 to 2501°F (-100 to 1372°C) - Resolution: 0.1° - Probe: Type K thermocouple, mini socket - Auto Shutoff after 10 min - Battery: 2 x AAA or equivalent to operate a minimum 5 years (10,000 hours) - Units: °F/°C switchable - Color: Not applicable <u>Mini Needle Probe:</u> <ul style="list-style-type: none"> - Range: -76 to 482°F (-60 to 250°C) - Response: < 2 second <u>Foam Tape:</u> <ul style="list-style-type: none"> - Range: -40 to 194°F (-40 to 90°C) - Color: Not applicable 	Sous Vide Kit Model: 860-036 Therma K Professional Sous Vide Kit	ThermoWorks Inc.	Not applicable	12	YES	NO					
118	SMAL-01_113	Tongs	<ul style="list-style-type: none"> - To serve cold or hot food - Maximum Length: 229 mm (9") - Plastic - Scallop grip - NSF International Certified - Color: No specific color required 	Plastic Model: 9TGS Camwear Tongs 229 mm (9") Long Scallop Grip (12 per case)	Cambro USA	Handle Color: Black	48	YES	NO					
119	SMAL-01_114	Tongs	<ul style="list-style-type: none"> - To serve cold or hot food - Maximum Length: 305 mm (12") - Plastic - Scallop grip - NSF International Certified - Color: No specific color required 	Plastic Model: 12TGS Camwear Tongs 305 mm (12") Long Scallop Grip	Cambro USA	Handle Color: Black	48	YES	NO					
120	SMAL-01_115	Tongs	<ul style="list-style-type: none"> - 20 gauge stainless steel - One-piece spring design - Maximum Length: 22.9 mm (9") Long - NSF International Certified - Antimicrobial - Insulated coating permanently bonded to tong - Handles are heat resistant up to 180°F (82°C) - Dishwasher safe - Color: No specific color required 	Stainless Steel Model: 47329 Kool-Touch Pom Tongs 22.9 mm (9") Long	The Volrath Company	Handle Color: Black	48	YES	NO					
121	SMAL-01_116	Tongs	<ul style="list-style-type: none"> - 20 gauge stainless steel - Maximum Length: 305 mm (12") Long - NSF International Certified - Antimicrobial - One-piece springless design - Cool-to-the-touch handle - Scalloped end - Handles are heat resistant up to 180°F (82°C) - Color: No specific color required 	Stainless Steel Model: 4781220 One-Piece Color-Coded Kool-Touch Tongs 305 mm (12") Long Grip Design: Utility (Scalloped)	The Volrath Company	Handle Color: Black	48	YES	NO					
122	SMAL-01_117	Tray - Cafeteria	<ul style="list-style-type: none"> - Maximum Size: 457 mm x 330 mm (18" x 13") - Minimum five (5) year guarantee against breakage - Construction high-impact fiberglass with reinforced edges - Stain, odor and scratch resistant - Built in separator to ensure even air flow between trays - Stacking lugs to keep trays stacked in place - NSF International Certified - Colour: Black 	Rectangular Camtrays 1318 451 mm x 321 mm (17-3/4" x 12-5/8") Five (5) Year guarantee against breakage	Cambro USA	Colour: Black (110)	480	YES	NO					

123	SMAL-01_118	Turner	<ul style="list-style-type: none">- Blade: 127 mm (5") Long x 101 (4") Wide- Maximum Handle Length: 127 mm (5")- Minimum Overall Length: 254 mm (10")- Textured, slip-resistant, polypropylene handle- Impervious blade-to-handle seal- Stainless steel blade- NSF International Certified- Color: No specific color required	Hamburger Product No.: S285-4H-PCP SKU No.: 19723H Series: Sani-Safe 127 mmL x 101 mmW (5"L x 4"W) Hamburger Turner, High Heat	Dexter-Russell, Inc.	Handle Color: Blue	12	YES	NO					
124	SMAL-01_119	Turner	<ul style="list-style-type: none">- Blade: 152 mm (6") Long x 76 (3") Wide- Minimum Handle Length: 114 mm (4-1/2")- Maximum Overall Length: 267 mm (10-1/2")- Slip-resistant polypropylene handle- Stainless steel blade- NSF International Certified- Color: No specific color required	Hamburger Product No.: P94855 SKU No.: 31645 Series: Dexter Basics 152 mmL x 76 mmW (6"L x 3"W) Hamburger Turner	Dexter-Russell, Inc.	Handle Color: Cream	12	YES	NO					
125	SMAL-01_120	Turner	<ul style="list-style-type: none">- Blade: 203 mm (8") Long x 76 (3") Wide- Maximum Handle Length: 127 mm (5")- Minimum Overall Length: 330 mm (13")- Textured, slip-resistant, polypropylene handle to withstand both high and low temperatures- Impervious blade-to-handle seal- Stainless steel blade, precision ground- NSF International Certified- Color: No specific color required	Product No.: S286-8SQH-PCP Sku No.: 19613H Series: Sani-Safe 203 mmL x 76 mm (8"L x 3"W), Square End Turner, High-Heat	Dexter-Russell, Inc.	Handle Color: Blue	12	YES	NO					
126	SMAL-02_002	Drinking Glass	<ul style="list-style-type: none">- Capacity: 266 ml (9 oz.)- Minimum Height: 127mm (5")- Maximum Top Diameter: 69mm (2-3/4")- Maximum Bottom Diameter: 51 mm (2")- Maximum Diameter: 146 mm (2-3/4")- Color: Clear glass	Model: 133 Hi Ball Glass Pattern: Heavy Base 266 ml (9 oz.) Capacity	Libbey Inc.	Color: Clear glass	2324	YES	NO					
127	SMAL-02_003	Pitcher - Complete with Lid	<ul style="list-style-type: none">- Pitcher: 1.72 Liters (58 oz.)- Maximum Height: 254 mm (10")- Maximum Top Diameter: 140 mm (5-1/2")- Matching Lid: To be Vented- Thick walls and optic bottom to give the look of glass- Break-resistant polycarbonate- Dishwasher safe- Color: Clear- Pitcher and Lid to be from same manufactuer	Pitcher: Item No.: 557007 Product No.: 5570 Elan Pitcher 58 oz. - Clear Pitcher Lid: Item No.: 557307 Product No.: 5573 Elan Vented Lid for Elan Pitcher - Clear	Carlisle Foodservice Prducts	Color: Clear (07)	524 (Pitcher): 524 (Pitcher Lid)	YES	NO					
128	SMAL-02_004	Tray - Serving	<ul style="list-style-type: none">- Size: 330-356mm (13-14") Diameter- 18-8 Stainless steel- Dishwasher safe- Finish: Combination satin / mirror	Round Model: 82009 Round Trays/Covers for Double- Wall Bowls 350 mm (13-3/4") Diameter	The Vollrath Company	Finish: Combination satin / mirror	262	YES	NO					
129	SMAL-01_104	Table Linen - Skirting	<ul style="list-style-type: none">- 737 mm to 762 mm (29" to 30") High x 3657 mm (12'-0") Long table skirting- Soil release technology- Protection against bleach- No lint transfer- Shrink resistant OR 2-4 % shrinkage- High color retention- Ability to wash at low temperature- No iron required- Box Pleat- Color: White- All linen to be from same manufacturer and series- All Table Linen - Skirting height and clips to coordinate with all tables (1 clip/ft. included to fit ¾" thick table is acceptable)- All Table Linen napkins, table cloths and skirting fabric to be from same manufacturer and series. All fabrication to be from same supplier.	Series: Visa Plus Specialty Linen - Skirting - Box Pleat 737 mm High x 3657 mm Long (29" High X 12'-0" Long) Including Clips	Milliken & Company	Color: White 9660	78	YES	NO					

130	SMAL-01_121	Table Linen - Skirting	<div>- 737 mm to 762 mm (29" to 30") High x 3657 mm (12'-0") Long table skirting</div> <div>- Soil release technology</div> <div>- Protection against bleach</div> <div>- No lint transfer</div> <div>- Shrink resistant OR 2-4 % shrinkage</div> <div>- High color retention</div> <div>- Ability to wash at low temperature</div> <div>- No iron required</div> <div>- Box Pleat</div> <div>- Color: Black</div> <div>- All linen to be from same manufacturer and series</div> <div>- All Table Linen - Skirting height and clips to coordinate with all tables (1 clip/ft. included to fit ¾" thick table is acceptable)</div> <div>- All Table Linen napkins, table cloths and skirting fabric to be from same manufacturer and series. All fabrication to be from same supplier.</div>	Series: Visa Plus Specialty Linen - Skirting - Box Pleat 737 mm High x 3657 mm Long (29" High X 12'-0" Long) Including Clips	Milliken & Company	Color: Black 5650	48	YES	NO					
131	SMAL-01_122	Table Linen - Table Cloth	<div>- 2286 mm (90") x 3048 mm (120")</div> <div>- Soil release technology</div> <div>- Protection against bleach</div> <div>- No lint transfer</div> <div>- Shrink resistant OR 2-4 % shrinkage</div> <div>- High color retention</div> <div>- Ability to wash at low temperature</div> <div>- No iron required</div> <div>- Color: black</div> <div>- All Table Linen napkins, table cloths and skirting fabric to be from same manufacturer and series. All fabrication to be from same supplier</div>	Series: Visa Plus 2286 mm x 3048 mm (90" X 120") Rectangular	Milliken & Company	Color: Black 5650	24	YES	NO					
132	SMAL-01_123	Table Linen - Skirting	<div>- Must be compatible with a 762mm (30") W x 1829mm (72") L x 737mm (29") H table with "T-Leg" (exact table leg distance will be provided after contract award)</div> <div>- To have a short drop in the back to allow for a chair to slide comfortably under the table</div> <div>- Machine washable/air tumble dry</div> <div>- Is made from a polyester/spandex blend</div> <div>- Durable rubber foot cups</div> <div>- No need for pinning and clips</div> <div>- Flame retardant</div> <div>- Colour: White</div>	SND0430 Conference Cut 762mm (30") W x 1829mm (72") L Contour Covers	Lieberman Tranchemontagne	Colour: White	48	YES	NO					
133	SMAL-01_124	Table Linen - Skirting	<div>- Must be compatible with a 762mm (30") W x 1829mm (72") L x 737mm (29") H table with "T-Leg" (exact table leg distance will be provided after contract award)</div> <div>- To have a short drop in the back to allow for a chair to slide comfortably under the table</div> <div>- Machine washable/air tumble dry</div> <div>- Is made from a polyester/spandex blend</div> <div>- Durable rubber foot cups</div> <div>- No need for pinning and clips</div> <div>- Flame retardant</div> <div>- Colour: Black</div>	SND0430 Conference Cut 762mm (30") W x 1829mm (72") L Contour Covers	Lieberman Tranchemontagne	Colour: Black	24	YES	NO					