



## RETURN BIDS TO:

## RETOURNER LES SOUMISSIONS À:

Bid Receiving Public Works and Government  
Services Canada/Réception des soumissions  
Travaux publics et Services gouvernementaux  
Canada

800 Burrard Street, Room 219

800, rue Burrard, pièce 219

Vancouver, BC V6Z 0B9

## Revision to a Request for a Standing Offer

## Révision à une demande d'offre à commandes

National Individual Standing Offer (NISO)

Offre à commandes individuelle nationale (OCIN)

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Offer remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'offre demeurent les mêmes.

## Comments - Commentaires

## Vendor/Firm Name and Address

Raison sociale et adresse du  
fournisseur/de l'entrepreneur

## Issuing Office - Bureau de distribution

Public Works and Government Services Canada -  
Pacific Region  
219 - 800 Burrard Street  
800, rue Burrard, pièce 219  
Vancouver, BC V6Z 0B9

<b>Title - Sujet</b> Documents Imaging Scanners		
<b>Solicitation No. - N° de l'invitation</b> EN929-150346/A		<b>Date</b> 2015-12-21
<b>Client Reference No. - N° de référence du client</b> EN929-150346		<b>Amendment No. - N° modif.</b> 004
<b>File No. - N° de dossier</b> VAN-5-38258 (576)	<b>CCC No./N° CCC - FMS No./N° VME</b>	
<b>GETS Reference No. - N° de référence de SEAG</b> PW-\$VAN-576-7648		
<b>Date of Original Request for Standing Offer</b> Date de la demande de l'offre à commandes originale		2015-10-23
<b>Solicitation Closes - L'invitation prend fin</b> <b>at - à 02:00 PM</b> <b>on - le 2016-01-15</b>		<b>Time Zone</b> <b>Fuseau horaire</b> Pacific Standard Time PST
<b>Address Enquiries to: - Adresser toutes questions à:</b> Sobhee, Sachin		<b>Buyer Id - Id de l'acheteur</b> van576
<b>Telephone No. - N° de téléphone</b> (604) 775-7022 ( )	<b>FAX No. - N° de FAX</b> ( ) -	
<b>Delivery Required - Livraison exigée</b>		
<b>Destination - of Goods, Services, and Construction:</b> <b>Destination - des biens, services et construction:</b> Matane QC and Winnipeg, MB		
<b>Security - Sécurité</b> This revision does not change the security requirements of the Offer. Cette révision ne change pas les besoins en matière de sécurité de la présente offre.		

Instructions: See Herein

Instructions: Voir aux présentes

<b>Acknowledgement copy required</b> <b>Accusé de réception requis</b>	<b>Yes - Oui</b> <input type="checkbox"/>	<b>No - Non</b> <input type="checkbox"/>
<b>The Offeror hereby acknowledges this revision to its Offer.</b> <b>Le proposant constate, par la présente, cette révision à son offre.</b>		
<b>Signature</b>	<b>Date</b>	
Name and title of person authorized to sign on behalf of offeror. (type or print) Nom et titre de la personne autorisée à signer au nom du proposant. (taper ou écrire en caractères d'imprimerie)		
<b>For the Minister - Pour le Ministre</b>		

---

**This amendment is raised to answer questions from bidders.**

## **Questions and Answers**

Q1) Under General Mandatory Requirements M-5 b. It requires that all scanners have 1 GIG Ethernet Connection. Is this correct? Normally, as with the Scanner NMSO, the requirement is USB. Please confirm.

A1) . Yes 1 GIG Ethernet Connection is required.

Q2) Category

1-Very High Volume Production Doc Scanner with TIFF Native

2-Very High Volume Production Document Scanner

Specification: Minimum speed of 250 pages per minute (ppm). Would the government consider a speed of 210 pages per minute?

A2) Answer: Yes. The absolute minimum would be 200 ppm at 200 DPI.

Q3) Specification: 1000 sheet Automatic Document Feeder Capacity. Would the government consider a 750 page document feeder?

A3) Yes

Q4) Specification: Handle multiple paper weights (onion to heavy bond paper: 12 lbs. Bond – 122 lbs. Tag [45 g/m2 – 200 g/m2] Asian rice paper to cardstock). Would the government consider changing the specification to a maximum of 110 lbs.?

A4) Yes

Q5) Specification: Flat Paper Path. Would the government consider a J or C Curve paper path?

A5) No for category 1 and Yes for category 2.

Q6) Specification: Must have multiple output trays. Would the government consider a specification of Controlled dual stacking? Can the government please elaborate on the number of scanning applications requiring out-sorting?

A6) We need a flat track for category 1 and a Controlled dual stacking will be also considered for category 2.

Q7) Specification: Optical Character Recognition (OCR). What is meant by this specification? Is the request for zonal OCR, or is the request to be able to create Searchable PDFs?

A7) The request is for zonal OCR. The machine needs to generate an image in TIFF format right away, not generate a TIFF image from a JPEG image.

Q8) Specification: Variable scan speeds. Would the government please elaborate on the meaning of and reasoning for variable scan speeds?

A8) We mean the possibility to adjust and/or decrease the speed when feeding some fragile documents.

Solicitation No. - N° de l'invitation  
EN929-150346/A  
Client Ref. No. - N° de réf. du client  
EN929-150346

Amd. No. - N° de la modif.  
004  
File No. - N° du dossier  
VAN-5-38258

Buyer ID - Id de l'acheteur  
VAN576  
CCC No./N° CCC - FMS No./N° VME

Q9) Specification: Use a modular vacuum conveyor track. Would the government consider changing or eliminating this specification?

A9) For category 1 we need a flat track paper path and we will also consider a different paper path as C or J Path for category 2.

Q10) Specification: optional 7-year period on-site maintenance service, Monday to Friday, from 7AM to 5 PM with 15 minutes call-response time, technician on-site within 2 hours (for equipment purchases). Would the government consider changing this to 8 AM from 7 AM to 5 PM is the standard support hours within the industry.

A10) No, our business hours are from 7 AM to 10 PM from Monday to Friday.

Q11) Questions:

3 - Mid Volume Production Document Scanner with flatbed

4 - Mid Volume Production Document Scanner with feeder

Would the government consider changing or having as an option the specification for service support to Advanced Unit Replacement (as opposed to on-site only)?

A11) Yes and note that for categories 3 to 11, the service maintenance calls have been changed for 48 hours on site.

Q12) In the category Mid volume Production Document Scanner with flatbed, there is a specification which states: Integrated A3 FlatBed scanning. The term integrated can mean different things to different people. Our Flatbed is integrated into the scanning device that would be quoted in this category. It is a tethered device via USB. There is a 5 foot cable that is attached to the scanner and the scanner automatically determines if the paper is in the Automatic Document Feeder or if it is on the flatbed. The device can be placed anywhere within the range of the scanner. I would hope that is satisfactory for the specification. Please respond.

A12) Unfortunately No.

**ALL OTHER TERMS AND CONDITIONS OF THE RFP REMAIN UNCHANGED.**