



**RETURN BIDS TO:**  
**RETOURNER LES SOUMISSIONS À:**  
**Bid Receiving Public Works and Government**  
**Services Canada/Réception des soumissions Travaux**  
**publics et Services gouvernementaux Canada**  
**Room 100,**  
**167 Lombard Ave.**  
**Winnipeg**  
**Manitoba**  
**R3B 0T6**  
**Bid Fax: (204) 983-0338**

## **SOLICITATION AMENDMENT**

## **MODIFICATION DE L'INVITATION**

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

### **Comments - Commentaires**

**Vendor/Firm Name and Address**  
**Raison sociale et adresse du**  
**fournisseur/de l'entrepreneur**

**Issuing Office - Bureau de distribution**  
Public Works and Government Services Canada -  
Western Region  
Room 100  
167 Lombard Ave.  
Winnipeg  
Manitoba  
R3B 0T6

<b>Title - Sujet</b> Staff Housing Furniture	
<b>Solicitation No. - N° de l'invitation</b> A7100-152002/A	<b>Amendment No. - N° modif.</b> 001
<b>Client Reference No. - N° de référence du client</b> A7100-152002	<b>Date</b> 2016-02-16
<b>GETS Reference No. - N° de référence de SEAG</b> PW-\$WPG-016-9754	
<b>File No. - N° de dossier</b> WPG-5-38277 (016)	<b>CCC No./N° CCC - FMS No./N° VME</b>
<b>Solicitation Closes - L'invitation prend fin</b> <b>at - à 02:00 PM</b> <b>on - le 2016-03-14</b>	<b>Time Zone</b> <b>Fuseau horaire</b> Central Daylight Saving Time CDT
<b>F.O.B. - F.A.B.</b> <b>Plant-Usine:</b> <input type="checkbox"/> <b>Destination:</b> <input checked="" type="checkbox"/> <b>Other-Autre:</b> <input type="checkbox"/>	
<b>Address Enquiries to: - Adresser toutes questions à:</b> Hall, Marlene	<b>Buyer Id - Id de l'acheteur</b> wpg016
<b>Telephone No. - N° de téléphone</b> (204) 230-0147 ( )	<b>FAX No. - N° de FAX</b> (204) 983-7796
<b>Destination - of Goods, Services, and Construction:</b> <b>Destination - des biens, services et construction:</b>	

**Instructions: See Herein**

**Instructions: Voir aux présentes**

<b>Delivery Required - Livraison exigée</b>	<b>Delivery Offered - Livraison proposée</b>
<b>Vendor/Firm Name and Address</b> <b>Raison sociale et adresse du fournisseur/de l'entrepreneur</b>	
<b>Telephone No. - N° de téléphone</b> <b>Facsimile No. - N° de télécopieur</b>	
<b>Name and title of person authorized to sign on behalf of Vendor/Firm</b> <b>(type or print)</b> <b>Nom et titre de la personne autorisée à signer au nom du fournisseur/</b> <b>de l'entrepreneur (taper ou écrire en caractères d'imprimerie)</b>	
<b>Signature</b>	<b>Date</b>

This **amendment # 001** is raised to modify **Solicitation #A7100-152002/A**, dated 2016-02-02, as follows:

1) Refer to page 16 of 30, **ANNEX “A” REQUIREMENT**

**Delete:** Delete the Compliance Matrix in its entirety.

**Insert:** Insert the following Compliance Matrix.

<p><b><u>Completion and submission of Mandatory Technical Specification is required to be considered responsive and for your bid to be given further consideration.</u></b></p> <p>Provide the specification being offered which meets or exceeds <b><u>and cross-reference as to where the supporting documentation is found within your proposal</u></b>. If there is insufficient space in the table, assign SIR # (Supplementary Information Reference) and provide the appropriate details on a separate page in your offer. Where published supporting documentation is not available in the form of brochures, technical data sheets etc., prepare a written narrative complete with a detailed explanation of how its offer demonstrates compliance.</p>		
<p><u>All work and materials herein specified must meet and maintain minimum Canadian and Provincial certification(s) and approval(s) as applicable by Industry Standards.</u></p>		
<b>Item</b>	<b>Specifications</b>	Bidder Response: indicate how they meet the specifications addressed below/ cross-reference where this technical specification is indicated in their bid documentation
<b>1.</b>	<b>3-Seater Sofa</b>	
1.1	Must be same manufacturer product line and finishes as lounge chair and 2-seater loveseat	
1.2	Dimensions Width: 2100mm – 2500mm Depth: 850mm – 1000mm Height: up to 950mm	
1.3	Enclosed fully upholstered outer frame	
1.4	Comfortably seat 3 adults	
1.5	Fabric must have an abrasion resistance of 50,000 double rubs or more (ASTM D4157)	
1.6	Fabric must meet flammability requirements as per CAN/CGSB-4.2 No. 27.5	
1.7	Fabric must be treated for stain resistance	
1.8	Fabric patterns must align at seams	
1.9	Removable cushions with zippered closure suitable for machine washing	

Solicitation No. - N° de l'invitation  
A7100-152002/A  
Client Ref. No. - N° de réf. du client  
A7100-152002

Amd. No. - N° de la modif.  
001  
File No. - N° du dossier  
WPG-5-38277

Buyer ID - Id de l'acheteur  
wpg016  
CCC No./N° CCC - FMS No./N° VME

1.10	Minimum 150mm legs/feet to allow for airflow, in a light hard wood or metal finish	
1.11	Backs – Foam Indentation Load Deflection rating of 20-30 and density of 1.2 – 2.8 lb/ft³	
1.12	Seats – Foam Indentation Load Deflection rating of 30-50 and density of 2.2 – 2.8 lb/ft³	
1.13	Hardwood Interior Frame	
1.14	Minimum 10 years industry standard warranty, provide details of warranty	
<b>2</b>	<b>2-Seater Loveseat</b>	
2.1	Must be same manufacturer product line and finishes as lounge chair and 3-seater sofa	
2.2	Dimensions Width: 1450mm – 1750mm Depth: 950mm – 1000mm Height: up to 950mm	
2.3	Enclosed, full upholstered outer frame	
2.4	Comfortably seat 2 adults	
2.5	Fabric must have an abrasion resistance of 50,000 double rubs or more (ASTM D4157)	
2.6	Fabric must meet flammability requirements as per CAN/CGSB-4.2 No. 27.5	
2.7	Fabric must be treated for stain resistance	
2.8	Fabric patterns must align at seams	
2.9	Removable cushions with zippered closure suitable for machine washing	
2.10	Minimum 150mm legs/feet to allow for airflow, in a light hard wood or metal finish	
2.11	Backs – Foam Indentation Load Deflection rating of 20-30 and density of 1.2 – 2.8 lb/ft³	
2.12	Seats – Foam Indentation Load Deflection rating of 30-50 and density of 2.2 – 2.8 lb/ft³	
2.13	Hardwood Interior Frame	
2.14	Minimum 10 years industry standard warranty, provide details of warranty	

<b>3</b>	<b>1-Seater Lounge Chair</b>	
3.1	Must be same manufacturer product line and finishes as 2-seater loveseat and 3-seater sofa	
3.2	Dimensions Width: 850mm – 950mm Depth: 950mm – 1000mm Height: up to 950mm	
3.3	Enclosed, full upholstered outer frame	
3.4	Comfortably seat 1 adult	
3.5	Fabric must have an abrasion resistance of 50,000 double rubs or more (ASTM D4157)	
3.6	Fabric must meet flammability requirements as per CAN/CGSB-4.2 No. 27.5	
3.7	Fabric must be treated for stain resistance	
3.8	Fabric patterns must align at seams	
3.9	Removable cushions with zippered closure suitable for machine washing	
3.10	Minimum 150mm legs/feet to allow for airflow, in a light hard wood or metal finish	
3.11	Backs – Foam Indentation Load Deflection rating of 20-30 and density of 1.2 – 2.8 lb/ft³	
3.12	Seats – Foam Indentation Load Deflection rating of 30-50 and density of 2.2 – 2.8 lb/ft³	
3.13	Hardwood Interior Frame	
3.14	Minimum 10 years industry standard warranty, provide details of warranty	
<b>4</b>	<b>Queen Mattress</b>	
4.1	Dimensions: Width: 1525mm Length: 2030mm Height: 200mm <b>60"W x 80"L x 8"H</b>	
4.2	Innerspring mattress with at least 400 individually pocketed 14 gauge coil springs	
4.3	Minimum 10mm (3/8") foam layer multi-quilted to fabric covering on both sides	
4.4	6 gauge border wire, comfort foam layer, side wall support	
4.5	Multi-quilted borders	

Solicitation No. - N° de l'invitation  
A7100-152002/A  
Client Ref. No. - N° de réf. du client  
A7100-152002

Amd. No. - N° de la modif.  
001  
File No. - N° du dossier  
WPG-5-38277

Buyer ID - Id de l'acheteur  
wpg016  
CCC No./N° CCC - FMS No./N° VME

4.6	Treated with a stain-resistant finish	
4.7	Meet or exceed the CAN/ULC-S137 flame requirements	
4.8	Minimum of 10 years industry standard warranty, provide details of warranty	
4.9	Flip-able, two-sided construction	
4.10	Fabric cover/ticking must be made from polyester or cotton-poly blend	
<b>5</b>	<b>Twin XL Mattress</b>	
5.1	Dimensions: Width: 990mm Length: 2030mm Height: 200mm <b>39"W x 80"L x 8"H</b>	
5.2	Innerspring mattress with at least 250 individually pocketed 14 gauge coil springs	
5.3	Minimum 10mm (3/8") foam layer multi-quilted to fabric covering on both sides	
5.4	6 gauge border wire, comfort foam layer, side wall support	
5.5	Multi-quilted borders	
5.6	Treated with a stain-resistant finish	
5.7	Meet or exceed the CAN/ULC-S137 flame requirements	
5.8	Minimum of 10 years industry standard warranty, provide details of warranty	
5.9	Flip-able, two-sided construction	
5.10	Fabric cover/ticking must be made from polyester or cotton-poly blend	
<b>6</b>	<b>Floor Lamp</b>	
6.1	Dimension: Height: 1525mm – 2000mm	
6.2	Satin chrome, brushed nickel or anodized metal or clear oak or clear maple base with removable shade	
6.3	CSA approved	
6.4	Fully assembled	

6.5	Switch allowing for lighting level (brightness) adjustment	
6.6	Single bulb design with one fully dimmable LED bulb (16 – 20W) included	
6.7	Lamps with flexibility to direct light is preferred	
6.8	To be same manufacturer, finishes and product line as Table Lamps	
<b>7</b>	<b>Table Lamp</b>	
7.1	Dimensions: Height: 610mm – 915mm	
7.2	Satin chrome, brushed nickel or anodized metal or clear oak or clear maple base with removable shade	
7.3	CSA approved	
7.4	Fully assembled	
7.5	Switch allowing for lighting level (brightness) adjustment	
7.6	Single bulb design with one fully dimmable LED bulb (16 – 20W) included	
7.7	To be same manufacturer, finishes and product line as Table Lamps	
<b>8</b>	<b>Wood Dining Chair</b>	
8.1	Dimensions: Width: 480 mm - 560 mm Depth: 540 mm - 610 mm Seat height: 440 mm - 510 mm Total Back height: 740 mm - 940 mm	
8.2	Frame to be of solid oak, complete with four legs, seat and back	
8.3	Type and joinery of chair to support an adult up to 140kg (300 lbs) and maintain integrity of chair	
8.4	All joints and joining to be fabricated in accordance with good industry practice to ensure maximum strength equal to ASTM D905	
8.5	All joints to be well fitting, with clear smooth finish, free of defects that may affect the integrity of the furniture	

Solicitation No. - N° de l'invitation  
A7100-152002/A  
Client Ref. No. - N° de réf. du client  
A7100-152002

Amd. No. - N° de la modif.  
001  
File No. - N° du dossier  
WPG-5-38277

Buyer ID - Id de l'acheteur  
wpg016  
CCC No./N° CCC - FMS No./N° VME

8.6	Design to support securing "off the shelf" removable seat cushion (not included)	
8.7	All exposed fasteners that are not decorative will be counter sunk and plugged for uniform finished appearance	
8.8	Minimum 5 year warranty for the entire chair. Provide details of warranty.	
8.9	Finish to support cleaning with regular multipurpose household cleaning products for the kitchen	
8.10	Dining chairs are to all be of the same product line, manufacturer, colour and finish	
9.	Must be delivered on or before April 15, 2016 to Cambridge Bay, Nunavut	
10.	On-site installation must be conducted and completed by a qualified installer on or before April 15, 2016.	

**ALL OTHER TERMS AND CONDITIONS REMAIN THE SAME.**