



**RETURN BIDS TO:**

**RETOURNER LES SOUMISSIONS À:**

**Bid Receiving - PWGSC / Réception des soumissions  
- TPSGC**

11 Laurier St./11, rue Laurier  
Place du Portage, Phase III  
Core 0B2 / Noyau 0B2

Gatineau  
Québec

K1A 0S5

Bid Fax: (819) 997-9776

**Revision to a Request for a Standing Offer**

**Révision à une demande d'offre à commandes**

National Master Standing Offer (NMSO)

Offre à commandes principale et nationale (OCPN)

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Offer remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'offre demeurent les mêmes.

**Comments - Commentaires**

**Vendor/Firm Name and Address**

**Raison sociale et adresse du  
fournisseur/de l'entrepreneur**

**Issuing Office - Bureau de distribution**

Armoured Vehicles Support/Soutien des véhicules blindés

11 Laurier St./11, rue Laurier  
Place du Portage Phase III 6C1  
Gatineau  
Québec  
K1A 0S5

<b>Title - Sujet</b> NISO-LEO 2 CHASSIS TRACK & SUSPENS		
<b>Solicitation No. - N° de l'invitation</b> W8486-155223/A		<b>Date</b> 2016-05-05
<b>Client Reference No. - N° de référence du client</b> W8486-155223		<b>Amendment No. - N° modif.</b> 003
<b>File No. - N° de dossier</b> 299bl.W8486-155223	<b>CCC No./N° CCC - FMS No./N° VME</b>	
<b>GETS Reference No. - N° de référence de SEAG</b> PW-\$\$BL-299-25712		
<b>Date of Original Request for Standing Offer</b>		2016-03-01
<b>Date de la demande de l'offre à commandes originale</b>		
<b>Solicitation Closes - L'invitation prend fin</b> <b>at - à 02:00 PM</b> <b>on - le 2016-06-22</b>		<b>Time Zone</b> <b>Fuseau horaire</b> Eastern Daylight Saving Time EDT
<b>Address Enquiries to: - Adresser toutes questions à:</b> Proulx, Sylvain		<b>Buyer Id - Id de l'acheteur</b> 299bl
<b>Telephone No. - N° de téléphone</b> (873) 469-4778 ( )	<b>FAX No. - N° de FAX</b> ( ) -	
<b>Delivery Required - Livraison exigée</b>		
<b>Destination - of Goods, Services, and Construction:</b> <b>Destination - des biens, services et construction:</b> Specified Herein		
<b>Security - Sécurité</b> This revision does not change the security requirements of the Offer. Cette révision ne change pas les besoins en matière de sécurité de la présente offre.		

**Instructions: See Herein**

**Instructions: Voir aux présentes**

<b>Acknowledgement copy required</b>	<b>Yes - Oui</b>	<b>No - Non</b>
<b>Accusé de réception requis</b>	<input type="checkbox"/>	<input type="checkbox"/>
<b>The Offeror hereby acknowledges this revision to its Offer.</b> <b>Le proposant constate, par la présente, cette révision à son offre.</b>		
<b>Signature</b>	<b>Date</b>	
Name and title of person authorized to sign on behalf of offeror. (type or print) Nom et titre de la personne autorisée à signer au nom du proposant. (taper ou écrire en caractères d'imprimerie)		
<b>For the Minister - Pour le Ministre</b>		

### AMENDMENT 003

This amendment (**003**) is raised to: **a)** extend the solicitation closing date, **b)** publish clarifications sought by Industry and **c)** amend the original solicitation terms and conditions by inserting 2 additional clauses and replace [Annex A](#) and [Annex F](#) with revised versions.

#### **a) Extend the Solicitation closing date**

The solicitation closing date and time, as stated on page one of this solicitation, is hereby amended to **2:00PM Eastern daylight saving time on June 22, 2016**.

#### **b) Questions and Clarifications:**

**Question 1:** Is it possible to deliver spare parts with the condition "surplus unused" or "used"? If so, please provide us with corresponding quality classification for such spare parts (e.g. German regulation ZK-A; Condition Level A).

**Clarification 1:** No, Canada will not accept spare parts with the condition "surplus unused" or "used".

**Question 2:** If a part is obsolete and can't be offered, is it possible to make a partial offer?

**Clarification 2:** No, Canada will not accept any partial offer. The Offeror is to advise the Contracting Authority no later than fifteen (15) calendar days before the bid closing date of products specified in the bid solicitation which are obsolete from the Original Equipment Manufacturer (OEM) and no replacement of the OEM part or equivalent products exist and are therefore unable to provide a proposal for the part. A copy of a certificate from the OEM providing justification/explanation that the part number is obsolete and no replacement of the OEM part or equivalent products exist must be provided. Once the information is validated the part will be removed from the solicitation (Annex A and F).

**Question 3:** If items can't be delivered (for example because of obsolescence) during the Standing Offer period, is it possible to delete these parts in the contract without any costs?

**Clarification 3:** If during the period of the Standing Offer an item becomes obsolete the Offeror is expected to propose any substitutes, alternatives or extensions to items for review and acceptance as per Part 7 – Standing Offer Resulting Contract Clauses, 7.15, Substitutes, Alternatives and Extensions, of the RFSO . If an item is obsolete and no replacement or equivalent products exist and are therefore unable to provide the part a copy of a certificate from the OEM providing that justification/explanation must be provided. Once the information is validated the part will be removed from the Standing Offer.

**Question 4:** What happens when an Offeror makes only a partial offer?

**Clarification 4:** Any Offeror making only a partial offer will be non-compliant as per clauses 3.2 and 3.3 of Part 3.

#### **c) Amend the original Solicitation as follow:**

##### **1 At Part 7B - RESULTING CONTRACT CLAUSES, Insert the following clauses 7.7.4 and 7.4.5**

##### **7.7.4 Preparation for Delivery – Canadian Forces Packaging Specifications**

The Contractor must prepare items for delivery in accordance with the latest issue of the following Canadian Forces packaging specifications:

- a. [D-LM-008-026/SF-001](#), Preformed Packing, Gaskets or Seals (rubber natural/synthetic, cork, asbestos or leather);
- b. [D-LM-008-030/SF-001](#), Hose, Rubber, Plastic, Fabric or Metal (including tubing) and Fittings, Nozzles and Strainers;
- c. [D-LM-008-035/SF-001](#), Electrostatic Discharge Protective Packaging - Electronic Parts, Assemblies and Equipment; and
- d. [D-LM-008-037/SF-000](#), Antifriction Bearings (other than instrument precision bearings).

#### **7.7.5 Packaging Requirement using Specification D-LM-008-036/SF-000**

The Contractor must prepare items for delivery in accordance with the latest issue of the Canadian Forces Packaging Specification [D-LM-008-036/SF-000](#), DND Minimum Requirements for Manufacturer's Standard Pack.

#### **2 Delete in its entirety the original Annexes "A" and "F" and replace by the following amended versions:**

- 2.1 [Annex A Version 2.0 - Requirement –Parts Item List v 2.0 -](#) (attached); and
- 2.2 [Annex F - Microsoft Excel Workbook.V2.0.xls](#)

**ALL OTHER TERMS AND CONDITIONS REMAIN THE SAME**

Solicitation No. - N° de l'invitation  
W8486-155223/A  
Client Ref. No. - N° de réf. du client  
W8486-155223

Amd. No. - N° de la modif.  
003  
File No. - N° du dossier  
299bl.W8486-155223

Buyer ID - Id de l'acheteur  
299bl  
Annex  
A

---

## **ANNEX A**

### **REQUIREMENT – PARTS ITEM LIST**

#### **Version 2.0**

Annex A v 2.0, Requirement - Parts List  
to W8486-155223, Leo 2 Chassis Track and Suspension NISO

ITEM	NSN	MIPN	NCAGE	CFSS ITEM NAME	PACKAGING REQUIREMENT
1	2530-12-343-0288	2300109-097500.000.0	D1871	Road wheel suspension arm assembly Left	Clause D3013C, Level A, packaged in quantities of 1 by package
2	2530-12-175-8488	2300109-091121.000.0	D1871	support arm hub wheel, with stud and bearing	Clause D3013C, Level A, packaged in quantities of 1 by package
3	2530-12-343-0287	2300109-097600.000.0	D1871	Road wheel suspension arm assembly Right	Clause D3013C, Level A, packaged in quantities of 1 by package
4	2530-12-343-0286	2300109-097700.000.0	D1871	Suspension arm assembly with bearing Left and Right	Clause D3013C, Level A, packaged in quantities of 1 by package
5	2510-12-353-5152	2300397-091510.000.0	D1871	Left torsion bar	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
6	2510-12-353-5153	2300397-091520.000.0	D1871	Right torsion bar	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
7	2530-12-175-8497	2300109-092600.000.0	D0354	Carrier, vehicle	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
8	3110-12-337-2538	2300109-092100.007.0	D1871	Bearing roller for idler wheel hub	Clause D3016C - D-LM-008-037/SF-000, packaged in quantities of 1 by package
9	2530-12-193-0045	2300109-980921-001-0	D1871	Idler Hub wheel	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
10	2530-12-353-5693	2300109-092100.001.0	D1871	Idler cap grease	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
11	2530-12-175-8498	1289291	D1871	Idler wheel arm assembly pivot Right	Clause D3013C, Level A, packaged in quantities of 1 by package
12	2530-12-175-8495	1289288	D1871	Idler wheel arm assembly pivot Left	Clause D3013C, Level A, packaged in quantities of 1 by package
13	2530-12-351-4949	DRS 3710	D8856	Idler Wheel solid rubber Steel	Clause D3013C, Level B, packaged in quantities of 1 by package
14	2530-12-197-6495	2300206-092400.000.0	D9448	Track Tension Adjuster Left	Clause D3013C, Level B, packaged in quantities of 1 by package
15	2530-12-197-6496	2300206-092500.000.0	D9448	Track Tension Adjuster Right	Clause D3013C, Level B, packaged in quantities of 1 by package
16	5365-12-387-7007	7171-0006-34 0624	D1871	Sleeve, coupling for track tension adjuster	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
17	2530-12-356-9972	2300436-093100.000.0	D1871	Support roller axle assy, New	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
18	4320-12-176-4731	2300109-093111.000.0	D1871	Seal assembly shaft	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
19	3110-12-146-7486	DIN720-32209J	D8286	Bearing roller	Clause D3016C - D-LM-008-037/SF-000, packaged in quantities of 1 by package
20	3110-12-126-5322	DIN720-32208J	D8286	Bearing roller	Clause D3016C - D-LM-008-037/SF-000, packaged in quantities of 1 by package
21	2530-12-145-6243	2360-135000.11.0	D1871	Road cap support roller	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
22	2530-12-175-8501	2300109-093200.000.0	D9448	Support roller track	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
23	2530-12-310-3357	7 208 04 00 A	D2239	End connector	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
24	2530-12-311-1935	7 208 05 00 A	D2239	Connector Center	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
25	2520-12-175-6634	1189-92-0110A	C7574	Flange Mount	Clause D3013C, Level C, packaged in quantities of 1 by package
26	5340-12-199-0917	700M36X1.5	D0730	Plug protective dust	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
27	2530-12-198-6868	2300109-090000.016.0	D1871	Cover end-stop	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
28	2530-12-196-4068	2300109-096395.000.0	D1871	Cover end-stop	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
29	2530-12-196-4067	2300109-096380.004.0	D1871	Cover end-stop	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
30	2530-12-196-3613	2300109-090000.015.0	D1871	Angle fastening	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
31	2530-12-333-9863	2300348-096300.000.0	D1871	Damper end stop	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
32	2530-12-193-0046	2300109-980931.001.0	D1871	Repair set, support roller	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package



70	4320-12-176-4731	76.97HS-39 WTNB50	SEAL ASSEMBLY SHAFT SPRING LOADED	C5419	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
71	5310-12-176-6476	2300109-092200.002.0	WASHER RECESSED	D1871	Clause D3018C - D-LM-008-036/SF-000
72	2530-12-187-4122	2300109-092110.004.0	SAFETY PIN	D1871	Clause D3018C - D-LM-008-036/SF-000
73	5306-12-187-5170	2300109-090000.001.0	BOLT,MACHINE	D1871	Clause D3018C - D-LM-008-036/SF-000
74	5340-12-194-9529	2300109-091123.000.0	COVER,ACCESS	D1871	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
75	2530-12-196-4067	2300109-096380.004.0	COVER,END-STOP	D1871	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
76	5331-12-303-1952	A1942-C3057	O-RING	D9800	Clause D3016C - D-LM-008-026/SF-001
77	5331-12-303-1953	A3208-C3057	O-RING	D9800	Clause D3016C - D-LM-008-026/SF-001
78	3110-12-307-5260	32219	BEARING ROLLER TAPERED	D2456	Clause D3016C - D-LM-008-037/SF-000, packaged in quantities of 1 by package
79	3110-12-307-5261	30314	BEARING ROLLER TAPERED	D2457	Clause D3016C - D-LM-008-037/SF-000, packaged in quantities of 1 by package
80	2530-12-311-1935	7 208 05 00 A	CONNECTOR CENTER	D2239	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
81	5340-12-336-7162	2300348-091720.005.0	COVER ACCESS	D1871	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
82	7510-12-182-9872	80-6109-2777-6	TAPE PRESSURE SENSITIVE ADHESIVE	D2607	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
83	3110-12-337-2538	33021	BEARING ROLLER TAPERED	D2456	Clause D3016C - D-LM-008-037/SF-000, packaged in quantities of 1 by package
84	5365-12-182-3026	2300109-092400.004.0	SPACER PLATE	D9448	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
85	4810-12-348-3672	MVB31.08.01	VALVE ASSEMBLY MANIFOLD	D0786	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
86	5330-12-146-5312	2360-135000.12.0	GASKET	D1871	Clause D3016C - D-LM-008-026/SF-001
87	5325-12-126-5160	DIN472 165X4	RING,RETAINING	D9909	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
88	5331-12-133-4320	OR108X4-72NBR/872	O-RING	D2480	Clause D3016C - D-LM-008-026/SF-001
89	5331-12-142-9982	492157-8.3NB6021	O-RING	C5834	Clause D3016C - D-LM-008-026/SF-001
90	5331-12-146-5291	492182-8NB6021	O-RING	C5834	Clause D3016C - D-LM-008-026/SF-001
91	5331-12-146-8557	OR122X4-72NBR/872	O-RING	D2480	Clause D3016C - D-LM-008-026/SF-001
92	5331-12-146-8572	OR60X5-72NBR/872	O-RING	D2480	Clause D3016C - D-LM-008-026/SF-001
93	5331-12-146-8576	OR69X3-72NBR/872	O-RING	D2480	Clause D3016C - D-LM-008-026/SF-001
94	5331-12-146-8578	OR78.5X6-72NBR/872	O-RING	D2480	Clause D3016C - D-LM-008-026/SF-001
95	5307-12-156-4582	136369	STUD,PLAIN	D0078	Clause D3018C - D-LM-008-036/SF-000
96	4730-12-160-0539	DIN71412-AM8X1-2.054	FITTING,LUBRICATION	D8286	Clause D3016C - D-LM-008-030/SF-001
97	5340-12-166-3892	2360-134000.06.0	SEAT,BALL SOCKET	D1871	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
98	2530-12-175-8497	1189-92-0013-A	CARRIER,VEHICLE	C4536	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
99	2530-12-175-8502	2300109-093110.000.0	HUB,SUPPORT ROLL	D1871	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
100	2530-12-182-4543	2300109-092400.003.0	SPINDLE,TRACK	D1871	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
101	5330-12-183-0907	B1FSF80-105-10/30 101/3	SEAL,PLAIN ENCASED	D2480	Clause D3016C - D-LM-008-026/SF-001
102	5310-12-187-4946	2300109-093100.002.0	WASHER,SHOULDERED AND RECESSED	D1871	Clause D3018C - D-LM-008-036/SF-000
103	5310-12-187-4947	2300109-093100.003.0	WASHER,RECESSED	D1871	Clause D3018C - D-LM-008-036/SF-000
104	5365-12-187-5614	2300109-092110.005.0	SPACER,SLEEVE	D1871	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
105	2530-12-187-7614	2300109-092110.002.0	LABYRINTH RING	D1871	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
106	2530-12-193-0044	2300109-980911-001-0	HUB,WHEEL	D1871	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package

139	5305-12-142-3031	DIN912-M24X260-10.9-A3P	D8286	Screw cap. Socket HE	Clause D3018C - D-LM-008-036/SF-000
140	4320-12-176-3292	LT1772	C4268	Seal assembly shaft, idler wheel hub	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
141	5331-12-142-9982	492157-8,3NB6021	C5834	O-Ring	Clause D3016C - D-LM-008-026/SF-001
142	5310-12-176-6476	2300109-092200.002.0	D1871	Washer, recessed	Clause D3018C - D-LM-008-036/SF-000
143	5310-12-175-8024	2300109-092200.004.0	D1871	Washer, key	Clause D3018C - D-LM-008-036/SF-000
144	5305-12-344-2461	ISO4017-M10X12-8.8-A3P	I9008	Screw, cap hexagon head	Clause D3018C - D-LM-008-036/SF-000
145	5365-12-351-8438	2300436-092200.003.0	D1871	Plug machine thread	Clause D3018C - D-LM-008-036/SF-000
146	5330-12-346-4847	2300109-092200.007.0	D1871	Gasket for idler wheel cap	Clause D3016C - D-LM-008-026/SF-001
147	5310-12-354-3898	ISO7089-10-200HV-A3P	I9008	Washer flat	Clause D3018C - D-LM-008-036/SF-000
148	5330-12-124-0980	DIN7603-A24X28-AL	D8286	Gasket	Clause D3016C - D-LM-008-026/SF-001
149	5308-12-187-5170	2300109-090000.001.0	D1871	Idler wheel bolt, machine (Stud)	Clause D3018C - D-LM-008-036/SF-000, packaged in quantities of 1 by package
150	5315-12-187-5912	2300109-091100.007.0	D1871	Pin, straight, Headle for support arm	Clause D3018C - D-LM-008-036/SF-000
151	5331-12-382-8983	OR159X11-72NBR/872	D2480	O-Ring idler wheel rocker,	Clause D3016C - D-LM-008-026/SF-001
152	5305-12-359-6163	ISO12474-M20X1,5X70-10.9-A3P	I9008	Screw,, cap socket hexagon for track tension adjuster	Clause D3018C - D-LM-008-036/SF-000
153	5330-12-156-4785	DIN7603-A48X55-CU	D8286	Gasket for track tension adjuster	Clause D3016C - D-LM-008-026/SF-001
154	5305-12-349-0596	ISO7045-M4X10-4.8-H-A2P	I9008	Screw machine	Clause D3018C - D-LM-008-036/SF-000
155	5330-12-156-8402	U60-22,7X30X2-72NBR/99041	D2480	Gasket for track tension adjuster	Clause D3016C - D-LM-008-026/SF-001
156	5331-12-146-5291	2360-135000.13.0	D1871	O-Ring	Clause D3016C - D-LM-008-026/SF-001
157	5310-12-187-4946	2300109-093100.002.0	D9448	Washer, shouldered	Clause D3018C - D-LM-008-036/SF-000
158	5307-12-156-4582	DIN835-M8X25-8.8	D8286	Stud plain	Clause D3018C - D-LM-008-036/SF-000
159	5307-12-187-5615	2300109-093110.002.0	D1871	Stud plain	Clause D3018C - D-LM-008-036/SF-000
160	5310-12-187-4947	2300109-093100.003.0	D9448	Washer, recessed	Clause D3018C - D-LM-008-036/SF-000
161	5315-12-346-8416	ISO1234-5X45-ST-A3P	I9008	Pin cutter	Clause D3018C - D-LM-008-036/SF-000
162	5310-12-182-0403	2300109-093100.004.0	D1871	Nut plain castellat	Clause D3018C - D-LM-008-036/SF-000
163	5330-12-146-5312	2360-135000.12.0	D1871	Gasket	Clause D3016C - D-LM-008-026/SF-001
164	5330-12-156-5014	DIN7603-ABX11,5-CU	D8286	Gasket	Clause D3016C - D-LM-008-026/SF-001
165	5310-12-334-2549	ISO4032-M8-8-A2P	I9008	Nut plug hexagon	Clause D3018C - D-LM-008-036/SF-000
166	5310-12-142-8173	DIN137-B8-FST-A3P	D8286	Washer spring tension	Clause D3018C - D-LM-008-036/SF-000
167	5310-12-328-4488	DIN982-M12X1,25-8-A2P	D8286	Nut self-locking hexagon	Clause D3018C - D-LM-008-036/SF-000
168	5306-12-318-2064	75700402A	D2239	Bolt end connector	Clause D3018C - D-LM-008-036/SF-000
169	5315-12-345-0165	ISO8752-16X26-N-ST	I9008	Pin Spring for final drive New	Clause D3018C - D-LM-008-036/SF-000
170	3020-12-182-4284	1504844	D1871	Sprocket wheel	Clause D3013C, Level C, packaged in quantities of 1 by package
171	5315-12-126-6730	DIN1481-8X20	D8286	Pin spring for final drive	Clause D3018C - D-LM-008-036/SF-000
172	5325-12-346-5924	4138 303 110	D8124	Insert screw thread	Clause D3018C - D-LM-008-036/SF-000
173	5315-12-124-4165	0631 308 018	D8124	Pin grooved headles	Clause D3018C - D-LM-008-036/SF-000
174	5305-12-367-3876	ISO8765-M20X1,5X70-10.9-A3P	I9008	Screw cap hexagon	Clause D3018C - D-LM-008-036/SF-000
175	5305-12-357-2104	ISO8676-M20X1,5X40-10.9-A3P	I9008	Screw cap hexagon	Clause D3018C - D-LM-008-036/SF-000



213	5305-12-142-3031	DIN912-M24X260-10.9-A3P	D8286	SCREW,CAP, SOCKET HEAD	Clause D3018C - D-LM-008-036/SF-000
214	5310-12-176-4112	2300109-0900000.002.0	D9448	WASHER	Clause D3018C - D-LM-008-036/SF-000
215	5310-12-182-0403	2300109-093100.004.0	D1871	NUT,PLAIN,CASTELLATED,HEXAGON	Clause D3018C - D-LM-008-036/SF-000
216	5305-12-185-5609	DIN912-M20X1,5X70-10.9-A3P	D8286	SCREW,CAP, SOCKET HEAD	Clause D3018C - D-LM-008-036/SF-000
217	5315-12-186-8742	DIN1481-16X26	D8286	PIN,SPRING	Clause D3018C - D-LM-008-036/SF-000
218	5307-12-187-5615	2300109-093110.002.0	D1871	STUD,PLAIN	Clause D3018C - D-LM-008-036/SF-000
219	5315-12-187-5912	2300109-091100.007.0	D1871	PIN,STRAIGHT,HEADLESS	Clause D3018C - D-LM-008-036/SF-000
220	5315-12-345-2156	ISO8752-6X10-N-A	I9008	PIN,SPRING	Clause D3018C - D-LM-008-036/SF-000
221	5315-12-346-8416	16860401	D8060	PIN,COTTER	Clause D3018C - D-LM-008-036/SF-000
222	5310-12-355-2649	7059402	C7535	WASHER,FLAT	Clause D3018C - D-LM-008-036/SF-000

ITEM	NSN	MPN	NCAGE	CFSS ITEM NAME	PACKAGING LEVEL
223	2530-12-312-5487	75700100FT	C4544	Track link vehicular	Clause D3013C, Level C, packaged in quantities of 4 sections (each section to be 6 to 7 links) by package
224	2530-12-175-7546	751	D2239	Track pad	Clause D3013C, Level C, packaged in quantities of 500 by package
225	2530-12-371-4186	22764	D2239	Track pad	Clause D3013C, Level C, packaged in quantities of 500 by package