

PLUMBING FIXTURE AND TRIM SCHEDULE																		
FIXTURE TAG	MANUF.	MODEL NO.	COLOUR	WATER CLOSET & URINAL TRIM			SINK & LAVATORY TRIM			SHOWER & BATH TRIM			MOUNTING	ROUGHING			REMARKS	
				SUPPLY/VALVE	TANK	CARRIER	SEAT	FAUCET	WASTE	TRAP	SUPPLIES	CARRIER		HEAD	FAUCET OR MIXING VALVE	WASTE & OVERFLOW		WASTE
WC-1	AMERICAN STANDARD	CHAMPION 4 2004 314	WHITE	DELTA 47P1316SD	-	-	BEAMS 212150T	-	-	-	-	-	FLOOR MTD	75mm	50mm	-	12mm	BURNER FREE, ELONGATED 419mm HIGH BOWL.
WC-2	AMERICAN STANDARD	CHAMPION 4 2004 314	WHITE	DELTA 47P1316SD	-	-	BEAMS 212150T	-	-	-	-	-	FLOOR MTD	75mm	50mm	-	12mm	ELONGATED 381mm HIGH BOWL.
UR-1	AMERICAN STANDARD	WASHROOM 6590.005	WHITE	DELTA 817231WMA	-	218M Z-1223	-	-	-	-	-	-	WALL MTD	50mm	40mm	-	40mm	C/W STAINLESS STEEL STRAINER AND SURFABLE REPAIRS/REPAIR FOR WALL SUPPORTS
LAV-1	AMERICAN STANDARD	QUARTZ 9442.000	WHITE	-	-	-	-	DELTA 252101	DELTA 331290	DELTA 331311	DELTA 47P2312SD	-	WALL MTD	32mm	40mm	12mm	12mm	INSULATE PIPES MORE EXPOSED C/W 6007187MM THICKNESS IN SPACED ROOF PROVIDE LOW VOLTAGE WIRING TO SHOWER CONTROL BOXES
SH-1	-	-	-	-	-	-	-	-	-	-	-	-	DELTA 8607187-88	-	-	-	-	C/W 6007187MM THICKNESS IN SPACED ROOF PROVIDE LOW VOLTAGE WIRING TO SHOWER CONTROL BOXES
SH-2	-	-	-	-	-	-	-	-	-	-	-	-	DELTA 8607187-88	30mm	40mm	12mm	12mm	C/W 6007187MM THICKNESS IN SPACED ROOF PROVIDE LOW VOLTAGE WIRING TO SHOWER CONTROL BOXES
TP	PPP WC	P1-500	-	-	-	-	-	-	-	-	-	-	-	30mm	40mm	12mm	12mm	C/W 6007187MM THICKNESS IN SPACED ROOF PROVIDE LOW VOLTAGE WIRING TO SHOWER CONTROL BOXES
SK-1	WATERCET	LD0750B-1	S.S	-	-	-	-	DELTA 252101	DELTA 331290	DELTA 331311	DELTA 47P2312SD	-	COUNTER MTD	50mm	40mm	12mm	12mm	C/W 6007187MM THICKNESS IN SPACED ROOF PROVIDE LOW VOLTAGE WIRING TO SHOWER CONTROL BOXES
TRV	STATIONS	7-200-B	-	-	-	-	-	-	-	-	-	-	-	-	-	-	12mm	TEMPERING MIXING VALVE FOR SHOWERS C/W CABINET
HWT-1	65 GALLON PROPANE HOT WATER TANK (312 Ltrs) MODEL TO BE RHEED-CDS-360	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	12mm	TEMPERING MIXING VALVE FOR SHOWERS C/W CABINET

FLOOR DRAIN SCHEDULE									
TAG NO.	MODEL NO.	MANUF.	COATING FINISHING	CLAMP	TRAP	TRAP SEAL PRIMER	SPECIAL REQUIREMENTS	AREA OF APPLICATION	REMARKS
FD-1	ZH-415-B-P	ZURN	YES	YES	REC'D	REC'D	-	SEE DRAWING	OUTLET SIZE AS PER DRAWING.
FD-2	ZH-415-B	ZURN	YES	YES	REC'D	NO	-	SEE DRAWING	OUTLET SIZE AS PER DRAWING.

FAN SCHEDULE									
TAG NO	SYSTEM SERVED	MANUF.	MODEL NO.	TYPE	FAN DATA				REMARKS
					AIR FLOW (L/s)	STATIC PRESS (Pa)	FAN SPEED RPM	SOUND POWER LEVEL (dB)	
F-1	WASHROOMS	GREENHECK	SP-A390	EXHAUST	153	124	1350	-	-

CROSBIE ENGINEERING LTD. CONSULTING ENGINEERS 21 Wood Road, 2nd Floor, P.O. Box 12251, Victoria, 3 Tel: (03) 751 1800 Fax: (03) 751 1800 www.crosbieengineering.com		Project: WASHROOM BUILDING RECAPITALIZATION SOUND CAMPGROUND TERRA NOVA NATIONAL PARK		Drawing title: PLUMBING SCHEDULES Date: MAY 12, 2016	
NO. 1		Issued with Addendum A		05/12/16	
REVISION DESCRIPTION		DATE		designed by: N.C. drawn by: N.H. approved by: N.H.	
Project no: 15-1992		Project no: 15-1992		Project no: 15-1992	
MSK-1		MSK-1		MSK-1	

