



RETURN BIDS TO:

RETOURNER LES SOUMISSIONS À:

Bid Receiving - PWGSC / Réception des soumissions
- TPSGC

11 Laurier St. / 11, rue Laurier

Place du Portage, Phase III

Core 0B2 / Noyau 0B2

Gatineau, Québec K1A 0S5

Bid Fax: (819) 997-9776

SOLICITATION AMENDMENT MODIFICATION DE L'INVITATION

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

Comments - Commentaires

Vendor/Firm Name and Address

Raison sociale et adresse du
fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution

Electrical & Electronics Products Division
11 Laurier St./11, rue Laurier
7B3, Place du Portage, Phase III
Gatineau, Québec K1A 0S5

Title - Sujet CCTV AT ATLANTIC INSTITUTIONS	
Solicitation No. - N° de l'invitation 21120-169589/A	Amendment No. - N° modif. 005
Client Reference No. - N° de référence du client 21120-16-2209589	Date 2016-06-15
GETS Reference No. - N° de référence de SEAG PW-\$\$HN-461-70697	
File No. - N° de dossier hn461.21120-169589	CCC No./N° CCC - FMS No./N° VME
Solicitation Closes - L'invitation prend fin at - à 02:00 PM on - le 2016-06-28	Time Zone Fuseau horaire Eastern Daylight Saving Time EDT
F.O.B. - F.A.B. Plant-Usine: <input type="checkbox"/> Destination: <input type="checkbox"/> Other-Autre: <input type="checkbox"/>	
Address Enquiries to: - Adresser toutes questions à: Hallman, Patti	Buyer Id - Id de l'acheteur hn461
Telephone No. - N° de téléphone (819) 420-0339 ()	FAX No. - N° de FAX () -
Destination - of Goods, Services, and Construction: Destination - des biens, services et construction:	

Instructions: See Herein

Instructions: Voir aux présentes

Delivery Required - Livraison exigée	Delivery Offered - Livraison proposée
Vendor/Firm Name and Address Raison sociale et adresse du fournisseur/de l'entrepreneur	
Telephone No. - N° de téléphone Facsimile No. - N° de télécopieur	
Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) Nom et titre de la personne autorisée à signer au nom du fournisseur/ de l'entrepreneur (taper ou écrire en caractères d'imprimerie)	
Signature	Date

Solicitation No. - N° de l'invitation
21120-169589/A
Client Ref. No. - N° de réf. du client
21120-169589

Amd. No. - N° de la modif.
005
File No. - N° du dossier
hn461.21120-169589

Buyer ID - Id de l'acheteur
hn461
CCC No./N° CCC - FMS No./N° VME

Amendment 005 is issued to add additional questions to Attachment 001 – Questions and Answers and to provide additional supporting documentation.

ATTACHMENT 2

QUESTIONS AND ANSWERS cont'd

Q89) Can you please provide the following standards: ES/STD 223, ES/STD 233, ES/STD 234.

A89) Documentation is included as 3 individual PDF's as part of this amendment.

ALL OTHER TERMS AND CONDITIONS REMAIN UNCHANGED



**CORRECTIONAL SERVICES CANADA
TECHNICAL SERVICES BRANCH
ELECTRONIC SECURITY SYSTEMS**



ES/STD-0223
Revision 4
July 2015

**ELECTRONIC ENGINEERING STANDARD
PAN/TILT/ZOOM NETWORK COLOUR DOME CAMERA
FOR USE IN FEDERAL CORRECTIONAL INSTITUTIONS**

AUTHORITY

Acquisition of a camera for the identified purposes that is not in compliance with this standard must be approved by the Design Authority.

Recommended corrections, additions or deletions should be addressed to the Design Authority at the following address:

Director, Electronic Security Systems
Correctional Service of Canada
340 Laurier Avenue West,
Ottawa, Ontario
K1A 0P9

Approved by:

Director,
Electronic Security Systems

TABLE OF REVISIONS

Revision	Paragraph	Comment
0	N/A	Original
1	Paragraph 7.12 Paragraph 7.21	Optical zoom increased to 30x Added electronic image stabilization
2	All	Reformat and indoor/outdoor standard merge
3	Definitions	Removed
	2.1	Added reference IEC EN 61000-4-3, Radiated RF immunity
	3.2.2.3	Changed humidity to non-condensing 20%-90%
	3.3.1	Interference now uses IEC EN 61000-4-3, Radiated RF immunity
4	2.1/3.3.1	Change IEC EN 61000-4-3, Radiated RF immunity to IEC EN 55024, Immunity characteristics
	3.2.1.11	Removed smoked dome
	5.2.1	Added operate from external 24VAC power source

TABLE OF CONTENTS

TABLE OF REVISIONS	2
TABLE OF CONTENTS	3
TABLE OF ABBREVIATIONS	4
1 INTRODUCTION	5
1.1 Overview	5
1.2 Purpose	5
2 REFERENCES	6
2.1 Specifications, Standards, and Statements of Work	6
3 PHYSICAL	7
3.1 Dimensions	7
3.2 Environment	7
3.3 Interference	7
3.4 Reliability	7
3.5 Safety	7
4 OPERATIONAL	8
4.1 Camera	8
4.2 Lens	8
4.3 PTZ	8
4.4 Video	8
5 INTERFACE	9
5.1 Ports	9
5.2 Power	9
5.3 Video Management System Compatibility	9

TABLE OF ABBREVIATIONS

Abbreviation	Expansion
AGC	Automatic Gain Control
CSC	Correctional Service Canada
IEC	International Electrotechnical Commission
IEEE	Institute of Electrical and Electronics Engineers
MJPEG	Motion Joint Photographic Experts Group
MTBF	Mean Time Between Failures
ONVIF	Open Network Video Interface Forum
PoE	Power over Ethernet
PTZ	Pan Tilt Zoom
TCP/IP	Transmission Control Protocol/Internet Protocol

1 INTRODUCTION

1.1 Overview

- .1 This standard defines the requirements of Correctional Service Canada (CSC) for a pan, tilt, zoom (PTZ), network capable, dome camera for use at federal correctional institutions. PTZ cameras are deployed to allow detailed examination of areas typically covered by fixed cameras or areas without regular evidentiary coverage.

1.2 Purpose

- .1 The cameras are deployed primarily for observation use. Given they may be pointed anywhere, they are not assumed to be evidentiary coverage.
- .2 These cameras are for deployment for all outdoor PTZ camera locations.
- .3 These cameras are for deployment for all indoor PTZ camera locations.

2 REFERENCES

2.1 Specifications, Standards, and Statements of Work

- .1 Access to non-government specifications is the responsibility of the contractor.
- IEC EN55024 – International Electrotechnical Commission Information technology equipment – Immunity characteristics – Limits and methods of measurement
- IEC EN60529 – International Electrotechnical Commission Degrees of protection provided by enclosures (IP Code)
- IEC EN60950-1 – International Electrotechnical Commission Information technology equipment – Safety
- IEC EN62262 – International Electrotechnical Commission Degrees of protection provided by enclosures for electrical equipment against external mechanical impacts
- IEEE 802.3at – IEEE Standard for Information technology – Telecommunications and information exchange between systems – Local and metropolitan area networks – Specific requirements Part 3: Carrier Sense Multiple Access with Collision Detection (CSMA/CD) Access Method and Physical Layer Specifications Amendment 3: Data Terminal Equipment (DTE) Power via the Media Dependent Interface (MDI) Enhancements
- IEEE 802.3u – IEEE Standards for Local and Metropolitan Area Networks: Supplement to Carrier Sense Multiple Access with Collision Detection (CSMA/CD) Access Method and Physical Layer Specifications Media Access Control (MAC) Parameters, Physical Layer, Medium Attachment Units, and Repeater for 100 Mb/s Operation, Type 100BASE-T

3 PHYSICAL

3.1 Dimensions

- .1 The camera case and dome must:
 - .1 measure a base diameter less than 250mm;
 - .2 measure from base to top of dome of less than 400mm excluding any mount;
 - .3 weigh less than 5kg excluding mounting hardware;

3.2 Environment

- .1 The camera case and dome must:
 - .1 meet or exceed IEC EN60529 IP66 dust and water resistance when mounted;
 - .2 if deployed within 5 metres of inmates, meet or exceed IEC EN62262 IK10 impact resistance;
 - .3 if surface mount, have threaded openings for conduits;
 - .4 if pendant mount, have all cables enter through the attachment pipe;
 - .5 if pendant mount, have no other openings in the enclosure excluding the dome assembly;
 - .6 have a threaded plug to seal all unused openings;
 - .7 have set-screws to secure all conduit and plugs from inside the dome;
 - .8 have tamper resistant heads on all externally accessible screws;
 - .9 have a permanently affixed label on the interior of the unit which identifies the manufacturer, the model or assembly number, the serial number and the power requirement;
 - .10 have a permanently affixed label on the exterior of the unit which identifies the manufacturer, the model or assembly number, the serial number and the power requirement;
- .2 The camera must:
 - .1 be capable of continuous operation;
 - .2 start and operate from -40°C to 50°C;
 - .3 start and operate from 20% to 90% non-condensing humidity;

3.3 Interference

- .1 The camera must be certified compliant to IEC EN 55024, Immunity characteristics.

3.4 Reliability

- .1 The camera must have an MTBF of at least 25,000 hours.

3.5 Safety

- .1 The camera must meet IEC 60950-1 or the CSA equivalent.

4 OPERATIONAL

4.1 Camera

- .1 The camera must retain its configuration over a power cycle.
- .2 The image sensor must:
 - .1 include automatic or remote back focus;
 - .2 have a minimum of 480,000 pixels (horizontal x vertical);
 - .3 have day (colour) and night (black and white) modes;
 - .4 automatic removable infrared cut filter for day/night transition;
 - .5 1.0 lux or less minimum illumination for day mode;
 - .6 0.1 lux or less minimum illumination for night mode;
 - .7 include Automatic Gain Control (AGC);
 - .8 include extended dynamic range processing;

4.2 Lens

- .1 The camera lens must:
 - .1 have a horizontal field of view optical zoom range including 3.5° to 50°;
 - .2 be integral to the camera assembly;

4.3 PTZ

- .1 The PTZ must:
 - .1 have a pan range of 360° continuous (endless);
 - .2 have a minimum tilt range of 180°;
 - .3 include automatic image inversion at 90° tilt;
 - .4 have a minimum pan and tilt speed of 0.1°/sec or slower;
 - .5 have a maximum pan and tilt speed of 100°/sec or faster;

4.4 Video

- .1 The video encoding must:
 - .1 support H.264 configurable I-frame frequency of at least 3 per second;
 - .2 support H.264 constant bit rate transmission mode;
 - .3 support H.264 frame rate transmission mode;
 - .4 support at least 3 levels of H.264 image quality;
 - .5 support at least 3 levels of MJPEG image quality;
- .2 The video output must:
 - .1 include an on-screen, programmable character generation overlay capability with a minimum of 8 visible characters;
 - .2 support at least two simultaneous H.264 video streams at 30 frames per second with at least 480,000 pixel resolution;
 - .3 support at least two simultaneous video streams, one H.264 and one MJPEG at 15 frames per second with at least 480,000 pixel resolution;

5 INTERFACE

5.1 Ports

- .1 The camera must:
 - .1 interface over IPV4 TCP/IP;
 - .2 be able to operate on 100Base-TX (IEEE 802.3u);
 - .3 connect using an RJ-45 connector;
 - .4 be ONVIF compliant;

5.2 Power

- .1 The camera must be a Type 1 or Type 2 powered device operating from Power over Ethernet (PoE) compliant with IEEE 802.3at Class 0, 1, 2, 3, or 4, or operating from an external 24VAC power source.

5.3 Video Management System Compatibility

- .1 The camera model must be identified as “Certified” or “Supported by Design” in the Genetec Omnicast Supported Hardware camera list.



**CORRECTIONAL SERVICES CANADA
TECHNICAL SERVICES BRANCH
ELECTRONIC SECURITY SYSTEMS**



ES/STD-0232
Revision 2
February 2014

**ELECTRONIC ENGINEERING STANDARD
FIXED NETWORK COLOUR DOME CAMERA
FOR USE IN FEDERAL CORRECTIONAL INSTITUTIONS**

AUTHORITY

Acquisition of a camera for the identified purposes that is not in compliance with this standard must be approved by the Design Authority.

Recommended corrections, additions or deletions should be addressed to the Design Authority at the following address:

Director, Electronic Security Systems
Correctional Service of Canada
340 Laurier Avenue West,
Ottawa, Ontario
K1A 0P9

Approved by:

Director,
Electronic Security Systems

TABLE OF REVISIONS

Revision	Paragraph	Comment
0	N/A	Original
1	All	New structure and change to merge indoor and outdoor.
2	Definitions	Removed
	2.1	Added reference IEC EN 61000-4-3, Radiated RF immunity
	3.2.2.3	Changed humidity to non-condensing 20%-90%
	3.3.1	Interference now uses IEC EN 61000-4-3, Radiated RF immunity

TABLE OF CONTENTS

TABLE OF REVISIONS	2
TABLE OF CONTENTS	3
TABLE OF ABBREVIATIONS	4
1 INTRODUCTION	5
1.1 Overview	5
1.2 Purpose	5
2 REFERENCES	6
2.1 Specifications, Standards, and Statements of Work	6
3 PHYSICAL	7
3.1 Dimensions	7
3.2 Environment	7
3.3 Interference	7
3.4 Reliability	7
3.5 Safety	7
4 OPERATIONAL	8
4.1 Camera	8
4.2 Lens	8
4.3 Video	8
5 INTERFACE	9
5.1 Ports	9
5.2 Power	9
5.3 Video Management System Compatibility	9

TABLE OF ABBREVIATIONS

Abbreviation	Expansion
AGC	Automatic Gain Control
CSC	Correctional Service Canada
IEC	International Electrotechnical Commission
IEEE	Institute of Electrical and Electronics Engineers
MJPEG	Motion Joint Photographic Experts Group
MTBF	Mean Time Between Failures
ONVIF	Open Network Video Interface Forum
PoE	Power over Ethernet
TCP/IP	Transmission Control Protocol/Internet Protocol

1 INTRODUCTION

1.1 Overview

- .1 This standard defines the requirements of Correctional Service Canada (CSC) for a fixed focus, network capable, dome camera for use at federal correctional institutions.

1.2 Purpose

- .1 The cameras are deployed for both observation and evidentiary use.
- .2 These cameras are for deployment for all outdoor fixed camera locations **except**:
 - .1 facility perimeter;
- .3 These cameras are for deployment for all indoor fixed camera locations **except**:
 - .1 observation cells;
 - .2 principal entrance panoramic;

2 REFERENCES

2.1 Specifications, Standards, and Statements of Work

- .1 Access to non-government specifications is the responsibility of the contractor.
- IEC EN60529 – International Electrotechnical Commission Degrees of protection provided by enclosures (IP Code)
- IEC EN60950-1 – International Electrotechnical Commission Information technology equipment – Safety
- IEC EN 61000-4-3 – International Electrotechnical Commission Radiated RF immunity
- IEC EN62262 – International Electrotechnical Commission Degrees of protection provided by enclosures for electrical equipment against external mechanical impacts
- IEEE 802.3at – IEEE Standard for Information technology – Telecommunications and information exchange between systems – Local and metropolitan area networks – Specific requirements Part 3: Carrier Sense Multiple Access with Collision Detection (CSMA/CD) Access Method and Physical Layer Specifications Amendment 3: Data Terminal Equipment (DTE) Power via the Media Dependent Interface (MDI) Enhancements
- IEEE 802.3u – IEEE Standards for Local and Metropolitan Area Networks: Supplement to Carrier Sense Multiple Access with Collision Detection (CSMA/CD) Access Method and Physical Layer Specifications Media Access Control (MAC) Parameters, Physical Layer, Medium Attachment Units, and Repeater for 100 Mb/s Operation, Type 100BASE-T

3 PHYSICAL

3.1 Dimensions

- .1 The camera case and dome must:
 - .1 measure a base diameter less than 200mm;
 - .2 measure from base to top of dome of less than 175mm excluding any mount;
 - .3 weigh less than 2.5kg;

3.2 Environment

- .1 The camera case and dome must:
 - .1 meet or exceed IEC EN60529 IP66 dust and water resistance when mounted;
 - .2 meet or exceed IEC EN62262 IK10 impact resistance;
 - .3 have threaded openings for conduits;
 - .4 have a threaded plug to seal all unused openings;
 - .5 have set-screws to secure all conduit and plugs from inside the dome;
 - .6 have tamper resistant heads on all externally accessible screws;
 - .7 have a permanently affixed label on the interior of the unit which identifies the manufacturer, the model or assembly number, the serial number and the power requirement;
 - .8 have a permanently affixed label on the exterior of the unit which identifies the manufacturer, the model or assembly number, the serial number and the power requirement;
- .2 The camera must:
 - .1 be capable of continuous operation;
 - .2 start and operate from -40°C to 50°C;
 - .3 start and operate from 20% to 90% non-condensing humidity;

3.3 Interference

- .1 The camera must be certified compliant to IEC EN 61000-4-3, Radiated RF immunity

3.4 Reliability

- .1 The camera must have an MTBF of at least 25,000 hours.

3.5 Safety

- .1 The camera must meet IEC 60950-1 or the CSA equivalent.

4 OPERATIONAL

4.1 Camera

- .1 The camera must retain its configuration over a power cycle.
- .2 The image sensor must:
 - .1 include automatic or remote back focus;
 - .2 have a minimum of 480,000 pixels (horizontal x vertical);
 - .3 have day (colour) and night (black and white) modes;
 - .4 automatic removable infrared cut filter for day/night transition;
 - .5 have 0.5 lux or less minimum illumination for day mode;
 - .6 have 0.1 lux or less minimum illumination for night mode;
 - .7 include Automatic Gain Control (AGC);
 - .8 include extended dynamic range processing;

4.2 Lens

- .1 The camera lens must:
 - .1 have a 35° to 80° or greater horizontal angular view varifocal lens
 - .2 be approved by the manufacturer of the camera for that camera;

4.3 Video

- .1 The video encoding must:
 - .1 support H.264 configurable I-frame frequency of at least 3 per second;
 - .2 support H.264 constant bit rate transmission mode;
 - .3 support H.264 frame rate transmission mode;
 - .4 support at least 3 levels of H.264 image quality;
 - .5 support at least 3 levels of MJPEG image quality;
- .2 The video output must:
 - .1 include an on-screen, programmable character generation overlay capability with a minimum of 8 visible characters;
 - .2 support at least two simultaneous H.264 video streams at 30 frames per second with at least 480,000 pixel resolution;
 - .3 support at least two simultaneous video streams, one H.264 and one MJPEG at 15 frames per second with at least 480,000 pixel resolution;

5 INTERFACE

5.1 Ports

- .1 The camera must:
 - .1 interface over IPV4 TCP/IP;
 - .2 be able to operate on 100Base-TX (IEEE 802.3u);
 - .3 connect using an RJ-45 connector;
 - .4 be ONVIF compliant;

5.2 Power

- .1 The camera must be a Type 1 powered device operating solely from Power over Ethernet (PoE) compliant with IEEE 802.3at Class 0, 1, 2, or 3.

5.3 Video Management System Compatibility

- .1 The camera model must be identified as “Certified” or “Supported by Design” in the Genetec Omnicast Supported Hardware camera list.



**CORRECTIONAL SERVICES CANADA
TECHNICAL SERVICES BRANCH
ELECTRONIC SECURITY SYSTEMS**



ES/STD-0233
Revision 2
February 2014

**ELECTRONIC ENGINEERING STANDARD
INDOOR NO-GRIP CORNER MOUNT NETWORK COLOUR CAMERA
FOR USE IN FEDERAL CORRECTIONAL INSTITUTIONS**

AUTHORITY

This Standard is approved by the Correctional Service Canada for the procurement and installation of this item in Canadian federal correctional institutions.

Acquisition of a camera for the identified purposes that is not in compliance with this standard must be approved by the Design Authority.

Recommended corrections, additions or deletions should be addressed to the Design Authority at the following address:

Director, Electronic Security Systems
Correctional Service of Canada
340 Laurier Avenue West,
Ottawa, Ontario
K1A 0P9

Approved by:

Director,
Electronic Security Systems

TABLE OF REVISIONS

Revision	Paragraph	Comment
0	N/A	Original
1	All	New document structure and addition of TCP/IP and PoE interfaces.
2	Definitions	Removed
	2.1	Added reference IEC EN 61000-4-3, Radiated RF immunity
	3.2.2.3	Changed humidity to non-condensing 20%-90%
	3.3.1	Interference now uses IEC EN 61000-4-3, Radiated RF immunity

TABLE OF CONTENTS

TABLE OF REVISIONS	2
TABLE OF CONTENTS	3
TABLE OF ABBREVIATIONS	4
1 INTRODUCTION	5
1.1 Overview	5
1.2 Purpose	5
2 REFERENCES	6
2.1 Specifications, Standards, and Statements of Work	6
3 PHYSICAL	7
3.1 Dimensions	7
3.2 Environment	7
3.3 Interference	7
3.4 Reliability	7
3.5 Safety	7
4 OPERATIONAL	8
4.1 Camera	8
4.2 Lens	8
4.3 Camera Case	8
4.4 Video	8
5 INTERFACE	9
5.1 Ports	9
5.2 Power	9
5.3 Video Management System Compatibility	9

TABLE OF ABBREVIATIONS

Abbreviation	Expansion
AGC	Automatic Gain Control
CSC	Correctional Service Canada
IEC	International Electrotechnical Commission
IEEE	Institute of Electrical and Electronics Engineers
MJPEG	Motion Joint Photographic Experts Group
MTBF	Mean Time Between Failures
ONVIF	Open Network Video Interface Forum
PoE	Power over Ethernet
TCP/IP	Transmission Control Protocol/Internet Protocol

1 INTRODUCTION

1.1 Overview

- .1 This standard defines the requirements of Correctional Service Canada (CSC) for an indoor, fixed focus, network capable, corner mounted, no-grip camera for use at federal correctional institutions.

1.2 Purpose

- .1 The cameras are deployed for both observation and evidentiary use.
- .2 These cameras are for deployment only in:
 - .1 observation cells;

2 REFERENCES

2.1 Specifications, Standards, and Statements of Work

- .1 Access to non-government specifications is the responsibility of the contractor.
- IEC EN60529*International Electrotechnical Commission Degrees of protection provided by enclosures (IP Code)
- IEC EN60950-1*International Electrotechnical Commission Information technology equipment – Safety
- IEC EN 61000-4-3 – International Electrotechnical Commission Radiated RF immunity
- IEC EN62262*International Electrotechnical Commission Degrees of protection provided by enclosures for electrical equipment against external mechanical impacts
- IEEE 802.3at*IEEE Standard for Information technology – Telecommunications and information exchange between systems – Local and metropolitan area networks – Specific requirements Part 3: Carrier Sense Multiple Access with Collision Detection (CSMA/CD) Access Method and Physical Layer Specifications Amendment 3: Data Terminal Equipment (DTE) Power via the Media Dependent Interface (MDI) Enhancements
- IEEE 802.3u*IEEE Standards for Local and Metropolitan Area Networks: Supplement to Carrier Sense Multiple Access with Collision Detection (CSMA/CD) Access Method and Physical Layer Specifications Media Access Control (MAC) Parameters, Physical Layer, Medium Attachment Units, and Repeater for 100 Mb/s Operation, Type 100BASE-T

3 PHYSICAL

3.1 Dimensions

- .1 The camera case must:
 - .1 measure less than 300mm in all dimensions;
 - .2 weigh less than 2.5kg;

3.2 Environment

- .1 The camera case must:
 - .1 meet or exceed IEC EN60529 IP65 dust and water resistance when mounted;
 - .2 meet or exceed IEC EN62262 IK10 impact resistance;
 - .3 have tamper resistant heads on all externally accessible screws;
 - .4 be grip-less and anchor-free;
 - .5 have a permanently affixed label on the interior of the unit which identifies the manufacturer, the model or assembly number, the serial number and the power requirement;
 - .6 have a permanently affixed label on the exterior of the unit which identifies the manufacturer, the model or assembly number, the serial number and the power requirement;
- .2 The camera must:
 - .1 be capable of continuous operation;
 - .2 start and operate from 0°C to 50°C;
 - .3 start and operate from 20% to 90% non-condensing humidity;

3.3 Interference

- .1 The camera must be certified compliant to IEC EN 61000-4-3, Radiated RF immunity

3.4 Reliability

- .1 The camera must have an MTBF of at least 25,000 hours.

3.5 Safety

- .1 The camera must meet IEC 60950-1 or the CSA equivalent.

4 OPERATIONAL

4.1 Camera

- .1 The camera must retain its configuration over a power cycle.
- .2 The image sensor must:
 - .1 include automatic or remote back focus;
 - .2 have a minimum of 480,000 pixels (horizontal x vertical);
 - .3 have day (colour) and night (black and white) modes;
 - .4 automatic removable infrared cut filter for day/night transition;
 - .5 have 0.5 lux or less minimum illumination for day mode;
 - .6 have 0 lux minimum illumination for night mode;
 - .7 if required for night mode, use invisible illumination (typically infra-red LEDs);
 - .8 include Automatic Gain Control (AGC);

4.2 Lens

- .1 The camera lens must:
 - .1 provide a view of the entire floor and all four walls of a room at least 3.5m x 3.5m including the walls to which it is attached from the mounting height to the floor;
 - .2 be approved by the manufacturer of the camera for that camera;

4.3 Camera Case

- .1 The camera case must:
 - .1 have a programmatically controlled visible LED indicator to show when the video feed is being observed;

4.4 Video

- .1 The video encoding must:
 - .1 support H.264 configurable I-frame frequency of at least 3 per second;
 - .2 support H.264 constant bit rate transmission mode;
 - .3 support H.264 frame rate transmission mode;
 - .4 support at least 3 levels of H.264 image quality;
 - .5 support at least 3 levels of MJPEG image quality;
- .2 The video output must:
 - .1 include an on-screen, programmable character generation overlay capability with a minimum of 8 visible characters;
 - .2 support at least two simultaneous H.264 video streams at 30 frames per second with at least 480,000 pixel resolution;
 - .3 support at least two simultaneous video streams, one H.264 and one MJPEG at 15 frames per second with at least 480,000 pixel resolution;

5 INTERFACE

5.1 Ports

- .1 The camera must:
 - .1 interface over IPV4 TCP/IP;
 - .2 be able to operate on 100Base-TX (IEEE 802.3u);
 - .3 connect using an RJ-45 connector;
 - .4 be ONVIF compliant;

5.2 Power

- .1 The camera must be a Type 1 powered device operating solely from Power over Ethernet (PoE) compliant with IEEE 802.3at Class 0, 1, 2, or 3.

5.3 Video Management System Compatibility

- .1 The camera model must be identified as “Certified” or “Supported by Design” in the Genetec Omnicast Supported Hardware camera list.