



**RETURN BIDS TO:
RETOURNER LES SOUMISSIONS À:**

**Bid Receiving - PWGSC / Réception des
soumissions - TPSGC**
11 Laurier St. / 11, rue Laurier
Place du Portage, Phase III
Core 0B2 / Noyau 0B2
Gatineau, Québec K1A 0S5
Bid Fax: (819) 997-9776

**REQUEST FOR PROPOSAL
DEMANDE DE PROPOSITION**

**Proposal To: Public Works and Government
Services Canada**

We hereby offer to sell to Her Majesty the Queen in right of Canada, in accordance with the terms and conditions set out herein, referred to herein or attached hereto, the goods, services, and construction listed herein and on any attached sheets at the price(s) set out therefor.

**Proposition aux: Travaux Publics et Services
Gouvernementaux Canada**

Nous offrons par la présente de vendre à Sa Majesté la Reine du chef du Canada, aux conditions énoncées ou incluses par référence dans la présente et aux annexes ci-jointes, les biens, services et construction énumérés ici sur toute feuille ci-annexée, au(x) prix indiqué(s).

Comments - Commentaires

Vendor/Firm Name and Address
Raison sociale et adresse du
fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution
Electrical & Electronics Products Division
11 Laurier St./11, rue Laurier
7B3, Place du Portage, Phase III
Gatineau, Québec K1A 0S5

| | |
|---|--|
| Title - Sujet CABLE ASSEMBLY, FIBER OPTIC | |
| Solicitation No. - N° de l'invitation W8486-173302/A | Date 2016-06-23 |
| Client Reference No. - N° de référence du client W8486-173302 | |
| GETS Reference No. - N° de référence de SEAG PW-\$\$HN-313-71137 | |
| File No. - N° de dossier hn313.W8486-173302 | CCC No./N° CCC - FMS No./N° VME |
| Solicitation Closes - L'invitation prend fin at - à 02:00 PM on - le 2016-07-12 | Time Zone Fuseau horaire Eastern Daylight Saving Time EDT |
| F.O.B. - F.A.B. Plant-Usine: <input type="checkbox"/> Destination: <input checked="" type="checkbox"/> Other-Autre: <input type="checkbox"/> | |
| Address Enquiries to: - Adresser toutes questions à: Kelly, Ruth | Buyer Id - Id de l'acheteur hn313 |
| Telephone No. - N° de téléphone (819) 420-0343 () | FAX No. - N° de FAX () - |
| Destination - of Goods, Services, and Construction: Destination - des biens, services et construction: Specified Herein Précisé dans les présentes | |

Instructions: See Herein

Instructions: Voir aux présentes

| | |
|---|--|
| Delivery Required - Livraison exigée See Herein | Delivery Offered - Livraison proposée |
| Vendor/Firm Name and Address Raison sociale et adresse du fournisseur/de l'entrepreneur Telephone No. - N° de téléphone Facsimile No. - N° de télécopieur | |
| Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) Nom et titre de la personne autorisée à signer au nom du fournisseur/ de l'entrepreneur (taper ou écrire en caractères d'imprimerie) Signature Date | |



| Destination Code - Code destinataire | Destination Address - Adresse de la destination | Invoice Code - Code bur.-comptable | Invoice Address - Adresse de facturation |
|---|---|---------------------------------------|--|
| W2481 | DEPARTMENT OF NATIONAL DEFENCE 7 CF SUPPLY DEPOT RECEIPTS & ISSUES SECTION EDMONTON Alberta T5J4J5 Canada | W2481 | DEPARTMENT OF NATIONAL DEFENCE 7 CF SUPPLY DEPOT STN FORCES P.O.BOX 10500 EDMONTON Alberta T5J4J5 Canada |
| WB941 | DEPARTMENT OF NATIONAL DEFENCE 25 CFSD MONTREAL 6363 RUE NOTRE DAME ST E. MONTREAL Quebec H1N2E9 Canada | W1941 | DEPARTMENT OF NATIONAL DEFENCE C.P. 4000 SUCC K 25 DAFB / MAGASIN MONTREAL Quebec H1N3R9 Canada |



| Item Article | Description | Dest. Code Dest. | Inv. Code Fact. | Qty Qté | U. of I. U. de D. | Destination | Unit Price/Prix unitaire FOB/FAM | Plant/Usine | Delivery Req. Livraison Req. | Del. Offered Liv. offerte | |
|-----------------|--|------------------------|-----------------------|------------|----------------------|-------------|-------------------------------------|--------------|---------------------------------|------------------------------|--|
| 1 | NSN - NNO: 6020-01-480-2955 CABLE ASSEMBLY, FIBER OPTIC CABLE ASSEMBLY, FIBER OPTIC, 4-CHANNEL PLUG TO PLUG P/N FS4H 1000 MILITARY TACTICAL FIBER OPTIC; BREAKOUT CABLE, 500 METERS LONG, ON RF0-1000 SHANE REEL, MINIMUM CABLE SPECIFICATION FIBER TYPE 62.5UM CORE DIA.; 125UM CLADDING DIA.; 500UM COATING DIA.; 900UM BUFFER DIA.; 0.275 NUMERICAL APERTURE; 100KPSI PROOF TEST LEVEL; 850NM WAVELENGTH 3.0 DB/KM ATTENUATION AND 160 MHZ-KM BANDWIDTH; 2200N MAX. TENSILE LOAD, MINIMUM OPERATING TEMPARATURE -45 CELCIUS; STORAGE TEMPERATURE MINIMUM -60 CELCIUS; CABLE OUTER JACKET MADE OF POLYURETHANE COLOR FLAT BLACK; ARAMID YARN STRENGTH MEMBER, MIN. 7.0MM CABLE DIAMETER 14 OCM BEND RADIUS; MARKING ON CABLE EVERY TWO (2) FEET ALONG LENGTH, ; 500M CABLE ASSEMBLY WITH CONNECTORS TFOCA II AND TFOCA II; PART NUMBER SUFFIX (XX) STANDS F OR: X= TFOCA II CONNECTOR AND X= TFOCA II CONNECTOR ===== | WB941 | W1941 | 100 | DR | \$ | | XXXXXXXXXXXX | | See Herein | |
| | NSCM P/N AND MANUFACTURER 3AG28 TTF64B0500RFO Dafocom Solutions Inc., Ottawa, Ontario ===== | | | | | | | | | | |
| | 0NSV6 RK000223XX62.5/125MM Optical Cable Corp., | | | | | | | | | | |



| Item Article | Description | Dest. Code Dest. | Inv. Code Fact. | Qty Qté | U. of I. U. de D. | Unit Price/Prix unitaire FOB/FAM Destination | Plant/Usine | Delivery Req. Livraison Req. | Del. Offered Liv. offerte |
|-----------------|--|------------------------|-----------------------|------------|----------------------|--|-------------|---------------------------------|------------------------------|
| 1 | Roanoke , VA ===== P/N Offered: _____ NSCM Offered: _____ | | | | | | | | |



| Item Article | Description | Dest. Code Dest. | Inv. Code Fact. | Qty Qté | U. of I. U. de D. | Destination | Unit Price/Prix unitaire FOB/FAM | Plant/Usine | Delivery Req. Livraison Req. | Del. Offered Liv. offerte |
|-----------------|---|------------------------|-----------------------|------------|----------------------|-------------|-------------------------------------|-------------|---------------------------------|------------------------------|
| 2 | NSN - NNO: 6020-01-480-2955 CABLE ASSEMBLY, FIBER OPTIC CABLE ASSEMBLY, FIBER OPTIC, 4-CHANNEL PLUG TO PLUG P/N FS4H 1000 MILITARY TACTICAL FIBER OPTIC; BREAKOUT CABLE, 500 METERS LONG, ON RF0-1000 SHANE REEL, MINIMUM CABLE SPECIFICATION FIBER TYPE 62.5UM CORE DIA.; 125UM CLADDING DIA.; 500UM COATING DIA.; 900UM BUFFER DIA.; 0.275 NUMERICAL APERTURE; 100KPSI PROOF TEST LEVEL; 850NM WAVELENGTH 3.0 DB/KM ATTENUATION AND 160 MHZ-KM BANDWIDTH; 2200N MAX. TENSILE LOAD, MINIMUM OPERATING TEMPARATURE -45 CELCIUS; STORAGE TEMPERATURE MINIMUM -60 CELCIUS; CABLE OUTER JACKET MADE OF POLYURETHANE COLOR FLAT BLACK; ARAMID YARN STRENGH MEMBER, MIN. 7.0MM CABLE DIAMETER 14 OCM BEND RADIUS; MARKING ON CABLE EVERY TWO (2) FEET ALONG LENGTH, ; 500M CABLE ASSEMBLY WITH CONNECTORS TFOCA II AND TFOCA II; PART NUMBER SUFFIX (XX) STANDS F OR: X= TFOCA II CONNECTOR AND X= TFOCA II CONNECTOR ===== | W2481 | W2481 | 50 | DR | \$ | XXXXXXXXXXXX | | See Herein | |
| | NSCM P/N AND MANUFACTURER 3AG28 TTF64B0500RFO Dafocom Solutions Inc., Ottawa, Ontario ===== | | | | | | | | | |
| | 0NSV6 RK000223XX62.5/125MM Optical Cable Corp., | | | | | | | | | |



| Item Article | Description | Dest. Code Dest. | Inv. Code Fact. | Qty Qté | U. of I. U. de D. | Unit Price/Prix unitaire FOB/FAM Destination Plant/Usine | Delivery Req. Livraison Req. | Del. Offered Liv. offerte |
|-----------------|--|------------------------|-----------------------|------------|----------------------|---|---------------------------------|------------------------------|
| 2 | Roanoke , VA ===== P/N Offered: _____ NSCM Offered: _____ | | | | | | | |



| Item Article | Description | Dest. Code Dest. | Inv. Code Fact. | Qty Qté | U. of I. U. de D. | Destination | Unit Price/Prix unitaire FOB/FAM | Plant/Usine | Delivery Req. Livraison Req. | Del. Offered Liv. offerte | |
|--------------|--|------------------|-----------------|---------|-------------------|-------------|----------------------------------|-------------|------------------------------|---------------------------|--|
| 3 | NSN - NNO: 6020-01-480-2634 CABLE ASSEMBLY, FIBER OPTIC CABLE ASSEMBLY, FIBER OPTIC 600 METER SINGLE MODE, 4-CHANNEL PLUG TO PLUG P/N FS4H 1000MILITARY TACTICAL FIBER RADIATION HARDENED OCC BREAKOUT CABLE, 600 METERS, PIN RK000228XX, ON RF0-1000 SHANE REELS MINIMUM CABLE SPECIFICATION FIBER TYPE 8.3UM CORE DIAMETER, RADIATION HARDENED. 125UM CLADDING DIAMETER, 500UM COATING DIAMETER, 900UM BUFFER DIAMETER, HARD ELASTOMERIC TIGHT BUFFERED; 2.00 MM ELASTOMERIC SUBCABLE JACKET FILLERS ARAMID YARN STRENGTH MEMBER; CORE-LOCKED FLAME RETARDANT POLYURETHANE TACTICAL JACKET COLOR FLAT BLACK, WAVELENGTH 1310 NM 1550 NM MAXIMUM ATTENUATION 0.5 dB/km 0.5 dB/km, NOMINAL ZERO DISPERSION SLOPE 0.092PS/(nm2-km), 100KPSI PROOF TEST CABLE WEIGHT 42 KG/KM (32 lbs/1000') CABLE DIAMETER 7.0 MM INSTALLATION MAX. TENSILE LOAD 2,200 N (490 lbs) MIN. BEND RADIUS 14.0 cm OPERATING MAX. TENSILE LOAD 550 N (120 lbs) MIN. BEND RADIUS 7.0 CM IMPACT RESISTANCE 200 IMPACTS (EIA-455-25, Military Req.) CRUSH RESISTANCE 440 N/CM (EIA-455-41, Military Req.) OPERATING TEMPERATURE -55°C to +85°C, STORAGE TEMPERATURE -70°C to +85°C CABLE OUTER JACKET MADE OF | WB941 | W1941 | 75 | RL | \$ | XXXXXXXXXXXX | | | See Herein | |



| Item Article | Description | Dest. Code Dest. | Inv. Code Fact. | Qty Qté | U. of I. U. de D. | Unit Price/Prix unitaire FOB/FAM Destination Plant/Usine | Delivery Req. Livraison Req. | Del. Offered Liv. offerte |
|-----------------|--|------------------------|-----------------------|------------|----------------------|---|---------------------------------|------------------------------|
| 3 | POLYURETHANE COLOR FLAT BLACK; ARAMID YARN STRENGTH MEMBER, MARKING ON CABLE EVERY TWO (2) FEET ALONG LENGTH; 600 METERS CABLE ASSEMBLY WITH CONNECTORS TFOCA II AND TFOCA II; PART NUMBER SUFFIX (XX) STANDS FOR: X= TFOCA II CONNECTOR AND X= TFOCA II CONNECTOR. ===== NSCM P/N AND MANUFACTURER 3AG28 TTF94B0600RFO Dafocom Solutions Inc., Ottawa, Ontario ===== 0NSV6 RK000228XX8.3/125MM Optical Cable Corp., Roanoke, VA ===== P/N Offered: _____ NSCM Offered: _____ | | | | | | | |



| Item Article | Description | Dest. Code Dest. | Inv. Code Fact. | Qty Qté | U. of I. U. de D. | Destination | Unit Price/Prix unitaire FOB/FAM | Plant/Usine | Delivery Req. Livraison Req. | Del. Offered Liv. offerte | |
|--------------|--|------------------|-----------------|---------|-------------------|-------------|----------------------------------|-------------|------------------------------|---------------------------|--|
| 4 | NSN - NNO: 6020-01-480-2634 CABLE ASSEMBLY, FIBER OPTIC CABLE ASSEMBLY, FIBER OPTIC 600 METER SINGLE MODE, 4-CHANNEL PLUG TO PLUG P/N FS4H 1000MILITARY TACTICAL FIBER RADIATION HARDENED OCC BREAKOUT CABLE, 600 METERS, PIN RK000228XX, ON RF0-1000 SHANE REELS MINIMUM CABLE SPECIFICATION FIBER TYPE 8.3UM CORE DIAMETER, RADIATION HARDENED. 125UM CLADDING DIAMETER, 500UM COATING DIAMETER, 900UM BUFFER DIAMETER, HARD ELASTOMERIC TIGHT BUFFERED; 2.00 MM ELASTOMERIC SUBCABLE JACKET FILLERS ARAMID YARN STRENGTH MEMBER; CORE-LOCKED FLAME RETARDANT POLYURETHANE TACTICAL JACKET COLOR FLAT BLACK, WAVELENGTH 1310 NM 1550 NM MAXIMUM ATTENUATION 0.5 dB/km 0.5 dB/km, NOMINAL ZERO DISPERSION SLOPE 0.092PS/(nm2-km), 100KPSI PROOF TEST CABLE WEIGHT 42 KG/KM (32 lbs/1000') CABLE DIAMETER 7.0 MM INSTALLATION MAX. TENSILE LOAD 2,200 N (490 lbs) MIN. BEND RADIUS 14.0 cm OPERATING MAX. TENSILE LOAD 550 N (120 lbs) MIN. BEND RADIUS 7.0 CM IMPACT RESISTANCE 200 IMPACTS (EIA-455-25, Military Req.) CRUSH RESISTANCE 440 N/CM (EIA-455-41, Military Req.) OPERATING TEMPERATURE -55°C to +85°C, STORAGE TEMPERATURE -70°C to +85°C CABLE OUTER JACKET MADE OF | W2481 | W2481 | 25 | RL | \$ | XXXXXXXXXXXX | | | See Herein | |



| Item Article | Description | Dest. Code Dest. | Inv. Code Fact. | Qty Qté | U. of I. U. de D. | Unit Price/Prix unitaire FOB/FAM Destination | Plant/Usine | Delivery Req. Livraison Req. | Del. Offered Liv. offerte |
|-----------------|--|------------------------|-----------------------|------------|----------------------|--|-------------|---------------------------------|------------------------------|
| 4 | POLYURETHANE COLOR FLAT BLACK; ARAMID YARN STRENGTH MEMBER, MARKING ON CABLE EVERY TWO (2) FEET ALONG LENGTH; 600 METERS CABLE ASSEMBLY WITH CONNECTORS TFOCA II AND TFOCA II; PART NUMBER SUFFIX (XX) STANDS FOR: X= TFOCA II CONNECTOR AND X= TFOCA II CONNECTOR. ===== NSCM P/N AND MANUFACTURER 3AG28 TTF94B0600RFO Dafocom Solutions Inc., Ottawa, Ontario ===== 0NSV6 RK000228XX8.3/125MM Optical Cable Corp., Roanoke, VA ===== P/N Offered: _____ NSCM Offered: _____ | | | | | | | | |



| Item Article | Description | Dest. Code Dest. | Inv. Code Fact. | Qty Qté | U. of I. U. de D. | Destination | Unit Price/Prix unitaire FOB/FAM | Plant/Usine | Delivery Req. Livraison Req. | Del. Offered Liv. offerte |
|-----------------|---|------------------------|-----------------------|------------|----------------------|-------------|-------------------------------------|-------------|---------------------------------|------------------------------|
| 5 | NSN - NNO: 6020-01-480-2953 CABLE ASSEMBLY, FIBER OPTIC CABLE ASSEMBLY FIBER OPTIC, 3 METER TAIL SINGLE MODE CABLE (TAIL) CABLE ASSEMBLY, 4-CHANNEL JAM NUT RECEPTACLE P/N FS4H8000 AND MILITARY TACTICAL FIBER RADIATION HARDENED OCC BREAKOUT CABLE, P/N RK000228XX, 3 METRES LONG TO ST ASSEMBLIES, MINIMUM CABLE SPECIFICATION FIBER TYPE 8.3UM CORE DIAMETER, RADIATION HARDENED. 125UM CLADDING DIAMETER, 500UM COATING DIAMETER, 900UM BUFFER DIAMETER, HARD ELASTOMERIC TIGHT BUFFERED; 2.00 MM ELASTOMERIC SUBCABLE JACKET FILLERS ARAMID YARN STRENGHT MEMBER; CORE-LOCKED FLAME RETARDANT POLYURETHANE TACTICAL JACKET COLOR FLAT BLACK. WAVELENGTH 1310 NM 1550 NM MAXIMUM ATTENUATION 0.5 dB/km 0.5 dB/km NOMINAL ZERO DISPERSION SLOPE 0.092 PS/(nm2-km), 100KPSI PROOF TEST CABLE WEIGHT 42 KG/KM (32 lbs/1000') CABLE DIAMETER 7.0 MM INSTALLATION MAX. TENSILE LOAD 2,200 N (490 lbs) MIN. BEND RADIUS 14.0 cm OPERATING MAX. TENSILE LOAD 550 N (120 lbs) MIN. BEND RADIUS 7.0 CM IMPACT RESISTANCE 200 IMPACTS (EIA-455-25, Military Req.) CRUSH RESISTANCE 440 N/CM (EIA-455-41, Military Req.) OPERATING TEMPERATURE -55°C to +85°C, | WB941 | W1941 | 150 | EA | \$ | XXXXXXXXXXXX | See Herein | | |



| Item Article | Description | Dest. Code Dest. | Inv. Code Fact. | Qty Qté | U. of I. U. de D. | Unit Price/Prix unitaire FOB/FAM Destination | Plant/Usine | Delivery Req. Livraison Req. | Del. Offered Liv. offerte |
|-----------------|---|------------------------|-----------------------|------------|----------------------|--|-------------|---------------------------------|------------------------------|
| 5 | STORAGE TEMPERATURE -70°C to +85°C CABLE OUTER JACKET MADE OF POLYURETHANE COLOR FLAT BLACK; ARAMIDYARN STRENGTH MEMBER; MARKING ON CABLE EVERY TWO (2) FEET ALONG LENGTH. STRAIN RELIEF MUST BE FROM TREAD OF THE RECEPTICAL CONNECTOR TO THE CABLE JACKET, 3 METERS CABLE ASSEMBLY WITH CONNECTORS TFOCA II AND MILL ST; PART NUMBER STANDS FOR: X= TFOCA II CONNECTOR AND Y= MILL ST CONNECTOR. ===== | | | | | | | | |
| | NSCM P/N AND MANUFACTURER 3AG28 TF2JN2S94B18/12003 Dafocom Soluitions Inc., Ottawa, Ontario ===== | | | | | | | | |
| | 0NSV6 RK00022801XY8.3/125MM Optical Cable Corp., Roanoke, VA ===== | | | | | | | | |
| | P/N Offered: _____ NSCM Offered: _____ | | | | | | | | |



| Item Article | Description | Dest. Code Dest. | Inv. Code Fact. | Qty Qté | U. of I. U. de D. | Destination | Unit Price/Prix unitaire FOB/FAM | Plant/Usine | Delivery Req. Livraison Req. | Del. Offered Liv. offerte | |
|--------------|---|------------------|-----------------|---------|-------------------|-------------|----------------------------------|-------------|------------------------------|---------------------------|--|
| 6 | NSN - NNO: 6020-01-480-2953 CABLE ASSEMBLY, FIBER OPTIC CABLE ASSEMBLY FIBER OPTIC, 3 METER TAIL SINGLE MODE CABLE (TAIL) CABLE ASSEMBLY, 4-CHANNEL JAM NUT RECEPTACLE P/N FS4H8000 AND MILITARY TACTICAL FIBER RADIATION HARDENED OCC BREAKOUT CABLE, P/N RK000228XX, 3 METRES LONG TO ST ASSEMBLIES, MINIMUM CABLE SPECIFICATION FIBER TYPE 8.3UM CORE DIAMETER, RADIATION HARDENED. 125UM CLADDING DIAMETER, 500UM COATING DIAMETER, 900UM BUFFER DIAMETER, HARD ELASTOMERIC TIGHT BUFFERED; 2.00 MM ELASTOMERIC SUBCABLE JACKET FILLERS ARAMID YARN STRENGTH MEMBER; CORE-LOCKED FLAME RETARDANT POLYURETHANE TACTICAL JACKET COLOR FLAT BLACK. WAVELENGTH 1310 NM 1550 NM MAXIMUM ATTENUATION 0.5 dB/km 0.5 dB/km NOMINAL ZERO DISPERSION SLOPE 0.092 PS/(nm2-km), 100KPSI PROOF TEST CABLE WEIGHT 42 KG/KM (32 lbs/1000') CABLE DIAMETER 7.0 MM INSTALLATION MAX. TENSILE LOAD 2,200 N (490 lbs) MIN. BEND RADIUS 14.0 cm OPERATING MAX. TENSILE LOAD 550 N (120 lbs) MIN. BEND RADIUS 7.0 CM IMPACT RESISTANCE 200 IMPACTS (EIA-455-25, Military Req.) CRUSH RESISTANCE 440 N/CM (EIA-455-41, Military Req.) OPERATING TEMPERATURE -55°C to +85°C, | W2481 | W2481 | 50 | EA | \$ | XXXXXXXXXXXX | | | See Herein | |



| Item Article | Description | Dest. Code Dest. | Inv. Code Fact. | Qty Qté | U. of I. U. de D. | Unit Price/Prix unitaire FOB/FAM Destination | Plant/Usine | Delivery Req. Livraison Req. | Del. Offered Liv. offerte |
|-----------------|---|------------------------|-----------------------|------------|----------------------|--|-------------|---------------------------------|------------------------------|
| 6 | STORAGE TEMPERATURE -70°C to +85°C CABLE OUTER JACKET MADE OF POLYURETHANE COLOR FLAT BLACK; ARAMIDYARN STRENGTH MEMBER; MARKING ON CABLE EVERY TWO (2) FEET ALONG LENGTH. STRAIN RELIEF MUST BE FROM TREAD OF THE RECEPTICAL CONNECTOR TO THE CABLE JACKET, 3 METERS CABLE ASSEMBLY WITH CONNECTORS TFOCA II AND MILL ST; PART NUMBER STANDS FOR: X= TFOCA II CONNECTOR AND Y= MILL ST CONNECTOR. ===== | | | | | | | | |
| | NSCM P/N AND MANUFACTURER 3AG28 TF2JN2S94B18/12003 Dafocom Soluitions Inc., Ottawa, Ontario ===== | | | | | | | | |
| | 0NSV6 RK00022801XY8.3/125MM Optical Cable Corp., Roanoke, VA ===== | | | | | | | | |
| | P/N Offered: _____ NSCM Offered: _____ | | | | | | | | |



| Item Article | Description | Dest. Code Dest. | Inv. Code Fact. | Qty Qté | U. of I. U. de D. | Destination | Unit Price/Prix unitaire FOB/FAM | Plant/Usine | Delivery Req. Livraison Req. | Del. Offered Liv. offerte |
|-----------------|---|------------------------|-----------------------|------------|----------------------|-------------|-------------------------------------|-------------|---------------------------------|------------------------------|
| 7 | NSN - NNO: 6020-20-007-9357 CABLE ASSEMBLY, FIBER OPTIC, BRANCHED, CABLE ASSEMBLY, FIBER OPTIC, 12-CHANNEL PLUG TO PLUG P/N FS8H1000-6A1E1 MTFP1100C-SC, DUAL SEAL, MILITARY TACTICAL FIBER OPTIC; BREAKOUT CABLE, 100 METERS LONG ON RFO-1000 SHANE REEL, MINIMUM CABLE SPECIFICATION FIBER TYPE 62.5UM CORE DIA.; 125UM CLADDING DIA.; 500UM COATING DIA.; 900 UM BUFFER DIA.; 0.275 NUMERICAL APERTURE; 100KPSI PROOF TEST LEVEL; 850NM WAVELENGTH 3.0 KB/KM ATTENUATION AND 160 MHZ-KM BANDWIDTH; 2200N MAX. TENSILE LOAD, MINIMUM OPERATING TEMPERATURE -45 CELCIUS; STORAGE TEMPERATURE MINIMUM -60 CELCIUS; CABLE OUTER JACKET MADE OF POLYURETHANE COLOR FLAT BLACK; ARAMID YARN STRENGTH MEMBER, MIN. 11.0MM CABLE DIAMETER 14 OCM BEND RADIUS; MARKING ON CABLE EVERY TWO (2) FEET ALONG LENGTH; 100M CABLE ASSEMBLY WITH CONNECTORS TFOCA II AND TFOCA II; PART NUMBER SUFFIX (XX) STANDS FOR: X = TFOCA II CONNECTOR AND X = TFOCA II CONNECTOR. ===== | WB941 | W1941 | 30 | EA | \$ | XXXXXXXXXXXX | | See Herein | |
| | NSCM P/N AND MANUFACTURER 3AG28 TFPP612MB100 Dafocom Solutions Inc., Ottawa, Ontario ===== | | | | | | | | | |



| Item Article | Description | Dest. Code Dest. | Inv. Code Fact. | Qty Qté | U. of I. U. de D. | Unit Price/Prix unitaire FOB/FAM Destination | Plant/Usine | Delivery Req. Livraison Req. | Del. Offered Liv. offerte |
|-----------------|---|------------------------|-----------------------|------------|----------------------|--|-------------|---------------------------------|------------------------------|
| 7 | P/N Offered: _____ NSCM Offered: _____ | | | | | | | | |



| Item Article | Description | Dest. Code Dest. | Inv. Code Fact. | Qty Qté | U. of I. U. de D. | Destination | Unit Price/Prix unitaire FOB/FAM | Plant/Usine | Delivery Req. Livraison Req. | Del. Offered Liv. offerte |
|-----------------|---|------------------------|-----------------------|------------|----------------------|-------------|-------------------------------------|-------------|---------------------------------|------------------------------|
| 8 | NSN - NNO: 6020-20-007-9357 CABLE ASSEMBLY, FIBER OPTIC, BRANCHED, CABLE ASSEMBLY, FIBER OPTIC, 12-CHANNEL PLUG TO PLUG P/N FS8H1000-6A1E1 MTFP1100C-SC, DUAL SEAL, MILITARY TACTICAL FIBER OPTIC; BREAKOUT CABLE, 100 METERS LONG ON RFO-1000 SHANE REEL, MINIMUM CABLE SPECIFICATION FIBER TYPE 62.5UM CORE DIA.; 125UM CLADDING DIA.; 500UM COATING DIA.; 900 UM BUFFER DIA.; 0.275 NUMERICAL APERTURE; 100KPSI PROOF TEST LEVEL; 850NM WAVELENGTH 3.0 KB/KM ATTENUATION AND 160 MHZ-KM BANDWIDTH; 2200N MAX. TENSILE LOAD, MINIMUM OPERATING TEMPERATURE -45 CELCIUS; STORAGE TEMPERATURE MINIMUM -60 CELCIUS; CABLE OUTER JACKET MADE OF POLYURETHANE COLOR FLAT BLACK; ARAMID YARN STRENGTH MEMBER, MIN. 11.0MM CABLE DIAMETER 14 OCM BEND RADIUS; MARKING ON CABLE EVERY TWO (2) FEET ALONG LENGTH; 100M CABLE ASSEMBLY WITH CONNECTORS TFOCA II AND TFOCA II; PART NUMBER SUFFIX (XX) STANDS FOR: X = TFOCA II CONNECTOR AND X = TFOCA II CONNECTOR. ===== NSCM P/N AND MANUFACTURER 3AG28 TFPP612MB100 Dafocom Solutions Inc., Ottawa, Ontario ===== | W2481 | W2481 | 10 | EA | \$ | XXXXXXXXXXXX | See Herein | | |



| Item Article | Description | Dest. Code Dest. | Inv. Code Fact. | Qty Qté | U. of I. U. de D. | Unit Price/Prix unitaire FOB/FAM Destination Plant/Usine | Delivery Req. Livraison Req. | Del. Offered Liv. offerte |
|-----------------|---|------------------------|-----------------------|------------|----------------------|---|---------------------------------|------------------------------|
| 8 | P/N Offered: _____ NSCM Offered: _____ | | | | | | | |

TABLE OF CONTENTS

| | |
|---|-----------|
| PART 1 - GENERAL INFORMATION | 2 |
| 1.1 SECURITY REQUIREMENTS | 2 |
| 1.2 REQUIREMENT | 2 |
| 1.3 DEBRIEFINGS | 2 |
| 1.4 TRADE AGREEMENTS | 2 |
| PART 2 - BIDDER INSTRUCTIONS | 3 |
| 2.1 STANDARD INSTRUCTIONS, CLAUSES AND CONDITIONS | 3 |
| 2.2 SUBMISSION OF BIDS | 3 |
| 2.3 ENQUIRIES - BID SOLICITATION | 3 |
| 2.4 APPLICABLE LAWS | 4 |
| PART 3 - BID PREPARATION INSTRUCTIONS | 5 |
| 3.1 BID PREPARATION INSTRUCTIONS | 5 |
| PART 4 - EVALUATION PROCEDURES AND BASIS OF SELECTION | 8 |
| 4.1 EVALUATION PROCEDURES | 8 |
| 4.2 BASIS OF SELECTION | 8 |
| PART 5 – CERTIFICATIONS AND ADDITIONAL INFORMATION | 9 |
| 5.1 CERTIFICATIONS REQUIRED WITH THE BID | 9 |
| 5.2 CERTIFICATIONS PRECEDENT TO CONTRACT AWARD AND ADDITIONAL INFORMATION | 9 |
| PART 6 - RESULTING CONTRACT CLAUSES | 11 |
| 6.1 SECURITY REQUIREMENTS | 11 |
| 6.2 REQUIREMENT | 11 |
| 6.3 STANDARD CLAUSES AND CONDITIONS | 11 |
| 6.4 TERM OF CONTRACT | 11 |
| 6.5 AUTHORITIES | 12 |
| 6.6 PAYMENT | 12 |
| 6.7 INVOICING INSTRUCTIONS | 14 |
| 6.8 CERTIFICATIONS | 14 |
| 6.9 APPLICABLE LAWS | 14 |
| 6.10 PRIORITY OF DOCUMENTS | 15 |
| 6.11 DEFENCE CONTRACT | 15 |
| 6.12 SACC MANUAL CLAUSES | 15 |
| 6.13 NATO COMMERCIAL AND GOVERNMENT ENTITY CODE (NCAGE) TRACEABILITY | 15 |
| 6.14 SACC MANUAL CLAUSES (DELIVERY) | 15 |
| 6.14.1 SHIPPING INSTRUCTIONS - DELIVERY AT DESTINATION | 16 |
| 6.14.2 PREPARATION FOR DELIVERY | 16 |
| 6.14.3 SHIPPING – SCHEDULING (DND) | 16 |

PART 1 - GENERAL INFORMATION

1.1 Security Requirements

There is no security requirement associated with the requirement.

1.2 Requirement

The contractor must provide the goods in accordance with the technical requirements stated herein.

1.2.1 Delivery Requirement

Delivery is requested to be completed by October 21, 2016.

1.3 Debriefings

Bidders may request a debriefing on the results of the bid solicitation process. Bidders should make the request to the Contracting Authority within 15 working days from receipt of the results of the bid solicitation process. The debriefing may be in writing, by telephone or in person.

1.4 Trade Agreements

The requirement is subject to the provisions of the Agreement on Internal Trade (AIT).

PART 2 - BIDDER INSTRUCTIONS

2.1 Standard Instructions, Clauses and Conditions

All instructions, clauses and conditions identified in the bid solicitation by number, date and title are set out in the [Standard Acquisition Clauses and Conditions Manual](https://buyandsell.gc.ca/policy-and-guidelines/standard-acquisition-clauses-and-conditions-manual) (<https://buyandsell.gc.ca/policy-and-guidelines/standard-acquisition-clauses-and-conditions-manual>) issued by Public Works and Government Services Canada.

Bidders who submit a bid agree to be bound by the instructions, clauses and conditions of the bid solicitation and accept the clauses and conditions of the resulting contract.

The [2003](#) (2016-04-04) Standard Instructions - Goods or Services - Competitive Requirements, are incorporated by reference into and form part of the bid solicitation.

Subsection 5.4 of [2003](#), Standard Instructions - Goods or Services - Competitive Requirements, is amended as follows:

Delete: 60 days

Insert: 90 days

2.1.1 SACC Manual Clauses

| SACC Reference | Section | Date |
|------------------------|-----------------------|------------|
| A9033T | Financial Capability | 2012-07-16 |
| B1000T | Condition of Material | 2014-06-26 |

2.2 Submission of Bids

Bids must be submitted only to Public Works and Government Services Canada (PWGSC) Bid Receiving Unit by the date, time and place indicated on page 1 of the bid solicitation.

2.3 Enquiries - Bid Solicitation

All enquiries must be submitted in writing to the Contracting Authority no later than five (5) calendar days before the bid closing date. Enquiries received after that time may not be answered.

Bidders should reference as accurately as possible the numbered item of the bid solicitation to which the enquiry relates. Care should be taken by Bidders to explain each question in sufficient detail in order to enable Canada to provide an accurate answer. Technical enquiries that are of a proprietary nature must be clearly marked "proprietary" at each relevant item. Items identified as "proprietary" will be treated as such except where Canada determines that the enquiry is not of a proprietary nature. Canada may edit the question(s) or may request that the Bidder do so, so that the proprietary nature of the question(s) is eliminated, and the enquiry can be answered to all Bidders. Enquiries not submitted in a form that can be distributed to all Bidders may not be answered by Canada.

Solicitation No. - N° de l'invitation
W8486-173302/A
Client Ref. No. - N° de réf. du client
W8486-173302

Amd. No. - N° de la modif.
File No. - N° du dossier
hn313.W8486-173302

Buyer ID - Id de l'acheteur
hn313
CCC No./N° CCC - FMS No./N° VME

2.4 Applicable Laws

Any resulting contract must be interpreted and governed, and the relations between the parties determined, by the laws in force in Ontario.

Bidders may, at their discretion, substitute the applicable laws of a Canadian province or territory of their choice without affecting the validity of their bid, by deleting the name of the Canadian province or territory specified and inserting the name of the Canadian province or territory of their choice. If no change is made, it acknowledges that the applicable laws specified are acceptable to the Bidders.

PART 3 - BID PREPARATION INSTRUCTIONS

3.1 Bid Preparation Instructions

Canada requests that Bidders provide their bid in separately bound sections as follows:

- Section I: Technical Bid (2 hard copies)
- Section II: Financial Bid (1 hard copies)
- Section III: Certifications (1 hard copies)
- Section IV: Additional Information (1 hard copies)

Prices must appear in the financial bid only. No prices must be indicated in any other section of the bid.

Canada requests that Bidders follow the format instructions described below in the preparation of their bid:

- (a) use 8.5 x 11 inch (216 mm x 279 mm) paper;
- (b) use a numbering system that corresponds to the bid solicitation.

In April 2006, Canada issued a policy directing federal departments and agencies to take the necessary steps to incorporate environmental considerations into the procurement process [Policy on Green Procurement](http://www.tpsgc-pwgsc.gc.ca/ecologisation-greening/achats-procurement/politique-policy-eng.html) (<http://www.tpsgc-pwgsc.gc.ca/ecologisation-greening/achats-procurement/politique-policy-eng.html>). To assist Canada in reaching its objectives, Bidders should:

- 1) use 8.5 x 11 inch (216 mm x 279 mm) paper containing fibre certified as originating from a sustainably-managed forest and containing minimum 30% recycled content; and
- 2) use an environmentally-preferable format including black and white printing instead of colour printing, printing double sided/duplex, using staples or clips instead of cerlox, duotangs or binders.

Section I: Technical Bid

In their technical bid, Bidders should explain and demonstrate how they propose to meet the requirements and how they will carry out the Work.

3.1.1 Equivalent Product

- 1. Products that are equivalent in form, fit, function and quality to the item(s) specified in the bid solicitation will be considered where the Bidder:
 - a. designates the brand name, model and/or part number of the substitute product;
 - b. states that the substitute product is fully interchangeable with the item specified;
 - c. **provides complete specifications and descriptive literature for each substitute product;**

-
- d. provides compliance statements that include technical specifics showing the substitute product meets all mandatory performance criteria that are specified in the bid solicitation; and
 - e. clearly identifies those areas in the specifications and descriptive literature that support the substitute product's compliance with any mandatory performance criteria.
 2. Products offered as equivalent in form, fit, function and quality will not be considered if:
 - f. the bid fails to provide all the information requested to allow the Contracting Authority to fully evaluate the equivalency of each substitute product; or
 - g. the substitute product fails to meet or exceed the mandatory performance criteria specified in the bid solicitation for that item.
 3. In conducting its evaluation of the bids, Canada may, but will have no obligation to, request bidders offering a substitute product to demonstrate, at the sole cost of bidders, that the substitute product is equivalent to the item specified in the bid solicitation.

3.1.1.1 Equivalent Products - Samples (DND)

If the Bidder offers a equivalent product, Canada reserves the right to request a sample from the Bidder in order to determine its equivalency in form, fit, function, quality and performance to the item specified in the bid solicitation.

The Bidder must, upon request from the Contracting Authority, provide a sample to the Technical Authority, transportation charges prepaid, and without charge to Canada, within twenty-one (21) calendar days from the date of request. The sample submitted by the Bidder will remain the property of Canada and will not be considered as part of the deliverables in any resulting contract. If the sample does not meet the requirements of the bid solicitation or the Bidder fails to comply with the request of the Contracting Authority, the bid will be declared non-responsive.

Section II: Financial Bid

Bidders must submit their financial bid in accordance with the Basis of Payment. The total amount of Applicable Taxes must be shown separately.

3.1.2.1 Exchange Rate Fluctuation Risk Mitigation

1. The Bidder may request Canada to assume the risks and benefits of exchange rate fluctuations. If the Bidder claims for an exchange rate adjustment, this request must be clearly indicated in the bid at time of bidding. The Bidder must submit form PWGSC-TPSGC 450, Claim for Exchange Rate Adjustments with its bid, indicating the Foreign Currency Component (FCC) in Canadian dollars for each line item for which an exchange rate adjustment is required.
2. The FCC is defined as the portion of the price or rate that will be directly affected by exchange rate fluctuations. The FCC should include all related taxes, duties and other costs paid by the Bidder and which are to be included in the adjustment amount.
3. The total price paid by Canada on each invoice will be adjusted at the time of payment, based on the FCC and the exchange rate fluctuation provision in the contract. The

exchange rate adjustment will only be applied where the exchange rate fluctuation is greater than 2% (increase or decrease).

4. At time of bidding, the Bidder must complete columns (1) to (4) on form PWGSC-TPSGC 450, for each line item where they want to invoke the exchange rate fluctuation provision. Where bids are evaluated in Canadian dollars, the dollar values provided in column (3) should also be in Canadian dollars, so that the adjustment amount is in the same currency as the payment.
5. Alternate rates or calculations proposed by the Bidder will not be accepted for the purposes of this exchange rate fluctuation provision.

Section III: Certifications

Bidders must submit the certifications required under Part 5.

Section IV: Additional Information

3.1.4 Delivery Offered

While delivery is requested as indicated above, the best delivery that could be offered is_____.

PART 4 - EVALUATION PROCEDURES AND BASIS OF SELECTION

4.1 Evaluation Procedures

- a) Bids will be assessed in accordance with the entire requirement of the bid solicitation including the technical and financial evaluation criteria.
- b) An evaluation team composed of representatives of Canada will evaluate the bids.

4.1.1 Technical Evaluation

All bids must be completed in full and provide all of the information requested in the bid solicitation to enable full and complete evaluation.

4.1.1.1 Mandatory Technical Criteria

The following Mandatory requirements must be submitted with the bid for evaluation

- Technical compliance herein;
- Bids must be submitted for all destinations per NSN.

4.1.2 Financial Evaluation

The bid price will be determined by processing the items as follows:

- a. Sum of items with identical NSN's total price (destination 1: unit price x qty. + destination 2: unit price x qty.)

4.1.2.1 Pricing Basis

The bidder must quote firm unit prices in Canadian dollars, DDP Delivered Duty Paid (destination), applicable taxes extra. Freight charges to destination and all applicable Custom duties and Excise taxes must be included.

4.2 Basis of Selection

A bid must comply with the requirements of the bid solicitation and meet all mandatory technical evaluation criteria to be declared responsive. The lowest responsive bid for items with identical NSN's to be delivered to multiple destination will be awarded on an aggregate basis (all destination per NSN)

PART 5 – CERTIFICATIONS AND ADDITIONAL INFORMATION

Bidders must provide the required certifications and additional information to be awarded a contract.

The certifications provided by Bidders to Canada are subject to verification by Canada at all times. Canada will declare a bid non-responsive, or will declare a contractor in default if any certification made by the Bidder is found to be untrue whether made knowingly or unknowingly, during the bid evaluation period or during the contract period.

The Contracting Authority will have the right to ask for additional information to verify the Bidder's certifications. Failure to comply and to cooperate with any request or requirement imposed by the Contracting Authority will render the bid non-responsive or constitute a default under the Contract.

5.1 Certifications Required with the Bid

Bidders must submit the following duly completed certifications as part of their bid.

5.1.1 Declaration of Convicted Offences

In accordance with the *Ineligibility and Suspension Policy* (<http://www.tpsgc-pwgsc.gc.ca/ci-if/politique-policy-eng.html>), the Bidder must provide with its bid the required documentation, as applicable, to be given further consideration in the procurement process.

5.2 Certifications Precedent to Contract Award and Additional Information

The certifications and additional information listed below should be submitted with the bid, but may be submitted afterwards. If any of these required certifications or additional information is not completed and submitted as requested, the Contracting Authority will inform the Bidder of a time frame within which to provide the information. Failure to provide the certifications or the additional information listed below within the time frame provided will render the bid non-responsive.

5.2.1 Integrity Provisions – List of Names

In accordance with the *Ineligibility and Suspension Policy* (<http://www.tpsgc-pwgsc.gc.ca/ci-if/politique-policy-eng.html>), the Bidder must provide the required documentation, as applicable, to be given further consideration in the procurement process.

5.2.2 General Environmental Criteria Certification

The Bidder must select and complete one of the following two certification statements.

- A) The Bidder certifies that the Bidder is registered or meets ISO 14001.

Bidders' Authorized Representative Signature

Date

or

- B) The Bidder certifies that the Bidder meets and will continue to meet throughout the duration of the contract, a minimum of four (4) out of six (6) criteria identified in the table below.

The Bidder must indicate which four (4) criteria, as a minimum, are met.

| Green Practices within the Bidders' organization | Insert a checkmark for each criterion that is met |
|--|--|
| Promotes a paperless environment through directives, procedures and/or programs | |
| All documents are printed double sided and in black and white for day to day business activity unless otherwise specified by your client | |
| Paper used for day to day business activity has a minimum of 30% recycled content and has a sustainable forestry management certification | |
| Utilizes environmentally preferable inks and purchase remanufactured ink cartridges or ink cartridges that can be returned to the manufacturer for reuse and recycling for day to day business activity. | |
| Recycling bins for paper, newsprint, plastic and aluminum containers available and emptied regularly in accordance with local recycling program. | |
| A minimum of 50% of office equipment has an energy efficient certification. | |

Bidders' Authorized Representative Signature

Date

5.2.3 Federal Contractors Program for Employment Equity - Bid Certification

By submitting a bid, the Bidder certifies that the Bidder, and any of the Bidder's members if the Bidder is a Joint Venture, is not named on the Federal Contractors Program (FCP) for employment equity "[FCP Limited Eligibility to Bid](#)" list available at the bottom of the page of the [Employment and Social Development Canada \(ESDC\) - Labour's](#) website (http://www.esdc.gc.ca/en/jobs/workplace/human_rights/employment_equity/federal_contractor_program.page?&_ga=1.229006812.1158694905.1413548969).

Canada will have the right to declare a bid non-responsive if the Bidder, or any member of the Bidder if the Bidder is a Joint Venture, appears on the "[FCP Limited Eligibility to Bid](#)" list at the time of contract award.

Canada will also have the right to terminate the Contract for default if a Contractor, or any member of the Contractor if the Contractor is a Joint Venture, appears on the "[FCP Limited Eligibility to Bid](#)" list during the period of the Contract.

The Bidder must provide the Contracting Authority with a completed annex [Federal Contractors Program for Employment Equity - Certification](#), before contract award. If the Bidder is a Joint Venture, the Bidder must provide the Contracting Authority with a completed annex Federal Contractors Program for Employment Equity - Certification, for each member of the Joint Venture.

PART 6 - RESULTING CONTRACT CLAUSES

The following clauses and conditions apply to and form part of any contract resulting from the bid solicitation.

6.1 Security Requirements

There is no security requirement applicable to this Contract.

6.2 Requirement

The contractor must provide the goods and/or services in accordance with the technical requirements stated herein.

6.2.1 SACC Manual Clauses

| SACC Reference | Section | Date |
|----------------|--------------|------------|
| <u>B7500C</u> | Excess Goods | 2006-06-16 |

6.3 Standard Clauses and Conditions

All clauses and conditions identified in the Contract by number, date and title are set out in the Standard Acquisition Clauses and Conditions Manual (<https://buyandsell.gc.ca/policy-and-guidelines/standard-acquisition-clauses-and-conditions-manual>) issued by Public Works and Government Services Canada.

6.3.1 General Conditions

2010A (2016-04-04), General Conditions - Goods (Medium Complexity), apply to and form part of the Contract.

6.3.1.1 SACC Manual Clauses

| SACC Reference | Section | Date |
|----------------|--|------------|
| <u>C2800C</u> | Priority Rating | 2013-01-28 |
| <u>C2801C</u> | Priority Rating - Canadian Contractors | 2014-11-27 |

6.4 Term of Contract

6.4.1 Delivery Date

All the deliverables must be received on or before _____ (Delivery as offered and as accepted will be inserted at contract award).

6.5 Authorities

6.5.1 Contracting Authority

The Contracting Authority for the Contract is:

Ruth Kelly – Supply Specialist
Public Works and Government Services Canada - Acquisitions Branch
Logistics, Electrical, Fuel and Transportation Directorate - "HN" Division
7B3, Place du Portage, Phase III, 11 Laurier Street, Gatineau, QC, K1A 0S5
Telephone: (819) 420-0343 Facsimile: (819) 953-4944
E-mail address: ruth.kelly@pwgsc-tpsgc.gc.ca

The Contracting Authority is responsible for the management of the Contract and any changes to the Contract must be authorized in writing by the Contracting Authority. The Contractor must not perform work in excess of or outside the scope of the Contract based on verbal or written requests or instructions from anybody other than the Contracting Authority.

6.5.2 Contractor's Representative

Name and telephone number of the person responsible for:

General enquiries

Name: _____
Telephone: _____ Facsimile: _____
E-mail: _____

Delivery follow-up

Name: _____
Telephone: _____ Facsimile: _____
E-mail: _____

6.6 Payment

6.6.1 Basis of Payment

In consideration of the Contractor satisfactorily completing all of its obligations under the Contract, the Contractor will be paid a firm unit prices as specified in the contract. Customs duties are included and Applicable Taxes are extra.

6.6.2 Multiple Payments

SACC Manual clause [H1001C](#) (2008-05-12) Multiple Payments

6.6.3 SACC Manual Clauses

| SACC Reference | Section | Date |
|----------------|-----------|------------|
| <u>G1005C</u> | Insurance | 2016-01-28 |

6.6.4 Exchange Rate Fluctuation Adjustment

1. The foreign currency component (FCC) is defined as the portion of the price or rate that will be directly affected by exchange rate fluctuation. The FCC should include all related taxes, duties and other costs paid by the Bidder and which are to be included in the adjustment amount.
2. For each line item where a FCC is identified, Canada assumes the risks and benefits for exchange rate fluctuation, as shown in the Basis of Payment. For such items, the exchange rate fluctuation amount is determined in accordance with the provision of this clause.
3. The total price paid by Canada on each invoice will be adjusted at the time of payment, based on the FCC and the exchange rate fluctuation provisions in the contract. The exchange rate adjustment amount will be calculated in accordance with the following formula:
$$\text{Adjustment} = \text{FCC} \times \text{Qty} \times (i1 - i0) / i0$$
where formula variables correspond to:
FCC: Foreign Currency Component (per unit)
i0: Initial exchange rate (CAN\$ per unit of foreign currency [e.g. US\$1])
i1: exchange rate for adjustments (CAN\$ per unit of foreign currency [e.g. US\$1])
Qty: quantity of units
4. The initial exchange rate is typically set as the noon rate as published by the Bank of Canada on the solicitation closing date.
5. For goods, the exchange rate for adjustment will be the noon rate as published by the Bank of Canada on the date the goods were delivered. For services, the exchange rate for adjustment will be the noon rate on the last business day of the month for which the services were performed. For advance payments, the exchange rate for adjustment will be the noon rate on the date the payment was due. The most recent noon rate will be used for non-business days.
6. The Contractor must indicate the total exchange rate adjustment amount (either upward, downward or no change) as a separate item on each invoice or claim for payment submitted under the Contract. Where an adjustment applies, the Contractor must submit with their invoice form PWGSC-TPSGC 450, Claim for Exchange Rate Adjustments.
7. The exchange rate adjustment will only be applied where the exchange rate fluctuation is greater than 2% (increase or decrease), calculated in accordance with column 8 of form PWGSC-TPSGC 450 (i.e. $[i1 - i0] / i0$).
8. Canada reserves the right to audit any revision to costs and prices under this clause.

6.7 Invoicing Instructions

1. The Contractor must submit invoices in accordance with the section entitled "Invoice Submission" of the general conditions. Invoices cannot be submitted until all work identified in the invoice is completed.
2. Invoices must be distributed as follows:
 - (a) The original and one (1) copy must be forwarded to the consignee.
 - (b) one (1) copy must be forwarded to the following address:

National Defence Headquarters - MGen George R. Pearkes Building
101 Colonel By Drive, Ottawa, ON, K1A 0K2
Attention: Guy Ouellet – DLP 3-3-1-2
 - (c) One (1) copy must be forwarded to the Contracting Authority identified under the section entitled "Authorities" of the Contract.

Department of Public Works and Government Services - "HN" Division
7B3 Place du Portage, Phase III, 11 Laurier Street, Gatineau, QC, K1A 0S5
Attention: Ruth Kelly

6.8 Certifications

6.8.1 Compliance

The continuous compliance with the certifications provided by the Contractor in its bid and the ongoing cooperation in providing additional information are conditions of the Contract. Certifications are subject to verification by Canada during the entire period of the Contract. If the Contractor does not comply with any certification, fails to provide the additional information, or if it is determined that any certification made by the Contractor in its bid is untrue, whether made knowingly or unknowingly, Canada has the right, pursuant to the default provision of the Contract, to terminate the Contract for default.

6.8.2 Federal Contractors Program for Employment Equity - Default by the Contractor

The Contractor understands and agrees that, when an Agreement to Implement Employment Equity (AIEE) exists between the Contractor and Employment and Social Development Canada (ESDC)-Labour, the AIEE must remain valid during the entire period of the Contract. If the AIEE becomes invalid, the name of the Contractor will be added to the "[FCP Limited Eligibility to Bid](#)" list. The imposition of such a sanction by ESDC will constitute the Contractor in default as per the terms of the Contract.

6.9 Applicable Laws

The Contract must be interpreted and governed, and the relations between the parties determined, by the laws in force in Ontario.

6.10 Priority of Documents

If there is a discrepancy between the wording of any documents that appear on the list, the wording of the document that first appears on the list has priority over the wording of any document that subsequently appears on the list.

- (a) the Articles of Agreement;
- (b) the general conditions 2010A (2016-04-04), General Conditions - Goods (Medium Complexity),
- (c) Requirement;
- (d) the Contractor's bid dated _____ (*insert date of bid*) (*If the bid was clarified or amended, insert at the time of contract award: “, as clarified on _____” or “, as amended on _____” and insert date(s) of clarification(s) or amendment(s)*)

6.11 Defence Contract

SACC Manual clause A9006C (2012-07-16) Defence Contract

6.12 SACC Manual Clauses

| SACC Reference | Section | Date |
|----------------|--|------------|
| <u>D5545C</u> | ISO 9001:2008 - Quality Management Systems - Requirements (Quality Assurance Code C) | 2010-08-16 |

6.13 NATO Commercial and Government Entity Code (NCAGE) Traceability

Material supplied for the items specified in this contract is subject to investigation by Canada. Material which can neither be demonstrated by the contractor as having originated directly from the NCAGE specified for the item in this contract, nor as supplied with the specific written permission of this specified NCAGE, are subject to the following action by Canada.

Canada may either:

- a) terminate the contract for default with respect to that item, return the item to the Contractor at the Contractor's risk and expense, and demand and receive from the Contractor (who shall forthwith so pay) all procurement and other costs incurred by Canada, including any increased costs required for the purpose of expediting production; or
- b) retain the item, and demand and receive from the Contractor (who shall forthwith so pay) the difference between the Contractor's costs relating to the item, as determined by Canada, and the costs which, in Canada's opinion, the Contractor would have incurred had it obtained and supplied an item which did not differ in any way from that specifically required under the contract.

6.14 SACC Manual Clauses (Delivery)

| SACC Reference | Section | Date |
|----------------|-----------------------|------------|
| <u>D2000C</u> | Marking | 2007-11-30 |
| <u>D2001C</u> | Labelling | 2007-11-30 |
| <u>D9002C</u> | Incomplete Assemblies | 2007-11-30 |

6.14.1 Shipping Instructions - Delivery at Destination

Goods must be consigned to the destination specified in the Contract and delivered:

Delivered Duty Paid (DDP) (Edmonton, Alberta and Montreal, Quebec) Incoterms 2000 for shipments from a commercial contractor.

6.14.2 Preparation for Delivery

The Contractor must prepare item numbers 001 - 008 for delivery in accordance with the latest issue of the Canadian Forces Packaging Specification D-LM-008-036/SF-000, DND Minimum Requirements for Manufacturer's Standard Pack.

The Contractor must package item numbers 001 – 008 in quantities of 1 by package.

6.14.3 Shipping – Scheduling (DND)

The Contractor must deliver the goods to Canadian Forces (CF) Supply Depots by appointment only. The Contractor or its carrier must arrange delivery appointments by contacting the Depot Traffic Section at the appropriate location shown below. The consignee may refuse shipments when prior arrangements have not been made.

- (a) 7 CF Supply Depot Lancaster Park
Edmonton, Alta
Telephone: 780-973-4011, ext. 4524
- (b) 25 CF Supply Depot Montreal
Montreal, Qc
Telephone: 1-866-935-8673 (toll free), or
514-252-2777, ext. 2363 / 4673 / 4282